

# HPE SAS Mixed Use Solid State Drives

HPE Alletra Storage Server 4XXX 1.6TB SAS Mixed Use LFF LPC Multi Vendor SSD (S3T29A)



## What's new

- Offering 800 GB, 1.6 TB, 3.2 TB, and 6.4 TB storage capacities on selected models of SAS SSDs.

## Overview

Do you need to accelerate the performance of your mixed use applications?

HPE SAS Mixed Use (MU) Solid State Drives (SSDs) deliver high performance and endurance for applications requiring high read and write IOPS performance. HPE Enterprise SAS MU SSDs transfer data at full duplex (bidirectional) allowing greater I/O bandwidth to alleviate bottlenecks at quadruple the 6Gb interface of SATA drives.

HPE Enterprise SAS MU SSDs are best suited for mission-critical applications requiring a balanced mix of read and write I/O to deliver significantly faster data transfers from storage than SATA SSDs. HPE SAS MU SSDs are ideal for big data analytics, high performance compute and virtualization workloads.

SAS technology continues to be the interface of choice for many workloads

for its reliability and 24x7 operation in the enterprise data center.

## Features

### Enable up to 24Gb Max performance when combined with appropriate backplanes.

HPE SAS Mixed Use (MU) SSDs are ideal for big data analytics, cloud computing, high performance compute, database applications and virtualization.

Achieve higher IOPS and lower latency to enhance the performance of your data center.

Maintain data accuracy with full data-path error detection and surprise power loss protection.

Choose from a broad portfolio of enhanced solutions in a wide variety of capacities.

Technical specifications	HPE Alletra Storage Server 4XXX 1.6TB SAS Mixed Use LFF LPC Multi Vendor SSD
Product Number	S3T29A
Endurance DWPD (Drive Writes Per Day)	Mixed Use (MU) Endurance >1 & <10 DWPD
Platform supported	HPE Alletra Storage Platforms, see QuickSpecs for more information
Product dimensions	27.9 x 22.1 x 15.8 cm
Weight	0.58 kg
Warranty	HPE Solid State Drives and Add-In Cards have a standard 3/0/0 warranty Customer Self Repair (CSR) subject to maximum usage limitations. Maximum usage limit is the maximum amount of data that can be written to the drive. Drives that have reached this limit will not be eligible for warranty coverage.

# HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

## Advisory & Professional services

Experts can help you map out your path to hybrid cloud and optimize your operations.

## Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

## Support services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.
- **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

## Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

## HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

**Defective Media Retention** is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

## **HPE GreenLake**

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

[For additional technical information, available models and options, please reference the QuickSpecs](#)

Visit [HPE.com](https://www.hpe.com)

[Chat now](#)

© Copyright 2025 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product.

[PSN1014843895WWEN](#), November, 2025.

HEWLETT PACKARD ENTERPRISE

[hpe.com](https://www.hpe.com)

