

# Comfort-Time

Low Back  
Drafting Chair  
MVL2878



## Features

- Height adjustable forward swept arms with oval soft touch self-skinned urethane armcaps
- Adjustable seat depth (tool required)
- Pneumatic seat height adjustment
- Height adjustable circular chromed footrest
- Contoured seat shape and waterfall edge effectively supports pelvis and hips in a comfortably balanced position, reducing pressure at the knee and allowing user to sit
- Standard with hard floor casters
- Weight capacity of 300 lbs.

## Upholstery Options

Available in all grade 1 seating textiles or bonded leather/polyurethane combination



## Specifications

Dimensions.....20.5"W x 24.5"D x 48"H  
Weight.....46 lbs / 20.9 kg  
Volume.....7 ft<sup>3</sup> / 0.2 m<sup>3</sup>

## Ergonomic Features

[click here for more info](#)

- Seat Height
- Seat Depth
- Waterfall Seat
- Contoured Cushion



MEMBER  
**BIFMA**



All chairs in this series are tested to meet or exceed ANSI / BIFMA seating standards. These test procedures evaluate seating for function, safety, durability and structural adequacy. Your assurance of a quality product. As a result, all of this series' seating products proudly carry a Limited Lifetime Warranty. We have made every effort to ensure accuracy. Specifications are subject to change.