

DATA SHEET

SonicWall Mid-Range Gen 8 NSa Series

Best-in-Class Threat Protection
for Distributed Enterprises & Campuses

SonicWall latest mid-range next-gen firewalls, Network Security Appliance (NSa) Series offer medium and large enterprises industry-leading threat prevention performance at the lowest total cost of ownership in their class. The firewalls are the cornerstones of the threat protection solution that includes simplified centralized firewall management, Zero Trust enablement, flexible licensing with an option of managed firewall services, and an embedded cyber warranty for risk mitigation.

The Gen 8 firewalls deliver comprehensive security features such as intrusion prevention, VPN, application control, malware analysis, URL filtering, DNS Security, Geo-IP and Bot-net services, protecting the perimeter from advanced threats without becoming a bottleneck.



NSa 2800



NSa 3800



NSa 4800



NSa 5800

Gen 8 NSa Series Spec Preview.

Up to 7 Gbps	Up to 30 Gbps	Up to 8 Million
Threat Prevention Throughput	Firewall Throughput	Connections

HIGHLIGHTS

- Form Factor: 1U Rackable Mounted
- Support for 40G/25G/10G/5G/2.5G/1G ports
- Multi-gigabit Threat and Malware Analysis Throughput
- Superior TLS performance (sessions and throughput)
- Best-in-class price-performance
- Expandable storage
- Advanced DNS Filtering
- Reputation-based Content Filtering Service (CFS 5.0)
- Simplified Centralized SaaS and On-Premises management via [Network Security Manager](#)
- Wi-Fi 6 firewall management
- [SonicWall Unified Management](#) Support
- Enterprise Internet Edge Ready
- Secure SD-WAN capability
- TLS 1.3 support
- Simplified licensing including Hardware Only, Advanced and Managed Protection Security Suites.
- Powered by SonicWall Capture Labs threat research team
- SonicWall Switch, SonicWave Access Point and Capture Client integration
- [Cloud Secure Edge Connector](#) Support
- [Embedded Warranty](#) up to USD\$200K by Cysurance included in Service Suites

Gen 8 NSa firewalls drives strong security with a comprehensive solution encompassing of threat protection, centralized management, reporting and analytics, security and managed service options, Secure Service Edge (SSE) integration, and cyber warranty.


Hardware

Gen 8 NSa Series, built with the latest hardware components, deliver multi-gigabit threat prevention throughput — even for encrypted traffic. Featuring a high port density, the firewall solutions support network and hardware redundancy with high availability and dual power adapters including one for redundancy.

Architecture

The Gen 8 NSa Series runs on SonicOS 8, a new operating system that delivers a modern user interface, intuitive workflows and user-first design principles. [SonicOS 8](#) provides multiple features designed to facilitate enterprise-level workflows. It offers easy policy configuration, zero-touch deployment and flexible management — all of which allow enterprises to improve both their security and operational efficiency.

The NSa Series supports advanced networking features, such as SD-WAN, dynamic routing, layer 4-7 high availability and high-speed VPN functionality. In addition to integrating firewall and switch capabilities, the appliances provide a single-pane-of-glass interface to manage both switches and access points.



Threat Protection and Security Services

Built to mitigate the advanced cyberattacks of today and tomorrow, the Gen 8 NSa Series offers access to SonicWall's advanced firewall security services, allowing you to protect your entire IT infrastructure. Solutions and services such as Cloud Application Security, Capture Advanced Threat Protection (ATP) cloud-based sandboxing, patented Real-Time Deep Memory Inspection (RTDMI™) and Reassembly-Free Deep Packet Inspection (RFDPI) — for all traffic including TLS 1.3 — offer comprehensive gateway protection from most stealthy and dangerous malware, including zero-day and encrypted threats.

Simplified licensing includes Hardware Only, Advanced (APSS) and Managed Protection Security Suite (MPSS) to meet your unique needs. MPSS augments resources with managed services for firewalls.

A Cloud Secure Edge Connector integration provides secure access to their private applications behind the firewalls. Users and devices can adhere to a Zero-Trust framework for application access.

Cyber Warranty

An embedded cyber warranty is offered as part of your security suite to mitigate costs of security breach, meet compliance requirements and promote peace of mind.


Deployments

The Gen 8 NSa Series has two main deployment options for medium and distributed enterprises:

Internet Edge Deployment

In this standard deployment option, the Gen 8 NSa Series NGFW protects private networks from malicious traffic coming from the internet, allowing you to:


- Deploy a proven NGFW solution with highest performance in its class
- Gain visibility and inspect encrypted traffic, including TLS 1.3, to block evasive threats coming from the Internet — all without compromising performance
- Protect your enterprise with integrated security, including malware analysis, cloud app security, URL filtering and reputation services
- Save space and money with an integrated NGFW solution that includes advanced security and networking capabilities
- Reduce complexity and maximize efficiency using a central management system delivered through an intuitive single-pane-of-glass user interface



Medium and Distributed Enterprises


The SonicWall Gen 8 NSa Series supports SD-WAN and can be centrally managed, making it an ideal fit for medium and distributed enterprises. This deployment allows organizations to:

- Future-proof against an ever-changing threat landscape by investing in a NGFW with multi-gigabit threat analysis performance
- Provide direct and secure internet access to distributed branch offices instead of back-hauling through corporate headquarters
- Allow distributed branch offices to securely access internal resources in corporate headquarters or in a public cloud, significantly improving application latency
- Automatically block threats that use encrypted protocols such as TLS 1.3, securing networks from the most advanced attacks.
- Reduce complexity and maximize efficiency using a central management system delivered through an intuitive single pane of glass user interface
- Leverage high port density that includes 40 GbE and 10 GbE connectivity to support a distributed enterprise and wide area networks




SonicWall Gen 8 NSa Series


NSa 2800




NSa 3800



NSa 4800



NSa 5800



Gen 8 NSa Series System Specifications

Firewall	NSa 2800	NSa 3800	NSa 4800	NSa 5800
Operating system	SonicOS 8			
Interfaces	16x1GbE, 3x10G SFP+, 2 USB 3.0, 1 Console, 1 Mgmt. port	24x1GbE, 10x10G SFP+, 2 USB 3.0, 1 Console, 1 Mgmt. port	24 * 1GbE Cu, 8*10G SFP+, 1 console (RJ45 to DB9), 2 USB (USB type-A)	24 * 1GbE Cu, 8*10G SFP+, 1 console (RJ45 to DB9), 2 USB (USB type-A)
Storage/(Expansion)	128 Gb (Up to 512 GB)	256 Gb (Up to 512 GB)	256 GB (Up to 1 TB)	256 GB (Up to 1 TB)
Centralized Management	Network Security Manager (NSM) 3.0 and above, CLI, SSH, Web UI, REST APIs			
Logical VLAN and tunnel interfaces (maximum)	256	256	512	512
SAML Single Sign-On Users ¹	40,000	40,000	50000	50000
Access points supported (maximum)	512	512	512	512
Firewall/VPN Performance				
Firewall inspection throughput ²	8 Gbps	12 Gbps	20 Gbps	30 Gbps
Threat Prevention throughput ³	6 Gbps	8 Gbps	13 Gbps	24 Gbps
Application inspection throughput ³	7 Gbps	9 Gbps	13 Gbps	24 Gbps
IPS throughput ²	7 Gbps	8 Gbps	13 Gbps	24 Gbps
Anti-malware inspection throughput ³	6 Gbps	8 Gbps	13 Gbps	24 Gbps
TLS/SSL inspection and decryption throughput ³	1.8 Gbps	3 Gbps	4.2 Gbps	8 Gbps
IPSec VPN throughput ⁴	5.5 Gbps	8 Gbps	11 Gbps	21 Gbps
Connections per second	50,000	90,000	140,000	240,000
Maximum Connections (SPI)	2,000,000	3,000,000	6M	8M
Maximum connections (DPI)	1,000,000	1,200,000	3M	5M
Maximum connections (TLS)	150,000	300,000	600K	750K
VPN and ZTNA				
Site-to-site VPN tunnels	2,000	3,000	4000	6000
IPSec VPN clients (max)	50 (1000)	50 (1000)	500(3000)	2000(4000)
SSL VPN licenses (max)	2 (500)	2 (500)	2(1000)	2(1500)
Encryption/Authentication	AES (128, 192, 256-bit)/MD5, SHA-1, Suite B Cryptography			
Key exchange	Diffie Hellman Groups 1, 2, 5, 14v			
Route-based VPN	RIP, OSPF, BGP			
Certificate support	Verisign, Thawte, Cybertrust, RSA Keon, Entrust and Microsoft CA for SonicWall-to-SonicWall VPN, SCEP			
VPN features	Dead Peer Detection, DHCP Over VPN, IPSec NAT Traversal, Redundant VPN Gateway, Route-based VPN			
Global VPN client platforms supported	Microsoft® Windows 10 and Windows 11			
NetExtender	Microsoft® Windows 10 and Windows 11, Linux			
Mobile Connect	Apple® iOS, Mac OS X, Google® Android™			
SonicWall Private Access powered by Cloud Secure Edge ⁵	Included in 3&Free Loyalty Program			
Security services				
Deep Packet Inspection services	Gateway Anti-Virus, Anti-Spyware, Intrusion Prevention, TLS Decryption			
Content Filtering Service (CFS)	Reputation-based URL filtering, HTTP URL, HTTPS IP, keyword and content scanning, Comprehensive filtering based on file types such as ActiveX, Java, Cookies for privacy, allow/forbid lists			

Gen 8 NSa Series System Specifications

Firewall	NSa 2800	NSa 3800	NSa 4800	NSa 5800
Comprehensive Anti-Spam Service	●	●	●	●
Application Visualization	●	●	●	●
Application Control	●	●	●	●
Capture Advanced Threat Protection	●	●	●	●
DNS Filtering	●	●	●	●
Networking				
IP address assignment	Static (DHCP, PPPoE, L2TP and PPTP client), Internal DHCP server, DHCP relay			
NAT modes	1:1, 1:many, many:1, many:many, flexible NAT (overlapping IPs), PAT, transparent mode			
Routing protocols	BGP, OSPF, RIPv1/v2, static routes, policy-based routing			
QoS	Bandwidth priority, max bandwidth, guaranteed bandwidth, DSCP marking, 802.1e (WMM)			
Authentication	LDAP (multiple domains), XAUTH/RADIUS, TACACS+, SAML SSO ¹ , Radius accounting NTLM, internal user database, 2FA, Terminal Services, Citrix, Common Access Card (CAC)			
Local user database	1000	1000	1000	1000
VoIP	Full H323-v1-5, SIP			
Standards	TCP/IP, UDP, ICMP, HTTP, HTTPS, IPSec, ISAKMP/IKE, SNMP, DHCP, PPPoE, L2TP, PPTP, RADIUS, IEEE 802.3			
Certifications	IPv6/USGv6			
High availability	Active/Passive with stateful synchronization			
Hardware				
Form factor	1U Rack Mountable			
Power supply	90W	150W	450W	450W
Maximum power consumption (W)	52.8	102.3W	110.4	119.4
Input power (AC)	100-240 VAC, 50-60 Hz	100-240 VAC, 50-60 Hz	100-240 VAC, 50-60Hz	100-240 VAC, 50-60Hz
Total heat dissipation (BTU)	180.01	341	377.4	407.5
Dimensions (Unit: cm)	43 x 32.5 x 4.5 Shipping: 57.5 x 47.5 x 18.5	43 x 32.5 x 4.5 57.5 x 47.5 x 18.5	43 x 46 x 4.5 Shipping: 69.5 x 59.5 x 21	43 x 46 x 4.5 Shipping: 69.5 x 59.5 x 21
Weight	4.6	4.6	7.4 Kg	7.4 Kg
WEEE weight	4.8	4.8	9.3 Kg	9.3 Kg
Shipping weight	7.2	7.2	13.2 Kg	13.2 Kg
Environment (Operating/Storage)	0oC to +40o C / -40oC to +70o C		0°C to +40°C / -40°C to +70°C	0°C to +40°C / -40°C to +70°C
Humidity	5-95% non-condensing	5-95% non-condensing	5-95% non-condensing	5-95% non-condensing
Regulatory				
Major regulatory compliance	FCC Class A, ICES Class A, CE (EMC, LVD, RoHS), UL, cUL, Mexico DGN Notice by UL, ANATEL, WEEE, REACH, SCIP, RCM, MIC Terminal, VCCI Class A, KCC/MSIP, BSMI, MTCTE/TEC, CB		CC Class A, ICES Class A, CE (EMC, LVD, RoHS), UL, cUL, Mexico DGN Notice by UL, ANATEL, WEEE, REACH, SCIP, RCM, VCCI Class A, KCC/MSIP, BSMI, MTCTE/TEC, CB	
Regulatory model numbers	1RK56-11C	1RK57-122	IRK58-123	1RK58-123

¹ SAML Single Sign-On is available with the upcoming SonicOS 8.1, releasing soon.

² Testing Methodologies: Maximum performance based on RFC 2544 (for firewall). Actual performance may vary depending on network conditions and activated services.

³ Threat Prevention/Gateway AV/Anti-Spyware/IPS throughput measured using industry standard Keysight HTTP performance test tools. Testing

done with multiple flows through multiple port pairs. Threat Prevention throughput measured with Gateway AV, Anti-Spyware, IPS and Application Control enabled.

⁴ VPN throughput measured with UDP traffic using 1418 byte packet size AESGMAC16-256 Encryption adhering to RFC 2544. All specifications, features and availability are subject to change.

⁵ Included with 3-year bundle

SonicOS 8 Feature Summary

Firewall

- Stateful packet inspection
- Reassembly-Free Deep Packet Inspection
- DDoS attack protection (UDP/ICMP/SYN flood)
- IPv4/IPv6 support
- Biometric authentication for remote access
- DNS proxy
- Full API support
- SonicWall Switch integration
- SonicWall Wi-Fi 6 AP integration
- SD-WAN scalability
- SD-WAN Usability Wizard
- Connections scalability (SPI, DPI, TLS)

Enhanced dashboard

- Enhanced device view
- Top traffic and user summary
- Insights to threats
- Notification center

TLS/SSL/SSH decryption and inspection

- TLS 1.3 with enhanced security
- Deep packet inspection for TLS/SSL/SSH
- Inclusion/exclusion of objects, groups or hostnames
- SSL control
- Enhancements for TLS with CFS
- Granular DPI SSL controls per zone or rule

Capture advanced threat protection¹

- Real-Time Deep Memory Inspection
- Cloud-based multi-engine analysis¹
- Virtualized sandboxing
- Hypervisor level analysis
- Full system emulation
- Broad file type examination
- Automated and manual submission
- Real-time threat intelligence updates¹
- Block until verdict
- Capture Client²

Intrusion prevention¹

- Signature-based scanning
- Network access control integration with Aruba ClearPass
- Automatic signature updates
- Bi-directional inspection
- Granular IPS rule capability

- GeolIP enforcement
- Botnet filtering with dynamic list
- Regular expression matching

Anti-malware¹

- Stream-based malware scanning
- Gateway anti-virus
- Gateway anti-spyware
- Bi-directional inspection
- No file size limitation
- Cloud malware database

Application identification¹

- Application control
- Application bandwidth management
- Custom application signature creation
- Data leakage prevention
- Application reporting over NetFlow/IPFIX
- Comprehensive application signature database

Traffic visualization and analytics

- User activity
- Application/bandwidth/threat usage
- Cloud-based analytics

Web content filtering¹

- URL filtering
- Proxy avoidance
- Keyword blocking
- Reputation-based Content Filtering Service (CFS 5.0)
- DNS filtering
- Policy-based filtering (exclusion/inclusion)
- HTTP header insertion
- Bandwidth manage CFS rating categories
- Unified policy model with app control
- Content Filtering Client

VPN & ZTNA

- Secure SD-WAN
- Auto-provision VPN
- IPsec VPN for site-to-site connectivity
- SSL VPN and IPsec client remote access
- Redundant VPN gateway
- Mobile Connect for iOS, Mac OS X, Windows, and Android
- Route-based VPN (OSPF, RIP, BGP)
- Secure Private Access by Cloud Secure Edge

Networking

- PortShield
- Jumbo frames
- Path MTU discovery
- Enhanced logging
- VLAN trunking
- Port mirroring (SonicWall Switch)
- Layer-2 QoS
- Port security
- Dynamic routing (RIP/OSPF/BGP)
- SonicWall wireless controller
- Policy-based routing (ToS/metric and ECMP)
- NAT
- DHCP server
- Bandwidth management
- A/P high availability with state sync
- Inbound/outbound load balancing
- High availability - Active/Standby with state sync
- L2 bridge, wire/virtual wire mode, tap mode, NAT mode
- Asymmetric routing
- Common Access Card (CAC) support

VoIP

- Granular QoS control
- Bandwidth management
- DPI for VoIP traffic
- H.323 gatekeeper and SIP proxy support

Management, monitoring and support

- Capture Security Appliance (CSa) support
- Capture Threat Assessment (CTA) v2.0
- New design or template
- Industry and global average comparison
- New UI/UX, Intuitive feature layout
- Dashboard
- Device information, application, threats
- Topology view
- Simplified policy creation and management
- Policy/Objects usage statistics
- Used vs Un-used
- Active vs Inactive
- Global search for static data
- Storage support

SonicOS 8.0 Feature Summary cont'd

Management, monitoring and support cont'd

- Internal and external storage management
- WWAN USB card support (5G/LTE/4G/3G)
- Network Security Manager (NSM) support
- SonicWall Unified Management and SonicWall AI for Monitoring and Insight (SAMI)
- Web GUI
- Command line interface (CLI)
- Zero-Touch registration & provisioning
- CSC Simple Reporting
- SonicExpress mobile app support
- SNMPv2/v3
- API for reporting and analytics
- Logging

- Netflow/IPFix exporting
- Cloud-based configuration backup
- BlueCoat security analytics platform
- Application and bandwidth visualization
- IPv4 and IPv6 management
- CD management screen
- Dell N-Series and X-Series switch management including cascaded switches

Debugging and diagnostics

- Enhanced packet monitoring
- SSH terminal on UI

Wireless

- SonicWave AP cloud and firewall management
- WIDS/WIPS
- Rogue AP prevention
- Fast roaming (802.11k/r/v)
- 802.11s mesh networking
- Auto-channel selection
- RF spectrum analysis
- Floor plan view
- Topology view
- Band steering
- Beamforming
- AirTime fairness
- Bluetooth Low Energy
- MiFi extender
- RF enhancements and improvements
- Guest cyclic quota

¹Requires Security Suite subscription

Learn more about SonicWall Gen 8 NSa Series

www.sonicwall.com/products/firewalls

SonicWall, Inc.

1033 McCarthy Boulevard | Milpitas, CA 95035 | Refer to our website for additional information.

© 2025 SonicWall Inc. ALL RIGHTS RESERVED.

SonicWall is a trademark or registered trademark of SonicWall Inc. and/or its affiliates in the U.S.A. and/or other countries. All other trademarks and registered trademarks are property of their respective owners. The information in this document is provided in connection with SonicWall Inc. and/or its affiliates' products. No license, express or implied, by estoppel or otherwise, to any intellectual property right is granted by this document or in connection with the sale of SonicWall products. Except as set forth in the terms and conditions as specified in the license agreement for this product, SonicWall and/or its affiliates assume no liability whatsoever and disclaims any express, implied or statutory warranty relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or non-infringement. In no event shall SonicWall and/or its affiliates be liable for any direct, indirect, consequential, punitive, special or incidental damages (including, without limitation, damages for loss of profits, business interruption or loss of information) arising out of the use or inability to use this document, even if SonicWall and/or its affiliates have been advised of the possibility of such damages. SonicWall and/or its affiliates make no representations or warranties with respect to the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. SonicWall Inc. and/or its affiliates do not make any commitment to update the information contained in this document.

Solution Brief - SonicWall Unified Management

sonicwall.com



SONICWALL®