

2.5GbE USB-C to Ethernet Adapter, 100W PD Pass-Through, NBASE-T NIC, USB 3.0 Type-C  
2.5/1G Multi Speed Network, Thunderbolt Compatible, Windows & Mac

**Product ID:** 2GPD3-USB-C-ETHERNET



Add 2.5GbE network access to laptops, tablets, and iPhones equipped with a USB-C port. This USB-C to Ethernet Adapter features a 100W PD pass-through port that allows you to connect a charger to the same USB-C port, enabling simultaneous Ethernet connection and device charging. Enable ethernet connection without losing access to the original USB-C port for charging or connecting additional peripherals; well-suited for devices with limited ports.

This slim form factor adapter is ideal for office use and hot desks. Download large files from a network more quickly, experience higher quality video conference streaming, and sync files to the cloud in the background, without impacting your other browsing. This adapter supports both current and legacy Ethernet networks down to 10Mbps, making it ideal for providing a reliable network connection almost anywhere whether at home, work or while traveling. The Realtek chipset is broadly supported on new and older laptops enabling PXE capabilities to aid IT departments with provisioning and maintaining systems along with Wake-on-LAN (WoL) support. The adapter provides a wired connection that is faster and more secure than wireless, making it ideal for IT professionals.

Simply plug this USB-C to Ethernet adapter into the USB port on a laptop and connect to a network. The network adapter Realtek chipset provides native driver support for Windows (10/11, ARM supported) Macbooks (macOS), Chromebooks (ChromeOS), Snapdragon, Linux, iPhones, and tablets. Any Windows operating systems without the driver will be automatically prompted to download the software directly from the adapter, ensuring quick and effective installation with no Internet access required.

## Certifications, Reports and Compatibility





## Applications

- Add 2.5 Ethernet network connectivity to a laptop or desktop computer through a USB Type-C port

## Features

- **100W CHARGING:** 100W PD pass-through port allows you to connect a charger to the same USB-C port, enabling simultaneous Ethernet connection and device charging; Devices with limited USB-C ports can share a port without an additional hub
- **BROAD COMPATIBILITY:** Auto-installs on most operating systems including Windows 7 and up, Linux LTS Kernel 4.19+ and up, MacOS/iOS/ChromeOS; Works with MacBooks, Chromebooks and all hardware platforms, including Intel, AMD, ARM (Snapdragon) & Apple Silicon
- **2.5G OVER CAT5E:** Leverage NBASE-T for 2.5Gbps speeds over existing Cat 5e cables without the expense of upgrading to Cat6A/Fiber; 4-speed auto-negotiation for optimal performance with network devices; Extend system longevity by retrofitting older systems
- **APPLICATIONS:** Slim form factor adapter for office/hot desks; Quickly download large files from a network, experience higher quality video conferencing & sync files to the cloud in the background with a faster/more secure connection compared to wireless
- **TECH SPECS:** USB-C (5Gbps); 1x RJ45; 6in (15cm) Attached Cable; 2.5Gbps Multi-Gigabit; 10/100Mbps & 1/2.5Gbps; Realtek Chipset; NBASE-T & 2.5GBASE-T; 16K Jumbo Frames (not supported in macOS); WoL; VLAN; PXE Boot; Bus-Powered; Thunderbolt Compatible

---

## Hardware

Warranty	2 Years
Ports	1
Interface	RJ45 (Gigabit Ethernet)
Bus Type	USB 3.2 Gen 1

USB Pass-Through	No
Industry Standards	IEEE 802.3i 10BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.1q VLAN Tagging IEEE 802.3x IEEE 802.3u 100Base-TX IEEE 802.3bz 2.5GBase-T USB Power Delivery 3.0
Chipset ID	Realtek - RTL8156BG

---

#### Performance

Wake On Lan	Yes
Compatible Networks	2.5G/1G/100Mbps/10Mbps
Auto MDIX	Yes
PXE	Yes
Full Duplex Support	Yes
Jumbo Frame Support	16K max.
Promiscuous Mode	Yes
MTBF	1,912,948 hours

---

#### Connector(s)

Connector A	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps) 1 - RJ-45
-------------	--

---

#### Software

OS Compatibility	Windows 11 ARM, Windows 11, Windows 10, Windows 8, Windows 8.1, Windows 7, Windows Server 2016, Windows Server 2012 R2, Windows Server 2008 R2 Windows Server 2019, Windows Server 2022, Linux Kernel 2.4.20 and up - <i>LTS Versions only</i> , macOS 10.11 - 10.15, 11.0, 12.0, 13.0, 14.0 <i>VLAN tagging is currently not supported in macOS</i>
------------------	---

---

**Special Notes / Requirements**

Note	- Jumbo Frames are no longer supported in macOS
------	---

---

**Indicators**

LED Indicators	<p>1 - Link/Activity LED:</p> <ul style="list-style-type: none"> <li>• Solid Green = Network port is connected</li> <li>• Flashing Green = Network port is active</li> </ul> <p>1 - Link Speed LED:</p> <ul style="list-style-type: none"> <li>• Solid Green = Highest Link Speed (ex. 2.5Gbps)</li> <li>• Solid Amber = Lower Link Speeds (ex. 1000/100/10Mbps)</li> </ul>
----------------	---

---

**Power**

Power Source	USB-Powered
Input Voltage	5V DC
Output Voltage	5 DC

---

**Environmental**

Operating Temperature	0 to 45 (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10% to 85% RH (no condensation)

---

**Physical Characteristics**

Color	Space Gray
Form Factor	Attached Cable
Product Length	0.8 in [2.2 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.6 in [1.5 cm]
Weight of Product	0.9 oz [24.7 g]

---

**Packaging Information**

Package Quantity	1
------------------	---

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.6 in [1.6 cm]
Shipping (Package) Weight	1.0 oz [27.0 g]

---

**What's in the Box**

Included in Package	1 - USB Ethernet Adapter
---------------------	--------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

