




MATERIALS LIST:

- 1 CABLE:UL2547 24AWG*2C+S
O.D=3.0MM COLOR:BLACK
- 2 CONNECTOR:Ø3.5 STEREO AUDIO PLUG MALE,NICKEL PLATED
- 3 PVC POWDER: BLACK
- 4.LABEL:BLACK BOX P/N LABELE
- 5.LABEL:YEAR/MONTH LABEL


ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: $0 < L \leq 10\text{FT}$ 2 ohm (MAX)
 $10\text{FT} \leq L < 15\text{FT}$ 3 ohm (MAX)
 $15\text{FT} \leq L < 30\text{FT}$ 4 ohm (MAX)
 $30\text{FT} \leq L < 100\text{FT}$ 6 ohm (MAX)
 $L > 100\text{FT}$ 10 ohm (MAX)

E.CPK Measure point Y1-Y3.

PIN OUT

P1	P2
1 RED	1
2 WHITE	2
3 SHIELD	3



PART	LENGTH	LENGTH
EJ110-0002	L=24"+2.95"/-0	2FT
EJ110-0005	L=60"+2.95"/-0	5FT
EJ110-0010	L=120"+5.9/-0	10FT
EJ110-0015	L=180"+5.9"/-0	15FT
EJ110-0020	L=240"+5.9"/-0	20FT
EJ110-0025	L=300"+5.9"/-0	25FT
EJ110-0030	L=360"+5.9"/-0	30FT

MARKING:BLACK BOX CORPORATION GUARANTEED FOR LIFE
(724)746-5500 E223178 卐 AWM STYLE 2547 80°C VW-1

BLACK BOX®

Tolerance:	Approved by:	
X. ±		
.X ±	Checked by:	BLACK BOX P/N: EJ110-****
.XX ±		
.XXX ±	Drawn by:	Description:
Angle:	jun	DC3.5 M/DC3.5 M
X* ±	Date:	DWG. NO:
.X* ±	11.07.23	
	Scale:	Unit:inch
		SHEET: 1 OF 4 REV: 00

REV	ECN NO	DESCRIPTION	APPD.	DATE