

3753RK

Creative Touch 3 Series 75" interactive display



- **Google EDLA certified display - Integrated Google Play Store**
- **Exclusive Optoma Solution Suite**
- **Zero bonding for increased touch sensitivity**
- **Android 14 OS**

Introducing the New Creative Touch 3 Series by Optoma
The classroom of the future needs powerful, adaptable, and user-friendly tools. That's where the New Creative Touch 3 Series comes in—Optoma's next-generation, Google EDLA-certified Interactive Display designed to transform learning environments while meeting the needs of modern educators.



Specifications

EAN: 5055387668744, Colour: Black



Display	
Back light	Direct type LED
Size (diagonal)	75"
Resolution	3840x2160
Brightness	450
Contrast ratio (dynamic)	5,000:1
Viewing angle	178°
Response time	6ms
Life	50,000 hours
Display colors	1,070
Speaker count	2
Watts per speaker	20W
Surface hardness	7H
Glass	Anti Glare + Anti Finger Print
Haze	25%
Ambient light sensor	Yes
Air gap	0.60mm
Pencil hardness	9H
Physical spec	
Dimensions (W x D x H)	67.13" x 4.37" x 40.39"
Wall-hanging screw spec	M8*25mm
VESA holes	800x400
In the box	European Standard Power Cord 3M American Standard Power Cord 3M British Standard Power Cord 3M USB Touch Cable 3M HDMI Cable 3M Writing Pen x2 Remote Control Battery QSG
Connections	Inputs 3 x HDMI 2.0, 1 x VGA, 1 x DisplayPort, 1 x Audio 3.5mm, 1 x USB-A 2.0, 4 x USB 3.0, 1 x RJ45, 1 x USB-C, 1 x Microphone, 1 x OPS slot Outputs 1 x HDMI 2.0, 1 x S/PDIF, 1 x Audio 3.5mm, 1 x RJ45 Control 2 x USB-B interactive, 1 x RS232
Bezel size (top)	28.60mm
Bezel size (bottom)	0.00mm
Bezel size (left)	28.60mm
Bezel size (right)	28.60mm
Operating temperature (max)	40°C
Net weight	99.21 lbs
Gross weight	127.87 lbs
Wireless - technology	Wifi 6, 2.4G/5G, 2T2R, BT5.2 (AZ932-HNG optional)
Wireless - operating frequency	2.4G/5G
Touch system	
System	Windows 7/8/10/WindowsXP/11/Linux/Mac/Android
Touch accuracy	<1.00mm
Touch point	40 android / 50 windows
Touch tool	Finger, Passive infrared pen
Pen/finger detection	Yes
Power	
Power supply	100-240V~ 50/60Hz 3.5A
Power consumption (standby)	0.5W
Power consumption (max)	400W
Power consumption - average (watts)	167.6
Power consumption - Energy Star (watts)	161.5
Operation System	
System version	Android 14
CPU	Octa-core A72 x4 + A53 x4
GPU	G52 MC3
RAM	8GB
Storage	64GB
OSD / display languages	21 languages: Arabic, Czech, Danish, Dutch, English, Finnish, French, German, Greek, Hungarian, Italian, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish