

# HPE 3.2TB NVMe Gen5 High Performance Mixed Use E3S EC1 EDSFF SPDM CM7 SSD (P61191-B21)



---

## What's new

- Offer 3.2 TB and 6.4 TB storage capacities for the E3.S.
- Offer better protection with support for Security Protocol and Data Model (SPDM).

## Overview

Do you need to accelerate the performance of your mixed use applications?

HPE NVMe High Performance Mixed Use (MU) Enterprise and Datacenter Standard Form Factor (EDSFF) E3.S Solid State Drives (SSDs) are best suited for high I/O applications that require a balanced performance between reads and writes to deliver high performance and endurance for data-intensive applications. NVMe High Performance MU SSDs communicate directly to applications via the PCIe Gen 5 bus to boost I/O bandwidth and reduce latency.

HPE NVMe High Performance MU EDSFF E3.S SSDs replace the traditional 2.5 inch small form factor SSD while supporting greater density of NVMe drives. It delivers high performance, lower latency data transfers from storage significantly faster than SAS or SATA SSDs. Designed to utilize the high bandwidth of PCIe Gen 5 in select servers for mixed use workloads such as Big Data analytics, HPC, and virtualization.

## Features

### **High Performance and Exceptional Reliability for Faster Business Results**

HPE NVMe High Performance Mixed Use Enterprise and Datacenter Standard Form Factor (EDSFF) E3.S Solid State Drives (SSDs) are ideal for Big Data analytics, cloud computing, high performance compute, business intelligence, database applications, and virtualization.

Achieve higher IOPS and lower latency to enhance the performance of your enterprise servers while maintaining data accuracy with full data-path error detection.

Improved thermals, power, and scalability provide better system efficiency for high I/O applications.

Faster PCIe Gen 5 technology only available with EDSFF E3.S SSDs.

### **Improved Design and Efficiency for Increased Performance on Gen11 Servers**

HPE NVMe High Performance Mixed Use EDSFF E3.S Solid State Drives dramatically increase density for a 1U server that can fit 20 E3.S or 10 E3.S 2T drives, or a 2U server that can fit 36 E3.S or 18 E3.S 2T drives.

Improved power management and density while utilizing less wattage per server with EDSFF E3.S SSDs.



**Technical specifications****HPE 3.2TB NVMe Gen5 High Performance Mixed Use E3S EC1 EDSFF SPDM CM7 SSD**

<b>Product Number</b>	P61191-B21
<b>Lifetime writes</b>	17,520
<b>Endurance DWPD (Drive Writes Per Day)</b>	3
<b>Read IOPS</b>	Random Read IOPS (4KiB, Q=16)= 215,995 Max Random Read IOPS (4KiB)= 1,159,100@Q128
<b>Write IOPS</b>	Random Write IOPS (4KiB, Q=16)= 599,050 Max Random Write IOPS (4KiB)= 649,489@Q16
<b>Power (Watts)</b>	24
<b>Plug type</b>	Hot Pluggable
<b>Height</b>	7.5 mm
<b>Platform supported</b>	HPE Mainstream Compute Platforms
<b>Product dimensions</b>	20 x 25.4 x 11.6 cm
<b>Weight</b>	0.54 kg
<b>Warranty</b>	HPE Solid State Drives and Add-In Cards have a standard 3/0/0 warranty Customer Self Repair (CSR) subject to maximum usage limitations. Maximum usage limit is the maximum amount of data that can be written to the drive. Drives that have reached this limit will not be eligible for warranty coverage.



For additional technical information, available models and options, please reference the [QuickSpecs](#)

## HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

### Consulting services

Experts can help you map out your path to hybrid cloud and optimize your operations.

### Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

### Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- HPE Complete Care Service: a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- HPE Tech Care Service: the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

### Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

### HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

The [Defective Media Retention \(DMR\)](#) service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction. [Comprehensive Defective Material Retention \(CDMR\)](#) allows you to keep all data retentive components.


## HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please explore them [here](#).

Make the right purchase decision.  
Contact our presales specialists.

[Call for availability](#)



Explore **HPE GreenLake**



Share now



Get updates

**Hewlett Packard  
Enterprise**

© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product  
[PSN1014786576WWEN](#), March, 2024.