

ThinkPad X1 Carbon Gen 12

Introducing the next-gen ThinkPad X1 Carbon featuring powerful Intel® Core™ Ultra processors, designed to enhance graphics performance and elevate AI capabilities. Compared to its predecessors, integrated Intel® Arc Graphics deliver 2x performance boost, ensuring seamless workflows, enriched visual experience, and maximum encoding speed without any slowdown. Experience optimized performance with 40% lower SoC power consumption, leading to more productivity on a single charge with a 57 Whr battery, and a cooler, quieter PC during extended work sessions.



Built for business with cutting-edge technology

The ultimate device for any mobile worker or executive, ThinkPad X1 Series combines the latest productivity and security technologies with sleek and lightweight designs.

Supercharge your work efficiency with its cutting-edge Computer Vision technology. The innovative Face Sensing feature activates the laptop upon detecting enrolled users in its range. Coupled with the high-performance 8MP camera and the low-light video enhancement feature, enjoy crisp and clear visuals in any lighting situation, ensuring optimal virtual collaborations.

Experience the synergy of form and function with the premium 14" screen boasting an impressive 89.20% screen-to-body ratio and 2.8K OLED display option. The expansive display ensures a more immersive visual experience, while the minimal bezel design with premium aesthetics maximizes viewing area with minimum distractions.

Enhance video conferencing with the high-quality 8MP camera with low-light enhancements, ensuring superior clarity. Furthermore, the auto-framing feature ensures you remain perfectly centered in meetings, while background blur minimizes distractions.



The highest performance notebook

Elevate your professional prowess with this laptop that integrates AI-accelerated experiences, performance, and reliability effortlessly. The revolutionary Intel Meteor Lake architecture delivers up to 2x graphics performance, running tasks independently and servicing AI workloads for a responsive user experience. Moreover, a 42% larger thermal capability ensures sustained performance during prolonged work sessions without overheating.

Personalized Control

The redesigned keyboard with tactile markings aids in typing accuracy and facilitates exact maneuvering for the visually impaired. The enhanced TrackPad with an optional Haptic TouchPad offers precise and controlled navigation with AI tuning and enhanced palm rejection algorithm, contributing to a more intuitive computing experience.

Seamless Functionality

The Flip to Start feature ensures quick access to the notebook, allowing swift startups during busy workdays. Additionally, fingerprint authentication is now on the keyboard, offering a secure login experience while also enhancing accessibility.

Redefining Minimalism

Designed for optimal functionality, the sleek body of the laptop boasts a minimal iconic silhouette, embodying sophistication without unnecessary visual complexity. The introduction of a new logo, elegantly debossed, ensures a smooth and distraction-free typing experience.



Built consciously for a sustainable future

Lenovo provides smarter technology that contributes to a sustainable future for customers, colleagues, communities, and the planet. As a global technology powerhouse, we are committed to achieving net-zero greenhouse gas emissions by 2050 with targets validated by Science Based Targets initiative.



Recycled or sustainable product materials

Lenovo is focused on integrating sustainable materials and minimizing waste through innovative product and packaging design. Incorporating substantial recycled content such as magnesium, aluminum, and postconsumer recycled content (PCC) in manufacturing contributes to a circular economy while reducing carbon footprint.

- Use of recycled materials (90% recycled magnesium C cover & 55% recycled aluminum + 45% hydro aluminum D cover)
- PCC in plastic parts



Recycled shipping/packaging content

Lenovo reduces its overall carbon footprint by integrating bio-based materials like bamboo and sugarcane into laptop packaging, ensuring it is 100% rapidly renewable. Our commitment to sustainability is reflected in our zero plastic packaging solutions across products, including the latest X1 Carbon.

- Made from 100% recyclable bamboo and sugarcane
- FSC Certified Plastic Free Packaging



Product PCC

85% PCC Plastic Key Caps,
90% PCC in Plastic
Speaker, Battery Pack
Enclosure, & AC Adapter,
30% PCC Plastic Cable
Holder

Asset Recovery Service (ARS)

Lenovo's Asset Recovery Services (ARS) enables secure destruction of data, with minimum impact on the environment and a fair financial return. The service also supports equipment from any manufacturer including PCs & tablets, monitors, servers, phones, printers, copiers and networking equipment.

Lenovo TruScale DaaS

TruScale Device as a Service is a fully managed subscription-based model that offers access to a complete portfolio of hardware (including workstations, laptops, tablets, and phones), software, and trusted services with a flexible payment approach with consistent solutions and a predictable, transparent fee.

Lenovo CO2 Offset Services

Lenovo's Co2 Offset Service makes offsetting carbon emissions simple and within the control of the customer. We offset the carbon emissions associated with each of our devices by providing the option at point of purchase, ensuring we do our part toward reducing the overall carbon footprint.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

- If a problem can't be fixed remotely, we will visit your location
- Normally next business day service
- Agreed appointment times

Accessories

Lenovo USB-C Dual Display Travel Dock



- Ultimate productivity companion
- Adjustable cable management
- Built innovatively and consciously

PN: Dock without Adapter : 40B90000WW, Dock with Adapter : 40B90100xx

Lenovo Go Wireless Multi-Device Mouse



- Compact ambidextrous design, programmable Utility Button on the side, default functions optimized for Teams calls
- Connects to up to 3 devices via 1x USB-C dongle, 2x Bluetooth 5.0; quick switch button to jump control across devices
- Comes with a blue optical sensor that tracks on most surfaces and wireless Qi or wired USB-C fast-chargeable battery

PN: 4Y51C21217



ThinkPad X1 Carbon Gen 12

Performance

Processor
Intel U or H Series Core Ultra 5/7 Processor (Series 1)

Operating System
Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Fedora Linux
Linux
Ubuntu Linux

Graphics
Intel Graphics (integrated)
Intel Arc Graphics (integrated)

Memory
16GB LPDDR5x-6400, soldered
32GB LPDDR5x-6400, soldered
64GB LPDDR5x-6400, soldered

Storage ¹
Up to 1x 2TB M.2 2280 PCIe NVMe SSD

¹The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Atmos
Dual-microphone array, far-field, Dolby Voice

Camera *
FHD 1080p + IR discrete, with privacy shutter
UHD 8.0MP + IR discrete, with privacy shutter, MIPI, Computer Vision

Battery ²
57Wh (up to 16.0 hr) battery, Rapid Charge

²Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter *
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display ³
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 400nits, 100% sRGB, low power, Eyesafe
- 400nits, 100% sRGB, low power, on-cell touch, Eyesafe
- 500nits, 100% sRGB, ThinkPad Privacy Guard, Eyesafe

14" 2.8K (2880x1800) OLED AGARAS 16:10
- 400nits, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Eyesafe
- 400nits, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Add-on Film touch, Eyesafe

³IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, spill-resistant, air intake design, backlight

Touchpad
TrackPoint and glass surface Haptic TouchPad 70.9 x 120 mm (2.76 x 4.72 inches)
TrackPoint and glass surface 3-button TrackPad 56 x 120 mm (2.24 x 4.72 inches)

Dimensions ⁴
312.80 x 214.75 x 14.96 mm (12.31 x 8.45 x 0.59 inches)

⁴The system dimensions may vary depending on configurations.

Weight ⁵
Starting at 1.08 kg (2.37 lbs)

⁵The system weight is approximate and may vary depending on configurations

Color
Black, paint
Black, weave

Case material
Carbon fiber (top), aluminium (bottom)

Connectivity

WLAN + Bluetooth* ⁶
802.11ax (Wi-Fi 6E) or 802.11be (Wi-Fi 7), Bluetooth 5.3
Up to Intel Wi-Fi 7 BE200, 802.11be, Bluetooth 5.3

⁶Wi-Fi 6E and Wi-Fi 7 are only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10. Bluetooth 5.3 operation requires Windows 11.

WWAN*
4G LTE CAT16 with embedded eSIM
5G Sub-6 GHz with embedded eSIM

NFC
Near Field Communication*

Ports
1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
2x USB-C (Thunderbolt 4 / USB4 40Gbps), with USB PD 3.0 & DP 2.1
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Security
Discrete TPM 2.0
Kensington Nano Security Slot
Touch style MOC fingerprint reader
Camera privacy shutter
IR camera for Windows Hello (facial recognition)
Privacy Guard with Privacy Alert*
Computer Vision-based User Presence Sensing (UHD 8.0MP models)*
Ultrasonic Human Presence Detection (FHD 1080p models)*

Manageability

System Management* ⁷
Intel vPro Enterprise*

⁷Intel vPro offers a superset of DASH's defined capabilities

Certifications

Green Certifications ^{8 9 10}
ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

⁸The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

⁹EPEAT registration and ENERGY STAR certification are dependent on system OS.

¹⁰EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications
Intel Evo Platform*
Eyesafe Certified 2.0
TUV Rheinland Dynamic Privacy Filter (DPF) Certification*
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.