

Product data sheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14, 1.2m, North America

AP8704S-NA

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

Product or Component Type	Power cord
Input Connection Type	IEC 60320 C14
Cable length	4 ft (1.2 m)
Number of cables	6

Physical

Color	Black
Height	9.4 in (24 cm)
Width	2.8 in (7 cm)
Depth	1.8 in (4.5 cm)
Net Weight	2.23 lb(US) (1.01 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Max line current	10 A
Input current limits	10 A

Output

Maximum Total Current Draw per Phase	10 A
Number of power socket outlets	1 IEC 60320 C13
Cord Length	4 ft (1.2 m)

Conformance

Product Certifications	CSA UL Listed
-------------------------------	------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient Air Temperature for Operation	32.0000000000...221.0000000000 °F (0...105 °C)
Relative Humidity	20...80 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13.0000000000...221.0000000000 °F (-25...105 °C)
Storage Relative Humidity	20...80 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304294382
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.4 in (24 cm)
Package 1 Width	1.8 in (4.5 cm)
Package 1 Length	2.8 in (7 cm)
Package 1 Weight	2.23 lb(US) (1.01 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov