

Product data sheet

Specifications



Power Cord Kit (6 ea), Locking, C13 to C14, 0.6m, North America

AP8702S-NA

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

| | |
|----------------------------------|---------------|
| Product or Component Type | Power cord |
| Input Connection Type | IEC 60320 C14 |
| Cable length | 2 ft (0.6 m) |
| Number of cables | 6 |

Physical

| | |
|----------------------------|---------------------|
| Color | Black |
| Height | 9.4 in (24 cm) |
| Width | 2.8 in (7 cm) |
| Depth | 1.6 in (4 cm) |
| Net Weight | 1.5 lb(US) (0.7 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |

Input

| | |
|-----------------------------|------|
| Max line current | 10 A |
| Input current limits | 10 A |

Output

| | |
|---|-----------------|
| Maximum Total Current Draw per Phase | 10 A |
| Number of power socket outlets | 1 IEC 60320 C13 |
| Cord Length | 2 ft (0.6 m) |

Conformance

| | |
|-------------------------------|------------------|
| Product Certifications | CSA UL Listed |
|-------------------------------|------------------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

| | |
|---------------------------------------|---|
| Ambient Air Temperature for Operation | 32.0000000000...221.0000000000 °F (0...105 °C) |
| Relative Humidity | 20...80 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | -13.0000000000...221.0000000000 °F (-25...105 °C) |
| Storage Relative Humidity | 20...80 % |
| Storage altitude | 0...50000 ft (0.0000000000...15240.0000000000 m) |

Ordering and shipping details

| | |
|------|--------------|
| GTIN | 731304294368 |
|------|--------------|

Packing Units

| | |
|------------------------------|---------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.4 in (24 cm) |
| Package 1 Width | 1.6 in (4 cm) |
| Package 1 Length | 2.8 in (7 cm) |
| Package 1 Weight | 1.5 lb(US) (0.7 kg) |

Contractual warranty

| | |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov