

OVERVIEW



1. Smart card reader *	6. 2x Thunderbolt 4
2. Nano-SIM card slot *	7. HDMI
3. USB-A (USB 5Gbps)	8. USB-A (USB 5Gbps), Always On
4. Ethernet (GbE RJ-45)	9. Headphone / microphone combo jack (3.5mm)
5. Kensington Nano Security Slot	

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ AI 5 / 7 / 9 PRO 300 Series Processor; supports up to 12 cores; up to 5.1GHz; TDP ratings of up to 29W

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	NPU
AMD Ryzen™ AI 5 PRO 340	6	12	2.0GHz	4.8GHz	6MB L2 / 16MB L3	AMD Radeon™ 840M	AMD Ryzen™ AI
AMD Ryzen™ AI 7 PRO 350	8	16	2.0GHz	5.0GHz	8MB L2 / 16MB L3	AMD Radeon™ 860M	AMD Ryzen™ AI
AMD Ryzen™ AI 9 HX PRO 370	12	24	2.0GHz	5.1GHz	12MB L2 / 24MB L3	AMD Radeon™ 890M	AMD Ryzen™ AI

AI (Artificial Intelligence)

AI PC Category

- AI-Ready Workstations^[1]
- Copilot+ PC^[2]

AI Performance

- Up to 59 overall TOPS (AMD Ryzen™ AI 5 PRO 340)
- Up to 66 overall TOPS (AMD Ryzen™ AI 7 PRO 350)
- Up to 80 overall TOPS (AMD Ryzen™ AI 9 HX PRO 370)

Notes:

[1] With scalable configurations of higher-performance CPUs and professional NVIDIA® RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.

[2] Copilot+ PCs have at least 16GB RAM, 256GB storage, and a NPU that runs 40+ TOPs to run the latest AI tools build-in latest Windows® 11 to accelerate productivity and creativity.

Operating System

Operating System

- Windows® 11 Pro
- Windows® 11 Home
- Fedora Linux^[1]
- Ubuntu Linux LTS^[2]
- Red Hat Enterprise Linux 10 (certified only, for detailed and latest information, please visit [Red Hat Certified Hardware](#))
- No preload operating system

Notes:

[1] Fedora Linux will be available after August 30th, 2025.

[2] Ubuntu Linux LTS will be available after July 25th, 2025.

Graphics

Graphics**

Graphics	Type	Memory	TGP	Key Features
AMD Radeon™ 840M	Integrated	Up to 48GB dedicated graphics memory (96GB system memory required) ^[1]	Share CPU TDP	DirectX® 12
AMD Radeon™ 860M	Integrated	Up to 48GB dedicated graphics memory (96GB system memory required) ^[2]	Share CPU TDP	DirectX® 12
AMD Radeon™ 890M	Integrated	Up to 48GB dedicated graphics memory (96GB system memory required) ^[3]	Share CPU TDP	DirectX® 12

Notes:

[1], [2], [3] The default dedicated graphics memory is 8GB, which can be set to 1GB, 2GB, 4GB, 8GB, 16GB, 32GB, or 48GB. The dedicated graphics memory setting must be less than or equal to 50% of the system memory.

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via 2x Thunderbolt™ 4 and 1x HDMI®).

Max resolution for multiple external display:

- 2x 5120x3200@60Hz / 3840x2160@120Hz (Thunderbolt™ 4)
- 1x 3840x2160@60Hz (HDMI®)

Max resolution for single external display:

- Thunderbolt™ 4 supports up to 7680x4320@60Hz (with DSC)
- HDMI® supports up to 3840x2160@60Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory

Up to 96GB (2x 48GB DDR5 SO-DIMM)

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type

DDR5-5600 non-ECC, maximum transfer speeds of up to 5600 MT/s

Storage

Max Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe® 4.0 x4 slot

Storage Type**

Disk Type	Interface	Offering	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	Opal 2.0
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4 Performance	512GB / 1TB / 2TB	Opal 2.0

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby Atmos®

Microphone

- Dual-microphone array, 360° far-field, Dolby Voice®
- No microphone (for special bid model)

Camera**

- 5.0MP + IR with privacy shutter and Ultrasonic Human Presence Detection, fixed focus, temporal noise reduction
- 5.0MP + IR with privacy shutter, fixed focus, temporal noise reduction
- 5.0MP with privacy shutter, fixed focus, temporal noise reduction

Battery

Battery**

- 52.5Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter
- 86Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr) with 100W AC adapter

Power Adapter

Power Adapter**^[1]

- 65W USB-C[®] (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C[®] (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C[®] nano GaN (2-pin, wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C[®] nano GaN (3-pin, wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C[®] slim GaN (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C[®] slim GaN (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 100W USB-C[®] slim (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

[1] AC adapter offerings depend on the country.

DESIGN

Display

Display**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle (L/R/U/D)	Key Features
16"	WUXGA (1920x1200)	None	IPS ^[1]	400nits	Anti-glare	16:10	1200:1	45% NTSC	85° / 85° / 85° / 85°	87% screen to body ratio, AICCP color calibration, DC dimming
16"	WUXGA (1920x1200)	On-cell touch	IPS ^[2]	400nits	Anti-glare	16:10	1200:1	45% NTSC	85° / 85° / 85° / 85°	87% screen to body ratio, Eyesafe [®] 2.0 Certified, AICCP color calibration, DC dimming
16"	WUXGA (1920x1200)	None	IPS ^[3]	500nits	Anti-glare	16:10	1200:1	100% sRGB	85° / 85° / 85° / 85°	87% screen to body ratio, AICCP color calibration, Low power, UL Low Blue Light, Eyesafe [®] 2.0 Certified, DC dimming
16"	WQUXGA (3840x2400)	Add On Film Touch	OLED	400nits	Anti-reflection / Anti-smudge	16:10	100,000:1	100% DCI-P3	85° / 85° / 85° / 85°	87% screen to body ratio, X-Rite [®] Factory Color Calibration, UL Low Blue Light, Eyesafe [®] 2.0 Certified

Color Calibration**

- AICCP color calibration (WUXGA display)
- X-Rite[®] factory color calibration (OLED display)

Touchscreen**

- Add-on Film Touch, supports 10-point touch (OLED models only)

- On-cell multi-touch, supports 10-point touch (selected WUXGA display)
- Non-touch

Notes:

[1], [2], [3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Pen

No support

Keyboard

6-row, spill-resistant, multimedia Fn keys, numeric keypad, Copilot key

Keyboard Backlight

- LED backlight
- Non-backlight

UltraNav™

3-button TrackPoint® pointing device and glass-like Mylar® surface multi-touch TrackPad, 67 x 115 mm (2.64 x 4.53 inches)

Mechanical

Dimensions (WxDxH)^[1]

Models	Dimensions
Non-WWAN models	359.70 x 251.70 x 11.80/18.14 (front/rear), 23.5 (maximum) mm; 14.16 x 9.91 x 0.47/0.71 (front/rear), 0.93 (maximum) inches
WWAN support models	359.70 x 251.70 x 11.80/18.14 (front/rear), 23.65 (maximum) mm; 14.16 x 9.91 x 0.47/0.71 (front/rear), 0.93 (maximum) inches

Weight^[2]

Starting at 1.71 kg (3.77 lbs)

Case Color

Black

Case Material**

- PC + 20% CF + 50% GF + 30% PCC (top), PC + 20% CF + 30% PCC (bottom)
- PC + 20% CF + 50% GF + 30% PCC (top), PC + 40% GF + 45% PCC (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®

MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4^[1]

WWAN**

- Wireless WAN upgradable to 5G (with antenna ready)
- Quectel RM520N-GL, 5G Sub-6 GHz, M.2 card, with embedded eSIM functionality
- No support

SIM Card

No physical SIM card inbox

Ethernet

Gigabit Ethernet, Realtek® RTL8111EPV, 1x RJ-45, supports Wake-on-LAN and AMD PRO Manageability

NFC

Near Field Communication

Notes:

[1] 6GHz Wi-Fi® 7 operation is subject to the regulation rules in each country.

Ports^[1]

Standard Ports

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with PD 3.0 and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Security keyhole

Optional Ports***

- 1x Smart card reader
- 1x Nano-SIM card slot (WWAN support models)

Notes:

[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

Docking

Docking

Various docking solutions supported via Thunderbolt™ or USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® P16s Gen 4 \(AMD\)](#)

SECURITY & PRIVACY

Security

Security Chip**

- Firmware TPM 2.0 integrated in SoC
- Discrete TPM 2.0 (TCG certified, FIPS 140-2 certified) and Microsoft® Pluton TPM 2.0, one enabled at one time

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

- Smart card reader
- No smart card reader

Fingerprint Reader

- Touch style fingerprint reader integrated in power button, match-on-chip
- No fingerprint reader

BIOS Security

- NVMe® password
- Power-on password
- Supervisor password
- Self-healing BIOS

Other Security

- Bottom cover tamper detection
- Camera privacy shutter (camera models)
- (Optional) Ultrasonic Human Presence Detection for IR camera
- (Optional) IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

System Management

AMD PRO Manageability

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ACCESSORIES

Bundled Accessories

Bundled Accessories***^[1]

- Lenovo® HDMI® to VGA Monitor Adapter
- Lenovo® USB-C® to DisplayPort™ Adapter
- Lenovo® USB-C® to VGA Adapter

Notes:

^[1] For more compatible accessory solutions, please visit [Accessories for ThinkPad® P16s Gen 4 \(AMD\)](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping packaging: -20°C (-4°F) to 60°C (140°F)
- Storage without package: 5°C (41°F) to 43°C (109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

^[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material^[1]

85% PCC recycled plastic used in backlit key caps
90% PCC recycled plastic used in speaker enclosure
97% PCC recycled plastic used in the battery
90% PCC recycled plastic used in power adapters
100% plastic-free with eco-friendly ink (standard / bulk)

Notes:

[1] PCC: Post Consumer Content, recycled materials from customers.

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[3]
- RoHS compliant
- TCO Certified 10.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

[3] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- (Optional) UL Low Blue Light
- (Optional) Eyesafe® Certified 2.0

ISV Certifications

ISV Certifications

Please visit [ISV certifications for Lenovo® Workstations](#)

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

