



CN1



1.58"±0.2"

Only one CABLE LABEL on cable unless
the cable is over 20 feet then each
side of cable get a CABLE LABEL

MARKING:

BLACK BOX CORPORATION GUARANTEED FOR LIFE (724) 746-5500---HDMI
Cable--- *FL* AWM E101344 STYLE 20379 80°C 30V

MATERIALS:

- 1.CABLE: UL20379 HDMI 1.3B(28AWG Bare Copper *1pair+Drain wire/AL/Mylar)* 4 core + 28AWG Tinned Copper*1 pair+ 28AWG Tinned Copper* 5 core +AL/Braid 90%
OD: 0.26" COLOR: BLACK
- 2.CONNECTOR: 19M PIN GOLD 15U" GOLD FRONT SHELL
- 3.CONNECTOR: DVI 18+1 M INSULATION BLACK FRONT SHELL GOLD ,
BACK SHELL NICKEL
- 4.MATEL CAN: 6.5 TWO SLICES STYLE
- 5.SCREW: #4-40UNC BLACK
- 6,PVC: BLACK
- 7,DUST COVER: PE
- 8,LABEL: YEAR MONTH LABEL

ELECTRONIC TEST:


- A.OPEN/SHORT/INTERMITTENCE: 100%
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: $0 < L \leq 10\text{FT}$ 2 ohm (MAX)
 $10\text{FT} < L \leq 15\text{FT}$ 3 ohm (MAX)
 $15\text{FT} < L \leq 30\text{FT}$ 4 ohm (MAX)
 $30\text{FT} < L \leq 100\text{FT}$ 6 ohm (MAX)
 $L > 100\text{FT}$ 10 ohm (MAX)

REV	ECN NO	DESCRIPTION	APPD.	DATE

MARKING:

BLACK BOX CORPORATION GUARANTEED FOR LIFE (724) 746-5500---HDMI
Cable--- *FL* AWM E101344 STYLE 20379 80°C 30V

CONNECTION

**BLACK BOX®**

Tolerance:	Approved by:	
X. ±		
.X ±	Checked by:	BLACK BOX P/N: EVHDMI02T-***M
.XX ±		
.XXX ±	Drawn by: Jingxu	Description: STANDARD HDMI TO DVI CABLE
Angle:	Date: 11.03.12	DWG. NO: RFS-97121802
X* ±	Scale:	Unit:mm
.X* ±		SHEET: 1 OF 2
		REV: 02