


OVERVIEW



1. 2x Thunderbolt 4	5. Nano-SIM card slot (WWAN model) *
2. USB-A (USB 5Gbps), Always On	6. USB-A (USB 5Gbps)
3. Headphone / microphone combo jack (3.5mm)	7. HDMI
4. Smart card reader *	8. Kensington Nano Security Slot

- Notes:
- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

Intel® U Series Core Ultra 5 / 7 Processor (Series 2)

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	NPU
Core Ultra 5 225U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 1.5GHz / E-core 1.3GHz / LPE-core 700MHz	P-core 4.8GHz / E-core 3.8GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost
Core Ultra 5 235U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 2.0GHz / E-core 1.6GHz / LPE-core 700MHz	P-core 4.9GHz / E-core 4.1GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost
Core Ultra 7 255U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 2GHz / E-core 1.7GHz / LPE-core 700MHz	P-core 5.2GHz / E-core 4.2GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost
Core Ultra 7 265U	12 (2 P-core + 8 E-core + 2 LPE-core)	14	P-core 2.1GHz / E-core 1.7GHz / LPE-core 700MHz	P-core 5.3GHz / E-core 4.2GHz / LPE-core 2.4GHz	12MB	Intel® Graphics	Intel® AI Boost

AI (Artificial Intelligence)

AI PC Category

AI PC^[1]

NPU

Integrated Intel® AI Boost, up to 12 TOPS

Notes:

[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft® Copilot key or using Win + C.

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Ubuntu Linux^[1]
- No preload operating system

Notes:

[1] Some features may not be supported on the system with Linux preload, including but not limited to Intel® RST RAID, MIPI computer vision camera, WWAN, Human Presence Detection, etc.

Graphics

Graphics

Graphics	Type	Memory	TGP	Key Features
Intel® Graphics	Integrated	Shared	Share CPU TDP	DirectX® 12.2

Monitor Support

Monitor Support^[1]

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and Thunderbolt™)

- HDMI® supports up to 3840x2160@60Hz
- Thunderbolt™ supports up to 7680x4320@60Hz^[2]

Notes:

[1] Refresh rates >60hz also supported, however max resolution will be limited.
[2] 8K resolution support needs 2 display pipes. That is, simultaneous display number will “-1” when 8K resolution displayed.

Chipset

Chipset
Intel® SoC (System on Chip) platform

Memory

Max Memory

- 16GB soldered memory, not upgradable
- 32GB soldered memory, not upgradable

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Memory Type
LPDDR5x-7467^[1]

Notes:
[1] Installed memory is actually LPDDR5x-8533 but run as LPDDR5x-7467 due to platform limitation.

Storage

Max Storage Support^[1]
One drive, up to 1TB M.2 2242 SSD

Storage Slot
One M.2 2242 PCIe® 4.0 x4 slot

Storage Type

Disk Type	Interface	Offering	Security
M.2 2242 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	Opal 2.0

Notes:
[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

Removable Storage

Card Reader
No card reader

Multi-Media

Audio Chip
High Definition (HD) Audio, Senary SN6147 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Microphone
Dual-microphone array, Elevoc Voice

Camera**

- HD 720p, with privacy shutter, fixed focus
- 5.0MP + IR discrete, with privacy shutter, fixed focus, temporal noise reduction

Battery

Battery**

- 41Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr)
- 54.7Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr)

Battery Life^[1]
Configuration 1 (max battery life)
MobileMark® 25: up to 12.8 hr with 556 performance score @250nits

JEITA-BAT 3.0 (Video/Idle): up to 12.5 hr / 26.4 hr @200nits
Local video playback: up to 22.5 hr @150nits

Alternate configuration 2
MobileMark® 25: up to 12.2 hr with 556 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 12.1 hr / 23.6 hr @200nits
Local video playback: up to 21.6 hr @150nits

Notes:

[1] Configuration 1 (max battery life): WUXGA (non-touch), Intel® Core™ Ultra 5 225U, 16GB LPDDR5x, Win 11, 54.7Wh battery, best power efficiency power mode
Alternate configuration 2: WUXGA (touch), Intel® Core™ Ultra 5 235U, 16GB LPDDR5x, Win 11, 54.7Wh battery, best power efficiency power mode

All battery life claims are approximate maximum and based on results using [MobileMark® 25](#), JEITA 3.0, continuous 1080p local video playback (using default Media Player in Fullscreen mode with 150nits brightness and default volume level), or Google Power Load Test (PLT) battery-life benchmark tests.
Actual battery life will vary depending on many factors such as product configuration, software, wireless functionality, power management settings, and screen brightness.
The maximum capacity of the battery will decrease with time, ambient temperature and use.
Refer to [Microsoft® link](#) for more information about the Windows® Performance power slider.

Power Adapter

- Power Adapter**[1]
- 65W USB-C® (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
 - 65W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
 - 65W USB-C® slim GaN (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
 - 65W USB-C® slim GaN (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
 - No power adapter[2]

Notes:

[1] AC adapter offerings depend on the country.
[2] No power adapter is for special bid only.

DESIGN

Display

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
13.3"	WUXGA (1920x1200)	None	IPS	400nits	Anti-glare	16:10	1000:1	45% NTSC	60Hz	85° / 85° / 85° / 85°	TÜV Low Blue Light (Software), 3M™ DBEF5
13.3"	WUXGA (1920x1200)	None	IPS	400nits	Anti-glare	16:10	1500:1	100% sRGB	60Hz	89° / 89° / 89° / 89°	Eyesafe® Certified 2.0
13.3"	WUXGA (1920x1200)	Multi-touch	IPS	400nits	Anti-glare	16:10	1500:1	100% sRGB	60Hz	89° / 89° / 89° / 89°	Eyesafe® Certified 2.0

- Touchscreen
- In-cell multi-touch, supports 10-point touch
 - Non-touch

Input Device

Pen
No support

Keyboard
6-row, spill-resistant, multimedia Fn keys, Copilot key

Keyboard Backlight

- LED backlight
- Non-backlight

UltraNav™**

- TrackPoint® pointing device, double-tap to open the TrackPoint® Quick Menu
Glass-like Mylar® surface multi-touch 3-button Trackpad, 60 x 115 mm (2.36 x 4.53 inches)^[1]
- TrackPoint® pointing device, double-tap to open the TrackPoint® Quick Menu
Mylar® surface multi-touch 3-button Trackpad, 60 x 115 mm (2.36 x 4.53 inches)^[2]

Notes:

[1] Glass-like Mylar® surface TrackPad is available for the NFC models.

[2] Mylar® surface TrackPad is available for the non-NFC models.

Mechanical**Dimensions (WxDxH)^[1]**

299.0 x 215.0 x 12.0/15.7 (front/rear), 18.95 (maximum) mm;
11.77 x 8.46 x 0.47/0.62 (front/rear), 0.75 (maximum) inches

Weight^[2]

Starting at 1.21 kg (2.67 lbs)

Case Color

Black

Case Material

Aluminium (top), PC + 40% GF (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY**Network****WLAN + Bluetooth®**^[1]**

- Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3^[2]
- Intel® Wi-Fi® 7 BE201, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4^[3]

WWAN**

- Wireless WAN upgradable to 4G (with antenna ready)
- Quectel EM061K-GL, 4G LTE CAT6, M.2 card, with embedded eSIM functionality
- No support

SIM Card

- KDDI eSIM Program (Japan)^[4]
- No physical SIM card inbox

Ethernet

No onboard Ethernet^[5]

NFC

- Near Field Communication
- No support

Notes:

[1] Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

[2] Wi-Fi® 6E operation is subject to the regulation rules in each country.

[3] Wi-Fi® 7 operation is subject to the regulation rules in each country.

[4] KDDI eSIM Program is for special bid only.

[5] Ethernet support via optional Lenovo® USB-C® to Ethernet Adapter.

Ports^[1]

Standard Ports

- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.1 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports***

- 1x Smart card reader
- 1x Nano-SIM card slot (WWAN support models)

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

Docking

Docking

Various docking solutions supported via Thunderbolt™.

For more compatible docking solutions, please visit [Docking for ThinkPad® L13 Gen 6 \(Intel®\)](#)

SECURITY & PRIVACY

Security

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-3 certified

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

- Smart card reader, supports ISO 7816 and EMV
- No smart card reader

Fingerprint Reader

- Touch style fingerprint reader integrated in power button, match-on-chip
- No fingerprint reader

BIOS Security

- NVMe® password
- Power-on password
- Supervisor password
- System management password
- Certificate-based BIOS authentication
- FIDO (Fast Identity Online) authentication
- Self-healing BIOS

Other Security

- Camera privacy shutter
- (Optional) IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management

System Management

- Intel® vPro® Enterprise^[1]
- Non-vPro®

Notes:

[1] Intel® vPro® offers a superset of DASH's defined capabilities.

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ACCESSORIES

Bundled Accessories

Bundled Accessories^[1]

- Lenovo® USB-C® to Ethernet Adapter (1Gbps)
- None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for ThinkPad® L13 Gen 6 \(Intel®\)](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping packaging: -20°C (-4°F) to 60°C (140°F)
- Storage without packaging: 5°C (41°F) to 43°C (109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material^[1]

50% recycled aluminium on top cover
50% PCC recycled on aluminium top cover top frame
50% PCC recycled on display cover bezel
30% PCC recycled on bottom cover
85% PCC recycled plastic used in key caps
90% PCC recycled plastic used in speaker enclosure
45% PCC recycled plastic + 5% OBP on dummy SMC and dummy SIM cover
25% OBP recycled on fan housing
12% recycled rare earth fan magnet
30% recycled rare earth speaker magnet
90% PCC recycled plastic used in slim GaN 65W adapters and standard 65W adapters
90% PCC recycled plastic used in the battery pack enclosure
90% recycled and/or sustainable content for packaging

Notes:

[1] PCC: Post Consumer Content, recycled materials from customers.

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[3]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

[3] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

(Optional) Eyesafe® Certified 2.0

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

