



HP 400 Quiet Wireless Mouse (AZ7B6AA)

Overview

Make what matters, with a mouse that's uniquely yours

Everything you do matters, so why not do it with personalized technology? The HP 400 Quiet Wireless Mouse comes in a range of modern colors, all made with soft-silicone material, so pick your favorite; then let this durable, ambidextrous mouse and its 24-month battery life[1] help you get down to business.

Personalize it. With colorful, durable silicone

Durable, with silicone rubber, this soft, easy-to-sanitize, ambidextrous mouse was designed for you. Pick your favorite from five color options.

A mouse that keeps up with you

Wireless connectivity via Bluetooth or a 2.4GHz Dongle, gets you up and running, then keeps you there. Up to 6000 adjustable DPI keeps you tracking almost any surface[5], while a 24-month battery life[1] ensures that you stay clicking day and night.

Quiet clicks and quick access

Quiet clicks, vertical/horizontal scrolling options, and access to the Microsoft® Wheel setting for easy shortcuts from one click of the center button, [2] help you do more, quickly and quietly.

Built for a better tomorrow

The HP 400 Quiet Wireless Mouse is made with at least 40% post-consumer recycled materials[3] and comes in FSC® certified packaging[4].

Features

Durable liquid silicone rubber

Engineered with liquid silicone that is soft to the touch, easy to clean and sanitize.

Scroll with It

Adapt it to your speed to effortlessly scroll through documents and webpages with the 2D scroll wheel--scroll up and down, side to side.

Access the Microsoft® Wheel setting

With one click, utilize shortcuts across Microsoft® apps with center-button access to the Microsoft® Wheel setting.^[2]

Long-lasting battery

Go all day and night with up to 24 months of battery life from one AA battery.^[1]

[1] From 1 AA battery. Battery life is an estimate and varies depending on many factors, including number of active, idle and asleep hours of use, number of applications running, environmental conditions and features used; actual battery life will vary with usage and environmental condition. The maximum capacity of battery will naturally decrease with time and usage.

[2] Requires Windows 10 or higher.

[3] Recycled material is expressed as a percentage of the weight of total recycled materials over the total product weight. The final percentage of recycled material is based on the definition of set by SCS Global service- SCS-103 Annex A Certification.

[4] Forest Stewardship Council® (FSC) Certified, meaning all components of our packaging come from responsibly managed forests to provide environmental benefits.

[5] Glass surface may affect functionality.

Specifications

Dimensions (W x D x H)	118 x 61 x 40 mm
Dimensions (W x D x H)	4.64 x 2.38 x 1.57 in
Weight	110 g
Weight	0.24 lb
Package dimensions (W x D x H)	125 x 85 x 53 mm
Package weight	175 g
Battery life	Up to 24 months
Sustainable impact specifications	FSC Certified Packaging; 40% recycled materials
Minimum System Requirements	USB Type-A port; Bluetooth®
UPC number	(ABA) 198701895367; (ABB) 198701895374; (UUF) 198701895381
Manufacturer Warranty	HP standard one-year limited warranty
What's in the box	Wireless mouse; USB dongle; 1 x AA battery; Quick start guide; Warranty card; R.E.D. Card (EMEA only)

Additional specifications

Advanced scroll wheel	Normal
Battery type	1 x AA
Bluetooth version	5.2
Buttons	5 buttons
Cartons per layer	9
Cartons per pallet	45
Color	Maple
Compatible Operating Systems	Windows 11; Windows 10; macOS; Android™; iOS; ChromeOS
Connection type	2.4 GHz wireless connection; Bluetooth®
Datasheet photo 1	https://prismptui-int.inc.hpinc.net/PRO.Crystal.1/DAMHandler/Accessories/Cooper_Mouse_Maple_Coreset_FrontLeft_GreyBg-removebg-preview.png
Datasheet photo 2	https://prismptui-int.inc.hpinc.net/PRO.Crystal.1/DAMHandler/Accessories/Cooper_Mouse_Maple_Coreset_Front_11GreyBg-removebg-preview.png
Datasheet photo 3	https://prismptui-int.inc.hpinc.net/PRO.Crystal.1/DAMHandler/Accessories/Cooper_Mouse_Maple_Coreset_LeftProfile_GreyBg-removebg-preview.png
Datasheet photo 4	https://prismptui-int.inc.hpinc.net/PRO.Crystal.1/DAMHandler/Accessories/Cooper_Mouse_Maple_Coreset_Bottom_GreyBg-removebg-preview.png
Ecolabels	Recycled Content for Electrical and Electronic Equipment
Indicator light	Battery; Connectivity
Master carton dimension (imperial)	14.25 x 11.22 x 11.61 in
Master carton dimension (metric)	36.2 x 28.5 x 29.5 cm
Package dimensions (W x D x H)	4.92 x 3.35 x 2.09 in
Package weight	0.39 lb
Pallet (layers)	5

Pallet dimensions	50.79 x 39.37 x 42.52 in
Pallet dimensions (W x D x H)	120 x 100 x 108 cm
Resolution	Up to 6000 dpi
Sensor nominal value	1200 dpi
Sensor technology	Multi surface tracking ^[2]
Technology logo 1	https://prismgui-int.inc.hplicorp.net/PRO.Crystal.1/DAMHandler/Accessories/SCS_Recycled_Content_Annex_A_Mouse_BL.png
UNSPSC code	43211708
Wireless range	Up to 10 m in open area
Wireless range (imperial)	Up to 32.81 ft in open area

[2] Glass surface may affect functionality.

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.