




HP 89X High Yield Black Original LaserJet Toner Cartridge (CF289X)

Overview



HP 89X LaserJet Toner Cartridge, black, 10,000 pages[10]

Original HP Toner cartridges with JetIntelligence deliver professional-quality pages, high-yield options,[2] peak printing performance, and innovative HP anti-fraud technology. Help reduce costs with energy-saving HP EcoSmart black toner.[3]

Achieve print quality and toner efficiency

Print crisp black text and use less energy when printing with Original HP EcoSmart black toner.[3]

Gain peace of mind using HP toner cartridges

Innovative anti-fraud technology helps you get the authentic HP quality you paid for.

Value in optional high-yield cartridges[2,4,5]

Print up to two times more pages, using Original HP High Yield Toner cartridges with JetIntelligence.[2,4]

Help protect your investment

Plan ahead—use HP Web Jetadmin to track toner usage and receive regular supplies updates.[7]

[2] HP 89X and HP 89Y High Yield Original LaserJet Toner cartridges are not included in printer purchase; purchase separately. For more information, see <http://www.hp.com/go/learnaboutsupplies>.

[3] HP calculations based on ENERGY STAR® normalized TEC data comparing HP LaserJet 200-500 series printers. See hp.com/ecosmart

[4] HP 89X High Yield Original LaserJet Toner cartridges compared to HP 89A Original LaserJet Toner cartridges with JetIntelligence. For more information, see <http://www.hp.com/go/learnaboutsupplies>.

[5] HP 89Y High Yield Original LaserJet Toner cartridges compared to HP 89A Original LaserJet Toner cartridges with JetIntelligence. For more information, see <http://www.hp.com/go/learnaboutsupplies>

[7] Refer to your device data sheet and HP Web Jetadmin supported feature list for details.

[10] Compared with standard-capacity HP cartridges. Based on published page yields <http://hp.com/learnaboutsupplies>

Specifications

Print Cartridge/Bottle, Color(s)	Black
Technology	Laser
Supply Type	Cartridges
Operating Temperature Range (celsius)	10 to 32.5°C
Storage Temperature Range (celsius)	-20 to 40°C
Operating Humidity Range	20 to 80% RH
Non-operating Humidity Range	10 to 90% RH
Print Resolution Technologies	JetIntelligence
Compatibility Statement	HP LaserJet Enterprise M507 Printer series, HP LaserJet Enterprise MFP M528 series
Product Count Per Unit	1
Quantity Per Pallet	135
Quantity Per European Pallet	84
Cartons Per Pallet	135
UPC Number	192018046634
Product Dimensions (metric)	362 x 102 x 227 mm
Product Dimensions (imperial)	14.25 x 4.02 x 8.94 in
Package Dimensions (metric)	362 x 102 x 227 mm
Package Dimensions (imperial)	14.25 x 4.02 x 8.94 in
Pallet Dimensions (metric)	1098 x 942 x 1279 mm
Pallet Dimensions (imperial)	43.2 x 37.1 x 50.4 in
Package Weight (metric)	1.35 kg
Package Weight (imperial)	2.97 lb
Pallet Weight (metric)	202.75 kg
Pallet Weight (imperial)	445.95 lb
Page Yield	10000
Average Page Yield For A4 Format, Black and White	~10,000 pages
What Is In The Box	1 Cartridge
Manufacturer Warranty	HP's Premium Protection Warranty. This HP product is warranted to be free from defects in materials and workmanship.

Additional specifications

Automation Feature Photo 01	https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c06319388.jpg
Business Filter	cMPS
Cartons Per Layer	27
Cartridge Color	Black
Cartridge Package Selectability	89X
Color Starter Yield	29500
Color Yield	29500
Compatibility Headline	HP 89 toner cartridges work with:
Component Type	Cartridges
Count of Cartons per Pallet Layer (European Pallet)	21
Count of Layers In Pallet	5
Datasheet Feature Photo 02	https://ssl-product-images.www8-hp.com/digmedialib/prodimg/lowres/c06319388.jpg
Euro Pallet Weight (metric)	133.9 kg
European Pallet Dimensions (metric)	1100 x 740 x 1057 mm
Mono Starter Yield	5000
Mono Yield	10000
Operating Temperature Range (fahrenheit)	50 to 90.5°F
Package Count	1
Page Yield (black)	1 Black (~10,000 pages)
Page Yield Footnote	Approximate average yield based on ISO/IEC 19752. Actual yield varies considerably based on content of printed pages and other factors. For details see http://www.hp.com/go/learnaboutsupplies .
Print Technology	Laser
Product Subgroup	High Capacity Toner Cartridges
Segment (filter)	JetIntelligence
Stacking Number For Carton	20
Storage Temperature Range (fahrenheit)	-4 to 104°F
Subgroup	High Capacity Cartridges
UNSPSC Code	44103103

Warranty Standard Statement

HP's Premium Protection Warranty. This HP product is warranted to be free from defects in materials and workmanship. This warranty does not apply to print cartridges that (a) have been refilled, refurbished, remanufactured or tampered with in any way, (b) experience problems resulting from misuse, improper storage, or operation outside of the published environmental specifications for the printer product or (c) exhibit wear from ordinary use. To obtain warranty service, please return the product to place of purchase (with a written description of the problem and print samples) or contact HP customer support. At HP's option, HP will either replace products that prove to be defective or refund your purchase price. TO THE EXTENT ALLOWED BY LOCAL LAW, THE ABOVE WARRANTY IS EXCLUSIVE AND NO OTHER WARRANTY OR CONDITION, WHETHER WRITTEN OR ORAL, IS EXPRESSED OR IMPLIED AND HP SPECIFICALLY DISCLAIMS ANY IMPLIED WARRANTIES OR CONDITIONS OF MERCHANTABILITY, SATISFACTORY QUALITY, AND FITNESS FOR A PARTICULAR PURPOSE. TO THE EXTENT ALLOWED BY LOCAL LAW, IN NO EVENT WILL HP OR ITS SUPPLIERS BE LIABLE FOR DIRECT, SPECIAL, INCIDENTAL, CONSEQUENTIAL (INCLUDING LOST PROFIT OR DATA), OR OTHER DAMAGE, WHETHER BASED IN CONTRACT, TORT, OR OTHERWISE. THE WARRANTY TERMS CONTAINED IN THIS STATEMENT, EXCEPT TO THE EXTENT LAWFULLY PERMITTED, DO NOT EXCLUDE, RESTRICT OR MODIFY AND ARE IN ADDITION TO THE MANDATORY STATUTORY RIGHTS APPLICABLE TO THE SALE OF THIS PRODUCT TO YOU.

Weight (imperial)	2.13 lb
Weight (metric)	0.97 kg

Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.