



# Introduction

Cisco Catalyst 9300 Series Switches are Cisco’s lead stackable access platforms for the next-generation enterprise and have been purpose-built to address emerging trends of Security, IoT, Mobility, and Cloud.

They deliver complete convergence with the rest of the Cisco Catalyst 9000 Series Switches in terms of ASIC architecture with a Unified Access Data Plane (UADP) 2.0. The platform runs an Open Cisco IOS XE that supports model driven programmability, has the capacity to host containers, and run 3rd party applications and scripts natively within the switch (by virtue of x86 CPU architecture, local storage, and a higher memory footprint). This series forms the foundational building block for SD-Access, which is Cisco’s lead enterprise architecture.

- [Supported Hardware, on page 1](#)

## Supported Hardware

### Cisco Catalyst 9300 Series Switches—Model Numbers

The following table lists the supported hardware models and the default license levels they are delivered with. For information about the available license levels, see section *License Levels* .

*Table 1: Cisco Catalyst 9300 Series Switches*

Switch Model	Default License Level <sup>1</sup>	Description
C9300-24H-A	Network Advantage	Stackable 24 10/100/1000 Mbps UPOE+ ports; PoE budget of 830 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-24H-E	Network Essentials	
C9300-24P-A	Network Advantage	Stackable 24 10/100/1000 PoE+ ports; PoE budget of 437W; 715 WAC power supply; supports StackWise-480 and StackPower
C9300-24P-E	Network Essentials	

Switch Model	Default License Level <sup>1</sup>	Description
C9300-24S-A	Network Advantage	Stackable 24 1G SFP ports; two power supply slots with 715 WAC power supply installed by default; supports StackWise-480 and StackPower.
C9300-24S-E	Network Essentials	
C9300-24T-A	Network Advantage	Stackable 24 10/100/1000 Ethernet ports; 350 WAC power supply; supports StackWise-480 and StackPower
C9300-24T-E	Network Essentials	
C9300-24U-A	Network Advantage	Stackable 24 10/100/1000 UPoE ports; PoE budget of 830W; 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-24U-E	Network Essentials	
C9300-24UB-A	Network Advantage	Stackable 24 10/100/1000 Mbps UPOE ports that provide deep buffers and higher scale; PoE budget of 830W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-24UB-E	Network Essentials	
C9300-24UX-A	Network Advantage	Stackable 24 Multigigabit Ethernet 100/1000/2500/5000/10000 UPoE ports; PoE budget of 490 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-24UX-E	Network Essentials	
C9300-24UXB-A	Network Advantage	Stackable 24 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE ports that provide deep buffers and higher scale; PoE budget of 560 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-24UXB-E	Network Essentials	
C9300-48H-A	Network Advantage	Stackable 48 10/100/1000 Mbps UPOE+ ports; PoE budget of 822 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-48H-E	Network Essentials	
C9300-48T-A	Network Advantage	Stackable 48 10/100/1000 Ethernet ports; 350 WAC power supply; supports StackWise-480 and StackPower
C9300-48T-E	Network Essentials	

Switch Model	Default License Level <sup>1</sup>	Description
C9300-48P-A	Network Advantage	Stackable 48 10/100/1000 PoE+ ports; PoE budget of 437W; 715 WAC power supply; supports StackWise-480 and StackPower
C9300-48P-E	Network Essentials	
C9300-48S-A	Network Advantage	Stackable 48 1G SFP ports; two power supply slots with 715 WAC power supply installed by default; supports StackWise-480 and StackPower.
C9300-48S-E	Network Essentials	
C9300-48T-A	Network Advantage	Stackable 48 10/100/1000 Ethernet ports; 350 WAC power supply; supports StackWise-480 and StackPower
C9300-48T-E	Network Essentials	
C9300-48U-A	Network Advantage	Stackable 48 10/100/1000 UPoE ports; PoE budget of 822 W; 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-48U-E	Network Essentials	
C9300-48UB-A	Network Advantage	Stackable 48 10/100/1000 Mbps UPOE ports that provide deep buffers and higher scale; PoE budget of 822 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-48UB-E	Network Essentials	
C9300-48UN-A	Network Advantage	Stackable 48 Multigigabit Ethernet (100 Mbps or 1/2.5/5 Gbps) UPoE ports; PoE budget of 610 W with 1100 WAC power supply; supports StackWise-480 and StackPower
C9300-48UN-E	Network Essentials	
C9300-48UXM-A	Network Advantage	Stackable 48 (36 2.5G Multigigabit Ethernet and 12 10G Multigigabit Ethernet Universal Power Over Ethernet (UPOE) ports)
C9300-48UXM-E	Network Essentials	

<sup>1</sup> See section *Licensing* → *Table: Permitted Combinations*, in this document for information about the add-on licenses that you can order.

Table 2: Cisco Catalyst 9300L Series Switches

Switch Model	Default License Level <sup>2</sup>	Description
C9300L-24T-4G-A	Network Advantage	Stackable 24x10/100/1000M Ethernet ports; 4x1G SFP fixed uplink ports; 350 WAC power supply; supports StackWise-320.
C9300L-24T-4G-E	Network Essentials	
C9300L-24P-4G-A	Network Advantage	Stackable 24x10/100/1000M PoE+ ports; 4x1G SFP fixed uplink ports; PoE budget of 505W with 715 WAC power supply; supports StackWise-320.
C9300L-24P-4G-E	Network Essentials	
C9300L-24T-4X-A	Network Advantage	Stackable 24x10/100/1000M Ethernet ports; 4x10G SFP+ fixed uplink ports; 350 WAC power supply; supports StackWise-320.
C9300L-24T-4X-E	Network Essentials	
C9300L-24P-4X-A	Network Advantage	Stackable 24x10/100/1000M PoE+ ports; 4x10G SFP+ fixed uplink ports; PoE budget of 505W with 715 WAC power supply; supports StackWise-320.
C9300L-24P-4X-E	Network Essentials	
C9300L-48T-4G-A	Network Advantage	Stackable 48x10/100/1000M Ethernet ports; 4x1G SFP fixed uplink ports; 350 WAC power supply; supports StackWise-320.
C9300L-48T-4G-E	Network Essentials	
C9300L-48P-4G-A	Network Advantage	Stackable 48x10/100/1000M PoE+ ports; 4x1G SFP fixed uplink ports; PoE budget of 505W with 715 WAC power supply; supports StackWise-320.
C9300L-48P-4G-E	Network Essentials	
C9300L-48T-4X-A	Network Advantage	Stackable 48x10/100/1000M Ethernet ports; 4x10G SFP+ fixed uplink ports; 350 WAC power supply; supports StackWise-320.
C9300L-48T-4X-E	Network Essentials	
C9300L-48P-4X-A	Network Advantage	Stackable 48x10/100/1000M PoE+ ports; 4x10G SFP+ fixed uplink ports; PoE budget of 505W with 715 WAC power supply; supports StackWise-320.
C9300L-48P-4X-E	Network Essentials	

Switch Model	Default License Level <sup>2</sup>	Description
C9300L-48PF-4G-A	Network Advantage	Stackable 48 10/100/1000 Mbps PoE+ ports; 4x1G SFP+ fixed uplink ports; PoE budget of 890 W with 1100 WAC power supply; supports StackWise-320.
C9300L-48PF-4G-E	Network Essentials	
C9300L-48PF-4X-A	Network Advantage	Stackable 48 10/100/1000 Mbps PoE+ ports; 4x10G SFP+ fixed uplink ports; PoE budget of 890 W with 1100 WAC power supply; supports StackWise-320.
C9300L-48PF-4X-E	Network Essentials	
C9300L-24UXG-4X-A	Network Advantage	Stackable 16 10/100/1000 Mbps and 8 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE ports; 4x10G SFP+ fixed uplink ports; PoE budget of 880 W with 1100 WAC power supply; supports StackWise-320.
C9300L-24UXG-4X-E	Network Essentials	
C9300L-24UXG-2Q-A	Network Advantage	Stackable 16 10/100/1000 Mbps and 8 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE ports; 2x40G QSFP+ fixed uplink ports; PoE budget of 722 W with 1100 WAC power supply; supports StackWise-320.
C9300L-24UXG-2Q-E	Network Essentials	
C9300L-48UXG-4X-A	Network Advantage	Stackable 36 10/100/1000 Mbps and 12 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE ports; 4x10G SFP+ fixed uplink ports; PoE budget of 675 W with 1100 WAC power supply; supports StackWise-320.
C9300L-48UXG-4X-E	Network Essentials	
C9300L-48UXG-2Q-A	Network Advantage	Stackable 36 10/100/1000 Mbps and 12 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE ports; 2x40G QSFP+ fixed uplink ports; PoE budget of 675 W with 1100 WAC power supply; supports StackWise-320.
C9300L-48UXG-2Q-E	Network Essentials	

<sup>2</sup> See section *Licensing* → *Table: Permitted Combinations*, in this document for information about the add-on licenses that you can order.

**Table 3: Cisco Catalyst 9300LM Series Switches**

Switch Model	Default License Level <sup>3</sup>	Description
C9300LM-48T-4Y-A	Network Advantage	Stackable 48 x 10/100/1000 M Ethernet ports; 4 x 25 GE SFP28 fixed uplink ports; 600 WAC power supply and fixed fans; supports StackWise-320.
C9300LM-48T-4Y-E	Network Essentials	

Switch Model	Default License Level <sup>3</sup>	Description
C9300LM-24U-4Y-A	Network Advantage	Stackable 24 x 10/100/1000 M UPOE ports; 4 x 25 GE SFP28 fixed uplink ports; PoE budget of 420 W with a single default 600 WAC power supply; supports StackWise-320.
C9300LM-24U-4Y-E	Network Essentials	
C9300LM-48U-4Y-A	Network Advantage	Stackable 48 x 10/100/1000 M UPOE ports; 4 x 25 GE SFP28 fixed uplink ports; PoE budget of 790 W with a single default 1000 WAC power supply; supports StackWise-320.
C9300LM-48U-4Y-E	Network Essentials	
C9300LM-48UX-4Y-A	Network Advantage	Stackable 40 x 10/100/1000 M and 8 Multigigabit Ethernet (100M/1000M/2.5GE/5GE/10GE) UPOE ports; 4 x 25 GE SFP28 fixed uplink ports; PoE budget of 790 W with a single default 1000 WAC power supply; supports StackWise-320.
C9300LM-48UX-4Y-E	Network Essentials	

<sup>3</sup> See section *Licensing* → *Table: Permitted Combinations*, in this document for information about the add-on licenses that you can order.

**Table 4: Cisco Catalyst 9300X Series Switches**

Switch Model	Default License Level <sup>4</sup>	Description
C9300X-12Y-A	Network Advantage	Stackable 12 1/10/25 GE SFP28 downlink ports; 715 WAC power supply; supports StackPower+, StackWise-1T and C9300X-NM network modules.
C9300X-12Y-E	Network Essentials	
C9300X-24Y-A	Network Advantage	Stackable 24 1/10/25 GE SFP28 downlink ports; 715 WAC power supply; supports StackPower+, StackWise-1 and C9300X-NM network modules.
C9300X-24Y-E	Network Essentials	
C9300X-24HX-A	Network Advantage	Stackable 24 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE+ ports; PoE budget of 735W with 1100WAC power supply; supports StackPower+, StackWise-1T and C9300X-NM network modules.
C9300X-24HX-E	Network Essentials	
C9300X-48HX-A	Network Advantage	Stackable 48 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) UPOE+ports; PoE budget of 590W with 1100 WAC power supply; supports StackPower+, StackWise-1T and C9300X-NM network modules.
C9300X-48HX-E	Network Essentials	
C9300X-48TX-A	Network Advantage	Stackable 48 Multigigabit Ethernet (100 Mbps or 1/2.5/5/10 Gbps) ports; 715WAC powersupply; supports StackPower+, StackWise-1T and C9300X-NM network modules.
C9300X-48TX-E	Network Essentials	
C9300X-48HXN-A	Network Advantage	Stackable 40 x 100/1000 M or 2.5/5 GE Multigigabit Ethernet and 8 x 100/1000 M or 2.5/5/10 GE Multigigabit Ethernet UPOE+ ports; PoE budget of 690W with 1100WAC power supply; supports StackPower+, StackWise-1T and C9300X-NM network modules
C9300X-48HXN-E	Network Essentials	

<sup>4</sup> See section *Licensing* → *Table: Permitted Combinations*, in this document for information about the add-on licenses that you can order.

## Network Modules

The following table lists the optional uplink network modules with 1-Gigabit, 10-Gigabit, 25-Gigabit, and 40-Gigabit slots. You should only operate the switch with either a network module or a blank module installed.

Network Module	Description
C3850-NM-4-1G <sup>1</sup>	Four 1 Gigabit Ethernet SFP module slots
C3850-NM-2-10G <sup>1</sup>	Two 10 Gigabit Ethernet SFP module slots
C3850-NM-4-10G <sup>1</sup>	Four 10 Gigabit Ethernet SFP module slots
C3850-NM-8-10G <sup>1</sup>	Eight 10 Gigabit Ethernet SFP module slots
C3850-NM-2-40G <sup>1</sup>	Two 40 Gigabit Ethernet SFP module slots
C9300-NM-4G <sup>2</sup>	Four 1 Gigabit Ethernet SFP module slots
C9300-NM-4M <sup>2</sup>	Four MultiGigabit Ethernet slots
C9300-NM-8X <sup>2</sup>	Eight 10 Gigabit Ethernet SFP+ module slots
C9300-NM-2Q <sup>2</sup>	Two 40 Gigabit Ethernet QSFP+ module slots
C9300-NM-2Y <sup>2</sup>	Two 25 Gigabit Ethernet SFP28 module slots
C9300X-NM-2C <sup>3</sup>	Two 40 Gigabit Ethernet/100 Gigabit Ethernet QSFP+ module slots
C9300X-NM-4C <sup>3</sup>	Four 40 Gigabit Ethernet/100 Gigabit Ethernet slots with a QSFP+ connector in each slot.
C9300X-NM-8M <sup>3</sup>	Eight Multigigabit Ethernet slots
C9300X-NM-8Y <sup>3</sup>	Eight 25 Gigabit Ethernet/10 Gigabit Ethernet/1 Gigabit Ethernet SFP+ module slots



- 
- Note**
1. These network modules are supported only on the C3850 and C9300 SKUs of the Cisco Catalyst 3850 Series Switches and Cisco Catalyst 9300 Series Switches respectively.
  2. These network modules are supported only on the C9300 SKUs of the Cisco Catalyst 9300 Series Switches.
  3. These network modules are supported only on the C9300X SKUs of the Cisco Catalyst 9300 Series Switches.
- 

## Optics Modules

Cisco Catalyst Series Switches support a wide range of optics and the list of supported optics is updated on a regular basis. Use the [Transceiver Module Group \(TMG\) Compatibility Matrix](#) tool, or consult the tables at this URL for the latest transceiver module compatibility information: [https://www.cisco.com/en/US/products/hw/modules/ps5455/products\\_device\\_support\\_tables\\_list.html](https://www.cisco.com/en/US/products/hw/modules/ps5455/products_device_support_tables_list.html)