



# HP 659X High Yield Magenta Original LaserJet Toner Cartridge (W2013X)

## Overview

HP 659X LaserJet Toner Cartridge, magenta, 29,000 pages[6]



Produce vibrant photo-like color in marketing materials with HP ColorSphere 3 technology. Keep business productivity high. Optional high-yield Original HP LaserJet Toner cartridges offer over two times more pages than standard cartridges.[1,2]

### Print standout documents and marketing materials.

Increase the impact of marketing materials with a wide range of colors from an enhanced print mode innovation.

### HP print gauge technology provides time-savings

Plan ahead—use HP Web Jetadmin to track toner usage and receive regular supplies updates.[3]

### Stay productive with reliable cartridges.

Get the full value from a toner purchase using the two-part design of Original HP cartridge and imaging drum.

### Designed for energy savings and long life

HP 659 cartridges use toner that is formulated to help save energy while printing.[4]

---

[1] High-yield cartridges are not included in printer purchase; purchase separately. Learn more at <http://www.hp.com/go/learnaboutsupplies>.

[2] HP 659A cartridge compared to HP 659X Original LaserJet Toner Cartridges. See <http://www.hp.com/go/learnaboutsupplies>.

[3] Learn more at <http://www.hp.com/go/webjetadmin>.

[4] HP JetIntelligence Toner cartridges introduced since 2015 compared to previous toner versions.

[6] Approximate average composite cyan, yellow, magenta yield based on ISO/IEC 19798. Actual yield varies considerably based on content of printed pages and other factors. For details see <http://www.hp.com/go/learnaboutsupplies>.

## Specifications

<b>Print Cartridge/Bottle, Color(s)</b>	Magenta
<b>Technology</b>	Laser
<b>Supply Type</b>	Cartridges
<b>Operating Temperature Range (celsius)</b>	10 to 32.5°C
<b>Storage Temperature Range (celsius)</b>	-20 to 40°C
<b>Operating Humidity Range</b>	20 to 80% RH
<b>Non-operating Humidity Range</b>	10 to 90% RH
<b>Print Resolution Technologies</b>	JetIntelligence
<b>Compatibility Statement</b>	HP Color LaserJet Enterprise M856 Printer series, HP Color LaserJet Enterprise MFP M776 series
<b>Product Count Per Unit</b>	1
<b>Quantity Per Pallet</b>	70
<b>Quantity Per European Pallet</b>	55
<b>Cartons Per Pallet</b>	70
<b>UPC Number</b>	192545650892
<b>Product Dimensions (metric)</b>	483 x 155 x 198 mm
<b>Product Dimensions (imperial)</b>	19.02 x 6.1 x 7.8 in
<b>Package Dimensions (metric)</b>	483 x 155 x 198 mm
<b>Package Dimensions (imperial)</b>	19.02 x 6.1 x 7.8 in
<b>Pallet Dimensions (metric)</b>	1127 x 956 x 1134 mm
<b>Pallet Dimensions (imperial)</b>	44.4 x 37.6 x 44.6 in
<b>Package Weight (metric)</b>	1.84 kg
<b>Package Weight (imperial)</b>	4.05 lb
<b>Pallet Weight (metric)</b>	149.3 kg
<b>Pallet Weight (imperial)</b>	328.4 lb
<b>Page Yield</b>	29000
<b>What Is In The Box</b>	Toner cartridge; Recycling guide
<b>Manufacturer Warranty</b>	HP's Premium Protection Warranty. This HP product is warranted to be free from defects in materials and workmanship.

## Additional specifications

<b>Average Page Yield For A4 Format, Color</b>	29,000 pages
<b>Business Filter</b>	cMPS
<b>Cartons Per Layer</b>	14
<b>Cartridge Color</b>	Magenta
<b>Cartridge Package Selectability</b>	659X
<b>Color Starter Yield</b>	13000
<b>Color Yield</b>	29000
<b>Compatibility Headline</b>	HP 659 toner cartridges work with:
<b>Component Type</b>	Cartridges
<b>Count of Cartons per Pallet Layer (European Pallet)</b>	11
<b>Count of Layers In Pallet</b>	5
<b>Euro Pallet Weight (metric)</b>	121.7 kg
<b>European Pallet Dimensions (metric)</b>	1127 x 785 x 1134 mm
<b>Operating Temperature Range (fahrenheit)</b>	50 to 90.5°F
<b>Package Count</b>	1
<b>Page Yield (magenta)</b>	1 Magenta (~29,000 pages)
<b>Page Yield Footnote</b>	Approximate average composite cyan, yellow, magenta yield based on ISO/IEC 19798. Actual yield varies considerably based on content of printed pages and other factors. For details see <a href="http://www.hp.com/go/learnaboutsupplies">http://www.hp.com/go/learnaboutsupplies</a> .
<b>Print Technology</b>	Laser
<b>Product Subgroup</b>	High Capacity Toner Cartridges
<b>Segment (filter)</b>	JetIntelligence
<b>Stacking Number For Carton</b>	20
<b>Storage Temperature Range (fahrenheit)</b>	-4 to 104°F
<b>Subgroup</b>	High Capacity Cartridges
<b>UNSPSC Code</b>	44103103

### Warranty Standard Statement

HP's Premium Protection Warranty. This HP product is warranted to be free from defects in materials and workmanship. This warranty does not apply to print cartridges that (a) have been refilled, refurbished, remanufactured or tampered with in any way, (b) experience problems resulting from misuse, improper storage, or operation outside of the published environmental specifications for the printer product or (c) exhibit wear from ordinary use. To obtain warranty service, please return the product to place of purchase (with a written description of the problem and print samples) or contact HP customer support. At HP's option, HP will either replace products that prove to be defective or refund your purchase price. TO THE EXTENT ALLOWED BY LOCAL LAW, THE ABOVE WARRANTY IS EXCLUSIVE AND NO OTHER WARRANTY OR CONDITION, WHETHER WRITTEN OR ORAL, IS EXPRESSED OR IMPLIED AND HP SPECIFICALLY DISCLAIMS ANY IMPLIED WARRANTIES OR CONDITIONS OF MERCHANTABILITY, SATISFACTORY QUALITY, AND FITNESS FOR A PARTICULAR PURPOSE. TO THE EXTENT ALLOWED BY LOCAL LAW, IN NO EVENT WILL HP OR ITS SUPPLIERS BE LIABLE FOR DIRECT, SPECIAL, INCIDENTAL, CONSEQUENTIAL (INCLUDING LOST PROFIT OR DATA), OR OTHER DAMAGE, WHETHER BASED IN CONTRACT, TORT, OR OTHERWISE. THE WARRANTY TERMS CONTAINED IN THIS STATEMENT, EXCEPT TO THE EXTENT LAWFULLY PERMITTED, DO NOT EXCLUDE, RESTRICT OR MODIFY AND ARE IN ADDITION TO THE MANDATORY STATUTORY RIGHTS APPLICABLE TO THE SALE OF THIS PRODUCT TO YOU.

**Weight (imperial)** 2.86 lb

**Weight (metric)** 1.3 kg

---

## Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Feb 27, 2026 9:20 PM UTC+0000