

# Cisco Wireless Solutions Software Compatibility Matrix

---

**First Published:** 2017-01-02

**Last Modified:** 2023-10-04

## Cisco Wireless Solutions Software Compatibility Matrix

This document lists the software compatibility matrix information for the Cisco wireless devices used in a Cisco centralized and distributed wireless LAN solution and in converged access solutions.



---

**Note** To view the legacy Cisco wireless devices and the compatible Cisco software releases, see <http://www.cisco.com/c/en/us/td/docs/wireless/compatibility/matrix-legacy/compatibility-matrix-legacy.html>

---

## Conventions

See [Cisco Technical Tips Conventions](#) for information about document conventions.

## Cisco Catalyst 9800 Series Wireless Controller Matrix

This section contains the Cisco Catalyst 9800 Series Wireless Controller's compatibility information with Cisco Identity Services Engine, Cisco Prime Infrastructure, Cisco DNA Center platforms and IRCM with the Cisco AireOS Wireless Controller platform.

Table 1: Cisco Catalyst 9800 Series Wireless Controllers Release Compatibility Matrix

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Dublin 17.12.1	3.2 3.1 3.0 2.7 * all with latest patches	3.10.4	8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.176.2 8.5.182.104	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Dublin 17.11.1	3.2 3.1 3.0 2.7 2.6 2.4	3.10.4 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.176.2 8.5.182.104	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Dublin 17.10.1	3.0 2.7 2.6 2.4	3.10.4 3.10.3 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.176.2 8.5.182.104	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.9.4	3.2 3.1 3.0 2.7 2.6 2.4	3.10.4 3.10.3 3.10.2 <sup>1</sup>	8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.176.2 8.5.182.104	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Cupertino 17.9.3	3.2	3.10.4	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.1	3.10.3	8.10.183.0	
	3.0	3.10.2 <sup>1</sup>	8.10.182.0	
	2.7		8.10.181.0	
	2.6		8.10.171.0	
	2.4		8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
		8.5.176.2		
		8.5.182.104		
Cisco IOS XE Cupertino 17.9.2	3.1	3.10.4	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.10.3	8.10.183.0	
	2.7	3.10.2 <sup>1</sup>	8.10.182.0	
	2.6		8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
		8.5.176.2		
		8.5.182.104		

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Cupertino 17.9.1	3.1	3.10.4	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.10.3	8.10.183.0	
	2.7	3.10.2 <sup>1</sup>	8.10.182.0	
	2.6		8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.176.2	
		8.5.182.104		
Cisco IOS XE Cupertino 17.8.1	3.0	3.10.2	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.7	3.10.1 <sup>1</sup>	8.10.183.0	
	2.6		8.10.182.0	
	2.4		8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.176.2	
		8.5.182.104		

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Cupertino 17.7.1	3.0	3.10.2	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.7	3.10.1 <sup>1</sup>	8.10.183.0	
	2.6		8.10.182.0	
	2.4		8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.176.2	
			8.5.182.104	
			8.5.152.103	
			8.5.164.216	
Cisco IOS XE Bengaluru 17.6.6	3.1	3.10	8.10.190.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.9	8.10.185.0	
	2.7		8.10.171.0	
	2.6		8.10.162.0	
	2.4		8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.182.104	
			8.5.176.0	
			8.5.176.2	
			8.5.164.0	
			8.5.164.216	

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Bengaluru 17.6.5	3.1 3.0 2.7 2.6 2.4	3.10.1 3.10 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.182.104 8.5.176.0 8.5.176.2 8.5.164.0 8.5.164.216	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.4	3.1 3.0 2.7 2.6 2.4	3.10.1 3.10 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.182.104 8.5.176.0 8.5.176.2 8.5.164.0 8.5.164.216	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Bengaluru 17.6.3	3.1	3.10.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.10 <sup>1</sup>	8.10.183.0	
	2.7		8.10.182.0	
	2.6		8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.182.104	
			8.5.176.0	
			8.5.176.2	
			8.5.164.0	
		8.5.164.216		
Cisco IOS XE Bengaluru 17.6.2	3.1	3.10.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.10 <sup>1</sup>	8.10.183.0	
	2.7		8.10.182.0	
	2.6		8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.164.0	
			8.5.182.104	
			8.5.152.103	
			8.5.164.216	
		8.5.176.2		



Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Bengaluru 17.6.1	3.1 3.0 2.7 2.6 2.4	3.10.1 3.10 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.5.176.2 8.5.182.104 8.5.152.103 8.5.164.216	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.5.1	3.0 2.7 2.6 2.4	3.10 3.9.1 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.5.164.216 8.5.182.104 8.5.152.103 8.5.164.216 8.5.176.2	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Bengaluru 17.4.1	3.0	3.10	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.7	3.9.1	8.10.183.0	
	2.6	3.9 <sup>1</sup>	8.10.182.0	
	2.4		8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.5.182.104	
			8.5.164.216	
			8.5.176.2	
		8.5.152.103		
Cisco IOS XE Amsterdam 17.3.6	3.1	3.10.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.9.1	8.10.183.0	
	2.7	3.9	8.10.182.0	
	2.6	3.8.1	8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.160.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.8.125.0	
			8.8.120.0	
		8.8.111.0		
		8.5.182.104		
		8.5.176.2		
		8.5.164.216		

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.5b	3.1 3.0 2.7 2.6 2.4	3.10.1 3.9.1 3.9 3.8.1 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.160.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.182.104 8.5.176.0 8.5.176.2 8.5.164.0 8.5.164.216	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.5a	3.1	3.10.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	3.0	3.9.1	8.10.183.0	
	2.7	3.9	8.10.182.0	
	2.6	3.8.1 <sup>1</sup>	8.10.181.0	
	2.4		8.10.171.0	
			8.10.162.0	
			8.10.160.0	
			8.10.151.0	
			8.10.142.0	
			8.10.130.0	
			8.8.130.0	
			8.8.125.0	
			8.8.120.0	
			8.8.111.0	
			8.5.182.104	
			8.5.176.0	
			8.5.176.2	
		8.5.164.0		
		8.5.164.216		

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.4c	3.0 2.7 2.6 2.4	3.9.1 3.9 3.8.1 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.160.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.176.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.4	3.0 2.7 2.6 2.4	3.9.1 3.9 3.8.1 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.160.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.176.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.3	2.7 2.6 2.4	3.9.1 3.9 3.8.1 <sup>1</sup>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0 8.5.182.104 8.5.152.103 8.5.164.216 8.5.176.2	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.2a	2.7 2.6 2.4	3.9.1 3.9 3.8.1 <a href="#">Cisco Catalyst 9800 Series Wireless Controller Matrix</a>	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0 8.5.182.104 8.5.152.103 8.5.164.216 8.5.176.2	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.3.1	2.7	3.9.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.6	3.9	8.10.183.0	
	2.4	3.8.1 <sup>1</sup>	8.10.182.0	
	8.10.181.0			
	8.10.171.0			
	8.10.162.0			
	8.10.142.0			
	8.10.130.0			
	8.10.122.0			
	8.10.121.0			
	8.10.113.0			
	8.10.112.0			
	8.10.105.0			
	8.9.111.0			
	8.9.100.0			
	8.8.125.0			
	8.8.120.0			
	8.8.111.0			
	8.5.164.0			
	8.5.182.104			
8.5.152.103				
8.5.164.216				
8.5.176.2				



Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Amsterdam 17.2.1a	2.7	3.9	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.2.1	2.6	3.8.1	8.10.183.0	
	2.4	3.8 <sup>1</sup>	8.10.182.0	
	8.10.181.0			
	8.10.171.0			
	8.10.162.0			
	8.10.122.0			
	8.10.121.0			
	8.10.113.0			
	8.10.112.0			
	8.10.105.0			
	8.9.111.0			
	8.9.100.0			
	8.8.125.0			
	8.8.120.0			
	8.8.111.0			
	8.5.164.0			
Cisco IOS XE Gibraltar 17.1.1t	2.7	3.8.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 17.1.1s	2.6	3.8	8.10.183.0	
	2.4	3.7.1	8.10.182.0	
	8.10.181.0			
	8.10.171.0			
	8.10.162.0			
	8.10.113.0			
	8.10.112.0			
	8.10.105.0			
	8.9.111.0			
	8.9.100.0			
	8.8.125.0			
	8.8.120.0			
	8.8.111.0			
	8.5.164.0			

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.8	2.6 2.4 2.3	3.7.1	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.5.176.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.12.7	2.6 2.4 2.3	3.7.1	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.10 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.5.176.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.6a	2.6 2.4 2.3	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.10 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.5.176.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.12.5	2.6 2.4 2.3	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.151.0 8.10.142.0 8.10.130.0 8.8.130.0 8.8.125.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.4a	2.6 2.4 2.3 2.2	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.142.0 8.10.130.0 8.10.122.0 8.10.121.0 8.10.113.0 8.10.112.0 8.10.105.0 8.9.111.0 8.9.100.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.3	2.6 2.4 2.3 2.2	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.10.113.0 8.10.112.0 8.10.105.0 8.9.111.0 8.9.100.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.12.2s	2.6 2.4 2.3 2.2	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.9.111.0 8.9.100.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.1t	2.6	3.7.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.4	3.7	8.10.183.0	
	2.3		8.10.182.0	
	2.2		8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.9.111.0	
			8.9.100.0	
			8.8.125.0	
			8.8.120.0	
Cisco IOS XE Gibraltar 16.12.1s	2.6	3.7.1	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.4	3.7	8.10.183.0	
	2.3		8.10.182.0	
	2.2		8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.9.111.0	
			8.9.100.0	
			8.8.125.0	
			8.8.120.0	
		8.8.111.0		
		8.5.164.0		

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.1	2.6 2.4 2.3 2.2	3.7.1 3.7	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.9.111.0 8.9.100.0 8.8.125.0 8.8.120.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.11.1c	2.6 2.4 2.3 2.2	3.6	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.9.100.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.11.1b	2.6 2.4 2.3 2.2	3.6	8.10.185.0 8.10.183.0 8.10.182.0 8.10.181.0 8.10.171.0 8.10.162.0 8.9.100.0 8.8.111.0 8.5.164.0	<a href="#">See Cisco DNA Center Compatibility Information</a>

Cisco Catalyst 9800 Series Wireless Controllers	Cisco Identity Services Engine (ISE)	Cisco Prime Infrastructure	Cisco AireOS-IRCM Interoperability	Cisco DNA Center
Cisco IOS XE Gibraltar 16.10.1	2.4	3.5	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.3	3.6	8.10.183.0	
	2.2		8.10.182.0	
			8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.8.111.0	
Cisco IOS XE Gibraltar 16.10.1e	2.4	3.5	8.10.185.0	<a href="#">See Cisco DNA Center Compatibility Information</a>
	2.3	3.6	8.10.183.0	
	2.2		8.10.182.0	
			8.10.181.0	
			8.10.171.0	
			8.10.162.0	
			8.8.111.0	
		8.5.164.0		

1	Base release of Cisco Prime infrastructure that supports corresponding Cisco Catalyst 9800 Series Wireless Controller platform release and its features.
---	--



**Note** For Cisco CMX compatibility details, see [Cisco Connected Mobile Experiences Compatibility Matrix](#).



- Note**
- Cisco Prime Infrastructure Release 3.8 does not support Cisco Catalyst 9800 Series Wireless Controllers 16.12.x and 17.1.x releases.
  - Cisco Catalyst 9800 Series Wireless Controllers use CAPWAP-based tunnels for mobility. The mobility control channel is encrypted and the mobility data channel can be optionally encrypted. This is termed as Secure Mobility. For more information about IRCM between Cisco IOS XE releases for Cisco Catalyst 9800 Series Wireless Controllers and Cisco Wireless Release for AireOS Controllers, see the [Cisco Catalyst 9800 Wireless Controller-AireOS IRCM Deployment Guide](#).



## Cisco Embedded Wireless Controller Matrix

This section contains the Cisco Embedded Wireless Controller compatibility information with Cisco Identity Services Engine (ISE) and DNA Center platforms.

**Table 2: Cisco Embedded Wireless Controller on Catalyst Access Points Release Compatibility Matrix**

Cisco Embedded Wireless Controller on Catalyst Access Points	Cisco ISE	Cisco DNA Center
Cisco IOS XE Dublin 17.12.1	3.2 3.1 3.0 2.7	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Dublin 17.11.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Dublin 17.10.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.9.4	3.2 3.1 3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.9.3	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>

<b>Cisco Embedded Wireless Controller on Catalyst Access Points</b>	<b>Cisco ISE</b>	<b>Cisco DNA Center</b>
Cisco IOS XE Cupertino 17.9.2	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.9.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.8.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Cupertino 17.7.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.6	3.0 2.7 2.6 2.4 2.3	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.5	3.0 2.7 2.6 2.4 2.3	<a href="#">See Cisco DNA Center Compatibility Information</a>

<b>Cisco Embedded Wireless Controller on Catalyst Access Points</b>	<b>Cisco ISE</b>	<b>Cisco DNA Center</b>
Cisco IOS XE Bengaluru 17.6.4	3.0 2.7 2.6 2.4 2.3	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.3	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.2	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.6.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.5.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Bengaluru 17.4.1	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.6	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>

<b>Cisco Embedded Wireless Controller on Catalyst Access Points</b>	<b>Cisco ISE</b>	<b>Cisco DNA Center</b>
Cisco IOS XE Amsterdam 17.3.5b	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.5a	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.4c	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.4	3.0 2.7 2.6 2.4	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.3	2.7 2.6	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.3.2a	2.4	
Cisco IOS XE Amsterdam 17.3.1		
Cisco IOS XE Amsterdam 17.2.1a	2.7 2.6	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Amsterdam 17.2.1	2.4	
Cisco IOS XE Gibraltar 17.1.1t		
Cisco IOS XE Gibraltar 17.1.1s		

Cisco Embedded Wireless Controller on Catalyst Access Points	Cisco ISE	Cisco DNA Center
Cisco IOS XE Gibraltar 16.12.8	2.6	<a href="#">See Cisco DNA Center Compatibility Information</a>
Cisco IOS XE Gibraltar 16.12.7	2.4	
Cisco IOS XE Gibraltar 16.12.6a	2.3	
Cisco IOS XE Gibraltar 16.12.5		
Cisco IOS XE Gibraltar 16.12.4a		
Cisco IOS XE Gibraltar 16.12.3		
Cisco IOS XE Gibraltar 16.12.2s		

Table 3: Wireless Controller Foreign and Anchor Support

Foreign + Anchor	Cisco Catalyst 9800 Wireless Controller for Cloud	Cisco Catalyst 9800-40 Wireless Controller	Cisco Catalyst 9800-80 Wireless Controller	Cisco Catalyst 9800-L Wireless Controller
Cisco 3504 Controller	Y	Y	Y	Y
Cisco 5520 Controller	Y	Y	Y	Y
Cisco 8540 Controller	Y	Y	Y	Y

## Cisco Access Points Supported in Cisco Wireless Controller Platform Software Releases

Information about the list of supported access points by respective wireless platforms is listed as follows:

- Cisco 9800 Wireless Controller Releases: [Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases, on page 31](#)
- Catalyst 9800 Embedded Wireless Controller Releases: [Supported Access Points in Cisco Catalyst 9800 Embedded Wireless Controller, on page 67](#)

- Cisco AireOS Wireless Controller Releases: [Supported Access Points in Cisco AireOS Wireless Software Releases, on page 83](#)

For information about the features supported on Wave 2 and Wi-Fi 6 Access Points across Cisco IOS XE and AireOS platforms, see the [Feature Matrix for Wave 2 and 802.11ax \(Wi-Fi 6\) Access Points](#) document.

For information about the compatibility of Cisco Prime Infrastructure with Cisco AireOS Controller software, see the *Compatibility Matrix for Legacy Cisco Wireless Solutions* document at:

[https://www.cisco.com/c/en/us/td/docs/wireless/compatibility/matrix-legacy/compatibility-matrix-legacy.html#prime\\_infrastructure](https://www.cisco.com/c/en/us/td/docs/wireless/compatibility/matrix-legacy/compatibility-matrix-legacy.html#prime_infrastructure)

For information about the compatibility of Cisco Mobility Services Engine with Cisco AireOS Controller software, see the *Compatibility Matrix for Legacy Cisco Wireless Solutions* document at:

[https://www.cisco.com/c/en/us/td/docs/wireless/compatibility/matrix-legacy/compatibility-matrix-legacy.html#mobility\\_services\\_engine](https://www.cisco.com/c/en/us/td/docs/wireless/compatibility/matrix-legacy/compatibility-matrix-legacy.html#mobility_services_engine)

For compatibility information about Cisco AireOS Controller software and Cisco ISE, see the [Cisco ISE Compatibility Information page](#).

## Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases

*Table 4: Cisco Catalyst 9800 Wireless Controller and Supported Access Points*

<b>IOS XE Release</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Dublin 17.12.1	17.12.1.5	15.3(3)JPQ	

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
			<p>Cisco Catalyst APs: 9105AX (I/W), 9115AX (I/E), 9117AX (I), 9120AX (I/E/P), 9130AX (I/E), 9136 (I), 9162 (I), 9164 (I), 9166 (I/D1)</p> <p>Cisco Aironet APs: 1815 (I/W/M/T), 1830 (I), 1840 (I), 1852 (I/E), 1700 (I), 1800i, 2700 (I/E), 2800 (I/E), 3700 (I/E/P), 3800 (I/E/P), 4800 (I)</p> <p>Outdoor and Industrial APs: 1542, 1560, and IW3702</p> <p>Integrated Access Point on Cisco 1100 ISR (ISR-AP1100AC-x, ISR-AP1101AC-x, and ISR-AP1101AX-x)</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Point, Cisco 6300 Series Embedded Services Access Point, Cisco Catalyst 9124AX (I/D/E) Access Points, Cisco Catalyst Industrial Wireless 9167 (I/E) Heavy Duty Access Points</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial</p>



IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
			Routers
Cisco IOS XE Dublin 17.11.1	17.11.0.155	15.3(3)JPP	<p>Cisco Catalyst APs: 9166I, 9164I, 9162I, 9136I, 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117I, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1815 (I/W), 1830I, 1840I, 1850 (I/E), 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point, Cisco Catalyst Industrial Wireless 9167 (E) Heavy Duty Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Dublin 17.10.1	17.10.0.181	15.3(3)JPO	<p>Cisco Catalyst APs: 9166I, 9164I, 9162I, 9136I, 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1850 (I/E), 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.9.4	17.9.4.27	15.3(3)JPN3	<p>Cisco Catalyst APs: 9166I, 9164I, 9162I, 9136I, 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1850 (I/E), 2800 (I/E), 3800 (I/E/P), 4800, 1570, 1700, 2700, 3700</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Catalyst Industrial Wireless 9167E Heavy Duty Access Points</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

## Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases

<b>IOS XE Release</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Cupertino 17.9.3	17.9.3.50	15.3(3)JPN2	

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
			<p>Cisco Catalyst APs: 9166I, 9164I, 9162I, 9136I, 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1850 (I/E), 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point, Cisco Catalyst Industrial Wireless 9167 (E) Heavy Duty Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p> <p>Support for the following Wave 1 APs are reintroduced from this release.<sup>1</sup></p> <ul style="list-style-type: none"> <li>• Cisco Aironet</li> </ul>

## Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
			1570 Series Access Point <ul style="list-style-type: none"><li>• Cisco Aironet 1700 Series Access Point</li><li>• Cisco Aironet 2700 Series Access Point</li><li>• Cisco Aironet 3700 Series Access Point</li></ul>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.9.2	17.9.2.52	15.3(3)JPN1	<p>Cisco Catalyst APs: 9166I, 9164I, 9162I, 9136I, 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1850 (I/E), 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.9.1	17.9.1.8	15.3(3)JPN	<p>Cisco Catalyst APs: 9166, 9164, 9136, *9130 (I/E), 9124, *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>



IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.8.1	17.8.0.144	15.3(3)JPM	<p>Cisco Catalyst APs: 9136, *9130 (I/E), 9124, *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.7.1	17.7.1.11	15.3(3)JPL	<p>Cisco Catalyst APs: 9136, *9130 (I/E), 9124, *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Pluggable Modules: Wi-Fi 6 Pluggable Module for Industrial Routers</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.6	17.6.6.66	15.3(3)JPK7	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.5	17.6.5.22	15.3(3)JPK6	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.4	17.6.4.56	15.3(3)JPK5	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.3	17.6.3.33	15.3(3)JPK4	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.2	17.6.2.43	15.3(3)JPK3	<p>Cisco Catalyst APs:  *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier  *9120 (I/E): VID 06 or earlier  *9105 (I): VID 03 or earlier  *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.1	17.6.1.13	15.3(3)JPK2	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>



IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.5.1	17.5.1.12	15.3(3)JPK1	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.4.1	17.4.1.6	15.3(3)JPK	<p>Cisco Catalyst APs:            *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560</p> <p>Integrated Access Point on Cisco 1100 ISR</p> <p>Cisco Industrial Wireless, 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points, Cisco 6300 Series Embedded Services Access Point</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.7	17.3.7.36	15.3(3)JPJ10	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E), 9120 (P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.6	17.3.6.76	15.3(3)JPJ9	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E), 9120 (P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.5b	17.3.5.43	15.3(3)JPJ8b	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.5a	17.3.5.42	15.3(3)JPJ8a	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.4c	17.3.4.40	15.3(3)JPJ7c	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.4	17.3.4.30	15.3(3)JPJ7	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D in B Domain), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco 6300 Series Embedded Services Access Point</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>



<b>IOS XE Release</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Amsterdam 17.3.3	17.3.3.26	15.3(3)JPJ6	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W) *9130 (I/E): VID 02 or earlier *9120 (I/E): VID 06 or earlier *9105 (I): VID 03 or earlier *9105 (W): VID 01 Cisco Aironet APs: 1700, 1800 (1810 OEAP, 1815, 1830, 1840, and 1852), 2700, 2800, 3700, 3800, 4800 Series Access Points Cisco 6300 Series Embedded Services Access Point Cisco Industrial Wireless 3700 Series Access Points Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points Outdoor and Industrial APs: 1542, 1560, 1570 Sensors: Cisco Aironet 1800s Active Sensor Integrated Access Point on Cisco 1100 ISR
Cisco IOS XE Amsterdam 17.3.2a	17.3.2.32	15.3(3)JPJ5	
Cisco IOS XE Amsterdam 17.3.1	17.3.1.9	15.3(3)JPJ4	

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.2.1a	17.2.1.15	15.3(3)JPJ3a	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W) *9130 (I/E): VID 02 or earlier *9120 (I/E): VID 06 or earlier *9105 (I): VID 03 or earlier *9105 (W): VID 01 Cisco Aironet APs: 9130, 9120, 9117, 9115, 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points Cisco 6300 Series Embedded Services Access Point Cisco Industrial Wireless 3700 Series Access Points Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points Outdoor and Industrial APs: 1542, 1560, 1570 Sensors: Cisco Aironet 1800s Active Sensor Integrated Access Point on Cisco 1100 ISR
Cisco IOS XE Amsterdam 17.2.1	17.2.1.11	15.3(3)JPJ3	
Cisco IOS XE Gibraltar 17.1.1t	17.1.1.32	15.3(3)JPJ2t	
Cisco IOS XE Gibraltar 17.1.1s	17.1.1.29	15.3(3)JPJ2	

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.12.8	16.12.8.5	15.3(3)JPI10	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.12.7	16.12.7.2	15.3(3)JPI9	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.12.6a	16.12.6.7	15.3(3)JPI8a	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

<b>IOS XE Release</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Gibraltar 16.12.5	16.12.5.13	15.3(3)JPI7	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115  *9130 (I/E): VID 02 or earlier  *9120 (I/E): VID 06 or earlier  Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points  Cisco Industrial Wireless 3700 Series Access Points  Outdoor and Industrial APs: 1542, 1560, 1570  Sensors: Cisco Aironet 1800s Active Sensor  Integrated Access Point on Cisco 1100 ISR
Cisco IOS XE Gibraltar 16.12.4a	16.12.4.31	15.3(3)JPI6a	
Cisco IOS XE Gibraltar 16.12.3	16.12.3.13	15.3(3)JPI5	

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.12.2s	16.12.2.132	15.3(3)JPI4	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

## Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases

<b>IOS XE Release</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Gibraltar 16.12.1t	16.12.1.140	15.3(3)JPI1t	Cisco Catalyst APs: *9120 (I/E), 9120 (P), 9117, 9115
Cisco IOS XE Gibraltar 16.12.1s	16.12.1.139	Not Supported	*9120 (I/E): VID 06 or earlier
Cisco IOS XE Gibraltar 16.12.1	16.12.0.42	15.3(3)JPI1	Cisco Aironet APs: 1700, 1800, 1840, 2700, 2800, 3700, 3800, 4800 Series Access Points  Cisco Industrial Wireless 3700 Series Access Points  Outdoor and Industrial APs: 1542, 1560, 1570  Sensors: Cisco Aironet 1800s Active Sensor  Integrated Access Point on Cisco 1100 ISR



IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.11.1c	16.11.1.134	15.3(3)JPH3	<p>Cisco Catalyst APs: *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.11.1b	16.11.1.133	15.3(3)JPH2	<p>Cisco Catalyst APs: *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1700, 1800, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Cisco Industrial Wireless 3700 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>
Cisco IOS XE Gibraltar 16.10.1e	16.10.1.48	15.3(3)JPG2	<p>Cisco Aironet APs: 1700, 1800, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p> <p>Integrated Access Point on Cisco 1100 ISR</p>

IOS XE Release	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.10.1	16.10.1.42	15.3(3)JI1	<p>Cisco Aironet APs: 1700, 1800, 2700, 2800, 3700, 3800, 4800 Series Access Points</p> <p>Outdoor and Industrial APs: 1542, 1560, 1570</p> <p>Sensors: Cisco Aironet 1800s Active Sensor</p>

<sup>1</sup> \* Support for the above mentioned Wave 1 APs does not extend beyond the normal product lifecycle support. Refer to the End of Support bulletins of individual APs.

\* Feature support is on parity with 17.3.x release. Features introduced in 17.4.1 or later are not supported on these APs in 17.9.3 release.

\* You can migrate directly to 17.9.3 from 17.3.x, where x=4c or above.

## Supported Access Points in Cisco Catalyst 9800 Embedded Wireless Controller

Table 5: Cisco Embedded Wireless Controller and Supported Access Points

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Dublin 17.12.1	17.12.1.5	15.3(3)JPQ	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1852, 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Dublin 17.11.1	17.11.0.155	15.3(3)JPP	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1852, 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points<sup>2</sup></p>
Cisco IOS XE Dublin 17.10.1	17.10.0.181	15.3(3)JPO	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1815 (I/W), 1830I, 1840I, 1852, 2800 (I/E), 3800 (I/E/P), 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points<sup>3</sup></p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.9.4	17.9.4.27	15.3(3)JPN3	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points <a href="#">4</a></p>
Cisco IOS XE Cupertino 17.9.3	17.9.3.50	15.3(3)JPN2	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points <a href="#">5</a></p>
Cisco IOS XE Cupertino 17.9.2	17.9.2.52	15.3(3)JPN1	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/D/E), 9120 (I/E/P), 9117, 9115 (I/E), 9105 (I/W)</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points <a href="#">6</a></p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.9.1	17.9.1.8	15.3(3)JPN	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D/E), *9120 (I/E), 9120 (P), 9117, 9115 (I/E), *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs:            1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p><a href="#">7</a></p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.8.1	17.8.0.144	15.3(3)JPM	<p>Cisco Catalyst APs:            *9130 (I/E), 9124 (I/D/E), *9120 (I/E), 9120 (P), 9117, 9115 (I/E), *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs:            1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p> <p><a href="#">8</a></p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Cupertino 17.7.1	17.7.1.11	15.3(3)JPL	<p>Cisco Catalyst APs:            *9130 (I/E), 9124,            *9120 (I/E), 9120 (P), 9117, 9115,            *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier            *9120 (I/E): VID 06 or earlier            *9105 (I): VID 03 or earlier            *9105 (W): VID 01</p> <p>Cisco Aironet APs:            1815, 1830, 1840,            1852, 2800, 3800,            4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points  <a href="#">9</a></p>
Cisco IOS XE Bengaluru 17.6.6	17.6.6.66	15.3(3)JPK7	<p>Cisco Catalyst APs:            9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs:            1815, 1830, 1840,            1852, 2800, 3800,            4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>



<b>IOS XE Releases</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Bengaluru 17.6.5	17.6.5.22	15.3(3)JPK6	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Bengaluru 17.6.4	17.6.4.56	15.3(3)JPK5	<p>Cisco Catalyst APs: 9130 (I/E), 9124 (I/E/D), 9120 (I/E/P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.3	17.6.3.33	15.3(3)JPK4	<p>Cisco Catalyst APs: *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Bengaluru 17.6.2	17.6.2.43	15.3(3)JPK3	<p>Cisco Catalyst APs: *9130 (I/E), 9124 (I/E/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Bengaluru 17.6.1	17.6.1.13	15.3(3)JPK2	<p>Cisco Catalyst APs: *9130 (I/E), 9124 (I/D), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1815, 1830, 1840, 1852, 2800, 3800, 4800</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Bengaluru 17.5.1	17.5.1.12	15.3(3)JPK1	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

<b>IOS XE Releases</b>	<b>Access Point Image Version Number</b>	<b>Access Point Release</b>	<b>Supported Access Points</b>
Cisco IOS XE Bengaluru 17.4.1	17.4.1.6	15.3(3)JPK	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800 (1815, 1830, 1840, and 1852), 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Amsterdam 17.3.7	17.3.7.36	15.3(3)JPJ10	<p>Cisco Catalyst APs: 9130 (I/E), 9120 (I/E), 9120 (P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.6	17.3.6.76	15.3(3)JPJ9	<p>Cisco Catalyst APs: 9130 (I/E), 9120 (I/E), 9120 (P), 9117, 9115, 9105 (I/W)</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Amsterdam 17.3.5b	17.3.5.43	15.3(3)JPJ8b	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.5a	17.3.5.42	15.3(3)JPJ8a	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>
Cisco IOS XE Amsterdam 17.3.4c	17.3.4.40	15.3(3)JPJ7c	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.4	17.3.4.30	15.3(3)JPJ7	<p>Cisco Catalyst APs:            *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W)</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>*9105 (I): VID 03 or earlier</p> <p>*9105 (W): VID 01</p> <p>Cisco Aironet APs:            1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p> <p>Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points</p>

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.3.3	17.3.3.26	15.3(3)JPJ6	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W) *9130 (I/E): VID 02 or earlier *9120 (I/E): VID 06 or earlier *9105 (I): VID 03 or earlier *9105 (W): VID 01 Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points
Cisco IOS XE Amsterdam 17.3.2a	17.3.2.32	15.3(3)JPJ5	
Cisco IOS XE Amsterdam 17.3.1	17.3.1.9	15.3(3)JPJ4	



IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Amsterdam 17.2.1a	17.2.1.15	15.3(3)JPJ3a	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115, *9105 (I/W) *9130 (I/E): VID 02 or earlier *9120 (I/E): VID 06 or earlier *9105 (I): VID 03 or earlier *9105 (W): VID 01 Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points Cisco Catalyst Industrial Wireless 6300 Heavy Duty Series Access Points
Cisco IOS XE Amsterdam 17.2.1	17.2.1.11	15.3(3)JPJ3	
Cisco IOS XE Gibraltar 17.1.1t	17.1.1.32	15.3(3)JPJ2t	
Cisco IOS XE Gibraltar 17.1.1s	17.1.1.29	15.3(3)JPJ2	
Cisco IOS XE Gibraltar 16.12.8	16.12.8.5	15.3(3)JPI10	Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115 *9130 (I/E): VID 02 or earlier *9120 (I/E): VID 06 or earlier Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points
Cisco IOS XE Gibraltar 16.12.7	16.12.7.2	15.3(3)JPI9	
Cisco IOS XE Gibraltar 16.12.6a	16.12.6.7	15.3(3)JPI8a	
Cisco IOS XE Gibraltar 16.12.5	16.12.5.13	15.3(3)JPI7	
Cisco IOS XE Gibraltar 16.12.4a	16.12.4.31	15.3(3)JPI6a	
Cisco IOS XE Gibraltar 16.12.3	16.12.3.13	15.3(3)JPI5	

IOS XE Releases	Access Point Image Version Number	Access Point Release	Supported Access Points
Cisco IOS XE Gibraltar 16.12.2s	16.12.2.132	15.3(3)JPI4	<p>Cisco Catalyst APs: *9130 (I/E), *9120 (I/E), 9120 (P), 9117, 9115</p> <p>*9130 (I/E): VID 02 or earlier</p> <p>*9120 (I/E): VID 06 or earlier</p> <p>Cisco Aironet APs: 1800I, 1810 OEAP, 1815, 1815W, 1830, 1840, 1850, 2800, 3800, 4800 Series Access Points</p>

<sup>2</sup> 9166I, 9164I, 9162I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>3</sup> 9166I, 9164I, 9162I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>4</sup> 9166I, 9164I, 9162I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>5</sup> 9166I, 9164I, 9162I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>6</sup> 9166I, 9164I, 9162I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>7</sup> 9166I, 9164I, 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>8</sup> 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

<sup>9</sup> 9136I only with Cisco Catalyst 9k switches with Embedded Wireless Controller in SDA mode.

## Supported Access Points in Cisco AireOS Wireless Software Releases

*Table 6: Cisco AireOS Controller Software Releases, AP IOS Releases, and Supported Access Points*

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.10.190.0	15.3(3)JK10	Lightweight APs: 9130E, 9130I, 9120, 9117, 9115, 9105, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1840, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803  Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, IW3700, IW6300 Heavy Duty Series, and 6300 Series Embedded Services  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M
8.10.185.0	15.3(3)JK9	
8.10.183.0	15.3(3)JK8b	
8.10.182.0	15.3(3)JK8a	
8.10.181.0	15.3(3)JK8	

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.10.171.0	15.3(3)JK7	Lightweight APs: 9130E*, 9130I*, 9120*, 9117, 9115, 9105*, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1840, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803  *9105 <ul style="list-style-type: none"> <li>• 9105AXI: VID 04 and earlier</li> <li>• 9105AXW: VID 01</li> </ul> *9130 <ul style="list-style-type: none"> <li>• 9130AXI, 9130AXE: VID 02 and earlier</li> </ul> *9120 <ul style="list-style-type: none"> <li>• 9120AXI and 9120AXE: VID 06 and earlier</li> <li>• 9120AXP: all VIDs</li> </ul> Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, IW3700, IW6300 Heavy Duty Series, and 6300 Series Embedded Services  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M
8.10.162.0	15.3(3)JK6	
8.10.151.0	15.3(3)JK5	
8.10.142.0	15.3(3)JK4	
8.10.130.0	15.3(3)JK3	

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.10.122.0	15.3(3)JK2a	Lightweight APs: 9130E*, 9130I*, 9120*, 9117, 9115, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1840, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803  *9130 <ul style="list-style-type: none"> <li>• 9130AXI, 9130AXE: VID 02 and earlier</li> </ul> *9120 <ul style="list-style-type: none"> <li>• 9120AXI and 9120AXE: VID 06 and earlier</li> <li>• 9120AXP: all VIDs</li> </ul> Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, IW3700, IW6300 Heavy Duty Series, and 6300 Series Embedded Services  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M
8.10.121.0	15.3(3)JK2	
8.10.113.0	15.3(3)JK1t	
8.10.112.0	15.3(3)JK1	

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.10.105.0	15.3(3)JK	<p>Lightweight APs: 9130I*, 9120*, 9117, 9115, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1840, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803</p> <p>*9130</p> <ul style="list-style-type: none"> <li>• 9130AXI: VID 02 and earlier</li> </ul> <p>*9120</p> <ul style="list-style-type: none"> <li>• 9120AXI: VID 06 and earlier</li> <li>• 9120AXP: all VIDs</li> </ul> <p>Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, IW3700, IW6300 Heavy Duty Series, and 6300 Series Embedded Services</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.9.111.0	15.3(3)JJ1	<p>Lightweight APs: 9120*, 9117, 9115, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803</p> <p>*9120</p> <ul style="list-style-type: none"> <li>• 9120AXI: VID 06 and earlier</li> </ul> <p>Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.9.100.0	15.3(3)JJ	<p>Lightweight APs: 9115, 9117, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803</p> <p>Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>
8.8.130.0	15.3(3)JI6	<p>Lightweight APs: 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803</p> <p>Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>
8.8.125.0	15.3(3)JI5	
8.8.120.0	15.3(3)JI4	



Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.8.111.0	15.3(3)JI3	Lightweight APs: 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803  Integrated Access Point on Cisco 1100 ISR, Cisco 1101 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M
8.8.100.0	15.3(3)JI1	
8.7.106.0	15.3(3)JH1	Lightweight APs: 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 4800, 700, 700W, AP803  Integrated Access Point on Cisco 1100 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.7.102.0	15.3(3)JH	<p>Lightweight APs: 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 700, 700W, AP803</p> <p>Integrated Access Point on Cisco 1100 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>
8.6.101.0	15.3(3)JG1	<p>Lightweight APs: 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2700, 2800, 3702e, 3702i, 3702p, 3800, 700, 700W, AP803</p> <p>Integrated Access Point on Cisco 1100 ISR, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1540, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.5.182.0	15.3(3)JF15	Lightweight APs: 1600, 1700, 1800i, 1810 OEAP, 1810W, 1815i, 1815m, 1815t, 1815w, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 700, 700W, AP802, AP803  Integrated Access Point on Cisco 1100 ISR, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1540, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1560, 1570, and IW3700 <sup>10</sup>  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M
8.5.171.0	15.3(3)JF14	
8.5.164.0	15.3(3)JF12i	
8.5.161.0	15.3(3)JF12	
8.5.160.0	15.3(3)JF11	
8.5.151.0	15.3(3)JF10	
8.5.140.0	15.3(3)JF9	
8.5.135.0	15.3(3)JF8	
8.5.131.0	15.3(3)JF7	
8.5.120.0	15.3(3)JF5	
8.5.110.0	15.3(3)JF4	
8.5.105.0	15.3(3)JF1	
8.5.103.0	15.3(3)JF	

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.4.100.0	15.3(3)JE	<p>Lightweight APs: 1600, 1700, 1810 OEAP, 1810W, 1815i, 1815w, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1560, 1570, and IW3700 <a href="#">11</a></p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.3.150.0	15.3(3)JD17 15.3(3)JDA17	Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810
8.3.143.0	15.3(3)JD16 15.3(3)JDA16	OEAP, 1810W, 1815i, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702
8.3.141.0	15.3(3)JD14 15.3(3)JDA14	
8.3.140.0	15.3(3)JD13 15.3(3)JDA13	
8.3.133.0	15.3(3)JD11 15.3(3)JDA11	Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1560, 1570, and IW3700
8.3.132.0	15.3(3)JD9 15.3(3)JDA9	
8.3.130.0	15.3(3)JD7 15.3(3)JDA7	
8.3.122.0 8.3.121.0	15.3(3)JD6 15.3(3)JD5	Modules: AIR-RM3010L-x-K9 and AIR-RM3000M  The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 or later are not supported on these access points.

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.3.112.0	15.3(3)JD4	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810 OEAP, 1810W, 1815i, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1560, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M</p> <p>The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 or later are not supported on these access points.</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.3.102.0	15.3(3)JD	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810 OEAP, 1810W, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">12</a></p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.2.170.0	15.3(3)JC15 15.3(3)JCA15	Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810
8.2.166.0	15.3(3)JC14 15.3(3)JCA14	OEAP, 1810W, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600
8.2.164.0	15.3(3)JC9 15.3(3)JCA9	OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702
8.2.161.0	15.3(3)JC8 15.3(3)JCA8	
8.2.160.0	15.3(3)JC7	Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">13</a>



Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.2.151.0	15.3(3)JC6	Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810 OEAP, 1810W, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702  Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700  Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">14</a>
8.2.141.0	15.3(3)JC5	
8.2.130.0	15.3(3)JC4	
8.2.121.0	15.3(3)JC3	

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.2.111.0	15.3(3)JC2	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810 OEAP, 1810W, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">15</a></p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.2.110.0	15.3(3)JC1	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1810 OEAP, 1810W, 1830, 1850, 2600, 2700, 2800, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 3800, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">16</a> <a href="#">17</a></p>
8.2.100.0	15.3(3)JC	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1830, 1850, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">18</a></p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.1.131.0	15.3(3)JBB6	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1830, 1850, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700</p> <p>Modules: AIR-RM3010L-x-K9 and AIR-RM3000M <a href="#">19</a></p>
8.1.122.0	15.3(3)JBB5	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1830, 1850, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP802, AP803, ASA5506W-AP702</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3700 <a href="#">20</a></p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.1.111.0	15.3(3)JBB1	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 1850, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, and AP802</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, and 1570 <a href="#">21</a></p>
8.1.102.0	15.3(3)JBB	<p>Lightweight APs: 1040, 1140, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, and AP802</p> <p>Outdoor and Industrial APs: 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, and 1570 <a href="#">22</a></p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.0.152.0	153-3.JA12 15.3(3)JAA12 12.4(25e)JAP12	Lightweight APs: 1040, 1130, 1140, 1240, 1250, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP801, and AP802 <a href="#">23</a>
8.0.150.0	15.3(3)JA11 15.3(3)JAA11 12.4(25e)JAP11	
8.0.140.0	15.3(3)JA10 12.4(25e)JAP10	Outdoor and Industrial APs: 1522, 1524PS, 1524SB, 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3702 <a href="#">24</a>
8.0.135.0	15.3(3)JA9 12.4(25e)JAP9	<ol style="list-style-type: none"> <li>1. The Cisco 1570 APs that are made available on or after June 2, 2016, for the USA region</li> <li>2. The Cisco 1570 APs that are identified with version ID 02 (V02)</li> </ol> <p>This release ensures that Cisco 1570 APs that are made available to customers in the USA are in compliance with the new FCC rules that come into effect on June 2, 2016.</p>

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.0.133.0	15.3(3)JA8 12.4(25e)JAP8	Lightweight APs: 1040, 1130, 1140, 1240, 1250, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP801, and AP802
8.0.132.0	15.3(3)JA7 12.4(25e)JAP7	Outdoor and Industrial APs: 1522, 1524PS, 1524SB, 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3702 <sup>25</sup>
8.0.121.0	15.3(3)JA5 12.4(25e)JAP5	Lightweight APs: 1040, 1130, 1140, 1240, 1250, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP801, and AP802
8.0.120.0	15.3(3)JA4 12.4(25e)JAP4	Outdoor and Industrial APs: 1522, 1524PS, 1524SB, 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, 1570, and IW3702

Cisco AireOS Controller Release	Access Point IOS Release	Supported Access Points
8.0.110.0 8.0.115.0	15.3(3)JA1 12.4(25e)JAP1	Lightweight APs: 1040, 1130, 1140, 1240, 1250, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP801, and AP802  Outdoor and Industrial APs: 1522, 1524PS, 1524SB, 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, 1552S, and 1570
8.0.100.0	15.3(3)JAB 12.4(25e)JAP	Lightweight APs: 1040, 1130, 1140, 1240, 1250, 1260, 1600, 1700, 2600, 2700, 3500e, 3500i, 3500p, 3600e, 3600i, 3600p, 3702e, 3702i, 3702p, 600 OEAP, 700, 700W, AP801, and AP802  Outdoor and Industrial APs: 1522, 1524PS, 1524SB, 1532E, 1532I, 1552E, 1552H, 1552I, 1552C, 1552EU, 1552CU, and 1552S

<sup>10</sup> The Cisco Aironet 1550 Series APs with 64-MB memory are not supported.

<sup>11</sup> The Cisco Aironet 1550 Series APs with 64-MB memory are not supported.

<sup>12</sup> The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.

<sup>13</sup> The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.



- 14 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 15 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 16 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 17 Initial support for 802.11n regulatory domain APs.
- 18 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 19 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 20 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 21 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 22 The Cisco 1040 Series, 1140 Series, and 1260 Series access points have feature parity with Cisco Wireless Release 8.0. Features introduced in Cisco Wireless Release 8.1 and later are not supported on these access points.
- 23 Cisco MSE Release 8.0.140.9 and later includes wIPS and CAS support for the Cisco Aironet 1800, 2800, and 3800 series.
- 24 The Cisco Wireless Release 8.0.135.0 is a repost of the Cisco Wireless Release 8.0.132.0 and 8.0.133.0. This release impacts only the Cisco Aironet 1570 Series APs with -B regulatory domain and meet the following criteria:
- 25 Initial support for 802.11n regulatory domain APs.

## Related Information

- See the relevant release notes before you perform any software upgrade:  
<https://www.cisco.com/c/en/us/support/wireless/wireless-lan-controller-software/products-release-notes-list.html>
- Product Approval Status: <https://cae-cnc-prd.cisco.com/ptcnc/#/>
- Wireless LAN Compliance Lookup:  
<https://www.cisco.com/c/dam/assets/prod/wireless/wireless-compliance-tool/index.html>

## Access Point Specific Wireless Controller Software Support

This section lists the Cisco Wireless Controller software releases that support specific Cisco Access Points. The First Support column lists the earliest Cisco Controller software release that supports the access point module. For access points not supported in ongoing releases, the Last Support column lists the last release that supported the access points.

Table 7: Software Support for Access Point Modules

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
1810 Series	AIR-CEAP1810-x-K9	8.2.110.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	Cisco IOS XE Amsterdam 17.3.x
1810W Series	AIR-AP1810W-x-K9	8.2.110.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	Cisco IOS XE Amsterdam 17.3.x
1815 Series	AIR-AP1815I-x-K9	8.3.112.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	—
	AIR-AP1815W-x-K9	8.4.100.0	8.10.x		—
	AIR-AP1815M-x-K9	8.5.103.0	8.10.x		—
	AIR-AP1815T-x-K9	8.5.103.0	8.10.x		—
1830 Series	AIR-AP1832HUXK9	8.1.122.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	—
	AIR-AP1832HUXK910				—
	AIR-AP1832HUXK9C				—
	AIR-AP1832HUXK910C				—
	AIR-AP1832I-x-K9				—
	AIR-AP1832I-x-K9C				—
1840 Series	AIR-AP1840I-x-K9C	8.10.105.0	8.10.x	Cisco IOS XE Gibraltar 16.12.1	—

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support					
1850 Series	AIR-AP1852HUXK9	8.1.111.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	—					
	AIR-AP1852HUXK910									
	AIR-AP1852HUXK9C									
	AIR-AP1852HUXK910C									
	AIR-AP1852EUXK9									
	AIR-AP1852EUXK910									
	AIR-AP1852EUXK9C	8.1.111.0	8.10.x	—	—					
	AIR-AP1852EUXK910C									
	AIR-AP1852E-x-K9									
	AIR-AP1852E-x-K9C									
	AIR-AP1852I-x-K9									
	AIR-AP1852I-x-K9C									
	Integrated Access Point on Cisco 1100 ISR					ISR-AP1100AC-X	8.5.103.0	8.10.x	— Cisco IOS XE Gibraltar 16.10.1e	—
	Integrated Access Point on Cisco 1101 ISR					ISR-AP1101AC-X	8.8.100.0	8.10.x	—	—
ISR-AP1101AC-LX		—	—							
1700 Series	AIR-CAP1702I	7.6.100.0	8.10.x	Cisco IOS XE Denali 16.3.1	Cisco IOS XE Amsterdam 17.3.x Cisco IOS XE Cupertino 17.9.3 <a href="#">26</a>					

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
2700 Series	AIR-CAP2702I	7.6.100.0	8.10.x	Cisco IOS XE Denali 16.3.1	Cisco IOS XE Amsterdam 17.3.x Cisco IOS XE Cupertino 17.9.3 <a href="#">27</a>
	AIR-CAP2702E				
2800 Series	AIR-AP2802E-x-K9	8.2.110.0	8.10.x	Cisco IOS XE Denali 16.3.1	—
	AIR-AP2802I-x-K9				—
3700 Series	AIR-CAP3702I	7.6.100.0	8.10.x	3.3.1SE	Cisco IOS XE Amsterdam 17.3.x Cisco IOS XE Cupertino 17.9.3 <a href="#">28</a>
	AIR-CAP3702E				
	AIR-CAP3702P				
3800 Series	AIR-AP3802E-x-K9	8.2.110.0	8.10.x	Cisco IOS XE Denali 16.3.1	—
	AIR-AP3802I-x-K9				—
	AIR-AP3802P-x-K9				—
4800 Series	AIR-AP4800-x-K9	8.7.106.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	—
	AIR-AP4800-x-K9C				—
9136	C9136I-x	—	—	Cisco IOS XE Cupertino 17.7.1	—
916X Series	CW9162I-x	—	—	Cisco IOS XE Cupertino 17.9.2	—
	CW9164I-x CW9166I-x	—	—	Cisco IOS XE Cupertino 17.9.1	—

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
9130	C9130AXE-STA-x	—	—	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9130AXE-x	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9130AXI-x	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9130AXE-STA-x VID 02 or earlier	—	—	Cisco IOS XE Bengaluru 17.6.1	—
	C9130AXE-x VID 02 or earlier	8.10.112.0	8.10.x	Cisco IOS XE Amsterdam 17.3.1	—
	C9130AXI-x VID 02 or earlier	8.10.105.0	8.10.x	Cisco IOS XE Gibraltar 16.12.2s	—

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
9124	C9124AXI-x	—	—	Cisco IOS XE	—
	C9124AXD-x	—	—	Bengaluru 17.5.1  Cisco IOS XE Amsterdam 17.3.4c (A, B, E, Q, Z, F, and R Domains)  Cisco IOS XE Amsterdam 17.3.4 (B Domain)  Cisco IOS XE Bengaluru 17.6.2 (For all Regulatory Domains)	—
	C9124AXE-x	—	—	Bengaluru 17.6.2  Cisco IOS XE Amsterdam 17.3.5a (A, B, E, and Z Domains)	—

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
9120 <sup>1</sup>	C9120AXE-x	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9120AXI-x	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9120AXE-x VID 06 or earlier	8.10.112.0	8.10.x	Cisco IOS XE Gibraltar 16.12.2s	—
	C9120AXI-x VID 06 or earlier	8.9.111.0	8.10.x	Cisco IOS XE Gibraltar 16.11.1b	—
	C9120AXP-x All VIDs	8.9.111.0	8.10.x	Cisco IOS XE Gibraltar 16.12.2s	—
9117	C9117AXI-x	8.9.100.0	8.10.x	Cisco IOS XE Gibraltar 16.11.1b	—
9115	C9115AXI-x	8.9.100.0	8.10.x	Cisco IOS XE Gibraltar 16.11.1b	—
	C9115AXE-x		8.10.x	Cisco IOS XE Gibraltar 16.11.1b	—

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
9105	C9105AX-W	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9105AX-I	8.10.181.0	8.10.x	Cisco IOS XE Amsterdam 17.3.6 Cisco IOS XE Bengaluru 17.6.4	—
	C9105AX-W VID 03 or earlier	8.10.130.0	8.10.x	Cisco IOS XE Amsterdam 17.3.1	—
	C9105AX-I VID 03 or earlier	8.10.130.0	8.10.x	Cisco IOS XE Amsterdam 17.3.1	—
1530 Series	AIR-CAP1532L-x-K9	7.6.100.0	8.10.x	3.6.0E <sup>3</sup>	Cisco IOS XE 16.3.x
	AIR-CAP1532E-x-K9				
1540 Series	AIR-AP1542L-x-K9	8.5.103.0	8.10.x	Cisco IOS XE	—
	AIR-AP1542D-x-K9			Gibraltar 16.10.1	—



Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support
1550 Series <sup>4</sup>	AIR-CAP1552I-x-K9	7.0.116.0	8.5.x	—	—
	AIR-CAP1552E-x-K9	7.0.116.0		—	—
	AIR-CAP1552C-x-K9	7.0.116.0		—	—
	AIR-CAP1552H-x-K9	7.0.116.0		—	—
	AIR-CAP1552SA-x-K9	7.0.220.0		—	—
	AIR-CAP1552SD-x-K9	7.0.220.0		—	—
	AIR-CAP1552CU-x-K9	7.3.101.0		—	—
	AIR-CAP1552EU-x-K9	7.3.101.0		—	—
1552S	AIR-CAP1552SA-x-K9	7.0.220.0	8.5.x	—	—
	AIR-CAP1552SD-x-K9				—
1560 Series	AIR-AP1562I-x-K9	8.3.111.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	—
	AIR-AP1562E-x-K9				—
	AIR-AP1562D-x-K9				—
1570 version ID 01 (V01)	AIR-AP1572EAC-x-K9	8.0.110.0	8.10.x	Cisco IOS XE Gibraltar 16.10.1	Cisco IOS XE Amsterdam 17.3.x
	AIR-AP1572ICy-x-K9 <sup>5</sup>				Cisco IOS XE Cupertino 17.9.3
	AIR-AP1572ECy-x-K9				<a href="#">29</a>
1570 version ID 02 (V02)	AIR-AP1572EAC-BK9	8.0.135.0	8.10.x	—	—
	AIR-AP1572EC1-BK9			—	—
	AIR-AP1572EC2-BK9			Cisco IOS XE Gibraltar 16.10.x	Cisco IOS XE Amsterdam 17.3.x
	AIR-AP1572IC1-BK9				
	AIR-AP1572IC2-BK9				
		<a href="#">30</a>			

Access Points	PID	First AireOS Release Support	Last AireOS Release Support	First Cisco IOS XE Release Support	Last Cisco IOS XE Release Support	
IW3700	IW3702-2E-UXXK9	8.0.120.0	8.10.x	—	—	
	IW3702-4E-UXXK9	8.0.120.0		—	—	
	IW3702-2E-B-K9	8.2.110.0		—	—	
	IW3702-4E-B-K9	8.2.110.0		—	—	
	IW3702-2E-M-K9	8.3.102.0		—	—	
	IW3702-4E-M-K9	8.3.102.0		Cisco IOS XE Gibraltar 16.11.1c	—	
	IW3702-2E-R-K9	8.3.102.0			—	
	IW3702-4E-R-K9	8.3.102.0			—	
	IW3702-2E-Q-K9	8.3.102.0			—	
	IW3702-4E-Q-K9	8.3.102.0			—	
	IW3702-2E-S-K9	8.3.102.0			—	
	IW3702-4E-S-K9	8.3.102.0			—	
IW9167 Heavy Duty Series	IW9167EH-x	—	—		Cisco IOS XE Cupertino 17.9.3	—
	IW9167IH-x	—	—		Cisco IOS XE Dublin 17.12.1	—
IW6300 Heavy Duty Series	IW-6300H-AC-x-K9	8.10.105.0	8.10.x		Cisco IOS XE Gibraltar 17.1.1s	—
	IW-6300HDCW-x-K9			—		
	IW-6300HDC-x-K9			—		
6300 Embedded Services	ESW-6300CON-x-K9	8.10.105.0	8.10.x	Cisco IOS XE Gibraltar 17.1.1s	—	
Wi-Fi 6 Pluggable Module for Cisco IR1800	WP-WIFI6-x	—	—	Cisco IOS XE Bengaluru 17.6.1	—	

<sup>26</sup> This AP is not supported in releases 17.4.1 to 17.9.2.

- 27 This AP is not supported in releases 17.4.1 â€“ 17.9.2.  
 28 This AP is not supported in releases 17.4.1 â€“ 17.9.2.  
 29 This AP is not supported in releases 17.4.1 â€“ 17.9.2.  
 30 This AP is not supported in releases 17.4.1 â€“ 17.9.2.

1	<p>Cisco Catalyst 9130, 9120, 9117, 9115 Access Points          Regulatory domains: Customers are responsible for verifying approval for use in their individual countries. To verify approval and to identify the regulatory domain that corresponds to a particular country, visit <a href="https://www.cisco.com/go/aironet/compliance">https://www.cisco.com/go/aironet/compliance</a>. Not all regulatory domains have been approved. As they are approved, the part numbers will be available on the Global Price List.</p>
2	<p>These access points are supported in the separate 4.1.19x.x mesh software release or with release 5.2 or later releases. These access points are not supported in the 4.2, 5.0, or 5.1 Releases.</p>
3	<p>The Cisco Aironet 1530 Series APs are supported operating only in Local mode; these APs in mesh mode are not supported.</p>

4	The Cisco Aironet 1550 Series APs with 64-MB memory are not supported from Release 8.4.
5	y—Country DOCSIS Compliance, see ordering guide for details.

## Cisco AireOS Wireless Controller Specific Software Release Support

This section lists the Cisco AireOS Wireless controller software releases in which the support started and ended, as applicable, for various Cisco AireOS Wireless Controller hardware platforms.

**Table 8: Cisco AireOS Wireless Controller Platform Support in Software Releases**

Cisco Wireless Controller Platform	First Support	Last Support
2100	4.2.x	7.x
2504	7.0.x	8.5
3504	8.5	8.10.x
4400	4.2.x	7.x
5508	6.0.x	8.5
5520	8.1.x	8.10.x
7510	7.0.x	8.5
8510	7.3.x	8.5
8540	8.1.x	8.10.x
Virtual Controller	7.3.x	8.10.x
WiSM	4.2.x	7.x
WiSM2 (1 DP)	7.0.x	8.5
WiSM2 (2 DP)	7.2.x	8.5
SRE	7.0.x	8.10.x

For information about supported hardware for Cisco Converged Access Solution, see [Supported Converged Access Solutions](#) section in the *Compatibility Matrix for Legacy Cisco Wireless Solutions* document.

## Cisco Aironet 1800s Active Sensor Compatibility Matrix

Table 9: Cisco Aironet 1800s Active Sensor Compatibility Matrix, on page 117 lists various Cisco Aironet 1800s Active Sensor software releases and the corresponding supported Cisco DNA Center versions.

Table 9: Cisco Aironet 1800s Active Sensor Compatibility Matrix

Cisco Aironet 1800s Active Sensor Software	Cisco DNA Center
2.2.2.0	2.2.2.x
2.2.1.0	2.2.1.x
2.1.1.0	2.1.1.x
1.3.3.0	1.3.3.x
1.3.1.2	1.3.1.2
8.8.263.0	1.3.0.3 or earlier
8.8.261.0	
8.8.259.0	
8.8.258.0	
8.7.258.0	

## Inter Release Compatibility Matrix within Platforms

### Inter Release Compatibility Matrix between IOS-XE Software Platforms

Table 10: IRCM for IOS-XE Releases

Base Release Number	Compatible Release Number
17.3.5a	17.9.1
17.3.4c	17.9.1
17.3.4	17.9.1

## Inter Release Compatibility Matrix between AireOS Releases

Mobility, or roaming, is a wireless LAN client's ability to maintain its association seamlessly from one AP to another securely and with as little latency as possible. For more information about mobility in AireOS releases, see the *Information About Mobility* section in the [Controller configuration guide](#).

This section lists compatibility information between various AireOS releases, starting from 8.0.x, that involve Layer 2 and Layer 3 roaming and guest tunneling.

**Table 11: IRCM Compatibility Matrix: 8.0.x to Later Releases**

Release	8.0.x	8.2.x	8.3.x	8.4.x	8.5.x	8.6.x	8.7.x	8.8.x	8.9.x	8.10.x
8.0.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.2.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.3.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.4.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.5.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.6.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.7.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.8.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.9.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y
8.10.x	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y

## Cisco Spaces Compatibility Matrix

**Table 12: Compatibility Matrix**

Application	Cisco AireOS Controller	Cisco Catalyst 9800 Series Wireless Controller	Cisco Embedded Wireless Controller	Cisco Prime/Cisco DNA Center
Cisco Spaces (with Detect and Locate, Captive Portal, Engagements, Location Personas, Behavior Metrics)	<ul style="list-style-type: none"> <li>Cisco Wireless Controller Native Cloud Connector - 8.3 or a later version (except 8.3.102 for Presence) <sup>31</sup></li> <li>Cisco Spaces - 8.0.119 or a later version.</li> </ul>	16.10 or a later version	16.11.1s or a later version	3.0 or a later version for maps <sup>32</sup>

<sup>31</sup> 8.3 is End-of-Life (EOL). We recommend that you migrate to one of the recommended releases as per the Guidelines for Cisco Wireless Software Release Product Bulletin at:

<https://www.cisco.com/c/en/us/products/collateral/wireless/wireless-controllers/bulletin-c25-738147.html>

<sup>32</sup> Cisco Prime support is not there for maps on Cisco Embedded Wireless Controller.



---

**Note** 3375 Appliance is not supported.

---

### Compatibility Matrix for Location Service

For detailed information about Location Service compatibility matrix, see [Compatibility Matrix for Location Service](#).

## Cisco Connected Mobile Experiences Compatibility Matrix

### Important Notes for Connected Mobile Experiences Platform

This section describes Cisco CMX compatibility limitations with the platforms and releases listed in the [Cisco CMX Compatibility Matrix, on page 122](#).

#### General

- We strongly recommend that you upgrade to Cisco CMX Release 10.4.1.x or later if you are running Cisco CMX Release 10.3 or earlier.

#### Cisco High Availability

- The High Availability feature on Cisco CMX:
  - Is supported only in Cisco CMX Release 10.3.x or later.
  - Is supported on all platforms supported by Cisco CMX Release 10.3.x or later.



---

**Note** The Cisco High Availability feature in Cisco CMX Release 10.3.x or later is not supported on the Cisco MSE 3355.

---

- Requires that both primary and standby servers have the same virtual machine size and the same virtual Cisco MSE appliances.

#### Cisco CMX Hyperlocation

- Cisco CMX Release 10.2.x (non-Cisco Hyperlocation apps) is compatible with Cisco Prime Infrastructure Release 2.2.x and 3.0.x.
- Cisco CMX Hyperlocation with the High Availability feature on Cisco CMX requires Cisco Controller Release 8.4.1.210 or later.

- Cisco CMX Hyperlocation requires Cisco Controller Release 8.1.131.0 or later.
- Cisco CMX Hyperlocation is not supported on the Cisco MSE 3355.
- Cisco CMX Hyperlocation is not supported on the Cisco Mobility Express Controllers.

### Cisco 3375 Appliance for Cisco Connected Mobile Experiences

- Cisco CMX Release 10.5.1 or later supports the Cisco 3375 Appliance for Cisco Connected Mobile Experiences.

### Cisco Access Points

Cisco access points that are supported on Cisco Controllers Release 8.0 up to 8.10 are supported on Cisco CMX.

- Cisco CMX supports Cisco 9166I and 9164I Wi-Fi 6E series access points.
- Cisco CMX supports Cisco 1830, 1840, 1850, 2700, 2800, 3702e, 3702i, 3800, and 4800 access points.
- Cisco CMX supports Catalyst 9105AX, 9115, 9117, 9120AX (with Cisco FastLocate), 9124AX, 9130AXE, 9130AX-E, and 9130AX-I access points.
- (CSCvr26395 and CSCvr26398) The Cisco CMX Location Accuracy Test tool supports only Cisco Hyperlocation-capable access points.

### Cisco Mobility Express

- Cisco CMX Release 10.5.0 supports Cisco ME Release 8.8 running on Cisco 1830 and 1850 access points.

### Cisco Mobility Services Engine 3355 Appliance (physical)

- Cisco CMX Release 10.4.x or later does not support the Cisco MSE 3355 platform.
- Cisco CMX Release 10.3.x release or earlier are supported on the Cisco MSE 3355 platform. However, the HA feature in Cisco CMX Release 10.3.x is not supported on the Cisco MSE 3355.
- Cisco CMX Release 10.2.x or later is supported on the Cisco MSE 3355 but on a limited scale in terms of number of tracked clients and number of controllers synchronized. Scale numbers for Location and Presence Analytics are documented in the [Cisco Connected Mobile Experiences Data Sheet](#).

### Cisco Switches

- Cisco CMX Releases 10.3.1 or later is not compatible with the following Cisco switch platforms:
  - Cisco Catalyst 2960-24TT switch running Cisco Release 15.0(2)SE11
  - Cisco Catalyst 2960-48-PST-L switch running Cisco Release 15.0(2)SE11
  - Cisco Catalyst 2960X-24PS-L switch running Cisco Release 15.2(2)E7
  - Cisco Catalyst 3650-24PS switch running Cisco Release 16.3.5b
  - Cisco Catalyst 3560-24PS switch running Cisco Release 12.2(55)SE11



- Cisco Catalyst 3850-24XS switch running Cisco Release 16.3.5.b
- Cisco Nexus 5596UP switch running Cisco Release 7.1(4)N1(1)

### Cisco Wireless Controllers

For additional information, see the [Cisco Access Points, on page 120](#) section.

- Cisco CMX Release 10.6.2 and later supports Catalyst 9800-L controller Release 16.12 and later.
- Cisco CMX Release 10.5.1 and later supports Cisco controller Release 8.8.100.
- The Cisco CMX Release 10.5 CMX Grouping feature requires Cisco controller Release 8.7 or later.
- Cisco controller Release 7.x supports the complete set of Cisco CMX Connect services. However:
  - Cisco controller Release 8.2 or later is required to use these features available on Cisco CMX Release 10.2.2: menu link, text link on login page, and DNS-ACL configuration.
  - Cisco controller Release 8.3 or later is required to use the PMS policy uplink bandwidth enforcement feature available on Cisco CMX Release 10.2.2.

## Cisco CMX Compatibility Matrix

Table 13: Cisco CMX Compatibility Matrix<sup>1</sup>

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
11.0.0-154	<p data-bbox="636 413 813 474"><b>Cisco Prime Infrastructure<sup>6</sup></b></p> <p data-bbox="636 493 686 520">3.10</p> <p data-bbox="636 541 691 569">3.9.1</p> <p data-bbox="636 590 691 617">3.9.0</p> <p data-bbox="636 638 878 665">3.8.0.310 with patches</p> <p data-bbox="636 686 740 714">3.8.0.310</p> <p data-bbox="636 735 938 856">3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Releases 16.12.4a and 17.1 and later);</p> <p data-bbox="636 877 691 905">3.7.0</p> <p data-bbox="636 926 760 953">3.6.0.0.172</p> <p data-bbox="636 974 906 1035">3.5.0.0.550 (with Critical Update 02)</p> <p data-bbox="636 1056 760 1083">3.4.0.0.348</p> <p data-bbox="636 1104 932 1283"> <b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.         </p>		

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			<b>Cisco Controller<sup>7,8</sup></b> 8.10 8.9 8.8 8.7 8.5 8.3 8.2 8.0  <b>Catalyst 9800 Controller<sup>5</sup></b> 17.12.1 17.11.1 17.10.1 17.9.4 17.9.3 17.9.2 17.9.1 17.8.1 17.7.1 17.6.5 17.6.4 17.6.3 17.6.1 (Non-FIPS only) 17.5.1 (Non-FIPS only) 17.4.1 (Non-FIPS only) 17.3.6 17.3.5b 17.3.5a 17.3.4 (Non-FIPS only) 17.3.4c 17.3.4 17.3.3 (Non-FIPS only) 17.3.3

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			17.3.2a (Non-FIPS only) 17.3.1 16.12.5 16.12.4a 16.12.3 17.2.1 (Non-FIPS only) 17.1.1s 16.12.2s 16.12.1s 16.11.1c 16.11.1b

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.3-146	<p><b>Cisco Prime Infrastructure<sup>6</sup></b></p> <p>3.10</p> <p>3.9.1</p> <p>3.9.0</p> <p>3.8.0.310 with patches</p> <p>3.8.0.310</p> <p>3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Releases 16.12.4a and 17.1 and later);</p> <p>3.7.0</p> <p>3.6.0.0.172</p> <p>3.5.0.0.550 (with Critical Update 02)</p> <p>3.4.0.0.348</p> <p><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p><b>Cisco CMX</b></p> <p>Cisco 3375 Appliance for CMX</p> <p><b>Cisco MSE</b></p> <p>Cisco MSE 3365 (physical) Appliance</p>	

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			<p data-bbox="1221 281 1442 310"><b>Cisco Controller<sup>7,8</sup></b></p> <p data-bbox="1221 331 1273 361">8.10</p> <p data-bbox="1221 382 1260 411">8.9</p> <p data-bbox="1221 432 1260 462">8.8</p> <p data-bbox="1221 483 1260 512">8.7</p> <p data-bbox="1221 533 1260 562">8.5</p> <p data-bbox="1221 583 1260 613">8.3</p> <p data-bbox="1221 634 1260 663">8.2</p> <p data-bbox="1221 684 1260 714">8.0</p> <p data-bbox="1221 714 1513 743"><b>Catalyst 9800 Controller<sup>5</sup></b></p> <p data-bbox="1221 764 1305 793">17.12.1</p> <p data-bbox="1221 814 1305 844">17.11.1</p> <p data-bbox="1221 865 1305 894">17.10.1</p> <p data-bbox="1221 915 1292 945">17.9.4</p> <p data-bbox="1221 966 1292 995">17.9.3</p> <p data-bbox="1221 1016 1292 1045">17.9.2</p> <p data-bbox="1221 1066 1292 1096">17.9.1</p> <p data-bbox="1221 1117 1292 1146">17.8.1</p> <p data-bbox="1221 1167 1292 1197">17.7.1</p> <p data-bbox="1221 1218 1292 1247">17.6.5</p> <p data-bbox="1221 1268 1292 1297">17.6.4</p> <p data-bbox="1221 1318 1292 1348">17.6.3</p> <p data-bbox="1221 1369 1477 1398">17.6.1 (Non-FIPS only)</p> <p data-bbox="1221 1419 1477 1449">17.5.1 (Non-FIPS only)</p> <p data-bbox="1221 1470 1477 1499">17.4.1 (Non-FIPS only)</p> <p data-bbox="1221 1520 1292 1549">17.3.6</p> <p data-bbox="1221 1570 1305 1600">17.3.5b</p> <p data-bbox="1221 1621 1305 1650">17.3.5a</p> <p data-bbox="1221 1671 1477 1701">17.3.4 (Non-FIPS only)</p> <p data-bbox="1221 1722 1305 1751">17.3.4c</p> <p data-bbox="1221 1772 1292 1801">17.3.4</p> <p data-bbox="1221 1822 1477 1852">17.3.3 (Non-FIPS only)</p> <p data-bbox="1221 1873 1292 1902">17.3.3</p>

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			17.3.2a (Non-FIPS only) 17.3.1 16.12.5 16.12.4a 16.12.3 17.2.1 (Non-FIPS only) 17.1.1s 16.12.2s 16.12.1s 16.11.1c 16.11.1b

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.3-105	<p><b>Cisco Prime Infrastructure</b><sup>6</sup></p> <p>3.10</p> <p>3.9.1</p> <p>3.9.0</p> <p>3.8.0.310 with patches</p> <p>3.8.0.310</p> <p>3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Releases 16.12.4a and 17.1 and later);</p> <p>3.7.0</p> <p>3.6.0.0.172</p> <p>3.5.0.0.550 (with Critical Update 02)</p> <p>3.4.0.0.348</p> <p><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p><b>Cisco CMX</b></p> <p>Cisco 3375 Appliance for CMX</p> <p><b>Cisco MSE</b></p> <p>Cisco MSE 3365 (physical) Appliance</p>	



Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			<b>Cisco Controller<sup>7,8</sup></b> 8.10 8.9 8.8 8.7 8.5 8.3 8.2 8.0  <b>Catalyst 9800 Controller<sup>5</sup></b> 17.9.1 17.8.1 17.7.1 17.6.5 17.6.4 17.6.3 17.6.1 (Non-FIPS only) 17.5.1 (Non-FIPS only) 17.4.1 (Non-FIPS only) 17.3.6 17.3.5b 17.3.5a 17.3.4 (Non-FIPS only) 17.3.4c 17.3.4 17.3.3 (Non-FIPS only) 17.3.3 17.3.2a (Non-FIPS only) 17.3.1 16.12.5 16.12.4a 16.12.3 17.2.1 (Non-FIPS only)

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			17.1.1s 16.12.2s 16.12.1s 16.11.1c 16.11.1b

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
<p>10.6.3-70</p> <p><b>Note</b> For CMX 10.6.3-70 on FIPS to work with 17.x controllers on FIPS, you must install a patch. We are working on the patch, which will be available soon.</p>	<p><b>Cisco Prime Infrastructure</b><sup>6</sup></p> <p>3.10</p> <p>3.9.1</p> <p>3.9.0</p> <p>3.8.0.310 with patches</p> <p>3.8.0.310</p> <p>3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Releases 16.12.4a and 17.1 and later);</p> <p>3.7.0</p> <p>3.6.0.0.172</p> <p>3.5.0.0.550 (with Critical Update 02)</p> <p>3.4.0.0.348</p> <p><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p><b>Cisco CMX</b></p> <p>Cisco 3375 Appliance for CMX</p> <p><b>Cisco MSE</b></p> <p>Cisco MSE 3365 (physical) Appliance</p>	

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			<p data-bbox="1221 281 1442 310"><b>Cisco Controller<sup>7,8</sup></b></p> <p data-bbox="1221 331 1273 361">8.10</p> <p data-bbox="1221 382 1260 411">8.9</p> <p data-bbox="1221 432 1260 462">8.8</p> <p data-bbox="1221 483 1260 512">8.7</p> <p data-bbox="1221 533 1260 562">8.5</p> <p data-bbox="1221 583 1260 613">8.3</p> <p data-bbox="1221 634 1260 663">8.2</p> <p data-bbox="1221 684 1260 714">8.0</p> <p data-bbox="1221 714 1513 743"><b>Catalyst 9800 Controller<sup>5</sup></b></p> <p data-bbox="1221 764 1292 793">17.9.3</p> <p data-bbox="1221 814 1292 844">17.9.1</p> <p data-bbox="1221 865 1292 894">17.8.1</p> <p data-bbox="1221 915 1292 945">17.7.1</p> <p data-bbox="1221 966 1292 995">17.6.5</p> <p data-bbox="1221 1016 1292 1045">17.6.4</p> <p data-bbox="1221 1066 1292 1096">17.6.3</p> <p data-bbox="1221 1117 1477 1146">17.6.1 (Non-FIPS only)</p> <p data-bbox="1221 1167 1477 1197">17.5.1 (Non-FIPS only)</p> <p data-bbox="1221 1218 1477 1247">17.4.1 (Non-FIPS only)</p> <p data-bbox="1221 1268 1292 1297">17.3.6</p> <p data-bbox="1221 1318 1305 1348">17.3.5b</p> <p data-bbox="1221 1369 1305 1398">17.3.5a</p> <p data-bbox="1221 1419 1477 1449">17.3.4 (Non-FIPS only)</p> <p data-bbox="1221 1470 1305 1499">17.3.4c</p> <p data-bbox="1221 1520 1292 1549">17.3.4</p> <p data-bbox="1221 1570 1477 1600">17.3.3 (Non-FIPS only)</p> <p data-bbox="1221 1621 1292 1650">17.3.3</p> <p data-bbox="1221 1671 1477 1701">17.3.2a (Non-FIPS only)</p> <p data-bbox="1221 1722 1292 1751">17.3.1</p> <p data-bbox="1221 1772 1305 1801">16.12.5</p> <p data-bbox="1221 1822 1318 1852">16.12.4a</p> <p data-bbox="1221 1873 1305 1902">16.12.3</p>

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
			17.2.1 (Non-FIPS only) 17.1.1s 16.12.2s 16.12.1s 16.11.1c 16.11.1b

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.2-89 <sup>33</sup>	<p data-bbox="636 289 941 352"><b>Cisco Prime Infrastructure<sup>6</sup></b></p> <p data-bbox="636 369 740 401">3.8.0.310</p> <p data-bbox="636 417 878 449">3.7.1 (with Update 02)</p> <p data-bbox="636 466 935 590">3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Release 17.1 and later)</p> <p data-bbox="636 606 695 638">3.7.0</p> <p data-bbox="636 655 760 686">3.6.0.0.172</p> <p data-bbox="636 703 911 766">3.5.0.0.550 (with Critical Update 02)</p> <p data-bbox="636 783 760 814">3.4.0.0.348</p> <p data-bbox="636 831 935 1020"><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p data-bbox="954 289 1091 321"><b>Cisco CMX</b></p> <p data-bbox="954 338 1195 401">Cisco 3375 Appliance for CMX</p> <p data-bbox="954 417 1084 449"><b>Cisco MSE</b></p> <p data-bbox="954 466 1179 529">Cisco MSE 3365 (physical) Appliance</p>	<p data-bbox="1221 289 1442 321"><b>Cisco Controller<sup>7,8</sup></b></p> <p data-bbox="1221 338 1271 369">8.10</p> <p data-bbox="1221 386 1256 417">8.9</p> <p data-bbox="1221 434 1256 466">8.8</p> <p data-bbox="1221 483 1256 514">8.7</p> <p data-bbox="1221 531 1256 562">8.5</p> <p data-bbox="1221 579 1256 611">8.3</p> <p data-bbox="1221 627 1256 659">8.2</p> <p data-bbox="1221 676 1256 707">8.0</p> <p data-bbox="1221 724 1513 756"><b>Catalyst 9800 Controller<sup>5</sup></b></p> <p data-bbox="1221 772 1474 804">17.6.1 (Non-FIPS only)</p> <p data-bbox="1221 821 1474 852">17.5.1 (Non-FIPS only)</p> <p data-bbox="1221 869 1474 900">17.4.1 (Non-FIPS only)</p> <p data-bbox="1221 917 1289 949">17.3.6</p> <p data-bbox="1221 966 1304 997">17.3.5b</p> <p data-bbox="1221 1014 1304 1045">17.3.5a</p> <p data-bbox="1221 1062 1304 1094">17.3.4c</p> <p data-bbox="1221 1110 1289 1142">17.3.4</p> <p data-bbox="1221 1159 1474 1190">17.3.4 (Non-FIPS only)</p> <p data-bbox="1221 1207 1289 1239">17.3.3</p> <p data-bbox="1221 1255 1304 1287">17.3.2a</p> <p data-bbox="1221 1304 1289 1335">17.3.1</p> <p data-bbox="1221 1352 1474 1383">17.2.1 (Non-FIPS only)</p> <p data-bbox="1221 1400 1304 1432">17.1.1s</p> <p data-bbox="1221 1449 1304 1480">16.12.5</p> <p data-bbox="1221 1497 1317 1528">16.12.4a</p> <p data-bbox="1221 1545 1304 1577">16.12.3</p> <p data-bbox="1221 1593 1317 1625">16.12.2s</p> <p data-bbox="1221 1642 1317 1673">16.12.1s</p> <p data-bbox="1221 1690 1317 1722">16.11.1c</p> <p data-bbox="1221 1738 1317 1770">16.11.1b</p>

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.2-72	<p data-bbox="673 289 852 352"><b>Cisco Prime Infrastructure</b><sup>6</sup></p> <p data-bbox="673 367 779 394">3.8.0.310</p> <p data-bbox="673 415 917 443">3.7.1 (with Update 02)</p> <p data-bbox="673 464 966 590">3.7.0.159 (with patches for Cisco Catalyst 9800 Controller Release 17.1 and later)</p> <p data-bbox="673 611 738 638">3.7.0</p> <p data-bbox="673 659 803 686">3.6.0.0.172</p> <p data-bbox="673 707 950 770">3.5.0.0.550 (with Critical Update 02)</p> <p data-bbox="673 791 803 819">3.4.0.0.348</p> <p data-bbox="673 835 966 1024"><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p data-bbox="993 289 1128 317"><b>Cisco CMX</b></p> <p data-bbox="993 338 1234 401">Cisco 3375 Appliance for CMX</p> <p data-bbox="993 422 1128 449"><b>Cisco MSE</b></p> <p data-bbox="993 470 1218 533">Cisco MSE 3365 (physical) Appliance</p>	<p data-bbox="1258 289 1485 317"><b>Cisco Controller</b><sup>7,8</sup></p> <p data-bbox="1258 338 1307 365">8.10</p> <p data-bbox="1258 386 1299 413">8.9</p> <p data-bbox="1258 434 1299 462">8.8</p> <p data-bbox="1258 483 1299 510">8.7</p> <p data-bbox="1258 531 1299 558">8.5</p> <p data-bbox="1258 579 1299 606">8.3</p> <p data-bbox="1258 627 1299 655">8.2</p> <p data-bbox="1258 676 1299 703">8.0</p> <p data-bbox="1258 724 1550 751"><b>Catalyst 9800 Controller</b><sup>5</sup></p> <p data-bbox="1258 772 1339 800">17.3.4c</p> <p data-bbox="1258 821 1331 848">17.3.4</p> <p data-bbox="1258 869 1331 896">17.3.3</p> <p data-bbox="1258 917 1339 945">17.3.2a</p> <p data-bbox="1258 966 1323 993">17.3.1</p> <p data-bbox="1258 1014 1339 1041">17.1.1s</p> <p data-bbox="1258 1062 1356 1089">16.12.2s</p> <p data-bbox="1258 1110 1356 1138">16.12.1s</p> <p data-bbox="1258 1159 1356 1186">16.11.1c</p> <p data-bbox="1258 1207 1356 1234">16.11.1b</p>

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.2	<p data-bbox="636 289 812 352"><b>Cisco Prime Infrastructure</b><sup>6</sup></p> <p data-bbox="636 369 695 399">3.7.0</p> <p data-bbox="636 417 760 447">3.6.0.0.172</p> <p data-bbox="636 466 909 529">3.5.0.0.550 (with Critical Update 02)</p> <p data-bbox="636 548 760 577">3.4.0.0.348</p> <p data-bbox="636 596 935 781"><b>Note</b> We recommend that you use Cisco Prime Infrastructure Release 3.7.0 or later.</p>	<p data-bbox="954 289 1091 319"><b>Cisco CMX</b></p> <p data-bbox="954 338 1195 401">Cisco 3375 Appliance for CMX</p> <p data-bbox="954 420 1084 449"><b>Cisco MSE</b></p> <p data-bbox="954 468 1182 531">Cisco MSE 3365 (physical) Appliance</p>	<p data-bbox="1221 289 1442 319"><b>Cisco Controller</b><sup>7,8</sup></p> <p data-bbox="1221 338 1273 367">8.10</p> <p data-bbox="1221 386 1260 415">8.9</p> <p data-bbox="1221 434 1260 464">8.8</p> <p data-bbox="1221 483 1260 512">8.7</p> <p data-bbox="1221 531 1260 560">8.5</p> <p data-bbox="1221 579 1260 609">8.3</p> <p data-bbox="1221 627 1260 657">8.2</p> <p data-bbox="1221 676 1260 705">8.0</p> <p data-bbox="1221 724 1513 753"><b>Catalyst 9800 Controller</b><sup>5</sup></p> <p data-bbox="1221 772 1305 802">17.3.4c</p> <p data-bbox="1221 821 1292 850">17.3.4</p> <p data-bbox="1221 869 1292 898">17.3.3</p> <p data-bbox="1221 917 1305 947">17.3.2a</p> <p data-bbox="1221 966 1292 995">17.3.1</p> <p data-bbox="1221 1014 1318 1043">16.12.1s</p> <p data-bbox="1221 1062 1318 1092">16.11.1c</p> <p data-bbox="1221 1110 1318 1140">16.11.1b</p>



Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.6.1	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.6.0.0.172 3.5.0.0.550 (with Critical Update 02) 3.4.0.0.348	<b>Cisco CMX</b> Cisco 3375 Appliance for CMX  <b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.9 8.8 8.7 8.5 8.3 8.2 8.0  <b>Catalyst 9800 Controller<sup>5</sup></b> 17.3.4c 17.3.4 17.3.3 17.3.2a 17.3.1 16.11.1b 16.10.1e
10.6.0	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.5.0.0.550 (with Critical Update 02) 3.4.0.0.348	<b>Cisco CMX</b> Cisco 3375 Appliance for CMX  <b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.9 8.8 8.7 8.5 8.3 8.2 8.0  <b>Catalyst 9800 Controller<sup>5</sup></b> 17.3.4c 17.3.4 17.3.3 17.3.2a 17.3.1 16.10.1e

Cisco CMX	Network Management <sup>2,3</sup>	Hardware Platforms <sup>4</sup>	
10.5.1	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.4.0.0.348 3.3.0.0.342 3.2.0.0.258	<b>Cisco CMX</b> Cisco 3375 Appliance for CMX  <b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.8 8.7 8.5 8.3 8.2 8.0  <b>Catalyst 9800 Controller<sup>5</sup></b> 17.3.4c 17.3.4 17.3.3 17.3.2a 17.3.1 16.10.1
10.5.0	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.4.0.0.348 3.3.0.0.342 3.2.0.0.258	<b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.7 8.5 8.3 8.2 8.0
10.4.x	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.3.0.0.342 3.2.0.0.258 3.1.0.0.132	<b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.6 8.5 8.3 8.2 8.0
10.3.x	<b>Cisco Prime Infrastructure<sup>6</sup></b> 3.0 to 3.2 2.2	<b>Cisco MSE</b> Cisco MSE 3365 (physical) Appliance  Cisco MSE 3355 (physical) Appliance	<b>Cisco Controller<sup>7,8</sup></b> 8.5 8.3 8.2 8.0

<sup>33</sup> For CMX 10.6.2-89 on FIPS to work with 17.x controllers on FIPS, you must install the **cmx-major-patch-10.6.2-1.cmxp** patch in CMX. 9

1	For Cisco CMX compatibility limitations, see the <a href="#">Important Notes for Connected Mobile Experiences Platform</a> section.
2	Cisco DNA Center Release 2.1.2.x or later supports Cisco CMX Release 10.6.2, 10.6.3 or later.  For Cisco DNA Center compatibility information, see the Cisco Digital Network Architecture Center Supported Devices matrix and the Cisco Software-Defined Access Hardware and Software Compatibility Matrix matrix.
3	Cisco CMX Release 10.6.0 and later is required to support Cisco DNA Spaces. For complete Cisco DNA Spaces compatibility information, see the <b>Prerequisites</b> chapter of the <i>Cisco DNA Spaces Configuration Guide</i> and the <b>Product Overview</b> chapter of the <i>Cisco DNA Spaces: Connector Configuration Guide</i> .
4	For Cisco Mobility Express Solution compatibility information, see the <a href="#">Cisco Mobility Express Solution Compatibility Matrix</a> section.
5	For Cisco Embedded Wireless Controller on Catalyst Access Points compatibility information, see the <a href="#">Cisco Embedded Wireless Controller Matrix</a> section.
6	For Cisco Prime Infrastructure compatibility information, see the <a href="#">Cisco Prime Infrastructure Compatibility Matrix</a> section in the <i>Compatibility Matrix for Legacy Cisco Wireless Solutions</i> document.
7	For Cisco Controller Release 8.x releases, we recommend that you install the latest maintenance release that corresponds to your software version.
8	For Cisco Controller and Cisco AP compatibility information, see the <a href="#">Supported Access Points in Cisco Catalyst 9800 Series Wireless Controller Software Releases</a> section.
9	For CMX 10.6.2-89 on FIPS to work with 17.x controllers on FIPS, you must install the <b>cmx-major-patch-10.6.2-1.cmxp</b> patch in CMX. This patch for <a href="#">CSCvx23734</a> is available on request and provides: <ul style="list-style-type: none"> <li>• CMX on FIPS and 17.x controllers on FIPS.</li> <li>• CMX on non-FIPS and 17.x controllers on FIPS.</li> </ul>

## Cisco Prime Infrastructure Compatibility Matrix

### Cisco Prime Infrastructure and Cisco Wireless Release Compatibility Matrix

Table 14: [Cisco Prime Infrastructure and Cisco Wireless Release Compatibility Matrix](#), on page 141 lists the Cisco Controller releases and Identity Services Engine (ISE) versions that are compatible with the Cisco Prime Infrastructure releases.

For information about wireless device support in Cisco Prime Infrastructure, see the following URL:  
<https://www.cisco.com/c/en/us/support/cloud-systems-management/prime-infrastructure/products-device-support-tables-list.html>

**Note**

- 
- For Cisco CMX and Cisco MSE compatibility details, see the [Cisco Connected Mobile Experiences Compatibility Matrix](#), and the [Cisco Mobility Services Engine Compatibility Matrix](#) respectively.
  - For Cisco MSE compatibility with Cisco Prime Infrastructure releases, see the applicable Cisco Prime Infrastructure release notes at: <https://www.cisco.com/c/en/us/support/cloud-systems-management/prime-infrastructure/products-release-notes-list.html>.
-

Table 14: Cisco Prime Infrastructure and Cisco Wireless Release Compatibility Matrix

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
3.10.4		2.7	Cisco Prime Infrastructure release might include support for older controller versions < 8.5, however it is recommended to use Cisco Controller versions 8.5.130.0 and above.
3.10.3		2.6	
3.10.2		2.4	
3.10.1		2.3	
3.10		2.2	
3.9.1		2.1	
3.9		2.0	
3.8.1		1.4	
3.8		1.3	<p>Cisco Prime Infrastructure release might include support for older controller versions &lt; 8.5, however it is recommended to use Cisco Controller versions 8.5.130.0 and above.</p> <p>Cisco Prime Infrastructure release 3.8 does not support Cisco Catalyst 9800 Controller releases 16.12 and 17.1.</p>

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
	8.10.190.0		
	8.10.185.0		
	8.10.183.0		
	8.10.182.0		
	8.10.181.0		
	8.10.171.0		
	8.10.162.0		
	8.10.151.0		
	8.10.142.0		
	8.10.130.0		
	8.10.122.0		
	8.10.121.0		
	8.10.113.0		
	8.10.112.0		
	8.10.105.0		
	8.9.111.0		
	8.9.100.0		
	8.8.130.0		
	8.8.125.0		
	8.8.120.0		
	8.8.111.0		
	8.8.100.0		
	8.7.106.0		
	8.7.102.0		
	8.6.101.0		
	8.5.182.0		
	8.5.171.0		
	8.5.164.0		
	8.5.161.0		
	8.5.160.0		
	8.5.151.0		
	8.5.140.0		
	8.5.135.0		

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
	8.5.131.0 8.5.120.0 8.5.110.0 8.5.105.0 8.5.103.0		

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
3.7.1	8.10.130.0	2.7	Cisco Prime Infrastructure release might include support for older controller versions < 8.5, however it is recommended to use Cisco Controller versions 8.5.130.0 and above.
	8.10.122.0	2.6	
	8.10.121.0	2.4	
	8.10.113.0	2.3	
	8.10.112.0	2.2	
	8.10.105.0	2.1	
	8.9.111.0	2.0	
	8.9.100.0	1.4	
	8.8.130.0	1.3	
	8.8.125.0		
	8.8.120.0		
	8.8.111.0		
	8.8.100.0		
	8.7.106.0		
	8.7.102.0		
	8.6.101.0		
	8.5.182.0		
	8.5.171.0		
	8.5.164.0		
	8.5.161.0		
	8.5.160.0		
	8.5.151.0		
	8.5.140.0		
	8.5.135.0		
	8.5.131.0		
	8.5.120.0		
	8.5.110.0		
8.5.105.0			
8.5.103.0			



Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
3.7	8.10.130.0 8.10.122.0 8.10.121.0 8.10.113.0 8.10.112.0 8.10.105.0 8.9.111.0 8.9.100.0 8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.8.100.0 8.7.106.0 8.7.102.0 8.6.101.0 8.5.182.0 8.5.171.0 8.5.164.0 8.5.161.0 8.5.160.0 8.5.151.0 8.5.140.0 8.5.135.0 8.5.131.0 8.5.120.0 8.5.110.0 8.5.105.0 8.5.103.0	2.6 2.4 2.3 2.2 2.1 2.0 1.4 1.3	Cisco Prime Infrastructure release might include support for older controller versions < 8.5, however it is recommended to use Cisco Controller versions 8.5.130.0 and above.

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
3.6	8.9.111.0	2.6	—
	8.9.100.0	2.4	
	8.8.130.0	2.3	
	8.8.125.0	2.2	
	8.8.120.0	2.1	
	8.8.111.0	2.0	
	8.8.100.0	1.4	
	8.7.106.0	1.3	
	8.7.102.0		
	8.6.101.0		
	8.5.182.0		
	8.5.171.0		
	8.5.164.0		
	8.5.161.0		
	8.5.160.0		
	8.5.151.0		
	8.5.140.0		
	8.5.135.0		
	8.5.131.0		
	8.5.120.0		
8.5.110.0			
8.5.105.0			
8.5.103.0			

Cisco Prime Infrastructure	Cisco Controller	Cisco ISE	Remarks
3.5	8.8.130.0	2.4	—
	8.8.125.0	2.3	
	8.8.120.0	2.2	
	8.8.111.0	2.1	
	8.8.100.0	2.0	
	8.7.106.0	1.4	
	8.7.102.0	1.3	
	8.6.101.0		
	8.5.182.0		
	8.5.171.0		
	8.5.164.0		
	8.5.161.0		
	8.5.160.0		
	8.5.151.0		
	8.5.140.0		
	8.5.135.0		
	8.5.131.0		
	8.5.120.0		
	8.5.110.0		
	8.5.105.0		
8.5.103.0			

## Cisco Prime Infrastructure, Cisco Catalyst 9800 Series Wireless Controllers and Cisco Converged Access Solution Compatibility Matrix

[Cisco Prime Infrastructure, Cisco Catalyst 9800 Series Wireless Controllers and Cisco Converged Access Solution Compatibility Matrix, on page 147](#) lists the Cisco IOS/IOS XE releases and the corresponding devices that are compatible with the Cisco Prime Infrastructure releases.

Table 15: Cisco Prime Infrastructure and Cisco IOS/IOS XE Release Compatibility Matrix

Cisco Prime Infrastructure	Cisco IOS/IOS XE Release		Device	Remarks
3.10.4	Current Release with N-2 supported	Dublin 17.12.1 Dublin 17.11.1 Dublin 17.10.1 Cupertino 17.9.4 Cupertino 17.9.3 Cupertino 17.9.2 Cupertino 17.9.1 Cupertino 17.8.1 Cupertino 17.7.1 Bengaluru 17.6.4	Cisco Catalyst 9800-40 Wireless Controller  Cisco Catalyst 9800-80 Wireless Controller  Cisco Catalyst 9800-L-F Wireless Controller  Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.10.4, 3.10.3, 3.10.2, 3.10.1, 3.10, 3.9.1 and 3.9 support Cisco IOS XE Amsterdam-17.3.5a  For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .  <b>Note:</b> Cisco Prime Infrastructure 3.9 and later releases do not support Cisco IOS/IOS XE Releases 16.11 and 16.10.
3.10.3	Current Release with N-2 supported	Dublin 17.10.1 Cupertino 17.9.4 Cupertino 17.9.3 Cupertino 17.9.2 Cupertino 17.9.1 Cupertino 17.8.1 Cupertino 17.7.1 Bengaluru 17.6.4	Cisco Catalyst 9800-40 Wireless Controller  Cisco Catalyst 9800-80 Wireless Controller  Cisco Catalyst 9800-L-F Wireless Controller  Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.10.3, 3.10.2, 3.10.1, 3.10, 3.9.1 and 3.9 support Cisco IOS XE Amsterdam-17.3.5a  For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .  <b>Note:</b> Cisco Prime Infrastructure 3.9 and later releases do not support Cisco IOS/IOS XE Releases 16.11 and 16.10.

Cisco Prime Infrastructure	Cisco IOS/IOS XE Release		Device	Remarks
3.10.2	Current Release with N-2 supported	Cupertino 17.9.4 Cupertino 17.9.3 Cupertino 17.9.2 Cupertino 17.9.1 Cupertino 17.8.1 Cupertino 17.7.1 Bengaluru 17.6.4	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.10.2, 3.10.1, 3.10, 3.9.1 and 3.9 support Cisco IOS XE Amsterdam-17.3.5a  For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .  <b>Note:</b> Cisco Prime Infrastructure 3.9 and later releases do not support Cisco IOS/IOS XE Releases 16.11 and 16.10.
3.10.1	Current Release with N-2 supported	Cupertino 17.8.1 Cupertino 17.7.1 Bengaluru 17.6.3 Bengaluru 17.6.4 Amsterdam 17.3.5a	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.10.1, 3.10, 3.9.1 and 3.9 support Cisco IOS XE Amsterdam-17.3.5a  For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .  <b>Note:</b> Cisco Prime Infrastructure 3.9 and later releases do not support Cisco IOS/IOS XE Releases 16.11 and 16.10.
3.10	Current Release with N-2 supported	Bengaluru 17.6.x Bengaluru 17.5.1 Bengaluru 17.4.1	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller	Cisco Prime Infrastructure Release 3.10, 3.9.1 and 3.9 support Cisco IOS XE Gibraltar 16.12.  For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .
3.9.1	Current Release with N-2 supported	Bengaluru 17.5.1 Bengaluru 17.4.1 Amsterdam 17.3.x	Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud	For instructions to enable support for release 16.12, see the Enable Backward Compatibility section in the latest <i>Cisco Prime Infrastructure Administrator Guide</i> .
3.9	Current Release with N-2 supported	Bengaluru 17.4.1 Amsterdam 17.3.x Amsterdam 17.2	Cisco Catalyst 9800-CL Wireless Controller for Cloud	<b>Note:</b> Cisco Prime Infrastructure 3.9 and later releases do not support Cisco IOS/IOS XE Releases 16.11 and 16.10.

Cisco Prime Infrastructure	Cisco IOS/IOS XE Release		Device	Remarks
3.8.1	Current Release with N-2 supported	Amsterdam 17.3.x Amsterdam 17.2 Amsterdam 17.1	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.8.1 does not support Cisco IOS/IOS XE Releases 16.12, 16.11, and 16.10.
3.8	Current Release with N-2 supported	Amsterdam 17.2.1 Amsterdam 17.1	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud	Cisco Prime Infrastructure Release 3.8 does not support Cisco IOS/IOS XE Release 17.1.x, 16.12.x, 16.12, 16.11 and 16.10.
3.7.1	Current Release with N-2 supported	Amsterdam 17.1 Gibraltar 16.12.x Gibraltar 16.11	Cisco Catalyst 9800-40 Wireless Controller Cisco Catalyst 9800-80 Wireless Controller Cisco Catalyst 9800-L-F Wireless Controller Cisco Catalyst 9800-CL Wireless Controller for Cloud.	—

Cisco Prime Infrastructure	Cisco IOS/IOS XE Release		Device	Remarks
3.7	Current Release	Gibraltar 16.12.x Gibraltar 16.11 Gibraltar 16.10	Cisco Catalyst 9800-40 Wireless Controller  Cisco Catalyst 9800-80 Wireless Controller  Cisco Catalyst 9800-L-F Wireless Controller  Cisco Catalyst 9800-CL Wireless Controller for Cloud.	—
3.6	Current Release	Gibraltar 16.10 Gibraltar 16.11 Gibraltar 16.9	Cisco Catalyst 9800-CL Wireless Controller for Cloud  Cisco Catalyst 9800-40 Wireless Controller	—
3.5	Current Release	Gibraltar 16.9 Gibraltar 16.10 Denali 16.3.3 Denali 16.3.2 Denali 16.3.1	Cisco Catalyst 9800-CL Wireless Controller for Cloud  Cisco Catalyst 9800-40 Wireless Controller	—

## Cisco Mobility Services Engine Compatibility Matrix

Information in this section cites cross-platform compatibility testing performed from only the Cisco MSE perspective and is limited to up to specific product releases cited in this section.

For Cisco MSE compatibility with product releases not cited in this section, see the compatibility matrix for the relevant product. For example, for the most recent compatibility information between Cisco CMX and Cisco MSE, see the [Cisco CMX Compatibility Matrix, on page 122](#).

### Important Notes

Information in this section cites cross-platform compatibility testing performed from only the Cisco MSE perspective and is limited to up to specific product releases cited in this section.

For Cisco MSE compatibility with product releases not cited in this section, see the compatibility matrix for the relevant product. For example, for the most recent compatibility information between Cisco CMX and Cisco MSE, see the [Cisco CMX Compatibility Matrix, on page 122](#).

For Cisco MSE compatibility with Cisco Prime Infrastructure releases, see the applicable [Cisco Prime Infrastructure release notes](#).

**General:**

- ISE 2.x or ISE 1.4 only works with Cisco MSE Release 8.0 or earlier.
- Cisco MSE release 7.5 or later is not bundled with AeroScout CLE. However, AeroScout CLE is compatible with Cisco MSE Release 7.5 or later, which uses the API interface.
- This compatibility matrix lists only the compatibility information of Cisco MSE with other Cisco wireless products. This matrix does not reflect compatibility information between Cisco Controller and Cisco Prime Infrastructure or Cisco NCS. For compatibility information about Cisco Prime Infrastructure with Cisco Controller and other wireless products, see the *Cisco Prime Infrastructure Release Notes*.
- For information about the Cisco Connected Mobile Experiences (CMX) 10.x solution compatibility matrix, see the [Cisco Connected Mobile Experiences Compatibility Matrix](#), on page 119 section.

**Cisco Prime Infrastructure**

- Cisco MSE Release 8.0.140.x or later is compatible with Cisco Prime Infrastructure Releases 3.1.7, 3.1.6, 3.1.5, 3.1.3, 3.1.1, 3.0.3.1, and 2.2.3.5. If you encounter reachability issues with the Cisco MSE, upgrade to Prime Infrastructure Release 3.1.3. (CSCuz19013)
- For Cisco MSE Release 8.0.x HA and Controller Release 8.0 or later, Prime Infrastructure Release 2.2.x is compatible.
- Cisco MSE 3365 supports Cisco Prime Infrastructure 2.1.1 or later. Cisco MSE 3365 does not support Cisco Prime Infrastructure 2.1.0.

**Cisco Access Points**

- Cisco MSE Release 8.0.140.9 and later includes wIPS and CAS support for the Cisco Aironet 1800, 2800, 3800, and 4800 series.

**Catalyst Switches**

- Cisco MSE platforms running Cisco MSE Release 8.x are not compatible with the following Cisco switch platforms:
  - Cisco Catalyst 2960-24TT switch running Cisco Release 15.0(2)SE11
  - Cisco Catalyst 2960-48-PST-L switch running Cisco Release 15.0(2)SE11
  - Cisco Catalyst 2960X-24PS-L switch running Cisco Release 15.2(2)E7
  - Cisco Catalyst 3650-24PS switch running Cisco Release 16.3.5b
  - Cisco Catalyst 3560-24PS switch running Cisco Release 12.2(55)SE11
  - Cisco Catalyst 3850-24XS switch running Cisco Release 16.3.5.b
  - Cisco Nexus 5596UP switch running Cisco Release 7.1(4)N1(1)

**Cisco MSE Compatibility Matrix for Software Versions 7.5.x through 8.x**

Information in this section cites cross-platform compatibility testing performed from only the Cisco MSE perspective and is limited to up to specific product releases cited in this section.



For Cisco MSE compatibility with product releases not cited in this section, see the compatibility matrix for the relevant product. For example, for the most recent compatibility information between Cisco CMX and Cisco MSE, see the [Cisco CMX Compatibility Matrix, on page 122](#) section.

For Cisco MSE compatibility with Cisco Prime Infrastructure releases, see the applicable [Cisco Prime Infrastructure release notes](#).

Table 16: Cisco MSE Compatibility Matrix for Software Versions 7.5.x through 8.x

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.150.x	8.0.150.x	8.0.150.x	3.10.x		3.7.x	
			3.9.1		3.6.x	
			3.8.x		3.3.5	
			3.7.x		3.3.4	
			3.6.x		3.3.3	
			3.5.x		3.3.2	
			3.4.x		3.3.0	
			3.3.1		3.2.3	
			3.3		3.2.2	
			3.2.2		3.2.0	
			3.2.1		3.1.6	
			3.2			
			3.1.7			
			3.1.6			
			3.1.5			
			3.1.3			
			3.1			
			3.0.3			
			2.2.3			

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.5.12x.0		Cisco MSE wIPS Release 8.0.150.x provides limited support for Cisco AireOS Releases 8.6, 8.7, 8.8, 8.9, and 8.10.  Supported signatures are: <ul style="list-style-type: none"> <li>• AirDrop Session detected</li> <li>• Airsnarf attack</li> <li>• Bad EAP-TLS frames</li> <li>• Beacon Fuzzed Frame Detected</li> <li>• Brute Force Hidden SSID</li> <li>• Dictionary attack on EAP methods</li> <li>• DoS: Association table overflow</li> <li>• DoS: Authentication flood</li> <li>• DoS: Authentication-failure attack</li> <li>• DoS: Beacon flood</li> <li>• DoS: De-Auth broadcast flood</li> <li>• DoS: Dis-Assoc broadcast flood</li> <li>• DoS: Dis-Assoc flood</li> <li>• DoS: Probe request flood</li> <li>• DoS: Re-association request flood</li> </ul>
				8.5.11x.0		
				8.5.10x.0		
				8.4.10x.0		
				8.3.14x.0		
				8.3.13x.0		
				8.3.12x.0		
				8.3.112.0		
				8.3.111.0		
				8.3.102.0		
				8.2.16x.0		
				8.2.160.0		
				8.2.151.0		
				8.2.141.0		
				8.2.130.0		
				8.2.121.0		
				8.2.111.0		
				8.2.110.0		
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0*		
				7.6.120.0*		
				7.6.110.0*		
				7.6.100.0*		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.5.102.0**		• DoS: RF jamming
				7.4.121.0**		• DoS:
				7.4.110.0**		Unauthenticated association
				7.4.100.60**		• Hotspotter tool detected
				7.4.100.0**		• Identical send and receive address
				7.3.112.0**		• Illegal Beacon
				7.3.101.0**		• Improper broadcast frames
				7.2.111.3**		• Malformed 802.11 packets detected
				7.2.110.0**		
				7.2.103.0**		
				7.0.240.0**		
				7.0.235.3**		
				7.0.235.0**		* For FIPS compliance, Cisco MSE Release 8.0 works with Cisco Prime Infrastructure 2.2, Cisco controller 8.0.100.0, and Converged Access 3.6.0.
				7.0.230.0**		
				7.1.91.0**		** The Cisco MSE Release 8.0 wIPS profile cannot be applied to Cisco controller release 7.5 or prior using Cisco Prime Infrastructure 2.2
				7.0.220.0**		*** If you are you are running Analytics and Context Aware Service (Location Service) on different machines and using Cisco Prime Infrastructure 1.4, then additional setup is required. You can download the Setup script from this location.
				7.0.116.0**		
				7.0.98.218**		
				7.0.98.0**		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.140.x	8.0.140.x	8.0.140.x	3.4.x 3.3.1 3.3 3.2.2 3.2.1 3.2 3.1.7 3.1.6 3.1.5 3.1.3 3.1 3.0.3 2.2.3		3.7.x 3.6.x 3.3.5 3.3.4 3.3.3 3.3.2 3.3.0 3.2.3 3.2.2 3.2.0 3.1.6	<p>* For FIPS compliance, Cisco MSE Release 8.0 works with Cisco Prime Infrastructure 2.2, Cisco controller 8.0.100.0, and Converged Access 3.6.0.</p> <p>** The Cisco MSE Release 8.0 wIPS profile cannot be applied to Cisco controller release 7.5 or prior using Cisco Prime Infrastructure 2.2</p> <p>*** If you are you are running Analytics and Context Aware Service (Location Service) on different machines and using Cisco Prime Infrastructure 1.4, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.5.12x.0		
				8.5.11x.0		
				8.5.10x.0		
				8.4.10x.0		
				8.3.14x.0		
				8.3.13x.0		
				8.3.12x.0		
				8.3.112.0		
				8.3.111.0		
				8.3.102.0		
				8.2.16x.0		
				8.2.160.0		
				8.2.151.0		
				8.2.141.0		
				8.2.130.0		
				8.2.121.0		
				8.2.111.0		
				8.2.110.0		
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0*		
				7.6.120.0*		
				7.6.110.0*		
				7.6.100.0*		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.5.102.0**		
				7.4.121.0**		
				7.4.110.0**		
				7.4.100.60**		
				7.4.100.0**		
				7.3.112.0**		
				7.3.101.0**		
				7.2.111.3**		
				7.2.110.0**		
				7.2.103.0**		
				7.0.240.0**		
				7.0.235.3**		
				7.0.235.0**		
				7.0.230.0**		
				7.1.91.0**		
				7.0.220.0**		
				7.0.116.0**		
				7.0.98.218**		
				7.0.98.0**		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.130.0	8.0.130.0	8.0.130.0	3.1 3.0.1 3.0 2.2 and later 1.4***		3.7.x 3.6.x 3.3.5 3.3.4 3.3.3 3.3.2 3.2.3 3.2.2	<p>* For FIPS compliance, Cisco MSE Release 8.0 works with Cisco Prime Infrastructure 2.2, Cisco controller 8.0.100.0, and Converged Access 3.6.0.</p> <p>** The Cisco MSE Release 8.0 wIPS44 profile cannot be applied to Cisco controller release 7.5 or prior using Cisco Prime Infrastructure 2.2</p> <p>*** If you are you are running Analytics and Context Aware Service (Location Service) on different machines and using Cisco Prime Infrastructure 1.4, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .</p>



MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.3.13x.0		
				8.3.111.0		
				8.3.102.0		
				8.2.16x.0		
				8.2.151.0		
				8.2.141.0		
				8.2.130.0		
				8.2.121.0		
				8.2.111.0		
				8.2.110.0		
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0*		
				7.6.120.0*		
				7.6.110.0*		
				7.6.100.0*		
				7.5.102.0**		
				7.4.121.0**		
				7.4.110.0**		
				7.4.100.60**		
				7.4.100.0**		
				7.3.112.0**		
				7.3.101.0**		
				7.2.111.3**		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.2.110.0**		
				7.2.103.0**		
				7.0.240.0**		
				7.0.235.3**		
				7.0.235.0**		
				7.0.230.0**		
				7.1.91.0**		
				7.0.220.0**		
				7.0.116.0**		
				7.0.98.218**		
				7.0.98.0**		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.120.7	8.0.120.7	8.0.120.7	3.0.1 3.0 2.2.2*** 2.2.1 2.2 2.1.2*** 2.1.1*** 1.4*****		3.7.x 3.6.x 3.3.5 3.3.4 3.3.3 3.3.2 3.2.3 3.2.2	<p>* For FIPS compliance, Cisco MSE Release 8.0 works with Cisco PI 2.2, Cisco controller 8.0.100.0, and Converged Access 3.6.0.</p> <p>****With Cisco MSE Release 8.0 wIPS feature: If you are using Cisco Prime Infrastructure 2.2 or later releases with Cisco controller 7.5 or earlier releases, use Cisco MSE Release 8.0.120 or later.</p> <p>***** If you are you are running Analytics and Context Aware Service (Location Service) on different machines and using Cisco PI 1.4 release, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0		
				7.6.120.0		
				7.6.110.0*		
				7.6.100.0*		
				7.5.102.0****		
				7.4.150.0****		
				7.4.140.0****		
				7.4.130.0****		
				7.4.121.0****		
				7.4.110.0****		
				7.4.100.60****		
				7.4.100.0****		
				7.3.112.0****		
				7.3.101.0****		
				7.2.111.3****		
				7.2.110.0****		
				7.2.103.0****		
				7.0.240.0****		
				7.0.235.3****		
				7.0.235.0****		
				7.0.230.0****		
				7.1.91.0****		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.0.220.0**** 7.0.116.0**** 7.0.98.218**** 7.0.98.0****		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.120.0	8.0.120.0	8.0.120.0	3.0.1 3.0 2.2.2*** 2.2.1 2.2 2.1.2*** 2.1.1*** 1.4*****		3.7.x 3.6.x 3.3.5 3.3.4 3.3.3 3.3.2 3.2.3 3.2.2	<p>* For FIPS compliance, Cisco MSE Release 8.0 works with Cisco PI 2.2, Cisco controller 8.0.100.0, and Converged Access 3.6.0.</p> <p>****With Cisco MSE Release 8.0 wIPS feature: If you are using Cisco Prime Infrastructure 2.2 or later releases with Cisco controller 7.5 or earlier releases, use Cisco MSE Release 8.0.120 or later.</p> <p>***** If you are you are running Analytics and Context Aware Service (Location Service) on different machines and using Cisco PI 1.4 release, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0		
				7.6.120.0		
				7.6.110.0*		
				7.6.100.0*		
				7.5.102.0****		
				7.4.150.0****		
				7.4.140.0****		
				7.4.130.0****		
				7.4.121.0****		
				7.4.110.0****		
				7.4.100.60****		
				7.4.100.0****		
				7.3.112.0****		
				7.3.101.0****		
				7.2.111.3****		
				7.2.110.0****		
				7.2.103.0****		
				7.0.240.0****		
				7.0.235.3****		
				7.0.235.0****		
				7.0.230.0****		
				7.1.91.0****		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.0.220.0**** 7.0.116.0**** 7.0.98.218**** 7.0.98.0****		



MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.110.0	—	8.0.110.0	2.2.1 2.2 2.1.2*** 2.1.1*** 2.1*** 2.0*** 1.4*****		3.7.x 3.6.x 3.3.x 3.2.x	<p>* For FIPS compliance, Cisco MSE Release 8.0 works with PI 2.2, Cisco controller 8.0.100.0, and Converged access 3.6.0.</p> <p>***While using PI 2.1.1 and 2.1.2, the Cisco MSE Release 8.0 wIPS will have Cisco MSE Release 7.4 feature parity.</p> <p>****With Cisco MSE Release 8.0 wIPS feature: If you are using Cisco Prime Infrastructure 2.2 or later releases with Cisco controller 7.5 or earlier releases, use Cisco MSE Release 8.0.120 or later.</p> <p>****With Cisco MSE Release 8.0 wIPS feature: If you are using Cisco Prime Infrastructure 2.2 or later releases with Cisco controller 7.5 or earlier releases, use Cisco MSE Release 8.0.120 or later.</p> <p>***** If you are you are running Analytics and Location services on different machines and using Cisco Prime Infrastructure 1.4 Version, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				8.1.131.0		
				8.1.122.0		
				8.1.111.0		
				8.1.102.0		
				8.0.15x.0		
				8.0.140.0		
				8.0.13x.0		
				8.0.121.0		
				8.0.120.0		
				8.0.115.0		
				8.0.110.0		
				8.0.100.0		
				7.6.130.0		
				7.6.120.0		
				7.6.110.0*		
				7.6.100.0*		
				7.5.102.0****		
				7.4.150.0****		
				7.4.140.0****		
				7.4.130.0****		
				7.4.121.0****		
				7.4.110.0****		
				7.4.100.60****		
				7.4.100.0****		
				7.3.112.0****		
				7.3.101.0****		
				7.2.111.3****		
				7.2.110.0****		
				7.2.103.0****		
				7.0.240.0****		
				7.0.235.3****		
				7.0.235.0****		
				7.0.230.0****		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
				7.1.91.0**** 7.0.220.0**** 7.0.116.0**** 7.0.98.218**** 7.0.98.0**** 7.0.250.0 7.0.251.0 7.0.252.0		

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
8.0.100.0*	—	8.0.100.0	2.2.1 2.2 2.1.2 2.1.1*** 2.1 2.0 1.4*****	8.1.131.0 8.1.122.0 8.1.111.0 8.1.102.0 8.0.100.0 7.6.130.0 7.6.120.0 7.6.110.0* 7.6.100.0* 7.5.102.0***** 7.4.150.0***** 7.4.140.0***** 7.4.130.0***** 7.4.121.0***** 7.4.110.0***** 7.4.100.60***** 7.4.100.0***** 7.3.112.0***** 7.3.101.0***** 7.2.111.3***** 7.2.110.0***** 7.2.103.0***** 7.0.240.0***** 7.0.235.3***** 7.0.235.0***** 7.0.230.0***** 7.1.91.0***** 7.0.220.0***** 7.0.116.0***** 7.0.98.218***** 7.0.98.0*****	3.7.x 3.6.x 3.3.5 3.3.4 3.3.3 3.3.2 3.2.3 3.2.2	* For FIPS compliance, Cisco MSE Release 8.0 works with PI 2.2, Cisco controller 8.0.100.0, and Converged access 3.6.0.  *** While using PI 2.1.1, the Cisco MSE Release 8.0 wIPS will have Cisco MSE Release 7.4 feature parity.  ****With Cisco MSE Release 8.0 wIPS feature: If you are using Cisco Prime Infrastructure 2.2 or later releases with Cisco controller 7.5 or earlier releases, use Cisco MSE Release 8.0.120 or later.  ***** If you are you are running Analytics and Location services on different machines and using Cisco Prime Infrastructure 1.4 Version, then additional setup is required. You can download the <a href="#">Setup script</a> from this location .

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.6.120.0	—	7.6.120.0	2.2.1 2.2 2.1.2 2.1.1** 2.1 2.0 1.4.2	7.6.120.0 7.6.110.0* 7.6.100.0* 7.5.102.0 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	—	<p>**Prime Infrastructure 2.1.1 allows you to manage Cisco MSE Releases 7.5.102.101 and 7.6.120.0 with feature compatibility of Cisco MSE Release 7.4.121.0. Prime Infrastructure 2.1.1 does not support any new features introduced in Cisco MSE Releases 7.5.102.101 and 7.6.120.0.</p> <p><b>Note:</b> For PI 2.1.1 to work with Cisco MSE Release 7.6, you need to install a patch for Cisco bug Id CSCup93101. Contact Cisco TAC for a patch.</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.6.132.0	—	7.6.132.0	2.2.1 2.2 2.1.2 2.1.1** 2.1 2.0 1.4.2	7.6.130.0 7.6.120.0 7.6.110.0* 7.6.100.0* 7.5.102.0 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	—	<p>**Prime Infrastructure 2.1.1 allows you to manage Cisco MSE Releases 7.5.102.101 and 7.6.120.0 with feature compatibility of Cisco MSE Release 7.4.121.0. Prime Infrastructure 2.1.1 does not support any new features introduced in Cisco MSE Releases 7.5.102.101 and 7.6.120.0.</p> <p><b>Note:</b> For PI 2.1.1 to work with Cisco MSE Release 7.6, you need to install a patch for Cisco bug Id CSCup93101. Contact Cisco TAC for a patch.</p>

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.6.100.0	—	7.6.100.0	2.2.1 2.2 2.1.2 2.1.1 2.1 2.0 Update 1 for 1.4.0.45* Update 2 for 1.4.0.45**	7.6.110.0* 7.6.100.0* 7.5.102.0 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	—	*The Update 1 for Cisco Prime Infrastructure 1.4.0.45 enables you to manage Cisco controller 7.6.x with the features of Cisco controller 7.5.102.0 and earlier releases. This release does not support any new features of Cisco controller 7.6.x including the new access point platforms.  **The Update 2 for Cisco Prime Infrastructure 1.4.0.45 enables you to manage Cisco controller 7.6.x with the features of Cisco controller 7.5.102.0 and earlier releases. This release does not support any new features of Cisco controller 7.6.x. However, this release supports two new AP platforms—Cisco 702w and Cisco 2700.

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.6.100.0	—	7.6.100.0	2.2.1 2.2 2.1.2 2.1.1 2.1 2.0*	7.6.110.0** 7.6.100.0** 7.5.102.0** 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	3.2.2** 3.3.2**	<p>*Cisco Prime Infrastructure 2.0 enables you to manage Cisco controller 7.5.102.0 with the features of Cisco controller 7.4.110.0 and earlier releases. Prime Infrastructure 2.0 does not support any features that are introduced in Cisco controller 7.5.102.0 or later releases including the new access point platforms.</p> <p>**Supports 7.4 MSE feature parity—CAS, Cisco MSE Release 8.0 wIPS, and CMX Analytics service.</p> <p><b>Note:</b> Cisco MSE Release 8.0 wIPS profile cannot be pushed to Cisco controller Version 7.5 or prior using the Prime Infrastructure 1.4.x or 2.x with Cisco MSE Release 7.6.</p>



MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.5.102.101	—	7.5.102.101	2.2.1 2.2 2.1.2 2.1.1 2.1 2.0 Update 1 for 1.4.0.45 1.4.0.45	7.5.102.0 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	—	—

MSE 3355	MSE 3365	MSE Virtual Appliance	Prime Infrastructure	Controller	Converged Access	Remarks
7.5.102.101	—	7.5.102.101	2.2.1 2.2 2.1.2 2.1.1 2.1 2.0*	7.5.102.0 7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	3.2.2** 3.3.2**	*Cisco Prime Infrastructure 2.0 enables you to manage Cisco controller 7.5.102.0 with the features of Cisco controller 7.4.110.0 and earlier releases. Prime Infrastructure 2.0 does not support any features that are introduced in Cisco controller 7.5.102.0 or later releases including the new access point platforms.  **Supports 7.4 MSE feature parity—CAS, Cisco MSE Release 8.0 wIPS, and CMX Analytics service.

## Cisco MSE Compatibility Matrix for Legacy Software Versions

Information in this section cites cross-platform compatibility testing performed from only the Cisco MSE perspective and is limited to up to specific product releases cited in this section.

For Cisco MSE compatibility with product releases not cited in this section, see the compatibility matrix for the relevant product. For example, for the most recent compatibility information between Cisco CMX and Cisco MSE, see the [Cisco CMX Compatibility Matrix, on page 122](#).

For Cisco MSE compatibility with Cisco Prime Infrastructure releases, see the applicable Cisco Prime Infrastructure release notes at:

<https://www.cisco.com/c/en/us/support/cloud-systems-management/prime-infrastructure/products-release-notes-list.html>

Table 17: Cisco MSE Compatibility Matrix—Legacy Software Versions

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.4.121.0	—	7.4.121.0	4.5.2.16 4.4.2.11	—	7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	2.0 Update 1 for 1.4.0.45 1.4.0.45 Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.4.110.0	—	7.4.110.0	4.4.2.11	—	7.4.110.0 7.4.100.60 7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	2.0 Update 1 for 1.4.0.45 1.4.0.45 Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20
7.4.100.0	—	7.4.100.0	442114427	—	7.4.100.0 7.3.112.0 7.3.101.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 1 for 1.4.0.45 1.4.0.45 Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.3.101.0	7.3.101.0	7.3.101.0	4.4.2.4	—	7.4.150.0 7.4.140.0 7.4.130.0 7.4.121.0 7.4.110.0 7.4.100.60 7.4.100.0 7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12
7.2.110.0	7.2.110.0	7.2.110.0	4.4.2.4	—	7.2.111.3 7.2.110.0 7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.2.103.0	7.2.103.0	7.2.103.0	4.4.1.4	—	7.2.103.0 7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.124 1.1.0.58
7.0.240.0	7.0.240.0	—	4.3.1.10	7.0.240.0	7.0.240.0 7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29
7.0.230.0	7.0.230.0	—	4.3.1.19	7.0.230.0	7.0.235.3 7.0.235.0 7.0.230.0 7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.0.220.0	7.0.220.0	—	4.3.1.19	7.0.220.0	7.1.91.0 7.0.220.0 7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29 1.0.1.4
70201204	70201204	—	4.2.4.4	7.0.172.0	7.0.116.0 7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29 1.0.1.4 1.0.0.96
7.0.112.0	7.0.112.0	—	4.2.4.4	7.0.164.3 7.0.164.0	7.0.98.218 7.0.98.0	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29 1.0.1.4 1.0.0.96

MSE 3355	MSE 3350	MSE Virtual Appliance	AeroScout CLE	WCS	Controller	Prime Infrastructure / NCS
7.0.105.0	7.0.105.0	—	4.2.4.4	7.0.164.3	7.0.98.218	Update 4 for 1.3.0.20 Update 1 for 1.3.0.20 1.3.0.20 1.2.1.12 1.1.1.24 1.1.0.58 1.0.2.29 1.0.1.4 1.0.0.96

## Cisco Mobility Express Solution Compatibility Matrix

This section contains compatibility information about the Cisco Mobility Express Solution.




---

**Note** The Cisco Mobility Express solution is not compatible with other Cisco Wireless LAN Controller deployments and Cisco Network Assistant.

---



Table 18: Mobility Express Software Compatibility Matrix

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.10.190.0	153(3)JK10	APs with integrated controller functionality:  Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, 3800 series, 4800 series, Cisco 6300 Series Embedded Services, and Cisco Catalyst IW6300 Heavy Duty Series	10.6.3-70	2.8	3.9.1	—
8.10.185.0	153(3)JK9			2.7	3.9	—
8.10.183.0	153(3)JK8b			3.8.1	—	
8.10.182.0	153(3)JK8a			3.8	—	
8.10.181.0	153(3)JK8			—		
8.10.171.0	153(3)JK7			—		
8.10.162.0	153(3)JK6			—		
8.10.151.0	153(3)JK5			10.6.3-70	—	
8.10.142.0	153(3)JK4			10.6.3-70	—	
8.10.130.0	153(3)JK3	APs without integrated controller functionality:  Cisco Aironet 700i, 700w, 1700 series, 1810i, 1810w, 2700 series, 3700 series, Industrial Wireless 3702, Cisco Catalyst 9100	10.6.3-70	2.6 2.4 2.3 2.2 2.1	3.8.1 3.8	—

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.10.122.0	153(3)JK2a	APs with integrated controller functionality:	10.6.3-70	2.6	3.7	—
8.10.121.0	153(3)JK2			2.4		
8.10.113.0	153(3)JK1t			2.3		
8.10.112.0	153(3)JK1			2.2		
8.10.105.0	15.3(3)JK	Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, 3800 series, 4800 series, Cisco 6300 Series Embedded Services, and Cisco Catalyst IW6300 Heavy Duty Series		2.1		
		APs without integrated controller functionality:  Cisco Aironet 700i, 700w, 1700 series, 1810i, 1810w, 2700 series, 3700 series, Industrial Wireless 3702, Cisco Catalyst 9100				

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.9.111.0 8.9.100.0	15.3(3)JI1 15.3(3)JI	<p>APs with integrated controller functionality:</p> <p>Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, 3800 series, and 4800 series.*</p> <p>APs without integrated controller functionality:</p> <p>Cisco Aironet 700i, 700w, 1700 series, 1810i, 1810w, 2700 series, 3700 series, Industrial Wireless 3702, Cisco Catalyst 9100 (with Release 8.9.111.0)</p>	10.2.2 and later	2.6 2.4 2.3 2.2 2.1	3.7 3.6	
8.8.130.0 8.8.125.0 8.8.120.0 8.8.111.0 8.8.100.0	15.3(3)JI6 15.3(3)JI5 15.3(3)JI4 15.3(3)JI3 15.3(3)JI1	<p>APs with integrated controller functionality:</p> <p>Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, 3800 series, and 4800 series.*</p> <p>APs without integrated controller functionality:</p> <p>Cisco Aironet 700i, 700w, 1700 series, 1810w, 2700 series, 3700 series</p>	10.2.2 and later	2.2 2.1	3.5 3.4 3.3 3.2 3.1.6 3.1.5	—

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.7.102.0	15.3(3)JH	<p>APs with integrated controller functionality:</p> <p>Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, and 3800 series.*</p> <p>APs without integrated controller functionality:</p> <p>Cisco Aironet 700i, 700w, 1700 series, 1810w, 2700 series, 3700 series</p>	10.2.2 and later	2.2 2.1	3.4 3.3 3.2 3.1.6 3.1.5	—
8.6.101.0	15.3(3)JG1	<p>APs with integrated controller functionality:</p> <p>Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, and 3800 series.*</p> <p>APs without integrated controller functionality:</p> <p>Cisco Aironet 700i, 700w, 1700 series, 1810w, 2700 series, 3700 series</p>	10.2.2 and later	2.2 2.1	3.4 3.3 3.2 3.1.6 3.1.5	—

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.5.182.0	153(3)JF15	<p>APs with integrated controller functionality:</p> <p>Cisco Aironet 1540 series, 1560 series, 1815i, 1815m, 1815w, 1830 series, 1850 series, 2800 series, and 3800 series.*</p> <p>APs without integrated controller functionality:</p> <p>Cisco Aironet 700i, 700w, 1600 series, 1700 series, 1810w series, 2600 series, 2700 series, 3500 series, 3600 series, 3700 series</p>	10.2.2 and later	2.2 2.1	3.9.1 3.9 3.8.1 3.8 3.7.1 3.7 3.6 3.5	*Cisco Aironet 1560 series, 1815i, and 1815w AP platforms are not supported on Cisco Prime Infrastructure.
8.5.17x.0	153(3)JF14					
8.5.16x.0	153(3)JF12 153(3)JF12 153(3)JF11					
8.5.151.0	153(3)JF10					
8.5.140.0	153(3)JF9					
8.5.13x.0	153(3)JF8 153(3)JF7					
8.5.120.0	153(3)JF5					
8.5.110.0	153(3)JF4					
8.5.10x.0	153(3)JF1 15.3(3)JF					
8.4.100.0	153(3)JE					

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.3.130.0	153(3)ID7, 153(3)DA7	APs with integrated controller functionality:	—	—	3.2	—
8.3.122.0	153(3)ID6	<ul style="list-style-type: none"> <li>• Cisco Aironet 1560, 1830, 1850, 2800, and 3800 series</li> </ul>	—	—	3.1.6	—
8.3.121.0	153(3)ID5				3.1.5	
8.3.112.0	153(3)ID4				APs without integrated controller functionality:	
		<ul style="list-style-type: none"> <li>• Cisco Aironet 700i, 700w, 1600 series, 1700 series, 1810w series, 2600 series, 2700 series, 3500 series, 3600 series, 3700 series</li> </ul>				
8.3.102.0	153(3)JD	APs with integrated controller functionality:	—	—	3.2	—
		<ul style="list-style-type: none"> <li>• Cisco Aironet 1830, 1850, 2800, and 3800 series</li> </ul>			3.1.6	
		APs without integrated controller functionality:			3.1.5	
		<ul style="list-style-type: none"> <li>• Cisco Aironet 700i, 700w, 1600 series, 1700 series, 1810w series, 2600 series, 2700 series, 3500 series, 3600 series, 3700 series</li> </ul>			3.1.4	

Cisco Mobility Express Solution	Access Point Software	Access Point Platforms	Cisco CMX	Cisco ISE	Cisco Prime Infrastructure	Remarks
8.2.100.0	15.3(3)JC	APs with integrated controller functionality:	—	1.4	1.4 1.3	—
8.1.122.0	15.3(3)JBB5	<ul style="list-style-type: none"> <li>Cisco Aironet 1850 series, 1830 series</li> </ul> APs without integrated controller functionality: <ul style="list-style-type: none"> <li>Cisco Aironet 700i, 700w, 1600 series, 1700 series, 2600 series, 2700 series, 3500 series, 3600 series, 3700 series</li> </ul>			1.3	—

## Cisco Support Community

Cisco Support Community is a forum for you to ask and answer questions, share suggestions, and collaborate with your peers. Join the forum at: <https://supportforums.cisco.com/index.jspa>.

## Communications, Services, and Additional Information

- To receive timely, relevant information from Cisco, sign up at [Cisco Profile Manager](#).
- To get the business impact you're looking for with the technologies that matter, visit [Cisco Services](#).
- To submit a service request, visit [Cisco Support](#).
- To discover and browse secure, validated enterprise-class apps, products, solutions, and services, visit [Cisco DevNet](#).
- To obtain general networking, training, and certification titles, visit [Cisco Press](#).
- To find warranty information for a specific product or product family, access [Cisco Warranty Finder](#).

## Cisco Bug Search Tool

[Cisco Bug Search Tool](#) (BST) is a gateway to the Cisco bug-tracking system, which maintains a comprehensive list of defects and vulnerabilities in Cisco products and software. The BST provides you with detailed defect information about your products and software.

## Documentation Feedback

To provide feedback about Cisco technical documentation, use the feedback form available in the right pane of every online document.



---

Cisco and the Cisco logo are trademarks or registered trademarks of Cisco and/or its affiliates in the U.S. and other countries. To view a list of Cisco trademarks, go to this URL: <https://www.cisco.com/c/en/us/about/legal/trademarks.html>. Third-party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1721R)

© 2017–2023 Cisco Systems, Inc. All rights reserved.