

OVERVIEW



1. Power button	4. USB-C (Hi-Speed USB), with charging
2. Card slot	5. Headphone / microphone combo jack (3.5mm)
3. Volume buttons	6. Pogo pin connector (3-point)

Notes:

- 3-point pogo pin connector is used to connect Lenovo Folio Keyboard for Tab K11 Gen 2. Keyboard availability varies by country/region.
- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)

PERFORMANCE

Processor

Processor

Processor Name	Cores	Max Frequency	Processor Graphics
MediaTek Dimensity 6300	Octa-core 2x A76 + 6x A55	A76@2.4 GHz A55@2.0 GHz	Arm Mali-G57 MC2 GPU

Operating System

Operating System^[1]

Android™ 15 or later

Notes:

[1] For latest operating system and security patches deliver plan, please visit <https://support.lenovo.com/solutions/ht501098>.

Graphics

Graphics

Arm Mali-G57 MC2 GPU

Memory

Max Memory

- 4GB soldered memory, not upgradable
- 8GB soldered memory, not upgradable

Memory Type

LPDDR4x

Storage

Max Storage Support**

- 128GB UFS 2.2 on systemboard
- 256GB UFS 2.2 on systemboard
- microSD card, supports up to 2TB (exFAT)

Removable Storage

Card Reader**

- Nano-SIM + microSD card slot (WWAN models)
- microSD card slot (WLAN models)

Multi-Media

Speakers

4 speakers, optimized with Dolby Atmos®

Microphone

Single microphone

Camera

Front 8.0MP, fixed focus, face unlock
Rear 13.0MP, autofocus, with flashlight

VoiceCall

- Voice call^[1]
- No support

Notes:

[1] Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

Sensor

Vibration Motor

- Vibration Motor^[1]
- No support

Sensors

- Accelerometer sensor
- Ambient light sensor (ALS)
- Hall sensor

Notes:

[1] Only available for Taiwan models

Battery

Battery

7040mAh (typical) Rechargeable Li-ion Battery

Max Battery Life^[1]

Video streaming: 12 hr of YouTube streaming
Web browsing: 14 hr of Chrome browsing

Notes:

[1] All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary depending on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

Power Adapter

Power Adapter

10V/2A (20W) AC adapter, 100-240V, 50-60Hz

DESIGN

Display

Display^[1]**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Key Features
11"	2.5K (2560x1600)	Multi-touch	IPS	500nits	Anti-fingerprint, Paper-like Anti-glare	16:10	1500:1	72% NTSC	90Hz	TÜV Rheinland® Reflection Free certified
11"	2.5K (2560x1600)	Multi-touch	IPS	500nits	Anti-fingerprint	16:10	1500:1	72% NTSC	90Hz	-

Touchscreen

In-cell multi-touch, supports 10-point touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Pen**

- Lenovo® Tab Pen, 4096 levels of pressure sensitivity, tilt detection, palm rejection
- Lenovo® Tab Pen Plus, remote control, 4096 levels of pressure sensitivity, tilt detection, palm rejection
- No pen (purchase separately)^[1]

Notes:

[1] For details upon pen compatibility, please check [Here](#). Pen availability may vary by country / region.

Mechanical

Dimensions (WxDxH)^{[1][2]}

254.59 x 166.15 x 6.99 mm (10.02 x 6.54 x 0.28 inches)

Weight^[3]

480 g ± 10 g (1.06 lbs ± 0.02 lbs)

Case Color**

- Luna grey
- Polar blue

Case Material

Metal

Buttons

- Power button
- Volume buttons

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The height is 8.29 mm (0.33 inches) with the camera bump.

[3] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth®

Wi-Fi® 5, 802.11ac 1x1 Wi-Fi® + Bluetooth® 5.2

WWAN

- 5G Sub-6 GHz
- No support

SIM Card

- Dual SIM (Nano-SIM + eSIM)
- No support

Cellular Bands^[1]

GSM: 850/900/1800/1900Mhz

UMTS: B1/2/4/5/6/8/19

FDD LTE: B1/2/3/4/5/7/8/12/13/18/19/20/25/26/28(a+b)/66

TDD LTE: B38/40/41

NR Sub-6: n1/2/3/5/7/8/20/26/28/38/40/41/66/71/77/78

Wi-Fi® Direct

Support

Wi-Fi® Display

Support

Location Services

Models	Location
WLAN models	GPS + GLONASS + Galileo
WWAN models	GPS + GLONASS + Galileo + A-GPS

Notes:

[1] For WWAN models

Ports

Standard Ports^[1]

- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Headphone / microphone combo jack (3.5mm)

- 1x Card slot

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

SERVICE

Warranty

Base Warranty^[1]**

- 1-year carry-in service
- 1-year mail-in service
- 1-year courier service
- 2-year (2-yr battery) courier or carry-in service

Notes:

[1] For warranty upgrade service, please go to <https://smartfind.lenovo.com/services>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

ACCESSORIES

Bundled Accessories

Bundled Accessories*^[1]**

- Film
- Folio case
- Lenovo® Folio Keyboard
- Lenovo® Tab Pen
- Lenovo® Tab Pen Plus
- None

Notes:

[1] For more compatible accessories, please click [Here](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature

Operating: 0°C (32°F) to 40°C (104°F)

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- Energy rating E (TB336FU). View details by EPREL registration number [2303451](#).^[2]
- Energy rating E (TB336ZU). View details by EPREL registration number [2303452](#).^[3]
- ENERGY STAR® 9.0 (only available for TB336FU)
- ErP Lot 6/26
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2], [3] Energy rating by EPREL is optional and only available in selected countries.

Other Certifications

Dust and Water Resistant

IP52

Other Certifications

- (Optional) TÜV Rheinland® Reflection Free
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

SOFTWARE

Preinstalled Software

Preinstalled Software^[1]

- Assistant
- Calculator
- Camera
- Chrome
- Clock
- Contacts
- Drive
- Entertainment Space
- Files
- Fitbit
- Find my device
- Gboard
- Gmail
- Google
- Google One
- Google TV
- Kids Space
- Lenovo® Vantage
- Maps
- Meet
- Messages
- MyScript® Calculator
- Nebo®
- News
- Notepad
- Play Books
- Play Games
- Phone^[2]
- Photos
- Play Store
- Recorder
- Smart Connect
- Squid
- Weather
- YouTube
- YouTube Kids
- YouTube Music

Notes:

[1] Actual application availability varies by country/region.

[2] For WWAN models, except TB336ZA models.

Additional Software

Additional Software^[1]

- Android™ Enterprise Recommended Certification
- Android™ zero-touch enrollment
- Commercial grade SW with limited monetization content^[2]
- Vantage Pro Software Solution Package:
 - Vantage Pro Customization (cloud-based Customization & Configuration)
 - Vantage Pro SDK (Device Management via SDK)

- Vantage Pro FOTA (Firmware Update Control Service)
- Security Patch Extension Service

Notes:

[1] For more information related to Lenovo® Android™ Tablet Commercial Solutions, please visit [Here](#). License/activation fees may be applicable.

[2] Google Mobile Services (GMS) contents are allowed; manufacturer related monetization and push contents are limited.

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

