

OVERVIEW



1. 3x USB 3.2 Gen 1	7. Microphone mute button
2. USB-C 3.2 Gen 2 (data transfer, 15W charging)	8. PC / monitor mode switch
3. Ethernet (RJ-45)	9. 3x USB 3.2 Gen 2
4. HDMI in/out combo port	10. Headphone / microphone combo jack (3.5mm)
5. DisplayPort 1.4	11. Card reader *
6. Power connector	12. Power button

Notes:

- Ports with * are only available on selected models

PERFORMANCE

Processor

Processor Family

Intel® Celeron®, Intel Pentium®, or 12th Generation Intel Core™ i3 / i5 / i7 / i9 Processor

Processor

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Celeron G6900	2	2	3.4GHz	-	4MB	DDR5-4800	Intel UHD Graphics 710
Pentium Gold G7400	2	4	3.7GHz	-	6MB	DDR5-4800	Intel UHD Graphics 710
Core i3-12100	4 (4 P-core + 0 E-core)	8	P-core 3.3GHz	P-core 4.3GHz	12MB	DDR5-4800	Intel UHD Graphics 730
Core i3-12300	4 (4 P-core + 0 E-core)	8	P-core 3.5GHz	P-core 4.4GHz	12MB	DDR5-4800	Intel UHD Graphics 730
Core i5-12600	6 (6 P-core + 0 E-core)	12	P-core 3.3GHz	P-core 4.8GHz	18MB	DDR5-4800	Intel UHD Graphics 770
Core i5-12400	6 (6 P-core + 0 E-core)	12	P-core 2.5GHz	P-core 4.4GHz	18MB	DDR5-4800	Intel UHD Graphics 730
Core i5-12500	6 (6 P-core + 0 E-core)	12	P-core 3.0GHz	P-core 4.6GHz	18MB	DDR5-4800	Intel UHD Graphics 770
Core i7-12700	12 (8 P-core + 4 E-core)	20	P-core 2.1GHz / E-core 1.6GHz	P-core 4.8GHz / E-core 3.6GHz	25MB	DDR5-4800	Intel UHD Graphics 770
Core i9-12900	16 (8 P-core + 8 E-core)	24	P-core 2.4GHz / E-core 1.8GHz	P-core 5.0GHz / E-core 3.8GHz	30MB	DDR5-4800	Intel UHD Graphics 770

Operating System

Operating System

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 DG Windows 10 Pro 64
- No operating system

Graphics

Graphics^[1]

Graphics	Type	Memory	Connector	Max Resolution	Key Features
Intel UHD graphics 710	Integrated	Shared	1x HDMI® 2.1 TMDS, 1x DP 1.4	4096x2160@60Hz(HDMI), 5120x2160@60Hz(DP)	DirectX® 12
Intel UHD graphics 730	Integrated	Shared	1x HDMI 2.1 TMDS, 1x DP 1.4	4096x2160@60Hz(HDMI), 5120x2160@60Hz(DP)	DirectX 12
Intel UHD graphics 770	Integrated	Shared	1x HDMI 2.1 TMDS, 1x DP 1.4	4096x2160@60Hz(HDMI), 5120x2160@60Hz(DP)	DirectX 12
NVIDIA® GeForce® MX550	Discrete	2GB GDDR6	1x HDMI 2.1 TMDS, 1x DP 1.4	4096x2160@60Hz(HDMI), 5120x2160@60Hz(DP)	DirectX 12

Notes:

- The information of integrated graphics are not applicable for the models without integrated graphics (for the details, please refer to processor section)

Monitor Support

Monitor Support

Supports up to 3 independent displays via native display and 2 external monitor; supports external monitors via

DisplayPort™ and HDMI; work as standalone monitor via HDMI (HDMI in / out combo)

Chipset

Chipset
Intel Q670 Chipset

Memory

Max Memory^[1]
Up to 64GB DDR5-4800
Memory Slots
Two DDR5 SO-DIMM slots, dual-channel capable

Memory Type
DDR5-4800

Notes:
1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^{[1][2]}
Up to three drives, 2x 2.5" HDD + 1x M.2 SSD
• 2.5" HDD up to 2TB each
• M.2 SSD up to 1TB

Storage Type

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-
2.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2280 SSD	PCIe® NVMe®, PCIe 3.0 x4	-	Opal2
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4 Value	-	Opal2
M.2 2280 SSD	PCIe NVMe, PCIe 4.0 x4 Performance	-	Opal2

RAID^[3]
RAID 0/1 support for HDDs

Notes:
1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.
2. 2nd 2.5" HDD occupies ODD bay, and needs ODD to HDD bracket kit (optional, come with 2nd 2.5" HDD)
3. RAID is not preset by default, user can config RAID 0/1 according to the demand.

Removable Storage

Optical
• DVD-ROM, SATA connector, slim (9.0mm)
• DVD burner (DVD±RW), SATA connector, slim (9.0mm)
• None

Card Reader
• 3-in-1 card reader (SD, SDHC, SDXC)
• No card reader

Multi-Media

Audio Chip
High Definition (HD) Audio, Realtek® ALC256-NL codec

Speakers
Stereo speakers, 3W x2, Dolby® Atmos®
Microphone

- Dual array microphone
- No microphone

Camera

- 5.0-megapixel, with ThinkShutter (physical switch on/off), ±20° view angle adjustable
- 5.0-megapixel, IR & RGB hybrid, with ThinkShutter (physical switch on/off), ±20° view angle adjustable, Windows Hello support
- No camera

Power Supply

Power Supply

Power	Type	Efficiency	Key Features
180W	Fixed	90%	100V - 240V, 50-60Hz
230W	Fixed	92%	100V - 240V, 50-60Hz

DESIGN

Display

Display^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
23.8"	QHD (2560x1440)	None	IPS	300 nits	Anti-glare	16:9	1000:1	99% sRGB	horizontal: +/- 89°, vertical: +/- 89°	Borderless design, low blue light (Hardware Solution), flicker free, Eye Safe

Touchscreen

Non-touch

Notes:

- California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

- Lenovo Calliope Keyboard (USB connector), black
- Lenovo Calliope Wireless Keyboard (2.4GHz via USB receiver), black
- Lenovo Traditional Keyboard (USB connector), black
- No keyboard

Mouse

- Lenovo Calliope Mouse (USB connector), black
- Lenovo Calliope Wireless Mouse (2.4GHz via USB receiver), black
- Lenovo Fingerprint Mouse (USB connector), Windows Hello support, black
- No mouse

Mechanical

Buttons

- Power button
- Microphone mute button
- Monitor / PC mode switch button

Form Factor

AIO (23.8 inches)

Dimensions (WxDxH)

Models	Dimensions
Models (with full function monitor stand, with camera)	539.6 x 217.31 x 394.65 mm (21.24 x 8.56 x 15.54 inches) 539.6 x 217.31 x 503.66 mm (21.24 x 8.56 x 19.83 inches)

Models (with full function monitor stand, without camera)	539.6 x 217.31 x 374.15 mm (21.24 x 8.56 x 14.73 inches) 539.6 x 217.31 x 483.16 mm (21.24 x 8.56 x 19.02 inches)
Models (with UltraFlex V stand, with camera)	Lowest in vertical mode: 539.6 x 216.32 x 387.63 mm (21.24 x 8.52 x 15.26 inches) Highest in vertical mode: 539.6 x 216.32 x 472 mm (21.24 x 8.52 x 18.58 inches)
Models (with UltraFlex V stand, without camera)	Lowest in vertical mode: 539.6 x 216.32 x 367.13 mm (21.24 x 8.52 x 14.45 inches) Highest in vertical mode: 539.6 x 216.32 x 451.5 mm (21.24 x 8.52 x 17.78 inches)

Packaging Dimensions (WxDxH)

- With Full Function Monitor Stand: 660 x 238 x 575 mm (25.98 x 9.37 x 22.64 inches)
- With UltraFlex V Stand: 660 x 238 x 545 mm (25.98 x 9.37 x 21.46 inches)

Weight^[1]

Models	Weight
Models (with full function monitor stand, with ODD, with camera)	8.235 kg (18.15 lbs)
Models (with UltraFlex V stand, with ODD, with camera)	8.742 kg (19.27 lbs)

Packaging Weight

- With Full Function Monitor Stand: 2.084 kg (4.59 lbs), packaging only
- With UltraDlex V Stand: 2.0658 kg (4.55 lbs), packaging only

Case Color

Black

Bays^[2]

- 2x 2.5" disk bay (2nd 2.5" HDD occupies ODD bay)
- 1x slim ODD bay

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

EOU

Toolless cover, stand, motherboard shielding, HDD, and memory assembly / removal

Stand

- UltraFlex V stand, supports -5° to +70° tilt, up to 70°±2° lift (up to 174.02mm lift in flat mode / up to 84.37mm lift in vertical mode)
- Full function monitor stand, supports -5° to +20° tilt, left & right 45° swivel, 90° pivot, up to 110mm lift
- No stand

Mounting

Supports VESA mount 100mm

Others

- (Optional) Conference Call Base, 3W x4 Harman speakers, 4 digital microphones array with AI noise suppression, Physical button for Teams, USB-C connector
- (Optional) Smart Human Presence Detection based on Radar Sensor
- Supports Smart Power On

Notes:

1. Weight may vary by configuration.
2. 2nd 2.5" HDD needs ODD to HDD bracket kit (optional, come with 2nd 2.5" HDD)

CONNECTIVITY

Network

Onboard Ethernet

Gigabit Ethernet, Intel Ethernet Connection I219-LM, 1x RJ-45, supports Wake-on-LAN

Optional Ethernet

No optional Ethernet

WLAN + Bluetooth^[1]

- AMD RZ616, Wi-Fi® 6E, 802.11ax Dual Band 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- Mediatek Wi-Fi 6 MT7921, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card
- Realtek Wi-Fi 6 RTL8852AE, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 card
- Intel Wi-Fi 6 AX201, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1, M.2 Card
- Intel Wi-Fi 6E AX211, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, Intel vPro technology support, M.2 Card
- No WLAN and Bluetooth

Notes:

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]**Rear Ports^{[1][2]}**

- 3x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 2 (support data transfer and 15W charging)
- 1x HDMI (HDMI in 1.4 / HDMI out 2.1 TMDS combo port)
- 1x DisplayPort 1.4
- 1x Ethernet (RJ-45)

Optional Rear Ports

1x serial

Right Ports

- 3x USB 3.2 Gen 2
- 1x headphone / microphone combo jack (3.5mm)

Optional Right Ports

1x card reader

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s;
FireWire 400: 400 Mbit/s;
FireWire 800: 800 Mbit/s
2. For video ports on discrete graphics, please see graphics section

Monitor Cable**Monitor Cable**

- DP to dual DP dongle
- DP to DVI-D dongle
- DP to HDMI dongle
- DP to VGA dongle
- HDMI to DVI dongle
- HDMI to VGA dongle
- No monitor cable

SECURITY & PRIVACY**Security****Security Chip**

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington® Security Slot, 3 x 7 mm

Chassis Intrusion Switch

- Chassis intrusion switch
- No chassis intrusion switch

Fingerprint Reader

- Touch style fingerprint reader on mouse
- No fingerprint reader

Other Security

(Optional) ThinkShutter camera cover

BIOS Security

- Administrator password
- Power-on password
- Hard disk password
- Boot sequence control
- Boot without keyboard and mouse
- Self-healing BIOS
- Smart USB protection (allows keyboard / mouse only, blocks all storage devices)
- Individual USB port disablement

MANAGEABILITY

System Management

System Management^[1]

- Intel vPro Enterprise
- Non-vPro

Notes:

1. Intel vPro offers a superset of DASH's defined capabilities.

SERVICE

Warranty

Base Warranty^[1]

- 1-year limited onsite service
- 3-year limited onsite service
- No base warranty

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -20°C (-4°F) to 60°C (140°F)

Humidity

Operating: 20% to 80%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

CERTIFICATIONS

Green Certifications

Green Certifications

- (Optional) EPEAT™ Gold
- (Optional) ENERGY STAR® 8.0

- ErP Lot 3
- TCO Certified 9.0
- TCO edge
- VOC Report
- RoHS compliant

Other Certifications

Other Certifications

- TÜV Rheinland® Eyesafe®
- TÜV Rheinland Flicker Free
- TÜV Rheinland Low Blue Light (Hardware Solution)
- (Optional) TÜV Rheinland Ultra Low Noise
- UL Anti-dust

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.