



Revision Number: 001.1

Issue date: 04/10/2025

1. IDENTIFICATION

Product name:	LPG 2G 2PK SG GEL TBE 6PG	IDH number:	2598079
Product type/	Cyanoacrylate		
Recommended use:			
Restriction of Use:	None identified	Region:	Canada
Company address:	Henkel Canada Corporation Meadowpine Boulevard 2515 Mississauga, Ontario L5N 6C3	Contact information:	
		Telephone: +1 (905) 814-6511	MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711
			TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887
			MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711
			TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887
			Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING:	H227 - COMBUSTIBLE LIQUID. H315 - CAUSES SKIN IRRITATION. H319 - CAUSES SERIOUS EYE IRRITATION. H335 - MAY CAUSE RESPIRATORY IRRITATION.
----------	---

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	4
SKIN IRRITATION	2
EYE IRRITATION	2A
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3

PICTOGRAM(S)



Precautionary Statements

Prevention:	P210 - Keep away from heat, sparks, open flames, hot surfaces - no smoking. P261 - Avoid breathing mist/vapours. P264 - Wash affected area thoroughly after handling. P271 - Use only outdoors or in a well-ventilated area. P280 - Wear protective gloves, clothing, eye and face protection. P302+P352 - IF ON SKIN: Wash with plenty of water. P304+P340+P312 - IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P332+P313 - If skin irritation occurs: Get medical attention.
Response:	

IDH number: 2598079

Product name: LPG 2G 2PK SG GEL TBE 6PG

Storage:	P337+P313 - If eye irritation persists: Get medical attention. P362+P364 - Take off contaminated clothing and wash it before reuse. P370+P378 - In case of fire: Use foam, dry chemical or carbon dioxide to extinguish. P403+P233 - Store in a well-ventilated place. Keep container tightly closed.
Disposal:	P405 - Store locked up. P501 - Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Other hazards Not available.

Classification complies with Canadian Hazardous Products Regulations and is consistent with the provision of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Weight %*
Ethyl 2-cyanoacrylate	7085-85-0	80 - 100

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

First Aid Measures by likely routes of exposure

Inhalation:	Move to fresh air. If symptoms persist, seek medical advice.
Skin contact:	Do not pull bonded skin apart. Soak in warm soapy water. Gently peel apart using a blunt instrument. If skin is burned due to the rapid generation of heat by a large drop, seek medical attention. If lips are bonded, apply warm water to the lips and encourage wetting and pressure from saliva in mouth. Peel or roll lips apart. Do not pull lips apart with direct opposing force.
Eye contact:	Immediately flush with plenty of water for at least 15 minutes. Get medical attention. If eyelids are bonded closed, release eyelashes with warm water by covering with a wet pad. Do not force eye open. Cyanoacrylate will bond to eye protein and will cause a lachrymatory effect which will help to debond the adhesive. Keep eye covered until debonding is complete, usually within 1-3 days. Medical attention should be sought in case solid particles of polymerized cyanoacrylate trapped behind the eyelid caused abrasive damage.
Ingestion:	Ensure breathing passages are not obstructed. The product will polymerize rapidly and bond to the mouth making it almost impossible to swallow. Saliva will separate any solidified product in several hours. Prevent the patient from swallowing any separated mass.

Most important symptoms and effects (acute and delayed): The most important known symptoms and effects, both acute and delayed, are described in Section 11: Toxicological Information.

Indication of any immediate medical attention / special treatment needed: Surgery is not necessary to separate accidentally bonded tissues. Experience has shown that bonded tissues are best treated by passive, non-surgical first aid. If rapid curing has caused thermal burns they should be treated symptomatically after adhesive is removed.

5. FIRE FIGHTING MEASURES

Extinguishing media: Foam, dry chemical or carbon dioxide.

Improper extinguishing agents:	Not available.
Special firefighting procedures:	Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode.
Unusual fire or explosion hazards:	Not available.
Hazardous combustion products:	Trace amounts of toxic and/or irritating fumes may be released and the use of breathing apparatus is recommended.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Ventilate area. Wear appropriate protective equipment and clothing during clean-up. Do not allow product to enter sewer or waterways.
Clean-up methods:	Do not use cloths for mopping up. Flood with water to complete polymerization and scrape off the floor. Cured material can be disposed of as non-hazardous waste. Dispose of according to Federal, State and local governmental regulations.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Avoid contact with fabric or paper goods. Contact with these materials may cause rapid polymerization which can generate smoke and strong irritating vapors, and cause thermal burns.
Storage:	For safe storage, store between 5 °C (41°F) and 25 °C (77°F) Keep in a cool, well ventilated area. Keep containers closed when not in use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Ethyl 2-cyanoacrylate	1 ppm STEL 0.2 ppm TWA (Respiratory sensitization) (Dermal sensitization)	None	None	None

Engineering controls:	Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.
Respiratory protection:	Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
Eye/face protection:	Safety glasses with side-shields.
Skin protection:	Use nitrile gloves and aprons as necessary to prevent contact. Do not use PVC, nylon or cotton.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Gel
Color:	Clear colorless
Odor:	Irritating
Odor threshold:	Not available.
pH:	6.00 - 7.00
Vapor pressure:	0.04 mm hg (25 °C (77°F))
Boiling point/range:	> 150.0 °C (> 302°F)None
Melting point/ range:	Not available.
Density/Relative density:	1.10
Relative vapor density:	Not available.
Flash point:	85 °C (185°F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility:	Reacts with water.
Partition coefficient n-octanol/water (logarithmic value):	Not applicable
VOC content:	< 2 %; < 20 g/l (California SCAQMD Method 316B) (Estimated)
Dynamic viscosity:	500 - 900 mPa.s
Kinematic viscosity:	Not available.
Particle characteristics:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	Rapid exothermic polymerization will occur in the presence of water, amines, alkalis and alcohols.
Hazardous decomposition products:	In the event of a fire, carbon monoxide (CO), carbon dioxide (CO ₂) and nitrogen oxides (NO _x) are released.
Incompatible materials:	Strong oxidizing agents. Water. Alcohols. Amines. Bases.
Reactivity:	Not available.
Conditions to avoid:	Heat. Direct sunlight. Keep away from open flames, hot surfaces and sources of ignition. Moisture. Humidity

11. TOXICOLOGICAL INFORMATION

Likely routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-----------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation:	May cause respiratory tract irritation.
Skin contact:	Causes skin irritation.
Eye contact:	Causes serious eye irritation.
Ingestion:	Not expected under normal conditions of use. May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s
Ethyl 2-cyanoacrylate	None

Hazardous Component(s)	Immediate Health Effects	Delayed Health Effects	Chronic Health Effects
Ethyl 2-cyanoacrylate	Irritant	Allergen	Respiratory

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Ethyl 2-cyanoacrylate	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any packaging.

Canada Transportation of Dangerous Goods - Ground

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

International Air Transportation (ICAO/IATA)

Proper shipping name:	Aviation regulated liquid, n.o.s. (Cyanoacrylate ester)
Hazard class or division:	9
Identification number:	UN 3334
Packing group:	III

Water Transportation (IMO/IMDG)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

15. REGULATORY INFORMATION

Canada Regulatory Information

CEPA DSL/NDSL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed as active or are exempt from listing on the Toxic Substances Control Act (TSCA) inventory.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: This Safety Data Sheet contains changes from the previous version in Section(s): 14,15

Prepared by: Product Safety and Regulatory Affairs

Issue date: 04/10/2025

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.

This Safety Data Sheet has been generated based on the Canadian Hazardous Products Regulations (WHMIS 2015) and provides information in accordance with Canadian law only. No warranty or representation of any kind is given with respect to the substantive or export laws of any other jurisdiction or country. Please confirm that the information provided herein conforms to the substantive export or other law of any other jurisdiction prior to export. Please contact Henkel Product Safety and Regulatory Affairs for additional assistance.