


OVERVIEW



1. Card slot	5. Microphone
2. Volume button	6. USB-C 2.0
3. Power button	7. Speaker
4. Headphone / microphone combo jack (3.5mm)	

Notes:

- Card slot is for microSD card (WLAN model) or nano-SIM + microSD card (WWAN model)

PERFORMANCE

Processor

Processor Family

MediaTek Processor

Processor

Processor Name	Cores	Max Frequency	Memory Support	Processor Graphics
MediaTek Helio G80	Octa-core 2x A75 + 6x A55	A75@2.0GHz / A55@1.8GHz	LPDDR4x	ARM Mali-G52 MC2 GPU

Operating System

Operating System^[1]

Android™ 12 or later

Notes:

1. Lenovo® tablets typically receive at least 1 Android OS upgrade cycle. May vary depending on models, countries, regions, retailers or operators. For latest software upgrade information, please visit [Android Upgrade Matrix](#).

Graphics

Graphics

Graphics	Type	Memory
ARM Mali-G52 MC2 GPU	Integrated	Shared

Chipset

Chipset

MediaTek SoC (System on Chip) platform

Memory

Max Memory

- 3GB soldered memory, not upgradable
- 4GB soldered memory, not upgradable

Memory Type

LPDDR4x

Storage

Storage Support^[1]

- 32GB eMMC 5.1 on systemboard
- 64GB eMMC 5.1 on systemboard
- 128GB eMMC 5.1 on systemboard
- microSD card, supports FAT32 up to 128GB, exFAT up to 2TB

Storage Type

Disk Type	Interface	Offering
Flash Memory	eMMC 5.1	32GB / 64GB / 128GB

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Card Reader

- microSD card slot (WLAN models)
- Nano-SIM + microSD card slot (WWAN models)

Multi-Media

Speakers

Dual speaker optimized with Dolby® Atmos®

Microphone

Single microphone

Camera

Front 2.0MP, f/2.2, 73° FoV (field of view) fixed focus, face unlock
Rear 8.0MP, f/2.2, 86.2° FoV, autofocus

VoiceCall^[1]

- No support
- Voice call

Notes:

1. Use of Voice call requires cellular data plan. Voice call functionality details may vary based on local operator network, data and messaging services. Please contact your carriers for details.

Sensor**Vibration Motor**

Eccentric Rotating Mass (ERM)

Sensors

- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Coulomb counter
- Hall sensor

Battery**Battery**

Integrated Li-Polymer 5100mAh (typical), capable of 15W rapid charge

Max Battery Life^[1]

Local video playback: 13 hr
Web browsing: 12 hr
Music playback: 15 hr

Notes:

1. All battery life claims are approximate and based on internal testing under optimal laboratory and network conditions. Actual battery performance will vary and depend on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage.

Power Adapter**Power Adapter**

5V/2A (10W) USB-C® AC adapter, 100-240V, 50-60Hz

DESIGN**Display****Display^[1]**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle (L/R/U/D)	Key Features
9"	HD (1340x800)	Multi-touch	IPS (TFT)	400 nits	Anti-fingerprint	15:9	1500:1	60% NTSC	80°/80°/80°/80°	TÜV Low Blue Light

Touchscreen

Capacitive-type in-cell TDDI multi-touch, supports 10-point touch

Notes:

1. California Electronic Waste Recycling Fee
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Pen

No support

Mechanical**Dimensions (WxDxH)^[1]**

215.43 x 136.76 x 7.99 mm (8.48 x 5.38 x 0.31 inches)

Weight^[2]

Around 344 g (0.76 lbs)

Case Color

- Arctic grey
- Frost blue

Case Material

Metal (back cover)

Buttons

- Power button
- Volume button

Notes:

1. The system dimensions may vary depending on configurations.
2. The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY**Network****WLAN + Bluetooth®**

802.11a/b/g/n/ac 1x1 Wi-Fi® + Bluetooth 5.1

WWAN

- 4G LTE
- No support

Cellular Bands

GSM: B2/B3/B5/B8

WCDMA: B1/B2/B4/B5(B6/B19)/B8

FDD LTE: B1/B2/B3/B4/B5(B19)/B7/B8/B18/B20/B26/B28(a+b)/B66

TDD LTE: B38/B40/B41 full band (2496 MHz-2690 MHz)

Wi-Fi Direct

Support

Wi-Fi Display

Support

Location Services

Models	Location
WLAN models	GPS + GLONASS + Galileo
WWAN models	GPS + GLONASS + Galileo + A-GPS

Ports^[1]**Standard Ports**

- 1x USB-C 2.0 (support data transfer and Power Delivery 3.0)
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports

- 1x Nano-SIM & microSD card slot (WWAN models)
- 1x microSD card slot (WLAN models)

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file

attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s

SERVICE

Warranty

Base Warranty

- 1-year carry-in service
- 1-year mail-in service
- 1-year courier or mail-in service
- 1-year courier service
- 2-year (1-yr battery) carry-in service
- 2-year (1-yr battery) mail-in service
- 2-year (1-yr battery) courier service
- 2-year (2-yr battery) carry-in service
- 2-year (2-yr battery) courier or carry-in service
- 3-year (1-yr battery) courier service

ENVIRONMENTAL

Operating Environment

Temperature

Operating: 0°C (32°F) to 40°C (104°F)

Humidity

Maximum humidity: 95%, 39°C (102.2°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft) / 0°C (32°F) to 40°C (104°F)

ACCESSORIES

Bundled Accessories

Bundled Accessories

- Clear case and film
- Folio case and film
- None

SOFTWARE

Preinstalled Software

Preinstalled Software^{[1][2]}

- Gmail
- Google
- Google Play
- Google Sheets
- Google TV
- Google Photos
- Google Podcasts
- Google One
- Google Camera Go
- Google Chrome
- Google Docs
- Google Duo
- Google Drive
- Google Kids Space

- Google Maps
- Google Entertainment Space
- Files by Google
- Messages
- Recorder
- YouTube
- YouTube Kids
- Netflix
- Tablet Center

Notes:

1. Actual application availability varies by country/region.
2. Books and video content not available in all regions. Video content subject to availability of YouTube Kids app. Books content requires the Play Books app. Availability of apps, books, and video content may change without notice. Google Assistant not available in Google Kids Space. Google Kids Space requires a Google Account for your child. Parental controls require the Family Link app on a supported Android, Chromebook, or iOS device.

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- (Optional) ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

Notes:

1. The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration.

Other Certifications

Other Certifications

TÜV Rheinland® Low Blue Light (Software Solution)

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

