Poly CCX 400 Business Media Phone with Open SIP with Power Supply

"Entry-level" just got sweeter

The Poly CCX 400 is an entry-level business phone that's easy to use. Its interface is simple and intuitive. And contacts and meetings are one swipe or one tap away on a color touch screen.



Sound your best

Hear every nuance with Poly HD Voice and Poly Acoustic Clarity technologies. Poly Acoustic Fence technology reduces distracting background noise and makes calling a pleasure.

Stylish, ultra-usable design

*Product image may differ from actual product

Enjoy the ergonomic design and the intuitive user touchscreen interface that saves you the hassle of learning new features and functions. When a phone is this easy, better collaboration and productivity aren't far behind.

Audio clarity

Conversations stay clear with Poly HD Voice and Poly Acoustic Clarity technologies.

Distraction-free calls

Reduce distracting background noise with Poly Acoustic Fence technology.

IT friendly

Easy for IT to manage with provisioning and management of telephony deployment and support.

Datasheet



Poly CCX 400 Business Media Phone with Open SIP with Power Supply

Specifications



Compatible with Compatible operating systems: Android 9

Display

Aspectratio: 16.9 Native resolution: 720 x 1280 Panel technology: Color LCD Display size (diagonal; 5" Display size (diagonal, metric): 12.7 cm (5") Touch-enabled: Gesture-based, multi-touch capable touchscreen

Connectivity and communications

External I/O ports: 1USB 2.0 Type-A (for media and storage applications) 2 RJ-45 (10/100/1000BASE-TX Mbps)

Battery

Power features: Built-in auto sensing IEEE 802.3af Power over Ethernet (Class 0) 13 W (maximum)²

User interface features

Languages:

Arabic; Chinese; Czech; Danish; Dutch; English; French; German; Hungarian; Italian; Japanese; Korean; Norwegian; Polish; picture frame Portuguese; Romanian; Russian; Slovenian; Spanish; Swedish

Audio

Audio features: Poly HD Voice Poly Acoustic Clarity technology provides full duplex conversations, acoustic echo cancellation, and background noise suppression Poly Acoustic Fence technology eliminates background noise when using a handset or wired headset Poly NoiseBlockAI technology removes most background noise when using the speakerphone TIA-920 wideband audio, type 1 compliant (IEEE 1329 full duplex) Individual volume settings with visual feedback for each audio path Voice activity detection Comfort noise generation DTMF tone generation (RFC 2833 and in-band) Low delay audio packet transmission Adaptive jitter buffers Frequency response (microphone): 150 Hz to 7 kHz Audio codecs:

G.711 (A-law and µ-law) G.722 G.7221 G.729AB ILBC OPUS



Environmental

Certifications and compliances: AS/NZS 62368-117; Australia RCM; Brazil ANATEL; CISPR22 Class B; EEA; CE Mark; EN55024; EN55032 Class B; EN 62368-1; FCC Part 15 (CFR 47) Class B; IEC 609501 & IEC 62368-1; ICES-003 Class B; Japan MIC/VCCI; NZ Telepermit; Saudi Arabia CITC; So. Africa ICASA; So. Korea KC; UL 62368-1; VCCI Class B; Canada ICES and NRTL; China RoHS 2.0; Indenesia SDPPI; Mexico NYCE; Russia Customs Union

Operating humidity range: 5 to 95%

Certifications Special features:

Unicode UTF-8 character support Adjustable desk stand (2 positions)

Applications supported

Management software: Poly Lens Poly Zero Touch Provisioning Polycom Device Management Service for Service Providers (PDMS-SP) Cloud Management Web UI to device IP address

Display features

Adjustable font size selection (regular, medium, large); Screensaver; Voicemail support; Normal and dark mode; Digital picture frame

Security

Security management 8021X Authentication and EAPOL Media encryption via SRTP Digest authentication Encrypted configuration files HTTPS secure provisioning Password login Support for signed software executables Support for URL syntax with password Transport Layer Security (TLS) SRTP media encryption using AES 256 bits

Network

Supported network protocols: Manual or dynamic host configuration protocol (DHCP) network setup 10/100/1000 Base-TX across LAN and PC ports Conforms to IEEE802.3-2005 (Clause 40) for physical media attachment Conforms to IEEE802.3-2002 (Clause 28) for link partner auto-negotiation IPv6

VoIP features:

24 lines (SIP registrations) IETF SIP (RFC 3261 and companion RFCs)

Poly CCX 400 Business Media Phone with Open SIP with Power Supply

Specifications



Headset and handset compatibility Headset ports:

Recused ports: 1RJ-9 1Electronic Hook Switch (EHS) port for optional adapter Headset and handset compatibility: Compatible with commercially available TTY adapter equipment Compliant with ADA Section 508 Subpart B 119423 (all) Hearing aid compatibility to ITU-TP.370 and TIA 504A standards Hearing aid compatible (HAC) handset for magnetic coupling to hearing aids USB Twoe-A headset support

Telephony and call handling features

Telephony and call handling features Busy Lamp Field (BLF) Call timer and call waiting Caller ID enable/disable Distinctive incoming call treatment/call waiting Do not disturb function One-touch speed dial, redial Shared call/bridged line appearance Automatic off-hook call placement (hot dialing) Call media recordina/playback Automatic/remote answer on headset using electronic hook-switch Call hold/resume, diversion (forward), transfer (consultation, blind), pickup Calling, called, connected party identification Call forward for shared lines Private hold for shared lines Call logs (missed, received, placed) Local contact directory Create local contact from call log Corporate directory Call server redundancy (failover) SBC line registration Conference bridging Local call forwarding (all, busy, no answer) with destination shown on idle display Automatic call distribution (ACD) Automatic answer (intercom) Call park/retrieve Directed call pickup Group call pickup Hunt group - sequential calling Last call return Auto-answer a page with a muted microphone PTT and Multicast group Exchange Calendar Integration Flexible line keys Key system emulation STIR/SHAKEN Caller ID validation Voice Quality Monitoring (VQMon)¹



manty HP shall not be liable for technical or edit

Weight and dimensions

Product Primary Color: Black Package dimensions (Imperial): 8.7 x 9.6 x 2.7 in Package dimensions (Imperial): 22.2 x 24.3 x 6.9 cm Package weight (Imperial): 22.3 lb Package Weight (metric): 1004 g UPC number: 197497515633 Product number: 84C14AA

Country of origin Country of origin: Made in China

Warranty Poly standard one-year limited warranty

What is in the box

Console Desk stand Handset with handset cord Network (LAN) cable-CAT-5E Setup sheet

Key Selling Points Footnotes

¹Visit https://www.poly.com/us/en/products/phones/ccx/ccx-400 for more detail.

nonv I P The information

Technical Specifications Footnotes

¹Nost software enabled features must be supported by the service provider platform. Please contact your IP PBX/softswitch vendor or service provider for a list of supported features.² External universal AC/DC adapter, 5 VDC, 3 A, 15 W (sold separately).

July 20