

HPE NVMe High Performance Mixed Use Solid State Drives

HPE 6.4TB NVMe Gen4 High Performance Mixed Use SFF BC U.3 Static PM1755 SSD (P78804-B21)



What's new

- Offering 1.6 TB, 3.2 TB, and 6.4 TB HPE NVMe High Performance Mixed Use SFF SSDs.

Overview

Do you need to accelerate the performance of your mixed use applications?

HPE NVMe High Performance Mixed Use (MU) Solid State Drives (SSDs) are best suited for high I/O applications that require a balanced performance between reads and writes to deliver high performance and endurance for data-intensive applications. NVMe High Performance MU SSDs communicate directly to applications via the PCIe bus to boost I/O bandwidth and reduce latency.

HPE NVMe High Performance MU SSDs deliver high performance and lower latency data transfers from storage significantly faster than SAS or SATA SSDs. They utilize the high bandwidth of PCIe Gen4 in select servers for mixed use workloads such as Big Data analytics, high-performance computing (HPC), and virtualization.

Features

High Performance, Exceptional Reliability, and Efficiency for Faster Business Results

HPE NVMe High Performance Mixed Use (MU) Solid State Drives are ideal for Big Data analytics, cloud computing, high performance compute, business intelligence, database applications, and virtualization.

Achieve higher IOPS and lower latency to enhance the performance of your data center.

Maintain data accuracy with full data-path error detection.

Choose from a broad portfolio of enhanced solutions in a wide variety of capacities.

HPE Continues to Enhance its SSD Portfolio by Offering NVMe PCIe Gen4 U.3 SSDs

HPE NVMe PCIe Gen4 U.3 SSDs deliver higher performance for server-storage solutions to better meet the challenges within high performance workloads.

HPE NVMe PCIe Gen4 U.3 Dynamic SSDs are 100% backwards compatible with NVMe U.2 SSD backplanes on selected HPE ProLiant servers.

Technical specifications	HPE 6.4TB NVMe Gen4 High Performance Mixed Use SFF BC U.3 Static PM1755 SSD
Product Number	P78804-B21
Lifetime writes	35,040 TB
Endurance DWPD (Drive Writes Per Day)	3.0 DWPD
Read IOPS	Random Read IOPS (4 KiB, Q=16) = 261,000 Max Random Read IOPS (4 KiB) = 1,763,400@256
Write IOPS	Random Write IOPS (4 KiB, Q=16) = 991,200 Max Random Write IOPS (4 KiB) = 992,800@16
Power (Watts)	18.39 W
Plug type	Hot pluggable
Height	15.00 mm
Platform supported	HPE Compute Mainstream Platforms, see QuickSpecs for more information
Warranty	HPE Solid State Drives and Add-In Cards have a standard 3/0/0 warranty Customer Self Repair (CSR) subject to maximum usage limitations. Maximum usage limit is the maximum amount of data that can be written to the drive. Drives that have reached this limit will not be eligible for warranty coverage.

HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

[Advisory & Professional services](#)

Experts can help you map out your path to hybrid cloud and optimize your operations.

[Managed services](#)

HPE runs your IT operations, giving you unified control, so can focus on innovation.

[Support services](#)

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- **HPE Complete Care Service:** a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- **HPE Tech Care Service:** the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.
- **HPE Multivendor Services:** Single point of accountability for managing on-site hardware and software support for multivendor products. HPE experts help manage your IT across technologies and platforms for HPE and non-HPE technologies, acting as the single point of contact for your IT operational needs.

[Lifecycle Services](#)

Address your specific IT deployment project needs with tailored project management and deployment services.

[HPE Education Services](#)

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options

Defective Media Retention is optional and allows you to retain Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

GreenLake

[GreenLake](#) is the cloud to run and manage your entire hybrid landscape—private, public, and edge. It helps you to:

- Streamline IT Operations across compute, storage, and networking without the chaos
- Unify and secure data, as you move faster
- Accelerate AI, from pilot to production

The result: greater operational efficiency, lower TCO, and faster AI delivery—all from one unified, intelligent platform built for today's hybrid enterprise.

For additional technical information,
available models and options, please
reference the QuickSpecs

Visit [HPE.com](https://www.hpe.com)

Chat now

© Copyright 2026 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Image may differ from the actual product.

PSN1014922771IEEN, July, 2026.

HEWLETT PACKARD ENTERPRISE

[hpe.com](https://www.hpe.com)

