



Poly Voyager Free 60 UC M Carbon Black Earbuds +BT700 USB-C Adapter +Basic Charge Case (7Y8L8AA)



Overview

True wireless earbuds for work and life

Tune into a world full of sound and free of noise with these earbuds. Whether you're on a video call or into your playlists, these wireless earbuds are designed to keep you productive, connected and entertained.

Say hello to your new work buds

Each bud has a three-mic array that triangulates on your voice and minimizes surrounding noise so you're always loud and clear. Whether you are in a video meeting or a call, these wireless earbuds are designed to keep you productive and connected.

Won't wear out its welcome before you finish your day

Designed for all day wear, these ear buds are lightweight, come with 3 sizes of conical-shaped ear tips engineered for maximum comfort, and advanced sidetone technology that keeps you aware of how loud you are speaking so you aren't straining your voice.

Features

Clear, distraction-free calling

Stay focused and keep out the distractions of the outside world with adjustable hybrid adaptive active noise cancelling (ANC).

Discrete, comfortable design

Designed for hours of comfortable use in even the most demanding enterprise environments, you'll look and sound your best on calls with these discreet wireless earbuds.

Easy management via Poly Lens

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

Advanced noise reduction

With three microphones per earbud and WindSmart technology for clearer outdoor calls, you'll always be heard above the background noise.

Easy connection to Bluetooth® devices

Connect up to two Bluetooth® devices at any time with multipoint technology (remembers up to 8 Bluetooth® devices).

Optimized for use with leading communications platforms.

An IT manager's dream, these earbuds were created for communication and are optimized and certified to work with top virtual meeting providers.

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Audio	Hybrid Active noise cancellation (ANC); Transparency mode
Battery life	Up to 16.5 hours (5.5 hours plus extra 11 hours with charge case (talk time)); Up to 24 hours (8 hours plus extra 16 hours with charge case (music time, ANC on)); Up to 30 days including charging case (standby time); Up to 1 hour and 12 minutes (talk timer after 15 minutes charging)
Battery recharge time	Supports battery fast charge
Battery type	Rechargeable Li-ion
Bluetooth version	5.3
Button user controls	Call answer/end
Charge time	2 hours (earbuds); 3 hours (case)
Charging plug	USB Type-C® to USB Type-C®
Color	Carbon black
Compatibility	Compatible with PCs via included BT700 Bluetooth® adapter; smartphone via Bluetooth®
Compatible Operating Systems	Windows 11; macOS; Android™; iOS
Connection type	USB Type-C®; Bluetooth®
Management Software	Poly Lens
Manufacturer Warranty	Poly standard two-year limited warranty
Microphone type	Three-microphone steerable array
Minimum System Requirements	Bluetooth®; USB Type-C® port
Minimum dimensions (W x D x H)	16 x 26.1 x 37.8 mm (earbuds); 53.5 x 72 x 28 mm (charging case)
Minimum dimensions (W x D x H)	0.63 x 1.03 x 1.49 in (earbuds); 2.11 x 2.83 x 1.10 (charging case)
Package dimensions (W x D x H)	135 x 103 x 44 mm
Package dimensions (W x D x H)	5.31 x 4.1 x 1.7 in
Package weight	186 g
Package weight	0.41 lb
Paired devices	Connects to two devices at the same time, remembers up to 8 devices
Speaker size	10 mm
Special features	Qi wireless charging
Supported bluetooth profiles	A2DP; AVRCP; HSP; HFP
Touch user controls	Mute; Volume +/-
UNSPSC code	52161554
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low

Voice assistant	Siri; Google
Weight	0.01 lb (each earbud); 0.12 lb (basic charging case)
Weight	5.8 g (each earbud); 52.6 g (basic charging case)
What's in the box	Wireless earbuds; BT700 Bluetooth® Type-C® adapter ; USB Type-C® charging cable; Charging case; S/M/L eartips; Carrying case
Wireless range	Up to 30 m
Wireless range (imperial)	Up to 98 ft

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 11, 2023 4:15 PM UTC+0000