


OVERVIEW



1. Ethernet (RJ-45)	6. Headphone / microphone combo jack (3.5mm)
2. 2x Thunderbolt 4	7. USB-A (Hi-Speed USB)
3. HDMI	8. USB-A (USB 5Gbps)
4. USB-A (USB 5Gbps), Always On	9. Kensington Nano Security Slot
5. Smart card reader *	10. Nano-SIM card slot (WWAN model) *

Notes:

- Items with * are only available on selected models

PERFORMANCE

Processor

Processor Family

- AMD Ryzen™ AI 5 / 7 400 Series Processor
- AMD Ryzen™ AI 5 / 7 PRO 400 Series Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics	NPU	Overall TOPS
AMD Ryzen™ AI 5 430	4	8	2.0GHz	4.5GHz	4MB L2 / 8MB L3	AMD Radeon™ 840M	AMD Ryzen™ AI, up to 50 TOPS	Up to 58 TOPS
AMD Ryzen™ AI 5 435	6	12	2.0GHz	4.5GHz	6MB L2 / 8MB L3	AMD Radeon™ 840M	AMD Ryzen™ AI, up to 50 TOPS	Up to 59 TOPS
AMD Ryzen™ AI 5 PRO 435	6	12	2.0GHz	4.5GHz	6MB L2 / 8MB L3	AMD Radeon™ 840M	AMD Ryzen™ AI, up to 50 TOPS	Up to 59 TOPS
AMD Ryzen™ AI 7 445	6	12	2.0GHz	4.6GHz	6MB L2 / 8MB L3	AMD Radeon™ 840M	AMD Ryzen™ AI, up to 50 TOPS	Up to 59 TOPS
AMD Ryzen™ AI 7 PRO 450	8	16	2.0GHz	5.1GHz	8MB L2 / 16MB L3	AMD Radeon™ 860M	AMD Ryzen™ AI, up to 50 TOPS	Up to 66 TOPS

AI (Artificial Intelligence)

AI PC Category

Copilot+ PC^[1]

NPU

Integrated AMD Ryzen™ AI, up to 50 TOPS

Notes:

[1] Copilot+ PCs have at least 16GB RAM, 256GB storage, and a NPU that runs 40+ TOPs to run the latest AI tools build-in latest Windows® 11 to accelerate productivity and creativity.

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Ubuntu Linux^[1]
- Linux^[2]
- No preload operating system

Notes:

[1], [2] Some features may not be supported on the system with Linux preload, including but not limited to Intel® RST RAID, MIPI computer vision camera, WWAN, Human Presence Detection, etc.

Graphics

Graphics**

Graphics	Type	Memory	Key Features
AMD Radeon™ 840M	Integrated	Shared	DirectX® 12
AMD Radeon™ 860M	Integrated	Shared	DirectX® 12

Monitor Support

Monitor Support^[1]

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and Thunderbolt™)

- HDMI® supports up to 3840x2160@60Hz
- Thunderbolt™ supports up to 7680x4320@60Hz^[2]

Notes:

[1] Refresh rates >60hz also supported, however max resolution will be limited.

[2] 8K resolution support needs 2 display pipes. That is, simultaneous display number will “-1” when 8K resolution displayed.

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory

Up to 64GB DDR5-5600^[1]

Memory Slots

Two DDR5 SODIMM slots, dual-channel capable

Memory Type

DDR5-5600

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Max Storage Support^[1]

One drive, up to 2TB M.2 2280 SSD

Storage Slot^[2]

One M.2 2280 PCIe® 4.0 x4 slot

Storage Type**

Disk Type	Interface	Offering	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB / 1TB	Opal 2.0
M.2 2280 SSD ^[3]	PCIe® NVMe®, PCIe® 5.0 x4 Performance	2TB	Opal 2.0

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

[2] The actual data transfer rate of the following PCIe® interface also depends on the capabilities of the connected PCIe® device. The listed values represent theoretical maximums.

PCIe® 3.0 (x2 / x4): 2 GB/s (16 Gbps) / 4 GB/s (32 Gbps);

PCIe® 4.0 (x2 / x4): 4 GB/s (32 Gbps) / 8 GB/s (64 Gbps);

PCIe® 5.0 (x2 / x4): 8 GB/s (64 Gbps) / 16 GB/s (128 Gbps).

[3] PCIe® 5.0 x4 SSD is downgraded to PCIe® 4.0 x4 performance due to the platform limitation.

Removable Storage

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, optimized with Dolby Atmos®

Microphone

Dual-microphone array, 360° far-field, Elevoc Voice

Camera**

- 5.0MP + IR discrete, with privacy shutter, fixed focus, temporal noise reduction
- HD 720p, with privacy shutter, fixed focus

Battery

Battery**

- 46.5Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter^[1]
- 57Wh Rechargeable Li-ion Battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter^[2]

Battery Life^[3]

Configuration 1 (max battery life)
MobileMark® 30: up to 13.8 hr with 871 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 14.21 hr / 24.93 hr @200nits
Local video playback: up to 25.15 hr @150nits

Alternate configuration 2
MobileMark® 30: up to 11.56 hr with 984 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 10.43 hr / 17.4 hr @200nits
Local video playback: up to 19.2 hr @150nits

Alternate configuration 3
MobileMark® 30: up to 8.98 hr with 886 performance score @250nits
JEITA-BAT 3.0 (Video/Idle): up to 10.46 hr / 15.88 hr @200nits
Local video playback: up to 17.13 hr @150nits

Notes:

[1], [2] Rapid charge is only guaranteed when the computer is turned off or in standby mode or in hibernation mode. When the computer is powered on, the Charge Time will vary depending on system power consumption and AC adapter power.

[3] Configuration 1: WUXGA (non-touch), AMD Ryzen™ AI 7 PRO 450, 8GB + 8GB DDR5-5600, Win 11, 57Wh battery, best power efficiency power mode
Configuration 2: WUXGA (non-touch), AMD Ryzen™ AI 5 435, 8GB + 8GB DDR5-5600, Win 11, 46,5Wh battery, best power efficiency power mode
Configuration 3: WUXGA (non-touch), AMD Ryzen™ AI 5 430, 32GB + 32GB DDR5-5600, Win 11, 46.5Wh battery, best power efficiency power mode

All battery life claims are approximate maximum and based on results using [MobileMark® 30](#), JEITA 3.0, continuous 1080p local video playback (using default Media Player in Fullscreen mode with 150nits brightness and default volume level), or Google Power Load Test (PLT) battery-life benchmark tests.
Actual battery life will vary and depends on many factors such as product configuration, software, wireless functionality, power management settings, and screen brightness.
The maximum capacity of the battery will decrease with time, ambient temperature and use.
Refer to [Microsoft® link](#) for more information about the Windows® Performance power slider.

Power Adapter

Power Adapter**^[1]

- 65W USB-C® (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim GaN (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C® slim GaN (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- No power adapter

Notes:

[1] AC adapter offerings depend on the country.

DESIGN

Display

Display**

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
14"	WUXGA	Non-	IPS ^[1]	400nits	Anti-	16:10	1000:1	45%	60Hz	89° / 89° /	3M™ DBEF5

	(1920x1200)	touch			glare			NTSC		89° / 89°	
14"	WUXGA (1920x1200)	Multi-touch	IPS ^[2]	400nits	Anti-glare	16:10	1000:1	45% NTSC	60Hz	89° / 89° / 89° / 89°	Eyesafe® Certified 2.0, 3M™ DBEF5
14"	WUXGA (1920x1200)	Non-touch	IPS ^[3]	500nits	Anti-glare	16:10	1500:1	100% sRGB	60Hz	89° / 89° / 89° / 89°	Low power, Eyesafe® Certified 2.0

Touchscreen

On-cell multi-touch, supports 10-point touch

Screen-to-Body Ratio

85.5%

Notes:

[1], [2], [3] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device

Pen

No support

Keyboard

6-row, spill-resistant, multimedia Fn keys, key travel 1.5mm / 1.35mm (Fn row & G/H/B), Copilot key

Keyboard Backlight

- LED backlight
- Non-backlight

UltraNav™

TrackPoint® pointing device, double-tap to open the TrackPoint® Quick Menu

Mylar® surface multi-touch 3-button Trackpad, 60 x 115 mm (2.36 x 4.53 inches)

Mechanical

Dimensions (WxDxH)^[1]

Models	Dimensions
Models with aluminium (top) and PC-ABS (bottom)	313.7 x 226 x 11.32/17.01 (front/rear), 21.7 (maximum) mm; 12.35 x 8.90 x 0.45/0.67 (front/rear), 0.85 (maximum) inches
Models with PC-ABS (top) and PC-ABS (bottom)	313.7 x 226 x 11.39/17.31 (front/rear), 22.9 (maximum) mm; 12.35 x 8.90 x 0.45/0.68 (front/rear), 0.90 (maximum) inches

Weight^[2]

Starting at 1.389 kg (3.06 lbs)

Case Color

Black

Case Material**

- Aluminium (top), PC-ABS (bottom)
- PC-ABS (top), PC-ABS (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

WLAN + Bluetooth^[1]

MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 Wi-Fi® + Bluetooth® 5.4

WWAN**

- Wireless WAN upgradable to 4G (with antenna ready)
- Snapdragon® X12 LTE Modem, 4G LTE CAT6, M.2 card, with embedded eSIM functionality
- Snapdragon® X12 LTE Modem, 4G LTE CAT12, M.2 card, with embedded eSIM functionality
- No support

SIM Card**

- KDDI eSIM Program 3-year (Japan)^[2]
- KDDI eSIM Program 3-year with international roaming (Japan)^[3]
- KDDI eSIM Program 4-year (Japan)^[4]
- KDDI eSIM Program 4-year with international roaming (Japan)^[5]
- KDDI eSIM Program 5-year (Japan)^[6]
- KDDI eSIM Program 5-year with international roaming (Japan)^[7]
- No physical SIM card included

Ethernet

Gigabit Ethernet, 1x RJ-45, supports Wake-on-LAN

NFC

- Near Field Communication
- No support

Notes:

[1] Wi-Fi® operation (including Wi-Fi® 6, Wi-Fi® 6E, Wi-Fi® 7, etc.) is subject to the regulatory requirements of each country. Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

[2], [3], [4], [5], [6], [7] KDDI eSIM Program has no physical SIM card inbox and is for special bid only.

Ports**Standard Ports**

- 1x USB-A (Hi-Speed USB)
- 1x USB-A (USB 5Gbps), Always On
- 1x USB-A (USB 5Gbps)
- 2x Thunderbolt™ 4, with USB PD 15-65W and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)

Optional Ports***

- 1x Nano-SIM card slot (WWAN support models)
- 1x Smart card reader

Docking**Docking**

Various docking solutions supported via Thunderbolt™ / USB-C®.

For more compatible docking solutions, please visit [Docking for ThinkPad® L14 Gen 7 \(AMD\)](#)

SECURITY & PRIVACY**Security****ThinkShield**

ThinkShield is a comprehensive security solution that encompasses hardware, software, and supply chain components. For more details, visit [here](#)

Security Chip

Discrete TPM 2.0, TCG certified, FIPS 140-3 certified

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader

- Smart card reader, supports ISO 7816 and EMV
- No smart card reader

Fingerprint Reader

- Touch style fingerprint reader integrated in power button, match-on-chip
- No fingerprint reader

BIOS Security

- Certificate-based BIOS authentication
- FIDO (Fast Identity Online) authentication
- NVMe® password
- Power-on password
- Supervisor password
- System management password
- Self-healing BIOS
- More BIOS security features, please visit [BIOS Simulator](#)

Other Security

- Camera privacy shutter
- (Optional) IR camera for Windows® Hello (facial recognition)
- Privacy Guard with Privacy Alert (software solution)

MANAGEABILITY

System Management

System Management

- DASH
- Non-DASH

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 1-year courier or carry-in with 2-year system board service (Korea only)
- 1-year limited onsite service
- 3-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) limited onsite service
- No base warranty

ACCESSORIES

Bundled Accessories

Bundled Accessories*[1]**

- Lenovo® HDMI® to VGA Monitor Adapter
- Lenovo® USB-C® to DisplayPort™ Adapter
- Lenovo® USB-C® to VGA Adapter
- None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for ThinkPad® L14 Gen 7 \(AMD\)](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage and transportation in original shipping packaging: -20°C (-4°F) to 60°C (140°F)
- Storage without packaging: 5°C (41°F) to 43°C (109°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

ENVIRONMENTAL

Sustainability

Material^[1]

50% recycled aluminium on top cover
50% PCC recycled on display cover bezel
60% PCC recycled on keyboard frame
Up to 50% PCC recycled on bottom cover
85% PCC recycled plastic used in key caps (backlight)
70% PCC recycled plastic used in key caps (non-backlight)
90% PCC recycled plastic used in speaker enclosure
90% PCC recycled plastic used in the battery pack enclosure
90% PCC recycled plastic used in slim GaN 65W adapters and standard 65W adapters
100% plastic-free primary packaging
TOTAL PCC: 24.23%-32.62%

Notes:

[1] PCC: Post Consumer Content, recycled materials from customers.

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 9.0
- EPEAT™ Gold Registered^[3]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

[3] EPEAT™ is registered where applicable, please visit epeat.net for registration status by country.

Other Certifications

Mil-Spec Test

MIL-STD-810H military test passed

Other Certifications

- (Optional) Eyesafe® Certified 2.0
- (Optional) TÜV Rheinland® Low Blue Light (Hardware Solution)

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.

- Feature with *** means that one or more options listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.

- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS",

WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



Copilot+PC

AMD



Copilot+PC

AMD



Copilot+PC

AMD



Copilot+PC

AMD



Copilot+PC

AMD



Copilot+PC

AMD