

ThinkEdge SE10

This next-level AI-edge platform is a powerful addition to an organization's IoT ecosystem and can modernize its surveillance system. Packed with Intel Atom X Series processor, up to 64GB DDR4 memory and up to 2 TB SSD storage, it's designed to empower enterprises and transform your normal IP camera into a computer-vision (CV)-enabled surveillance system. There are plenty of ports and wireless connectivity options to connect everything from sensors, IoT endpoints, and legacy devices to cloud-based servers.



Rugged compact performance primed for business

Lenovo's range of globally certified ThinkEdge® PCs gives modern businesses greater power in a smaller footprint, so reliable processing power can be discreetly tucked away at the edge of the business, ready for action.


Lenovo ThinkShield security solutions including a discrete TPM 2.0 chip for data encryption provide comprehensive end-to-end security, whether protecting against any potential data breach attempts or ensuring the security of the device itself.

Connectivity options include Wi-Fi, Bluetooth, 4G LTE or WWAN for transporting IoT data to the business cloud without any hassle.

With an ultra-small form factor, the SE10 packs more computing power into a smaller footprint. Easy to mount, it can be tucked behind a monitor, placed under the desk, or mounted on the wall—wherever you like it.

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Lenovo Professional Wireless Keyboard & Mouse

- Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection
- Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs
- Contoured design of the mouse suits both left-handed & right-handed users



PN: 4X30H56796

Lenovo Go Wireless Multi-Device Mouse

- Compact ambidextrous design, programmable Utility Button on the side, default functions optimized for Teams calls
- Connects to up to 3 devices via 1x USB-C dongle, 2x Bluetooth 5.0; quick switch button to jump control across devices
- Comes with a blue optical sensor that tracks on most surfaces and wireless Qi or wired USB-C fast-chargeable battery



PN: 4Y51C21217

ThinkEdge SE10



Performance

Processor

Intel Atom x6214RE, x6425RE

Operating System

IGEL Linux
Windows 11 IoT Enterprise LTSC 2024
Windows 10 IoT Enterprise LTSC 2021
Ubuntu Core 22 64 Bit (kernel 5.15)
Ubuntu (Server) 22.04 LTS 64 Bit (kernel 5.15)

Graphics

Intel UHD Graphics (integrated)

Memory

Up to 32GB DDR4-3200, 2x SO-DIMM

Storage ¹

SE10: One drive, up to 1TB M.2 SSD
SE10-I: Up to two drives, 64GB eMMC 5.1 on systemboard + 1x M.2 SSD
• M.2 SSD up to 1TB
• 64GB eMMC 5.1, for SE10-I (-20~60°C) only

¹The storage capacity supported is based on the test results with current
Lenovo storage offerings.

Power Supply *

SE10: 65W AC adapter
SE10-I: Industrial power inlet 9~36VDC or 65W AC adapter

Design

Dimensions ²

1.4L models (SE10-I (-20~60°C)): 179 x 135 x 60 mm (7.05 x 5.31 x 1.45 inches)
0.8L models (SE10 (0~50°C)): 179 x 135 x 34.5 mm (7.05 x 5.31 x 1.35 inches)

²The system dimensions may vary depending on configurations.

Weight ³

1.4L models (SE10-I (-20~60°C)): 2.0 kg (5.73 lb)
0.8L models (SE10 (0~50°C)): 1.5 kg (3.31 lb)

³The system weight is approximate and may vary depending on
configurations

Connectivity

Ethernet

2x 2.5GbE, 2x RJ-45

WLAN + Bluetooth *

SE10:
802.11ax (Wi-Fi 6), Bluetooth 5.1
Up to Intel Wi-Fi 6E AX210 11ax Bluetooth 5.1
SE10-I:
802.11ac (Wi-Fi 5) or 802.11ax (Wi-Fi 6), Bluetooth 5.1
Up to Intel Wi-Fi 6E AX210 11ax Bluetooth 5.1

WWAN *

4G LTE CAT4*

Front ports

2x USB 3.2 Gen 2
1x line-out (3.5mm)
1x microphone (3.5mm)
2x serial (RS232 / RS422 / RS485, BIOS selectable)
3x LED (LED1: storage / LED2: Wireless / LED3: User defined or WWAN)

SE10-I only:
4x DI / 4x DO *
2x RP-SMA Female, WWAN antenna*
Expansion IO*:
2x 2.5 GbE (RJ-45, PoE, PSE 15.4W)
or 2x CAN (BUS / OPEN)
or 2x Serial (RS232 / RS422 / RS485, Driver selectable)

Rear ports

2x USB 2.0
1x HDMI 1.4b
1x DisplayPort 1.4
2x 2.5GbE Ethernet (RJ-45)
2x RP-SMA Female, Wi-Fi antenna*

SE10-I only:
1x 2pin remote power switch
1x DC-in 3pin Phoenix connector for 9-36V WDC
1x Slim Tip power connector

Left ports

1x Nano SIM slot
1x SD card slot

Security & Privacy

Security

Discrete TPM 2.0
NITS SP800-147B compliant
ThinkShield

Lenovo services

Base Warranty

Up to 3-year limited onsite service

Certifications

Green Certifications ⁴

ErP Lot 6/26
Low Halogen
RoHS compliant
REACH
TED (ECO-declaration)
WEEE

⁴The items listed under the "Green Certifications" section may not only refer to
certification but also registration or self-declaration.

Other Certifications

Microsoft Azure IoT Edge certified, AWS IoT Greengrass certified, Ubuntu
Core certified, Ubuntu Server certified, Red Hat Enterprise Linux certified
EMC: EMC CE / FCC Class B, FCC, IC, RCM, VCCI, BSMI, CCC, CE, KCC
Safety: EAC, NRTL (ETL, cETL), Ukrsepro, CE, CM, CB, CCC, BIS, GS, KEBS,
KUCAS, KVALITET, NOM-019, SABS, SONCAP, STZ, UKCA
RF: CE, SRR, SUBTEL, UKCA, WPC, TELEC/JATE, IC, KCC, NBTC, NCC ,
NOM-208, NTC, SDPPI, SIRIM, ANRT, FCC
MIL-STD-810H military test passed

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.