

OVERVIEW



1. USB-C (USB 10Gbps), data transfer and 15W charging	7. USB-A (Hi-Speed USB)
2. Headphone / microphone combo jack (3.5mm)	8. USB-A (USB 10Gbps)
3. HDMI-in 1.4	9. HDMI-out 2.1 TMDS
4. Power-in	10. Kensington Security Slot *
5. USB-A (Hi-Speed USB)	11. Power button
6. Ethernet (RJ-45)	12. Camera shutter latch

- Notes:
- Items with * are only available on selected models
 - The Kensington security slot is only available on models launched after 2025/2/10.

PERFORMANCE

Processor

Processor Family

Intel® U-series, 13th Generation Intel® Core™ i3 / i5 / i7 Processor or Intel® H Series Core 5 / 7 Processor (Series 2)

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics
U300	5 (1 P-core + 4 E-core)	6	-	P-core 4.4GHz / E-core 3.3GHz	8MB Intel® Smart Cache	Intel® UHD Graphics
Core i3-1315U	6 (2 P-core + 4 E-core)	8	-	P-core 4.5GHz / E-core 3.3GHz	10MB Intel® Smart Cache	Intel® UHD Graphics
Core i5-13420H	8 (4 P-core + 4 E-core)	12	-	P-core 4.6GHz / E-core 3.4GHz	12MB Intel® Smart Cache	Intel® UHD Graphics
Core i7-13620H	10 (6 P-core + 4 E-core)	16	-	P-core 4.9GHz / E-core 3.6GHz	24MB Intel® Smart Cache	Intel® UHD Graphics
Core 5 210H	8 (4 P-core + 4 E-core)	12	P-core 2.2GHz / E-core 1.6GHz	P-core 4.8GHz / E-core 3.6GHz	12MB Intel® Smart Cache	Intel® Graphics
Core 7 240H	10 (6 P-core + 4 E-core)	16	P-core 2.5GHz / E-core 1.8GHz	P-core 5.2GHz / E-core 4GHz	24MB Intel® Smart Cache	Intel® Graphics

Operating System

Operating System**

- Windows® 11 Pro
- Windows® 11 Home
- Windows® 11 Home Single Language
- Ubuntu Linux
- No preload operating system

Graphics

Graphics^[1]

Graphics	Type	Memory	Max Resolution	Connector	Key Features
Intel® UHD Graphics	Integrated	Shared	4096x2160@60Hz(HDMI®)	1x HDMI® 2.1 TMDS	DirectX® 12.1

Notes:

[1] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

Monitor Support

Monitor Support

Supports up to 2 independent displays via native display and 1 external monitor; supports external monitor via HDMI®

Chipset

Chipset

Intel® SoC (System on Chip) platform

Memory

Max Memory^[1]

Up to 32GB DDR5-5200

Memory Slots

Two DDR5 SODIMM slots, dual-channel capable

Memory Type

DDR5-5200

Notes:

[1] The max memory is based on the test results with current Lenovo® memory offerings.

Storage

Max Storage Support^[1]

One drive, up to 1TB M.2 2280 SSD

Storage Type**

Disk Type	Interface	Security
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	-
M.2 2280 SSD	PCIe® NVMe®, PCIe® 4.0 x4	Opal 2.0

Notes:

[1] The max capacity of each disk type is based on the test results with current Lenovo® storage offerings.

Removable Storage

Optical

None

Card Reader

No card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC233-CG codec

Speakers

Stereo speakers, 3W x2, Audio by HARMAN

Microphone

Dual-microphone array

Camera**

- 5.0-megapixel
- 5.0-megapixel IR camera

Power Supply

Power Supply**

Power	Type	Efficiency	Key Features
90W	Adapter	89%	Autosensing
135W	Adapter	90%	Autosensing

DESIGN

Display

Display**^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Refresh Rate	Viewing Angle (L/R/U/D)	Key Features
23.8"	FHD (1920x1080)	Multi-touch	IPS	250nits	Anti-glare	16:9	1300:1	99% sRGB	100Hz	89° / 89° / 89° / 89°	14ms response time, borderless design, low blue light, flicker free
23.8"	FHD (1920x1080)	Non-touch	IPS	250nits	Anti-glare	16:9	1300:1	99% sRGB	100Hz	89° / 89° / 89° / 89°	14ms response time, borderless design, low blue light, flicker free

Touchscreen

- 10-point multi-touch
- Non-touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Input Device**Keyboard****

- Lenovo® Calliope Keyboard (USB connector), black
- Wireless EOS Keyboard, black
- No keyboard

Mouse**

- Lenovo® Calliope Mouse (USB connector), black
- Wireless EOS Mouse, black
- No mouse

Mechanical**Buttons**

- Camera Shutter Latch
- Power button

Form Factor

AIO (23.8 inches)

Dimensions (WxDxH)^[1]

540 x 192 x 431 mm (21.25 x 7.56 x 16.97 inches)

Packaging Dimensions (WxDxH)

670 x 229 x 553 mm (26.38 x 9.02 x 21.77 inches)

Weight^[2]

Around 6.0 kg (13.23 lbs)

Packaging Weight

Around 9.55 kg (21.05 lbs)

Case Color

Luna grey

Bays

No bays

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Stand

Monitor stand, supports -5° to +15° tilt.

Mounting

None

Others

(Optional) Wireless charger 15W

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY**Network**

WLAN + Bluetooth®^[1]**

- Realtek® Wi-Fi® 6 RTL8852BE, 802.11ax Dual Band 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 card
- Intel® Wi-Fi® 6 AX201, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.2, M.2 card
- No WLAN and Bluetooth®

Onboard Ethernet

Gigabit Ethernet, Realtek® RTL8111H, 1x RJ-45

Notes:

^[1] Wi-Fi® operation (including Wi-Fi® 6, Wi-Fi® 6E, Wi-Fi® 7, etc.) is subject to the regulatory requirements of each country. Bluetooth® may operate at a lower version than hardware design depending on the factors such as operating system, driver, etc.

Ports^[1]**Rear Ports**

- 1x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 1x HDMI®-in 1.4
- 1x HDMI®-out 2.1 TMDS
- 1x Ethernet (RJ-45)
- 1x power connector

Left Ports

- 1x headphone / microphone combo jack (3.5mm)
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), data transfer and 15W charging

Notes:

^[1] The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

USB 2.0: 480 Mbit/s;

USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;

USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;

USB4® 20Gbps / USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;

USB4® 40Gbps (USB 40Gbps): 40 Gbit/s;

Thunderbolt™ 3/4: 40 Gbit/s.

Thunderbolt™ 5: 80 Gbit/s (bidirectional), up to 120 Gbit/s in bandwidth boost mode for video-intensive applications.

SECURITY & PRIVACY**Security****Security Chip**

Firmware TPM 2.0 integrated in SoC

Physical Locks

Kensington® Security Slot™, 3 x 7 mm^[1]

Chassis Intrusion Switch

No chassis intrusion switch

BIOS Security

- Administrator password
- Boot sequence control
- Boot without keyboard and mouse
- Intel® BIOS guard
- Power-on password
- Never crash Self-healing
- Secure boot
- More BIOS security features, please visit [BIOS Simulator](#)^[2]

Notes:

^[1] The Kensington® security slot is standard on models manufactured on or after February 10, 2025. For models

manufactured before this date, the Kensington® security slot may not be configured, please refer to the actual product.
[2] The BIOS simulator is just for reference. Default settings and some options may vary depending on the hardware, operating system and BIOS version.

MANAGEABILITY

System Management

System Management

None

SERVICE

Warranty^[1]

Base Warranty**

- 1-year courier or carry-in service
- 1-year limited onsite service

Notes:

[1] The warranty upgrades may be bundled with some models, please check the "Included upgrade" column in the specific model's configurations. For more service extensions, please go to <https://smartfind.lenovo.com/>. To learn more details of warranty policy, please access <https://support.lenovo.com/warrantylookup/warrantypolicy>.

OPERATING REQUIREMENTS

Operating Environment

Temperature

- Operating: 5°C (41°F) to 35°C (95°F)
- Storage: -20°C (-4°F) to 60°C (140°F)

Relative Humidity

- Operating: 20% to 80%
- Storage: 10% to 90%

Altitude

- Operating: 0 m (0 ft) to 3048 m (10,000 ft)
- Storage: 0 m (0 ft) to 12192 m (40,000 ft)

ENVIRONMENTAL

Sustainability

Material

65% PCC ABS bezel
95% PCC recycled plastic used in USB keyboard/mouse
90% PIC recycled plastic EPE cushion
30% OBP used in bag
FSC certified paper in packaging

CERTIFICATIONS

Green Certifications^[1]

Green Certifications

- (Optional) ENERGY STAR® 8.0
- (Optional) EPEAT™ Gold Registered
- ErP Lot 3/7
- GREENGUARD®
- RoHS / WEEE / REACH

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

Other Certifications

Other Certifications

- TÜV Rheinland® Flicker Free
 - TÜV Rheinland® Low Blue Light
 - TÜV Rheinland® Ultra Low Noise
-
- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
 - Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS", WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
 - The specifications on this page may not be available in all regions, and may be changed or updated without notice.

