

Specifications

Eaton PR25

TAA-Compliant 25-Amp DC Power Supply,
13.8VDC, Precision Regulated AC-to-DC
Conversion - Not for sale in the USA.

General specifications

PRODUCT NAME	Eaton Tripp Lite series DC power supply
CATALOG NUMBER	PR25
UPC	037332060037
PRODUCT LENGTH/DEPTH	14.1 in
PRODUCT HEIGHT	7 in
PRODUCT WIDTH	7.1 in
PRODUCT WEIGHT	13.98 lb

Product specifications

FEATURES	Flex Center
INPUT FREQUENCY	60Hz
INPUT CURRENT	5
OUTPUT NOMINAL VOLTAGE	13.8V (+/- 0.5VDC)
OUTPUT VOLTAGE REGULATION	0.15V Max Ripple Voltage
OUTPUT CONNECTOR TYPE	1/4" DC Terminal Posts support Ring and U Style connectors or bare wire.
RECOMMENDED ELECTRICAL SERVICE	120V 15A
SWITCHES	Lighted (Red) ON/OFF Rocker Switch - Illuminates Red when in ON position indicating DC output is available
INPUT PLUG TYPE	NEMA 5-15P
INPUT CORD LENGTH	6 ft
UNIT WEIGHT	18.739 lb
OUTPUT CAPACITY DETAILS	25A Intermittent Communication System (ICS); 20A Continuous Duty Amps
OPERATING TEMPERATURE RANGE	32° to 104°F (0°C to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
OPERATING HUMIDITY RANGE	0 to 95% humidity, non-condensing
INPUT NOMINAL VOLTAGE	120 VAC
INTERMITTENT AMPS	25

Resources

MANUALS AND USER GUIDES

[Owner's Manual for PR/TL Power](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

