

S1102

AMD EPYC™ 4004 Server Barebone



SPECIFICATIONS

Dimensions (Width x Height x Depth)

438.5mm x 43.5mm x 547.6mm [21.56" deep] (Air Cooled)
438.5mm x 43.5mm x 660mm [26" deep] (Liquid Cooled)

Processor

Single AMD Socket AM5, supports EPYC™ 4004 / AMD Ryzen™ 7000 Processor
Maximum CPU TDP up to 105W (Air Cooled SKU)
Maximum CPU TDP up to 170W (Liquid Cooled SKU)

Chipset

AMD B650

Memory

(4) DDR5 DIMM slots, 2DPC, ECC/non-ECC UDIMM
Max. Frequency 5200MT/s(1DPC) and 3600MT/s(2DPC)
Max. Capacity per DIMM: 48GB

Expansion Slots

(1) PCIe 4.0 x16 slot from CPU support FHHL PCIe card

Networking

(2) 10GBase-T Ethernet ports (Intel® X710AT2)

Storage

(4) Hot-swap front 3.5"/2.5" drive bays support SATA 3.0
(2) Internal 2.5" drive bays support SATA 2.0
(2) M.2 2280/22110 PCIe4.0 x4 ports

Server Management

(1) 1000Base-T Dedicated Server Management Port
ASPEED AST2600 with AMI MegaRAC based firmware supporting IPMI 2.0 and DMTF Redfish API

Security

(1) TPM header with SPI interface supports TPM2.0

1U AMD EPYC 4004 Server with Optional Liquid Cooler

- (1) AMD Socket AM5 EPYC 4004 / Ryzen 7000 Processor
- Optional closed loop liquid cooling with TDP up to 170W
- (4) DDR5 DIMM slots (2 memory channels)
- (6) SATA 3/6G drive bays (four front 3.5" + two internal 2.5")
- (2) 10GBase-T Ethernet ports
- (1) PCIe Gen4 x16 slot

Applications

Private cloud, email server, object storage server, web-hosting, computer assisted design (CAD), backup system application, small office server

Front I/O

- (4) Hot-swap 3.5"/2.5" drive bays
- (2) USB3.2 Gen1 Type-A ports
- (1) System power button
- (1) UID button
- (1) UID LED
- (5) Status LEDs: Power/Fault/HDD/(2)LAN

Rear I/O Ports

- (2) 10GBase-T Ethernet Ports
- (1) 1000Base-T Dedicated Server Management Port
- (4) USB3.2 Gen1 Type-A Ports
- (1) VGA D-Sub Port
- (1) COM DB9 Port
- (1) UID LED Button

Power Supply

- (1+1) 450W Redundant PSU 80+ Platinum (Air Cooled SKU)
- (1+1) 600W Redundant PSU 80+ Platinum (Liquid Cooled SKU)

Environmental

System Operating Temperature: 0°C ~ 35°C
Non-operating Temperature: -20°C ~ 70°C
Non-operating Relative Humidity: 5% to 85% (non-condensing)


Regulatory

FCC (Class A), CE

Package Contents

- (1) 1U Barebone
- (1) Quick guide
- (1) Slide rail kit
- (1) Vaper chamber air cooling module (Air Cooled SKU)
- (1) Closed loop liquid cooling module (Liquid Cooled SKU)
- (4) Power cables

S1102 System Block Diagram




Learn more about MSI servers
visit <https://eps.msi.com>

Top View



S1102-01 (Air Cooled) Top System View



S1102-02 (Liquid Cooled) Top System View

Specifications are subject to change without notice. Please visit our website for the latest information.



Headquarters Tel: +886-2-32355599
eps.business@msi.com

USA Tel: +1-8884476546
epssales@msi.com

© 2024 Micro-Star Int'l Co.Ltd. MSI is a registered trademark of Micro-Star Int'l Co.Ltd. All rights reserved.