


REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	09/26/2018
B	ADD SCREEN PRINTING LOGO	12/06/2018




ELECTRICAL TEST :

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms
- 5.100% of image Test

PRODUCT SPECIFICATIONS :

- 1.Connector Type: MINI DisplayPort MALE TO VGA FEMALE
- 2.Connector Plating and Material:
MINI Display Port to VGA Adapter VGA Plug Nickel Plated Grey Insulation Terminal+PCB
MINI DisplayPort M Shell Nickel Plated Terminal Gold Plated 3U" White Insulation
- 3.Color: Black connectors and Black Cable
- 4.RoHS 2.0: Yes
- 5.Resolution Supported: 1920X1200 / 60Hz
- 6.Cable Specifications:
DISPLAY PORT UL20276[34AWG(7/0.06TC)*1P+EAM]*3C+32AWG(7/0.08TC)*5C
+AEB (16/7/0.12MM 85%AL) OD:4.5MM Black

PIN Assignment



The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL ±
ANGULAR: MACH ± BEND ±
TWO PLACE DECIMAL ±
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC TOLERANCING PER:
MATERIAL: CRS
FINISH: POWDER COAT
DO NOT SCALE DRAWING

BLACK BOX			
DRAWN	NAME	DATE	TITLE:
JX YAO		09/26/2018	MDP to VGA Adapter
ENG APPR.	CHECKED		SIZE DWG. NO.
	COMMENTS		B ENVMPD-VGA
			REV B
			SCALE: 1:1
			SHEET 1 OF 1