





REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	2016.09.20



PIN Assignment					
C1	C1	6	6	16	16
C2	C2	7	7	17	17
C3	C3	8	8	18	18
C4	C4	9	9	19	19
C5	C5	10	10	20	20
1	1	11	11	21	21
2	2	12	12	22	22
3	3	13	13	23	23
4	4	14	14	24	24
5	5	15	15	SHELL	SHELL

**ELECTRICAL TEST:**

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms
- 5.100% of image Test

**PRODUCT SPECIFICATIONS :**

- 1.Connector Type: DVI-I FEMALE TO FEMALE
- 2.Connector Plating and Material:  
DVI-I FEMALE Shell Nickel Plated
- 3.Color: Black DVI connectors and Black PVC
- 4.RoHS2: Yes
- 5.Resolution Supported: 2560 x 1600
- 6.Cable Specifications:  
UL1007 28AWG Black OD:1.2mm
- 7.Passive Adapter Supports TMDS

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ±  
ANGULAR, RAD, MAX ± BEND ±  
TWO PLACE DECIMAL ±  
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC TOLERANCING PER

MATERIAL CRS

FINISH POWDER COAT

DO NOT SCALE DRAWING

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.  
©Copyright 2012 Black Box Corporation of Pennsylvania a/e/o Black Box Network Services. All Rights Reserved.



NAME	DATE	TITLE
AXJing	9/20/2016	DVI FEMALE TO FEMALE ADAPTER
DRAWN		
ENG APPR.		
CHECKED		
COMMENTS		
SIZE	DWG. NDL	REV
B	VA-DVI-CPL	A
SCALE: 1:1	SHEET 1 OF 1	