



## VSM-4x4A

4x4 Seamless AV Matrix  
Switcher/Multi-Scaler

| HDMI | Ethernet - RJ-45 | HDCP Compliant



VSM-4x4A is a 4x4 seamless matrix switcher that can also be used as a video wall driver (2x2 or 1x4) or dual and quad multi-viewers. The unit enables switching between inputs with a clean video cut (frame-to-frame switching with no glitches). It supports HDMI resolutions with deep color, up to eight channels of audio and includes per-port HDCP and EDID settings

## FEATURES

**PixPerfect™ Scaling Technology** - Kramer's precision pixel mapping and high-quality scaling technology

**HDTV Compatible**

**HDCP Compliant**

**4 HDMI Inputs & 4 Scaled HDMI Outputs**

**Audio** - 4 balanced and 4 unbalanced audio outputs with independent volume settings per output, embedded audio on the HDMI inputs and outputs

**Selectable Operation Modes** - 4x4 matrix switcher, video wall (2x2 or 1x4 configuration), dual display (Split/PIP/POP) or quad display

**Bezel Correction Options** - In video wall mode

**Matrix Switching Modes** - Seamless switching mode (zero-time video cuts), or fade-through-black mode (enabling independent output resolutions)

**Constant Output Sync** - For all modes of operation

**HDMI Support** - Deep Color, Dolby Digital Plus, DTS, DTS-HD®, LPCM 2CH/6CH/8CH, AC3

**Per Port HDCP and EDID Settings**

**Input Resolution Range** - VGA to WUXGA and 480i to 1080p

**Output Resolution Range** - 480p to 1080p

**Multiple Aspect Ratio Selections** - Full, 4:3, 16:9 and best fit

**Built-in ProcAmp** - Color, hue, sharpness, noise, contrast and brightness

**Front Panel Control** - Operation mode, TAKE button and menu buttons

**4 Preset Memory Locations** - For each operation mode for quick access to common IN-OUT configurations

**Front Panel Lockout**

**Non-Volatile Memory** - Saves final settings

**Additional Internal Memory** - Supports larger firmware code

**Firmware Upgrade** - Via Ethernet or the program mini USB connector

**Varied Control Options** - Front panel buttons, RS-232 serial commands transmitted by a touch screen system, PC, or other serial controller; infrared remote control transmitter with OSD (on-screen display), Ethernet with built-in web pages



## TECHNICAL SPECIFICATIONS

INPUTS:	4 HDMI connectors (HDMI, HDCP version 1.1)
OUTPUTS:	4 HDMI connectors (HDMI, HDCP version 1.1), 4 balanced stereo audio on terminal block connectors, 4 unbalanced audio on 3.5mm mini jacks
PORTS:	1 RS-232 on 9-pin connector, 1 Ethernet on RJ-45 connector, 1 USB on Type-A connector
OUTPUT RESOLUTIONS:	NATIVE, 480p, 576p, 720p50, 720p59, 720p60, 1080p24, 1080p50, 1080p60, 1024x768, 1280x800, 1280x1024, 1366x768, 1440x900, 1600x900, 1680x1050 or 1920x1200
VIDEO LATENCY:	Progressive input: 30ms (typical)
CONTROLS:	Front panel buttons, IR with customized remote control, RS-232, Ethernet with built-in Web pages, USB port for programming
POWER SOURCE:	100–240V AC, 27VA max
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F)
STORAGE TEMPERATURE:	–40° to +70°C (–40° to 158°F)
HUMIDITY:	10% to 90%, RHL non-condensing
INCLUDED ACCESSORIES:	Power cord, rack ears, IR remote control
Product Dimensions	19" x 9.34 x 1U (43.6cm x 23.72cm x 4.36cm) W, D, H
Product Weight	1.8kg (4.0lbs) approx
Shipping Dimensions	52.50cm x 33.00cm x 10.70cm (20.67" x 12.99" x 4.21" ) W, D, H
Shipping Weight	2.7kg (6.0lbs) approx

