




NOTE:

- 1.CABLE: JUMP WIRE UL1061 28AWG  
MANUFACTURER:SPACE SHUTTLE HI-TECH CO,LTD
- 2.CONNECTOR: DVI(12+5) M INSULATOR BLACK PIN G/F NICKEL PLATED SHELL  
MANUFACTURER: SWEETRAY &EQUIVALENT
- 3.CONNECTOR: HDD15P F+UNC INSULATOR BLACK PIN G/F NICKEL PLATED SHELL  
MANUFACTURER: SWEETRAY &EQUIVALENT
- 4.SCREW: 0.187"\*1.08"  
MANUFACTURER: BAN JUN &EQUIVALENT
- 5.MOLDING PVC COLOR:BLACK  
MANUFACTURER:SPACE SHUTTLE HI-TECH CO,LTD

ELECTRIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M (MIN)
- D.CONDUCTIVE RESISTANCE: 2 (MAX)

PIN OUT

| CN1   | CN2   |
|-------|-------|
| C1    | 1     |
| C2    | 2     |
| C3    | 3     |
| C4    | 13    |
| C5    | 6,7,8 |
| 6     | 15    |
| 7     | 12    |
| 8     | 14    |
| 14    | 9     |
| 15    | 5.10  |
| 16    |       |
| SHELL | SHELL |

| BLACK BOX® |   |               |  |                  |
|------------|---|---------------|--|------------------|
| Tolerance: |   | Approved by:  |  |                  |
| X.         | ± | Checked by:   |  | BLACK BOX P/N:   |
| .X         | ± | Drawn by:     |  | FA461            |
| .XX        | ± | jun           |  | Description:     |
| .XXX       | ± | Date:         |  | DVI M / HDD 15 F |
| Angle:     |   | 11.07.23      |  | DWG. NO:         |
| X"         | ± | Scale:        |  |                  |
| .X"        | ± | Unit: inch    |  |                  |
|            |   | SHEET: 1 OF 1 |  | REV: 00          |

| REV | ECN NO | DESCRIPTION | APPD. | DATE |
|-----|--------|-------------|-------|------|
|     |        |             |       |      |
|     |        |             |       |      |
|     |        |             |       |      |
|     |        |             |       |      |
|     |        |             |       |      |