



CN1	PIN OUT	CN2
1	RED/COAX	1
2	GREEN/COAX	2
3	BLUE/COAX	3
4	BLACK	4
5	BROWN	5
6	RED/Spiral	6
7	GREEN/Spiral	7
8	BLUE/Spiral	8
9	YELLOW	9
10	ORANGE	10
11	GREEN	11
12	VIOLET	12
13	RED	13
14	BLUE	14
15	GRAY	15
	SHELL — BRAID — SHELL	

NOTE:

- 1.CABLE: 1354(S)28#*3C+24#*9C+AEB 85% COLOR: BEIGE OD: 8.5mm
MARKING: BLACK BOX CORPORATION GUARANTEED FOR LIFE (724)
746-5500 E223179(UL)TYPE CL2 3C/28AWG AND 9C/24AWG 75°C
- 2.CONNECTOR: HDD15M BLUE INSULATOR NICKEL SHELL
- 3.THUMBSCREW: HD 8*50mm K022
- 4.FERRITE CORE: CORE: 0.68"*1.12"*0.37"
- 5.PVC: BEIGE 45P
- 6.LABEL: P/N LABEL
- 7.COVER: DUST COVERHDD15PTRANSPANRENCE.
- 8.LABEL: YEAR/MONTH LABEL

ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 0<L<10FT 2 ohm (MAX)
10FT<L<15FT 3 ohm (MAX)
15FT<L<30FT 4 ohm (MAX)
30FT<L<100FT 6 ohm (MAX)
L>100FT 10 ohm (MAX)

BBOX P/N	LENGTH
EVNPS06-0003-MM	3FT
EVNPS06-0005-MM	5FT
EVNPS06-0010-MM	10FT
EVNPS06-0015-MM	15FT
EVNPS06-0020-MM	20FT
EVNPS06-0025-MM	25FT
EVNPS06-0035-MM	35FT
EVNPS06-0050-MM	50FT
EVNPS06-0075-MM	75FT
EVNPS06-0100-MM	100FT

REV	ECN NO	DESCRIPTION	APPD	DATE
07	980601001			09.06.02
06	960622001		Wayne	03.01.18
09	R101215002		Jingxu	11.02.10
08	R100122008			10.01.23

BLACK BOX

Tolerance:	Approved by:	
X. ±	Checked by:	BLACK BOX P/N: EVNPS06-****-MM
.X ±	Drawn by:	Description: Video Cable
.XX ±	Jingxu	
.XXX ±	Date:	DWG. NO:
Angle:	11.02.10	
X* ±	Scale:	Unit: inch
.X* ±		SHEET: 1 OF 3

REV: 09