


Overview

Rated up to 1500 VA / 1340 Watts, the new HP UPS R1500 XR features a 2U rack-mountable design, and an improved easy-to-configure front panel display. Ideal for rack-mountable storage and server environment, this Uninterruptible Power System (UPS) is an enhancement of the legacy R1500 UPS, and is an integral part of the proven family of HP Power Management Products. The new UPS R1500 XR is a high power density solution, designed for customers who want to provide power protection in space-constrained rack enterprise environments. In addition, the new UPS R1500 XR has the capability of being connected to two, maximum, optional Extended Runtime Modules (ERM). Customers can further increase the run-time on their UPS R1500 XR by using this ERM. The Compaq UPS "XR" models denote "eXtended Runtime Capable" UPS models. This product is a refresh of our existing R1500 UPS, and brings increased power density and innovative features to the proven HP family of rack-mountable UPS products.



- | | |
|---|---------------------------------|
| 1. LED indicating Overload capacity | 10. ON Button |
| 2. LED indicating 76% to 100% load capacity | 11. General Alarm |
| 3. LED indicating 51% to 75% load capacity | 12. On Battery |
| 4. LED indicating 26% to 50% load capacity | 13. Bad Battery/Low Battery |
| 5. LED indicating 0% to 25% load capacity | 14. Site Wiring Fault Indicator |
| 6. Configure mode on LED* | 15. Utility LED |
| 7. Configure Button* | A. Voltage Configuration Panel* |
| 8. TEST/ALARM RESET Button | |
| 9. STANDBY Button | |
- *Accessible only when the front bezel is removed

Models

UPS R1500 XR - Low Voltage (US)	204404-001
UPS R1500 XR - Low Voltage (JPN)	204404-291
UPS R1500 XR High Voltage (INT'L)	204404-B31
Extended Runtime Module (ERM), R1500 XR (WW)	218971-B21

Overview

Key Features

- Increased power density with up to 1500VA/1340Watts of power packed in just 2U rack space
- Greater system uptime with support for Extended Runtime Module (ERM)
- Easy configuration through enhanced front panel display
- Enterprise-wide intelligent manageability with bundled power management software
- Support for HP Option Cards that extend the power management capabilities of the UPS
- More efficient voltage regulation with revolutionary technology
- Ultimate long-term battery reliability with HP Enhanced Battery Management
- Enhanced system flexibility with two independently controlled load segments
- Support for Remote Emergency Power Off (REPO) circuitry
- Easy serviceability through modular design
- Hot-Swappable Batteries
- Backed by a three-year warranty with the first year including parts and labor Pre-Failure warranty, and a \$25,000 load protection guarantee

NOTE: Certain restrictions and exclusions apply

Product Highlights

2U Power Packed Design

Rated up to 1500VA/1340W, the HP UPS R1500 XR packs more power in space-conserving rack-mount design, allowing you to support more critical equipment in your rack.

Increase System Uptime with Extended Runtime Modules

The Extended Runtime Modules are rack mounted battery modules that occupy 2U (3.5 inches) of rack space. The UPS R1500 XR supports two, maximum, Extended Runtime Modules (ERM), which extend your overall battery runtime.

Lower Cost of Ownership with Innovative Technology

The UPS R1500 XR utilizes a line-interactive plus topology which features sine wave output and superior input/output voltage regulation. This technology is inherently reliable and highly efficient. The HP UPS can correct input voltage variations as low as -35% of nominal voltage without transferring to the battery. This will ensure the battery is preserved and ready for the next power anomaly

Investment Protection with HP Enhanced Battery Management

The UPS R1500 XR incorporates Enhanced Battery Management: an exclusive, patented technology that doubles battery service life, optimizes battery recharge time, and provides advance notice of pending battery failure. With Enhanced Battery Management, you have a lower total cost of ownership and receive the best in the industry protection for your critical equipment.

Enhanced System Flexibility with HP Option Cards

The UPS R1500 XR models are equipped with a standard serial communications port via an internal slot. This option slot supports two option cards, the Six Port Card and the SNMP / Serial Port Card. These option cards seamlessly integrate into the back of the R1500 XR and provide increased system flexibility.

Remotely Monitor UPSs on the Network

The SNMP/Serial Port Card features the ability to perform simultaneous network and out-of-band communications. It enables network administrators to remotely monitor UPSs and reboot network devices. It provides SNMP functionality, including power event alerts, network power diagnostics, and remote UPS reboot and testing. Used in conjunction with the provided Online power management software or SNMP capable Network Management Software, power-related problems on the network are quickly discovered and remedied.

Easy Configuration via Enhanced Front Panel Display

LED and switch membrane integrated into the front panel with four button controls (three buttons for UPS power control and one button under the front bezel for configuration)

Intelligent Manageability

HP Power Management Software, an integrated component of HP Insight Manager, the industry-leading hardware management platform, is included with the R1500 XR models. The HP Power Management Software enables you to monitor and control HP UPSs locally or remotely. This software is a versatile, fully configurable, alert response tool that gives system administrators a full overview of the network's conditions. It enables you to monitor system status and power conditions, configure shut down timing, customize alert messages, and perform UPS diagnostic checks quickly and easily.

Product Highlights

Independently Controllable Load Segments

With two load segments, you have the flexibility to configure scheduled startups and shutdowns, in addition to independently control the separate load segments. Working in conjunction with HP Power Management Software, the HP UPS R1500 XR can be configured to extend the runtime for more critical devices.

Ease of Maintenance with Hot-Swappable Batteries and Electronics Modules

The UPS R1500 XR is modular in design, and both the battery and the electronics modules are hot swappable. HP UPSs are designed with simple access through the front panel. Users can safely install new batteries and even the electronics module without ever powering down connected server and server options.

HP Quality

HP's hardware qualification is the toughest in the industry. Extensive evaluation, testing, product improvement, and an unsurpassed warranty guarantee the highest level of system protection, electrical performance, product quality and compatibility.

Warranty

The HP UPS R1500 XR is covered by a three year warranty, with the first year including parts and labor. Also, standard on all HP UPS units is our exclusive Pre-Failure Warranty which extends the advantage of a HP three-year, limited warranty by applying it to the battery before it actually fails. This warranty is offered worldwide. Specifically, the Pre-Failure Battery Warranty ensures that when customers receive notification from HP Power Management Software that the battery may fail, the battery is replaced free of charge under the warranty.

NOTE: \$25,000 Computer/Load Protection Guarantee is also provided, in addition to the HP three year, limited warranty.

Service and Support, HP Care Pack, and Warranty Information

HP Care Pack Installation

Hardware Installation (Electronic)

U4690E

HP Care Pack Services provide a range of life cycle support options that let you choose the service levels that meet your business requirements, from basis to mission-critical.

A full range of HP Care Pack hardware and software services are available including:

- Installation and start up
- Education courses
- Extended onsite hardware coverage hours from same business day 13 hours, 5 day to 24 hours, 7 days call window with options including 4-hour response or 6-hour Call to Repair
- Comprehensive range of software technical support for Microsoft, Linux, ProLiant essentials and VMware-based IT solutions helping to deliver high level of application availability. Response times range from 30 mins for critical problems to 2 hours.
- System Management, Performance Services and Mission Critical Support Solution

NOTE: For more information on HP Care Pack Services, contact any of our worldwide sales offices or resellers or visit our worldwide web site on the internet at: <http://www.hp.com/hps/carepack>

NOTE: For more complete information on HP Services offerings, customers and resellers, please visit us at: <http://www.hp.com/hps>

NOTE: Additional information regarding worldwide limited warranty and technical support is available at:

<http://h18004.www1.hp.com/products/servers/platforms/warranty/index.html>

NOTE: For additional information on Server Services, Rack and Power Options, please visit:

<http://h20219.www2.hp.com/services/cache/111072-0-0-225-121.html>

NOTE: The information contained herein is subject to change without notice and is provided "as is" without warranty of any kind.

NOTE: The warranties for HP products and services are set forth in the express limited warranty statements accompanying such products and services.

Warranty Upgrade Options

- Response – Upgrade on-site response from next business day to same day 4-hours
- Coverage – Extend hours of coverage from 5 days x 9 hours to 7 days x 24 hours
- Duration – Select duration of coverage for a minimum period of 1 year or multiple years

UPS R1500 XR Model Matrix

Part Number	Operating Voltage Settings	Power Out (VA/Watts)	Input Connection	Output Connection
Low-Voltage Models				
204404-001	120V	1440/1340	NEMA 5-15P	(6) 5-15R
204404-291	100V	1500/1340	NEMA 5-20P	(6) 5-15R
NOTE: Part Number 204404-001 is user selectable for 110V, 120V, or 127V via front panel.				
High Voltage Model				
204404-B31	230V	1500/1340	IEC-320 C14	(6) IEC 320-C13
NOTE: Part Number 204404-B31 is user selectable for 220V, 230V, or 240V via front panel.				
Kit Contents	HP UPS R1500 XR HP Power Management Software CD Power Products Documentation CD Depth adjustable fixed rack mounting rails Communications cable (12 ft) Additional IEC to IEC jumper cords, and detachable country specific input cord with the high voltage INTL model			
Unit Dimensions	19.1 x 3.4 x 17.0 in (48.51 x 8.64 x 43.18 cm)			
Shipping Dimensions	32 x 11.5 x 26.75 in (81.28 x 29.21 x 67.95 cm)			
Unit Weight	50 lb (23 kg)			
Shipping Weight	76 lb (34.5 kg)			

Technical Specifications

Electrical Input	Voltage Range	100, 120 and 230V models. See Model Matrix for nominal and user selectable voltage settings
	Frequency	50/60 Hz \pm 5Hz (auto sensing)
	Input Plug	See Model Matrix
	Online Efficiency	95%
	Surge Suppression	High Energy 6500A peak
Electrical Output	REPO	Remote Emergency Power-Off disables AC power to load
	Online Regulation	-10% to +6% of nominal voltage
	On battery Regulation	\pm 5% of nominal voltage
	Voltage Wave Form	Sine wave
	Connections	See Model Selection Matrix; divided into 2 Load Segments
Battery	Output Protection	Re-settable circuit protectors
	Type	Maintenance-free, sealed, valve-regulated lead acid (VRLA)
	Extended Batteries	ERM with two battery strings
	Backup Time	See Backup Times Chart
	Recharge Time	<3 hours to 80% usable capacity; <24 hours for complete recharge
Communications	Voltage	48V Battery String
	Serial Ports	Standard DB-9 ports (ships with communication cable)
	Option Slot	One
	Option Cards	Six Port Card and SNMP / Serial Port Card
	LED Indicators	LED and switch membrane integrated into the front panel; with four-button control (three buttons for UPS power control and one button under the front bezel for configuration).
Environmental and Safety	Software	Compaq Power Management Software
	Operating Temperature	50° to 104° F (10° to 40° C)
	Transit Temperature	-13° to 131° F (-25° to 55° C)
	Storage Temperature	32° to 77° F (0° to 25° C)
	Humidity (Operation)	20% to 80% (non-condensing)
	Humidity (Non-operating)	5% to 95%
	Operating Altitude	Up to 10,000 ft (3048 m) above sea level
	Storage Altitude	30,000 ft (9,144 m) above sea level
	Audible Noise	<46db (at 1m from surface of unit)
	Safety Markings	FCS, UL, CSA, VDE, NEMKO, FIMKO, DEMKO, SEMKO, NOM
	Safety Certifications	UL1778; CSA22.2 No.107.1, No.107.2, No.950; CB Bulletin No.86A1; EN50091-1; EN60950; EMKO-TSE207/95; NOM-019-SCFI-1993
	EMC Markings	FCC; CISPR; VCCI; CE
	Emissions	FCC CFR 47, Part 15 Class A, EN50091-2
	Immunity	IEC 801-2, IEC 801-3, IEC 801-4, IEC 801-5
	Surge Suppression	Conforms to IEEE 587B and ANSI C62.41
REPO Port	Meets NEC code 645-11 intent and UL requirements	

Estimated Backup Times Chart (Minutes)

Technical Specifications

Load (Percent*)	With Standby Battery	With 1 ERM	With 2 ERMs
20	34	146	290
50	13	57	161
80	6	32	63
100	5	23	49

* Percent of 1500VA or 1340W of load

NOTE: Backup times are estimated for typical applications. Actual performance will depend on load and battery conditions.

Compatibility Compatible with all HP servers, storage, racks, rack options, and other rack mountable HP equipment.

© Copyright 2005 Hewlett-Packard Development Company, L.P.
The information contained herein is subject to change without notice.

Microsoft and Windows NT are US registered trademarks of Microsoft Corporation. Intel is a US registered trademark of Intel Corporation. Unix is a registered trademark of The Open Group.

The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.