



HyperX QuadCast 2 - USB Microphone (Black) (872V1AA)

Overview

The New Standard.

The HyperX QuadCast 2 refines everything that made the original such a favorite amongst gamers, streamers, and content creators around the world. All the fan-favorite features are still here: the iconic stunning lighting, the tap-to-mute sensor, 4 selectable polar patterns, the 3.5mm headphone jack, and included shock mount and desktop stand but now with a range of innovative additions packaged in a new sleek, full aluminum silhouette. QuadCast 2 features upgraded 24-bit, 96kHz recording for a studio-quality recording experience. It also features a redesigned detachable shock mount with improved performance and innovative spring-loaded pins, making removal easy and allowing the use of universal shock mounts[1]. In response to our fan's feedback, QuadCast 2 now includes a multi-function knob so you can do everything on-board without needing to alt-tab. The knob allows users to choose between microphone gain, playback volume, and microphone monitoring volume, and can also switch polar patterns. The LED indicator also makes it easy to determine the current mic status without the hassle of going into the software. Users can choose different lighting effects and tune their mic via HyperX NGENUITY. The HyperX QuadCast 2 – the new standard for streaming microphones.



Hi-Res Studio-Quality Recording

The QuadCast 2 will help take your recordings to the next level by capturing more sound detail and allowing the subtleties of your voice to shine through.

Intuitive On-Board Controls

The multifunction knob lets you quickly and easily adjust your microphone gain, playback volume, monitoring volume, and switch between 4 polar patterns.

Tap-to-Mute Sensor

Simply tap the top of the QuadCast 2 to prevent audio accidents and quickly mute the microphone.

Mic Status LED indicator

The easy-to-see LED indicator and customizable grille lighting lets you spot whether or not the mic is live.

[1] Universal shock mount must be able to accommodate 55mm mic diameter and not obstruct multifunction knob.

Specifications

Weight	Weight (Microphone) 335 g; (Shock mount and stand) 137 g; (Microphone stand) 273 g; Total Weight (with cable) 819 g.
Weight	Weight (Microphone) 11.8 oz; (Shock mount and stand) 4.8 oz; (Microphone stand) 9.6 oz; Total Weight (with cable) 28.8 oz.
UPC number	197497651058
Manufacturer Warranty	2 year
What's in the box	HyperX QuadCast 2 USB Microphone, 3m USB-C to USB-C cable, USB-C to USB-A adapter, Quick Start Guide.

Additional specifications

Bit-depth	16-bit, 24-bit
Cable length	3 m
Cable length (imperial)	9.84 ft
Cable type	USB-C to USB-C with USB-A adapter
Color	Black
Compatibility	PC, Mac, PS4, PS5, Nintendo Switch, Steam Deck. Software Compatibility: HyperX NGENUITY.
Connection type	USB-C, 3.5mm headphone output
Datasheet photo 1	https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08913126.png
Datasheet photo 2	https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08913096.png
Datasheet photo 3	https://ssl-product-images.www8-hp.com/digmedialib/proding/lowres/c08913276.png
Datasheet photo 5	Publication logos/HyperX_header_bydefault.png
Element	Three 14mm electret condenser capsules
Frequency response (headphone)	20Hz - 20kHz
Handle	hyperx-quadcast-2-usb-microphone
High-pass filter	'-3dBf@75Hz, -12dB/Oct
Impedance	1 Ω
Light effects	16 zones
Lighting	Red
Multiple order quantity	Minimum Purchase Quantity corresponds to the Carton's Units Quantity.
Noise (RMS) (headphone)	\leq -110dBV (A-weighted)
Noise (RMS) (microphone)	\leq -77dBV (A-weighted)
Polar pattern	Cardioid, omnidirectional, stereo, bidirectional
Power consumption	5V 240mA (all lights on)
Power output maximum	\geq 7mW
Product long name specifications	HyperX QuadCast 2 – USB Microphone for Gaming, Streaming and Podcasting, with On-Board Controls, LED Lighting, Removable Shock Mount, PC, Mac, PS5, PS4, USB-C - Black.
Published	draft
Sampling rates	44.1kHz, 48kHz, 96kHz
Sensitivity (microphone)	'-7.5dB (1V/Pa at 1kHz)
Signal-to-noise ratio	\geq 100dB (at 1kHz/0dBFS, A-weighted)
Status	FALSE

Total harmonic distortion	≤ 0.05% (1kHz/0dBFS)
----------------------------------	----------------------

UNSPSC code	52161520
--------------------	----------

USB audio class	UAC-1
------------------------	-------

USB specification	USB 2.0 (full speed)
--------------------------	----------------------

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 17, 2024 2:54 PM UTC+0000