



REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	11/01/2018



**ELECTRICAL TEST :**


- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE: 2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms
- 5.100% of image Test



**PRODUCT SPECIFICATIONS :**

- 1.Connector Type: MINI DisplayPort MALE TO DVI FEMALE
- 2.Connector Plating and Material:  
MINI Display Port to DVI Adapter DVI Plug Nickel Plated Terminal+PCB  
MINI DisplayPort M Shell Nickel Plated Terminal Gold Plated 3U" White Insulation
- 3.Color: Black connectors and Black Cable
- 4.RoHS 2.0: Yes
- 5.Resolution Supported: 1920\*1080P/60Hz
- 6.Cable Specifications:  
DP~[34AWG(7/0.06TC)+EAM]\*5P+32AWG(7/0.08TC)\*5C+AE(7/0.08BC)B(16/5/0.12AL 85%AL)OD:4.5MM~Black
- 7.Passive Adapter Supports TMDS

**PIN Assignment**



The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
TOLERANCES:  
FRACTIONAL ±  
ANGULAR: MACH ± BEND ±  
TWO PLACE DECIMAL ±  
THREE PLACE DECIMAL ±

INTERPRET GEOMETRIC TOLERANCING PER:  
MATERIAL: CRS  
FINISH: POWDER COAT  
DO NOT SCALE DRAWING



NAME	DATE	TITLE:
JX YAO	11/01/2018	MiniDisplay Port to DVI Adapter - Black
ENG APPR.		SIZE DWG. NO. B
CHECKED		REV A
COMMENTS		SCALE: 1:1 SHEET 1 OF 1