Schneider Electric is extending the superior features and performance of the WX cabinet to Edge applications.



Schneider Electric is excited to announce the expansion of the WX cabinet line with the addition of 6 new models. These globally available wall mount racks are ideal for storage of industry standard hardware including network switches and patch panels required for Edge applications.

The cabinets are compatible with a wide range of Schneider Electric UPSs, PDUs and with NetBotz; simply replace the standard swing handle with the NetBotz Rack Access swing handle. NetBotz provides the functionality required at the Edge including remote access, video capture, environmental monitoring with optional smoke and fluid detection. A complete solution can be configured for your edge applications in the Schneider Electric Local Edge Configurator. Schneider Electric's turn key solutions allow the

cabinet to be deployed in remote locations with confidence and peace of mind.

All cabinets are UL2416 listed and ship fully assembled. All WX cabinets have a static weight capacity of 91 kg (200 pounds) making it ideal for roll outs for retail, medical and education. The 600mm deep (23.6") cabinet also provides versatility to mount deep equipment at the point of compute in Edge applications.







Part Numbers of Assembled Units

Part Number	U Space	Width	Depth	Static Weight Capacity	Color
AR106SH4	6U	600mm (23.6")	400mm (15.75")	91kg (200 pounds)	Black
AR109SH4	9U	600mm (23.6")	400mm (15.75")	91kg (200 pounds)	Black
AR112SH4	12U	600mm (23.6")	400mm (15.75")	91kg (200 pounds)	Black
AR106SH6	6U	600mm (23.6")	600mm (23.6")	91kg (200 pounds)	Black
AR109SH6	9U	600mm (23.6")	600mm (23.6")	91kg (200 pounds)	Black
AR112SH6	12U	600mm (23.6")	600mm (23.6")	91kg (200 pounds)	Black

Feature	Benefit		
Standard swing handle (upgradable to NetBotz Rack Access)	High security handle with optional NetBotz upgrade option to provide remote access, increased security and environmental monitoring		
Field reversible door	Allows for mounting near an adjacent wall		
1U & 2U knock-outs	Additional 6U of mounting space allows for mounting of patch panels, fan trays or brush pass-thrus on the top and bottom		
UL2416 Listed	Stated weight load verified by independent third party		
Depth option of 23.6" (600mm)	Ideal for mounting deep equipment at compute point		
Local Edge Configurator Availability	Configure a complete solution that meets your application requirements including UPS, PDU, NetBotz and EcoStruxure software		

Technical Specifications

- Heights 6U, 9U or 12U
- Widths 600mm (23.6")
- Weight Capacities: 6U, 9U and 12U - 91kg (200 pounds) static
- UL2416 Listed
- · Cage nuts and screws included
- Optional fan tray (AR8213) can be top or bottom mounted
- Color Black
- · Ships fully assembled
- Global Availability

The original flat-packed units will remain available, please refer to the data sheet for product specifications. The part numbers are:

Part Number	U Space	Width	Depth	Static Weight Capacity	Color
AR106	6U	600mm (23.6")	400mm (15.75")	91kg (200 pounds)	Black
AR109	9U	600mm (23.6")	400mm (15.75")	91kg (200 pounds)	Black
AR112	12U	600mm (23.6")	600mm (23.6")	91kg (200 pounds)	Black

apc.com

Life Is On



Schneider Electric Industries SAS 35, rue Joseph Monier - CS 30323 F92506 Rueil-Malmaison Cedex