



CN1



CN2

- 1.Paste one label on the side of DVI When the cable is below 20 feet
- 2.Paste one label on each side When the cable is over 20 feet

MATERIALS LIST:

- 1.Cable: 1354(B)7/0.102TA*3C+7/0.127TA*1PR+7/0.127TA*4C+AEB 85%
OD=7.0mm COLOR:BLACK
- 2.CONNECTOR: DVI-I (12+5) MALE INSULATOR BLACK NICKEL SHELL
- 3.CONNECTOR: HDD 15Pin MALE INSULATOR BLACK NICKEL SHELL
- 4.MOLDING PVC:COLOR:BLACK 45P
- 5.FERRITE CORE: F5B RH 14.2*28.5*8.1mm
- 6.SCREW: #4-40 4*28.5MM COLOR:BLACK
- 7.SCREW: HDS40.5#3.8MM #4-40UNC COLOR:BLACK
- 8.LABEL: YEAR MONTH LABEL

ELECTRONIC TEST:

- A.OPEN/SHORT/INTERMITTENCE: 100%.
- B.HI-POT: 300V DC/sec
- C.INSULATION RESISTANCE: 20M ohm (MIN)
- D.CONDUCTIVE RESISTANCE: 0<L≤10FT 2 ohm (MAX)
10FT<L≤15FT 3 ohm (MAX)
15FT<L≤30FT 4 ohm (MAX)
30FT<L≤100FT 6 ohm (MAX)
L>100FT 10 ohm (MAX)

COMPUTER TEST:

A: under 15ft....UXGA,15.1~25ft.....SXGA

BBOX P/N	LENGTH
EVNDVI01-0006	6FT
EVNDVI01-0010	10FT
EVNDVI01-0015	15FT
EVNDVI01-0025	25FT

CONNECTION

DVI	WIRE	COLOR	HDD15M
C1	RED	(CEN)	1
C2	GREEN	(CEN)	2
C3	BLUE	(CEN)	3
C4	ORANGE		13
C5	R.G.B/GND		6,7,8
6	GREEN		15
7	BROWN		12
8	YELLOW		14
14	RED		9
15	BLACK		5,10
16			
SHELL	BRAID		SHELL

06	R101215002		Jingxu	11.03.12
05	R100406001		Wayne	10.04.06
04	980601001		Wayne	09.06.02
03	960725001		Wayne	07.07.26
02	960622001		Wayne	07.06.26
REV	ECN NO	DESCRIPTION	APPD.	DATE

MARKING: BLACK BOX CORPORATION GUARANTEED FOR LIFE
(724) 746-5500 - - -DVI ANALOG CABLE - - -
AWM E223178 STYLE 20276 VW-1 80℃ 30V

BLACK BOX			
Tolerance:	Approved by:		
X. ±			
.X ±	Checked by:	BLACK BOX P/N:	
.XX ±		EVNDVI01-****	
.XXX ±	Drawn by:	Description:	
Angle:	Jingxu	DVI12+5 M / HDD 15P M	
X' ±	Date:	DWG. NO:	
.X' ±	11.03.12	RFS-95071004	
	Scale:	Unit: mm	SHEET: 1 OF 4
			REV: 06