



HSM SECURIO document shredders

Product Overview

HSM[®]

Great Products, Great People.

HSM SECURIO document shredders

Quality of the highest level – HSM SECURIO document shredders.

Regardless of whether you have chosen the AF-series with automatic paper feed, the C-series for the home office, the B-series for the workplace or the P-series with IntelligentDrive for professional use: you are protected with shredders from HSM!

Small Office



HSM SECURIO C-series
For the home or small office

P-2 P-4 P-5

Office



HSM SECURIO B-series
For the workplace

P-2 P-4 P-5 P-6 P-7

Large Office



HSM SECURIO B-series
For the large office

P-2 P-4 P-5 P-6 P-7


Department



HSM SECURIO P-series
For the department

P-2 P-4 P-5 P-6 P-7

Autofeed



HSM SECURIO AF-series
With automatic paper feed

P-4 P-5 P-6

How high is the protection requirement of your data storage device?



HSM SECURIO document shredders have the following features:



The HSM SECURIO document shredders are issued with a 3 year warranty.



Lifetime warranty on steel cutting rollers in HSM SECURIO document shredders at security levels P-2 to P-5.



HSM SECURIO document shredders have been awarded the Blue Angel certificate. www.blauer-engel.de/uz174



The HSM SECURIO document shredders are developed and produced in Germany.



Actual zero power consumption in stand-by mode, for the models HSM SECURIO C14, C16 and AF100.



EcoSmart: 0.1 Watt power consumption in stand-by mode for the document shredders HSM SECURIO AF150 to AF500 and C18 to P44i.

You can find the corresponding consumables at www.hsm.eu



HSM SECURIO C-series

Space-saving, efficient and secure. The C-series impresses with its appealing compact design and ease of use. Perfect for document shredding at the office or at home.

The advantages:

- Paper feed with overload protection reduces paper jams.
- Easy emptying via removable housing top or waste container.
- Level indicator through inspection window, from HSM SECURIO C16.
- An LED display shows the operating status, HSM SECURIO C18.
- A full bin is indicated optically, HSM SECURIO C18.

- 1 Quiet operation**
Quiet operation minimises noise development in the workplace.
- 2 High level of user safety**
A slight pressure on the safety element immediately stops the paper feed.
- 3 Automatic start/stop**
The devices start automatically when fed paper and automatically stop after shredding is complete.




Learn more, scan the QR-Code.



Model	HSM SECURIO C14		HSM SECURIO C16		HSM SECURIO C18	
Scope of application	Home /small office, up to 3 persons		Home /small office, up to 3 persons		Home /small office, up to 3 persons	
Cutting type	strip	particle	strip	particle	strip	particle
Cutting size in mm / Product number	3.9 / 2250111	4 x 25 / 2253111	5.8 / 1901111	4 x 25 / 1902111	5.8 / 1911121	3.9 x 30 / 1913121
			3.9 / 1900111		3.9 / 1910121	1.9 x 15 / 1912121
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2/T-2/E-2 	P-4/T-4/E-3/F-1 	P-2/T-2/E-2 	P-4/T-4/E-3/F-1 	P-2/O-2/T-2/E-2 	P-4/T-4/E-3/F-1
			P-2/T-2/E-2 		P-2/T-2/E-2 	P-5/T-5/E-4/F-2
Cutting capacity in sheets DIN A4 80 g/m ²	10-12	5-6	15-17	6-7	17-19	8-9
			12-14		13-15	6-7
Noise level in dB(A)*	55	55	55	55	55	55
Intake width in mm	225	225	225	225	230	230
Power consumption in W	160	160	185	185	360	360
Size (W x D x H) in mm		366 x 258 x 405		366 x 258 x 455		365 x 280 x 542
Weight in kg	4	5	4	5	10	11
Collection volume in l	20	20	25	25	25	25

*in idle operation. All specifications are listed without guarantee. Technical and design modifications reserved.



HSM SECURIO B-series

Economical, reliable and versatile. The B-series impresses with its high level of performance and maximum functionality. The product range offers document shredders for the workplace or small working groups of up to 5 persons.

The advantages:

- Safety element prevents unintentional entry.
- Effortless emptying via removable waste container.
- High quality wooden base cabinet with door and reusable collecting bag, from HSM SECURIO B26.
- Mobile on castors, from HSM SECURIO B24.
- External oiler provides for consistently high cutting performance, optional for cutting units in particle cut, from HSM SECURIO B24.

- 1 Continuous operation**
The powerful motor ensures a high cutting capacity and reliable continuous operation.
- 2 Multifunction element**
The device can be intuitively operated with the multifunction element.
- 3 Solid steel cutting rollers**
The hardened solid steel cutting rollers with a lifetime warranty in security levels P-2 to P-5 can easily cope with staples and paper clips and guarantee durability.



Learn more,
scan the QR-Code.



Model	HSM SECURIO B22		HSM SECURIO B24		HSM SECURIO B26 DIN A3		HSM SECURIO B32 DIN A3	
Scope of application	Office, up to 5 persons		Office, up to 5 persons		Office, up to 5 persons		Office, up to 5 persons	
Cutting type	strip	particle	strip	particle	strip	particle	strip	particle
Cutting size in mm / Product number	5.8 / 1831121 3.9 / 1830121	3.9 x 30 / 1833121 1.9 x 15 / 1832121 0.78 x 11 / 1835121	5.8 / 1781111 3.9 / 1780111	4.5 x 30 / 1783111 1.9 x 15 / 1782111 0.78 x 11 / 1785111 1 x 5 / 1784111	5.8 / 1801111 3.9 / 1800111	4.5 x 30 / 1803111 1.9 x 15 / 1802111 0.78 x 11 / 1805111 1 x 5 / 1804111	5.8 / 1821111 3.9 / 1820111	4.5 x 30 / 1823111 1.9 x 15 / 1822111 0.78 x 11 / 1825111 1 x 5 / 1824111
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2/O-2/T-2/E-2 P-2/T-2/E-2	P-4/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 P-7/F-3	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 P-7/F-3	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 P-7/F-3
Cutting capacity in sheets DIN A4 80 g/m ²	17-19 13-15	9-11 7-9 4-5	25-27 19-21	14-16 9-11 6 4	25-27 19-21	14-16 9-11 6 4	25-27 19-21	14-16 9-11 6 4
Noise level in dB(A)*	57	57	54	54	55	55	56	56
Intake width in mm	240	240	240	240	310	310	310	310
Power consumption in W	440	440	610	610	610	610	610	610
Size (W x D x H) in mm	375 x 310 x 600		395 x 317 x 605		497 x 397 x 676		497 x 398 x 793	
Weight in kg	11	13 / 12 / 12	15	19 / 16 / 21 / 21	24	26 / 27 / 28 / 28	26	27
Collection volume in l	33	33	35	35	55	55	82	82

*in idle operation. All specifications are listed without guarantee. Technical and design modifications reserved.



HSM SECURIO B-series

Elegant, reliable and powerful. The B-series shredders with a large bin capacity are characterized by a robust construction with maximum functionality. This range of document shredders is designed for use by up to 8 persons.

The advantages:

- The hardened solid steel cutting rollers with a lifetime warranty in security levels P-2 to P-5 can easily cope with staples and paper clips and guarantee durability.
- The device can be intuitively operated with the multifunction element.
- Safety element prevents unintentional entry.
- Mobile on castors.



Learn more, scan the QR-Code.



- 1 Convenient emptying**
After opening the door, the reusable collecting bag can be easily removed and emptied.
- 2 Continuous operation**
The powerful motor ensures a high cutting capacity and reliable continuous operation.
- 3 Automatic start/stop**
An integrated light barrier automatically starts the device when paper is introduced into the feed and it automatically stops after shredding is complete.




Optional
Prod.-No. + O

External oiler provides for consistently high cutting performance.

Model	HSM SECURIO B34 DIN A3		HSM SECURIO B35 DIN A3	
Scope of application	Large office, up to 8 persons		Large office, up to 8 persons	
Cutting type	strip	particle	strip	particle
Cutting size in mm / Product number	5.8 / 1841111 3.9 / 1840111	4.5 x 30 / 1843111 1.9 x 15 / 1842111 0.78 x 11 / 1845111 1 x 5 / 1844111	5.8 / 1921111 3.9 / 1920111	4.5 x 30 / 1923111 1.9 x 15 / 1922111 0.78 x 11 / 1925111 1 x 5 / 1924111
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2/O-2/T-2/E-2 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 P-7/F-3 	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 P-7/F-3
Cutting capacity in sheets DIN A4 80 g/m ²	30-32 25-27	20-22 13-15 8 5	35-37 26-28	21-22 14-15 9 5
Noise level in dB(A)*	56	56	56	56
Intake width in mm	310	310	400	400
Power consumption in W	700	700	700	700
Size (W x D x H) in mm	541 x 439 x 845		620 x 525 x 870	
Weight in kg	35	42	48	54 / 53 / 54 / 54
Collection volume in l	100	100	130	130

These media types can be destroyed:



Information in original format, e.g. paper



e.g. CDs, DVDs, Blu-ray discs



e.g. floppy disks, ID cards with magnetic strips




e.g. USB sticks, chip cards, flash memory, memory cards from digital cameras



e.g. films, foils

*in idle operation. All specifications are listed without guarantee. Technical and design modifications reserved.



Super Silent
only 45 dB(A) in Silent Mode

HSM SECURIO P-series

Data destruction at the highest level. The shredders in the Professional series are equipped with the impressive and innovative IntelligentDrive motor and operating technologies – up to 40% more performance, intelligent prevention of paper jams and a reduced operating noise level. Perfect for large working groups of up to 15 persons.

The advantages:

- Intelligent paper jam prevention. The machine recognises very quickly if too much paper has been fed in and reacts autonomously.
- EcoSmart: exceptionally low power consumption of 0.1 Watts in stand-by mode.
- Powerful motor for continuous operation.
- High degree of user safety with the pressure sensitive safety element.
- Convenient emptying: after opening the door, the reusable collecting bag can be easily removed and emptied.
- Document shredders with particle cut have an integrated automatic oiler for a consistently high cutting performance. Reduction in oil quantity by using manual configuration.
- Mobile on castors.



Learn more,
scan the QR-Code.

- 1 Touch display**
Intuitive operation and menu selection via the high resolution touch display.
- 2 IntelligentDrive**
Silent, Standard and Performance operating modes for destroying data efficiently and conveniently.
- 3 Super Silent**
In operating mode Silent up to 30% quieter than in Standard mode.



HSM SECURIO
P36i/P40i/P44i



www.blauer-engel.de/uz174

Model	HSM SECURIO P36i DIN A3		HSM SECURIO P40i DIN A3		HSM SECURIO P44i DIN A3	
Scope of application	Department, up to 15 persons		Department, up to 15 persons		Department, up to 15 persons	
Cutting type	strip	particle	strip	particle	strip	particle
Cutting size in mm / Product number	5.8 / 1851121 3.9 / 1850121	4.5 x 30 / 1853121 1.9 x 15 / 1852121 0.78 x 11 / 1855121 1 x 5 / 1854121	5.8 / 1881121 3.9 / 1880121	4.5 x 30 / 1883121 1.9 x 15 / 1882121 0.78 x 11 / 1885121 1 x 5 / 1884121	5.8 / 1871121 3.9 / 1870121	3.9 x 40 / 1873121 1.9 x 15 / 1872121 0.78 x 11 / 1875121 1 x 5 / 1874121
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/O-4/T-5/E-4/F-2 P-6/T-6/E-5/F-3 P-7/F-3	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/O-4/T-5/E-4/F-2 P-6/T-6/E-5/F-3 P-7/F-3	P-2/O-2/T-2/E-2 P-2/O-2/T-2/E-2	P-4/O-3/T-4/E-3/F-1 P-5/O-4/T-5/E-4/F-2 P-6/T-6/E-5/F-3 P-7/F-3
Cutting capacity in sheets DIN A4 80 g/m ²	43-45 34-36	27-29 16-18 11-13 8	56-58 44-46	34-36 19-21 13-15 9	77-79 61-63	43-45 25-27 17-19 11
Noise level in dB(A)*	55	55	55	55	55	55
Intake width in mm	330	330	330	330	400	400
Power consumption in W 1000		1000	1300	1300	1900	1900
Size (W x D x H) in mm		580 x 550 x 1020		580 x 550 x 1020		700 x 592 x 1105
Weight in kg	64	68	67	72	105	105
Collection volume in l	145	145	145	145	205	205

Optional
Prod.-No. + letter



C Separate CD cutting unit in cutting size 4 x 7 mm

M Separate OMDD cutting unit in cutting size 2 x 2 mm



N Separate OMDD cutting unit + metal detection

*in standard operation mode (idle operation). All specifications are listed without guarantee. Technical and design modifications reserved.



HSM SECURIO AF-series

Innovative, convenient and time-saving. The autofeed shredders of the AF-series with Nanogrip Technology combine functionality and operating convenience. For reliable and easy destruction of document stacks and single sheets.

The advantages:

- Time-saving autofeed document shredding.
- Automatic start/stop.
- Paper feed with overload protection reduces paper jams.

HSM SECURIO AF100:

- Zero power consumption in stand-by mode.
- Effortless emptying of the waste container via the removable housing top.

HSM SECURIO AF150 / AF300 / AF350 / AF500:

- Powerful motor for continuous operation.
- Removable waste container for effortless emptying.
- High quality wooden base cabinet with door and reusable collecting bag, HSM SECURIO AF500.
- Mobile on castors.

1 Nanogrip Technology
For reliable sheet intake.

2 Useful dual function
Manual paper feeding during autofeed stack processing.

3 Lock-and-Go function
Protects the inserted paper stack against unauthorized access, HSM SECURIO AF350 / AF500.



Learn more, scan the QR-Code.



HSM SECURIO AF150 / AF300



Model	HSM SECURIO AF100	HSM SECURIO AF150	HSM SECURIO AF300	HSM SECURIO AF350	HSM SECURIO AF500
Scope of application	Home / small office, up to 3 pers.	Office, up to 5 persons	Office, up to 5 persons	Office, up to 5 persons	Office, up to 5 persons
Cutting type	particle	particle	particle	particle	particle
Cutting size in mm / Product number	4 x 25 / 2063111	4.5 x 30 / 2083111 1.9 x 15 / 2082111 0.78 x 11 / 2085111	4.5 x 30 / 2093121 1.9 x 15 / 2092121 0.78 x 11 / 2095121	4.5 x 30 / 2113111 1.9 x 15 / 2112111 0.78 x 11 / 2115111	4.5 x 30 / 2103111 1.9 x 15 / 2102111 0.78 x 11 / 2105111
Security level ISO/IEC 21964 (DIN 66399) / Shredder material	P-4/T-4/E-3/F-1 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3 	P-4/O-3/T-4/E-3/F-1 P-5/T-5/E-4/F-2 P-6/F-3
Cutting capacity in sheets DIN A4 80 g/m ²	5-6	8-10 6-7 5	12-14 8-10 6	12-14 8-10 6	14-16 9-11 6
Capacity of autofeed unit*	max. 100 sheets	max. 150 sheets	max. 300 sheets	max. 350 sheets	max. 500 sheets
Noise level in dB(A)**	56	56	56	56	56
Intake width in mm	225	240	240	240	240
Power consumption in W	185	610	610	610	610
Size (W x D x H) in mm	375 x 260 x 620	395 x 381 x 740	395 x 381 x 740	395 x 435 x 837	497 x 491 x 1002
Weight in kg	7	18 / 18 / 19	18 / 18 / 19	19	29 / 29 / 30
Collection volume in l	25	35	35	35	82

*Autofeed paper tray is for paper only, **in idle operation. All specifications are listed without guarantee. Technical and design modifications reserved.

HSM – the company

Shredding and Compressing.



Since 1971, HSM has been pursuing a clear strategy – a consistent commitment to “Made in Germany” quality. This product and service quality is the key to our success in both the office technology and environmental technology business sectors. As a specialist in products and services for data protection as well as technologies for improving logistics and recycling processes, HSM is one of the world’s leading providers in these sectors.

Contact us now! We are always glad to help.

Head office in Germany:

HSM GmbH + Co. KG · Austraße 1-9 · 88699 Frickingen / Germany
Tel. +49 7554 2100-0 · Fax +49 7554 2100-160
info@hsm.eu · www.hsm.eu

E-mail / hotline:

Gratis Hotline
DE, AT, IT, ES, BE, NL, LU
Tel. 00800 44 77 77 66

HSM Vertrieb Deutschland
deutschland@hsm.eu

HSM Vertrieb Österreich
austria@hsm.eu

HSM Vertrieb Schweiz
schweiz@hsm.eu

HSM Verkoop België, Nederland,
Luxemburg
benelux@hsm.eu

HSM Commerciale Italia
italia@hsm.eu

HSM Ventas Portugal
iberia@hsm.eu

HSM subsidiaries:

HSM Técnica de Oficina y
Medioambiente España, S.L.U.
Calle de José Echegaray, 10
28100 Alcobendas, Madrid
Spain
Tel. +34 91 103 4859
Fax +34 91 103 4858
iberia@hsm.eu
www.hsm.eu

HSM France SAS
Parc de Genève
240, Rue Ferdinand Perrier
69800 Saint-Priest
France
Tél. +33 472 210580
Fax +33 472 517481
france@hsm.eu
www.hsm.eu

HSM (UK) Ltd.
14 Attwood Road / Zone 1
Burntwood Business Park
Burntwood · Staffordshire
WS7 3GJ
United Kingdom
Tel. +44 1543 272-480
Fax +44 1543 272-080
sales.uk@hsm.eu
www.hsm.eu

HSM Polska Sp. z o.o.
ul. Emaliowa 28
02-295 Warsaw
Poland
Tel. +48 22 862-2369
Fax +48 22 862-2368
handlowy@hsm.eu
www.hsm.eu

HSM of America LLC
419 Boot Road
Downingtown, PA 19335
USA
Tel. +1 800 613 2110
Fax +1 484 698 7978
customerservice@hsm.us
info@hsm.us
www.hsm.us

HSM China Ltd.
Room 504, Building C
Hangcheng Guangchang
Nanfaxin Town
Shunyi District
Beijing, PRC, 101300
China
Tel. +86 10 61429168
Fax +86 10 61429169
info@hsm-china.cn
www.hsm-china.cn