

External 12V DC 55AH Battery Module for 120V AC Extreme Temperature Network UPS, TAA

MODEL NUMBER: RBC12V55ET



Extreme-temperature battery cartridge reinforces UPS runtime in harsh environments with very wide operating temperature ranges.

Features

UPS Battery Cartridge for High-Temperature Applications

The RBC12V55ET external battery pack provides extended battery runtime when paired with expandable 24V or 48V Extreme Temperature Network Class UPS systems (sold separately). Each battery pack includes all necessary M6 terminal hardware to secure the battery cable (not included; see the user guide for details). The Extreme Temp UPS comes with an Anderson PA75 DC Connection kit for safe and straightforward installation. The battery temperature sensor cable protects the battery system from overcharging in high-temperature environments.

TAA-Compliant for GSA Schedule Purchases

The RBC12V55ET is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Specifications

OVERVIEW	
UPC Code	037332285904
INPUT	
Input Phase	Single-Phase
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Expandable Runtime Description	Multiple RBC12V55ET can be combined in a series configuration to match 24V or 48V of the Extreme Temperature Network Class UPS DC system. Configure additional battery strings in series-parallel configuration for increased runtime (See manual for more information)
DC System Voltage (VDC)	12

Highlights

- Battery module for the 120V Extreme Temperature Network Class UPS
- Recommended for operating temperatures -40°C to 80°C
- Ensures predictable runtimes are attained in harsh environment applications
- Rugged leakproof construction requires no regular maintenance
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- RBC12V55ET Extreme Temperature Battery
- (2) M6 bolts
- (2) Lock washers
- (2) Flat washers
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Typical Battery Lifespan	3 - 5 years, depending on host UPS operating conditions
Capacity (Ah)	55
PHYSICAL	
Shipping Dimensions (hwd / in.)	11.50 x 10.00 x 7.50
Shipping Weight (kg)	18.64
Unit Dimensions (hwd / in.)	8.120 x 8.980 x 5.450
Unit Dimensions (hwd / cm)	20.62 x 22.81 x 13.84
Unit Weight (lbs.)	39.45
Unit Weight (kg)	17.89
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Elevation	0 - 10,000
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	18-month limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.