Overview

HPE Aruba Networking CX 9300 Switch Series

High Performance Enterprise Data Center Switch

The HPE Aruba Networking CX 9300 Switch Seriesis a next-generation 25.6Tbps, 1U fixed configuration switch supporting 32ports of 100GbE, 200GbE or 400GbE*. The switch is an ideal solution for flexible, cost-effective, high-density 400GbE networking for server, storage, and intra-fabric connectivity. This solution helps protect enterprises investment as they transition server farms from 10GbE and 10GbE/25GbE to 100GbE/400GbE EVPN-VXLAN leaf and/or spine configurations at reduced power and a smaller footprint.

The HPE Aruba Networking CX 9300 Switch Series supports large Data Center PODS of up to 6,000 x 25GbE servers or up to 2,000 x 100GbE servers. This is an 8x jump in scaling/density over current HPE Aruba CX 8325-32C which scales to 700 x 25GbE servers.

HPE Aruba Networking CX 9300 Switch Seriescan be used as a 100GbE Leaf or 100GbE/400GbE Spine switch (128 x 100GbE or 64 x 200GbE ports using breakouts).

When deployed as a Spine, the HPE Aruba Networking CX 9300 Switch Series flexibility connects to a range of leaf switches including HPE Aruba Networking CX 8325 Switch Series, HPE Aruba Networking CX 8360 Switch Series, or HPE Aruba Networking CX 10000 Switch Series.

With Aruba's most recent AOS-CX release, the CX 9300-32D and CX 8325 switches provides an ideal solution for data center, cloud and storage use cases that support top-of-rack server/storage connectivity and scale-out leaf-spine fabric topologies. These innovative AOS-CX enhancements provide storage-optimization to ensure low-latency and "lossless" network QoS and connectivity characteristics that storage requires.

Notes: *25GbE or 50GbE split-out feature to be enabled in a future software release



HPE Aruba Networking CX 9300 Switch Series

Key Features

- High performance 25.6Tbps with 5Bpps
- High Density 32 x 400GbE connectivity in 1RU form factor
- High availability with industry-leading VSX redundancy, and redundant power supplies and fans
- Designed for Spine, Core/Aggregation, Top of Rack or Leaf, or End of Row in the data center
- AOS-CX automation and programmability using built-in REST APIs and Python scripts
- Advanced Layer 2/3 feature set includes BGP, OSPF, VRF-Lite, and IPv6
- Dynamic VXLAN with BGP-EVPN for deep segmentation in data center and campus networks
- Intelligent monitoring, visibility, and remediation with HPE Aruba Network Analytics Engine
- HPE Storage Networking Optimized
- HPE Aruba NetEdit support for automated configuration and verification

Hewlett Packard Enterprise

AOS-CX - A Modern Software System

The HPE Aruba Networking CX 9300 Switch Series is based on AOS-CX, a modern, database-driven operating system that automates and simplifies many critical and complex network tasks. A built-in time series database enables customers and developers to utilize software scripts for historical troubleshooting, as well as analysis of past trends. This helps predict and avoid future problems due to scale, security, and performance bottlenecks. AOS-CX operating system features are organized into HPE Aruba CX Foundation and HPE Aruba CX Advanced software licenses.

Every HPE Aruba CX switch includes an active, embedded HPE Aruba CX Foundation license at no additional cost with the option to upgrade to an HPE Aruba CX Advanced license.

The CX Foundation license has everything needed to deploy, connect, and troubleshoot an enterprise network, including:

- HPE Aruba Network Analytics Engine (NAE)
- Dynamic Segmentation
- Switch Stacking
- High Availability and Resiliency
- Quality of Service (QoS)
- Layer 2 Switching
- Layer 3 Services and Routing
- IP Multicast
- Network Security
- Support for HPE Aruba NetEdit

The HPE Aruba CX Advanced license includes HPE Aruba CX Edge Insights, offering deep visibility with application recognition, identification, and flow capture from layer 4 to layer 7.

For more information on the CX Advanced License, read the HPE Aruba CX Switch License Ordering Guide.

Because AOS-CX is built on a modular Linux architecture with a stateful database, our operating system provides the following unique capabilities:

- Easy access to all network state information allows unique visibility and analytics
- REST APIs and Python scripting for fine-grained programmability of network tasks
- A micro-services architecture that enables full integration with other workflow systems and services
- Continual state synchronization that provides superior fault tolerance and high availability
- Supports HPE Aruba Fabric Composer a software-defined orchestration solution that simplifies and accelerates leafspine network provisioning and day-to-day operations across rack-scale compute and storage infrastructure.
- All software processes communicate with the database rather than each other, ensuring near real-time state and resiliency and allowing individual software modules to be independently upgraded for higher availability

HPE Aruba Central, Cloud-Based Network Management

Flexible cloud-based or on-premises management for unified network operations of wired, WLAN, SD-WAN, and public cloud infrastructure. Designed to simplify day zero through day two operations with streamlined workflows. Switch management capabilities include configuration, onboarding, monitoring, troubleshooting, and reporting.

A HPE Aruba Central Foundation license subscription enables comprehensive switch management capabilities that include configuration, onboarding, monitoring, troubleshooting, and reporting. A HPE Aruba Central Advanced license expands these capabilities with premium security and AIOps, including the HPE Aruba Central NetConductor Fabric Wizard and Policy Manager to enable dynamic segmentation and distributed enforcement at a global scale.

With the HPE Aruba Central Advanced license there is no need to purchase a CX Advanced license. This streamlines operational efficiency, reducing the need for your IT team to keep track of multiple licenses, active terms, and renewal dates. For more information on Aruba Central licensing, see the HPE Aruba Central SaaS Subscription Ordering Guide.



HPE Aruba Networking CX 9300 Switch Series

HPE Aruba Network Analytics Engine

For enhanced visibility and troubleshooting, HPE Aruba's Network Analytics Engine (NAE) automatically interrogates and analyzes events that can impact a networks health. Advanced telemetry and automation provide the ability to easily identify and troubleshoot network, system, application and security related issues easily, through the use of python agents, CLIbased agents and REST APIs.

The Time Series Database (TSDB) stores configuration and operational state data, making it available to quickly resolve network issues. The data may also be used to analyze trends, identify anomalies and predict future capacity requirements.

HPE Aruba NetEdit – Automated Switch Configuration and Management

The entire HPE Aruba CX portfolio empowers IT teams to orchestrate multiple switch configuration changes for smooth end-toend service rollouts. HPE Aruba NetEdit introduces automation that allows for rapid network-wide changes, and ensures policy conformance post network updates. Intelligent capabilities include search, edit, validation (including conformance checking), deployment and audit features. Capabilities include:

- Centralized configuration with validation for consistency and compliance.
- Time savings via simultaneous viewing and editing of multiple configurations.
- Customized validation tests for corporate compliance and network design.
- Automated large-scale configuration deployment without programming.
- Network health and topology visibility via HPE Aruba NAE integration.

Notes: A separate software license is required to use HPE Aruba NetEdit.

HPE Ethernet Storage Fabric Optimized

HPE Aruba Networking CX 9300 Switch Series provides an ideal solution for data center, cloud and storage use cases that support top-of-rack server and storage connectivity and scale-out leaf-spine fabrics. AOS-CX adds storage-optimization enhancements to ensure the low-latency, lossless network QoS and connectivity characteristics that storage requires.

HPE Aruba Virtual Switching Extension

The ability of AOS-CX to maintain synchronous state across dual control planes allows a unique high availability solution called HPE Aruba Virtual Switching Extension (VSX). VSX is delivered through redundancy gained by deploying two chassis with an interswitch link, with each chassis maintaining its independent control.

Designed using the best features of existing HA technologies such as Multi-chassis Link Aggregation (MC-LAG) and Virtual Switching Framework (VSF), HPE Aruba VSX enables a distributed architecture that is highly available during upgrades or control plane events. Features include:

- Continuous configuration synchronization via AOS-CX
- Flexible active-active network designs at Layers 2 and 3
- Operational simplicity and usability for easy configuration
- High availability by design during upgrades including support for VSX Live Upgrade with LACP traffic draining.

Product Capabilities

Performance

High-Speed Fully Distributed Architecture

• Provides 25.6Tbps for bidirectional switching and 5Bpps for forwarding. All switching and routing are wire-speed to meet the demands of bandwidth-intensive applications today and in the future

Scalable System Design

• Provides investment protection to support future technologies and higher-speed connectivity

Connectivity

High Density Port Options

Choice of compact high density port 1U switches with airflow direction flexibility include model with:

• 32-ports of 100GbE, 200GbE or 400GbE. 400 Gbps Ports can be configured as 4x100GbE, 2x200GbE, or 1x400GbE.

Jumbo Frames

• Allows high-performance backups and disaster-recovery systems; supports a maximum frame size of 9K bytes

Unsupported Transceiver Mode (UTM)

- Allows enabling unsupported transceiver and cable for up to 400G
- Using unsupported transceiver/cable can void warranty, gets no support, and comes with no guarantee of operating

Loopback

• Supports internal loopback testing for maintenance purposes and increased availability; loopback detection protects against incorrect cabling or network configurations and can be enabled on a per-port or per-VLAN basis for added flexibility

Packet Storm Protection

• Protects against unknown broadcast, multicast, or unicast storms with user-defined thresholds

Quality of Service (QoS)

Strict Priority (SP) Queuing and Deficit Weighted Round Robin (DWRR)

- Enable congestion avoidance
- Data Center Bridging (DCB)
 - Supports lossless Ethernet networking standards to eliminate packet loss due to queue overflow
 - Priority Flow Control (PFC) 7 priorities per port
 - Enhanced Transmission Service (ETS)
 - DCB Exchange Protocol (Pre-standard LLDP DCBX IEEE 1.01 version)
- Flow-Control Guard
 - Prevents accumulation of excessive congestion with periodic flushing. Avoids packets buffering for an extended time period
- ECN with slope
 - Marks packets as ECN-CE (Congestion Experienced. Helps TCP to reduce receive window size during congestion
- Advanced lossless pool configuration
- Global buffering statistics
- Storage Solution Support
 - iSCSI, Lossless iSCSI, RDMA over Converged Ethernet version 2 (RoCE v1 and v2) and Non-Volatile Memory Express (NVMeOF)



Resiliency and High Availability

Redundant and Load-Sharing Fans and Power Supplies

Increases total performance and power availability

Hot swappable Power Supply and Fan Modules

• Allows replacement of accessory modules without any operational impact on other modules or the switch operations

Separate Data and Control Paths

• Separates control from services and keeps service processing isolated; increases security and performance

HPE Aruba Virtual Switching Extension (VSX)

• VSX enables a distributed and redundant architecture by deploying two switches with each switch maintaining independent control yet staying synchronized during upgrades or failover. Also supports upgrades during live operation

Virtual Router Redundancy Protocol (VRRP)

- VRRP allows a group of switches to dynamically back each other up to create highly available routed environments
- It also supports route-leaking to/from default VRF

Bidirectional Forward Detection (BFD)

• Enable sub-second failure detection for rapid routing protocol re-balancing

Ethernet Ring Protection Switching (ERPS)

• Supports rapid protection and recovery in a ring topology.

Unidirectional Link Detection (UDLD)

• Monitors link connectivity and shuts down ports at both ends if unidirectional traffic is detected, preventing loops in STPbased networks

IEEE 802.3ad LACP

• Supports up to 128 LAGs, with up to 16 members per LAG (32 for a VSX pair), with a user-selectable L1- 4 hashing algorithm

Management

In addition to the HPE Aruba CX Mobile App, HPE Aruba NetEdit and HPE Aruba Network Analytics Engine, the HPE Aruba Networking CX 9300 Switch Series offers the following:

Built-in programmable and easy to use **REST API interface**

Industry-Standard CLI with a Hierarchical Structure

• Reduces training time and expenses, and increases productivity in multivendor installations

Management Security

- Restricts access to critical configuration commands; offers multiple privilege levels with password protection; ACLs provide SNMP access; local and remote Syslog capabilities allow logging of all access.
- Private VLAN (PVLAN) provides traffic isolation between users on the same VLAN. Typically a switch port can only
 communicate with other ports in the same community and/or an uplink port, regardless of VLAN ID or destination MAC
 address. This extends network security by restricting peer-peer communication to prevent variety of malicious attacks.

IPSLA

- Monitors the network for degradation of various services, including voice.
- Monitoring is enabled via the NAE for history and for immediate automated gathering of additional information when anomalies are detected



SNMP v2c/v3

- Provides SNMP read and trap support of industry standard Management Information Base (MIB), and private extensions
- It supports STP TCN Trap, STP New Root and SNMP-Write- Set-Description on Interface.

sFlow® (RFC 3176)

• Provides scalable ASIC-based wire speed network monitoring and accounting with no impact on network performance; this allows network operators to gather a variety of sophisticated network statistics and information for capacity planning and real-time network monitoring purposes

Remote Monitoring (RMON)

• Uses standard SNMP to monitor essential network functions and supports events, alarms, history, and statistics groups as well as a private alarm extension group

TFTP and SFTP Support

- Offers different mechanisms for configuration updates; trivial FTP (TFTP) allows bidirectional transfers over a TCP/ IP network
- Secure File Transfer Protocol (SFTP) runs over an SSH tunnel to provide additional security

Debug and Sampler Utility

• Supports ping and traceroute for IPv4 and IPv6

Network Time Protocol (NTP)

- Synchronizes timekeeping among distributed time servers and clients; keeps timekeeping consistent among all clockdependent devices within the network
- Can serve as the NTP server in a customer network

IEEE 802.1AB Link Layer Discovery Protocol (LLDP)

• Advertises and receives management information from adjacent devices on a network, facilitating easy mapping by network management applications

LACP-fallback

• Enables Zero Touch Provisioning over Link Aggregation Groups.

Dual Flash Images

• Provides independent primary and secondary operating system files for backup while upgrading

Multiple Configuration Files

• Stores files easily to the flash image

Layer 2 Switching

VLAN

• Supports up to 4,040 port-based or IEEE 802.1Q-based VLANs

VLAN Translation

Remaps VLANs during transit across a core network

Bridge Protocol Data Unit (BPDU) Tunneling

• Transmits STP BPDUs transparently, allowing correct tree calculations across service providers, WANs, or MANs

Port Mirroring

• Duplicates port traffic (ingress and egress) to a local or remote monitoring port; supports 4 mirroring groups, with an unlimited number of ports per group



STP

• Supports standard IEEE 802.1D STP, IEEE 802.1w Rapid Spanning Tree Protocol (RSTP) for faster convergence, and IEEE 802.1s Multiple Spanning Tree Protocol (MSTP)

Rapid Per-VLAN Spanning Tree Plus (RPVST+)

 Allows each VLAN to build a separate spanning tree to improve link bandwidth usage in network environments with multiple VLANs

Internet Group Management Protocol (IGMP)

• Controls and manages the flooding of multicast packets in a Layer 2 network

Static VXLAN

• Allows operators to manually connect two or more VXLAN tunnel endpoints (VTEP)

Dynamic VXLAN with BGP-EVPN

- Deep segmentation for Spine/Leaf data center networks or Layer 3 campus designs with centralized gateway and symmetric Integrated Routing and Bridging (IRB) based distributed gateways VXLAN tunnels.
- EVPN and VXLAN features include inbound and outbound route map support, matching L3VNI matching, localpreference setting, ip next-hop, as-path prepend, ip/ipv6 address prefix-list matching.
- VXLAN DC multi-fabric DCI support.

Multicast

- PIM Multicast Boundary (v4)
- VSX Graceful shutdown for IGMP/MLD
- Multicast NSF

IPv4 Multicast in VXLAN/EVPN Overlay

• Enable PIM-SM/IGMP snooping in the VXLAN Overlay

IPv6 VXLAN/EVPN Overlay Support

• Enables IPv6 traffic over the VXLAN overlay

VXLAN Distributed Anycast Gateway

- Addressing mechanism that enables the use of the same gateway IP addresses across all the leaf switches part of a VXLAN network.
- It supports VSX active forwarding for VXLAN underlay.

VXLAN ARP/ND Suppression

• Allows minimization of ARP and ND traffic flooding within individual VXLAN segments, thus optimizing the VXLAN network

Layer 3 Services

Address Resolution Protocol (ARP)

- Determines the MAC address of another IP host in the same subnet; supports static ARPs
- Gratuitous ARP allows detection of duplicate IP addresses
- Proxy ARP allows normal ARP operation between subnets or when subnets are separated by a Layer 2 network

IP Directed Broadcast

• Supports directed broadcast on configured network subnets

Dynamic Host Configuration Protocol (DHCP)

- DHCP services are offered within a client network to simplify network management
- DHCP Relay enables DHCP operation across subnets

DHCP Server

- Supports DHCP Smart Relay services (for IPv4 and IPv6) in customer networks
- DHCP relay coexistence with server
- Allows DHCP relay coexistence with DHCP server for both IPv4 and IPv6

Domain Name System (DNS)

- Provides a distributed database that translates domain names and IP addresses, which simplifies network design; supports client and server
- It also supports mDNS Gateway.

Generic Routing Encapsulation (GRE)

• Enables tunneling traffic from site to site over a Layer 3 path

Layer 3 Routing

Static IPv4 routing

• Provides simple manually configured IPv4 routing

Open shortest path first (OSPF)

- Delivers faster convergence; uses link-state routing Interior Gateway Protocol (IGP), which supports ECMP, NSSA, and MD5 authentication for increased security and graceful restart for faster failure recovery.
- Enhanced features include configurable OSPF distance for type-5 LSA and configurable default-metric for OSPF defaultinformation guide.

Loopback IP redistribution in OSPF

• Allows redistribution of IPv4 and IPv6 addresses of loopback interface in OSFPv2/v3

Border Gateway Protocol 4 (BGP-4)

• Delivers an implementation of the Exterior Gateway Protocol (EGP) utilizing path vectors; uses TCP for enhanced reliability for the route discovery process; reduces bandwidth consumption by advertising only incremental updates; supports extensive policies for increased flexibility; scales to very large networks

Dynamic BGP Peering

• Simplifies BGP configuration for ZTP scenarios and enables CX for Azure stack integration

Routing Information Protocol version 2 (RIPv2)

• Easy to configure routing protocol for small networks relying on User Datagram Protocol (UDP)

Routing Information Protocol Next Generation (RIPng)

• Extension of RIPv2 for support of IPv6 networking

Multiprotocol BGP (MP-BGP) with IPv6 Address Family

• Enables sharing of IPv6 routes using BGP and connections to BGP peers using IPv6

Policy Based Routing (PBR)

• Enables using a classifier to select traffic that can be forwarded based on policy set by the network administrator

6in4 Tunnels

• Supports the tunneling of IPv6 traffic in an IPv4 network

IP Performance Optimization

• Provides a set of tools to improve the performance of IPv4 networks; includes directed broadcasts, customization of TCP parameters, support of ICMP error packets, and extensive display capabilities

Dynamic Pool Configuration

• Enables lossless pool configuration without switch reboot

Static IPv6 Routing

• Provides simple manually configured IPv6 routing

Dual IP Stack

• Maintains separate stacks for IPv4 and IPv6 to ease the transition from an IPv4-only network to an IPv6-only network design

OSPFv3

• Provides OSPF support for IPv6

Equal-Cost Multipath (ECMP)

• Enables multiple equal-cost links in a routing environment to increase link redundancy and scale bandwidth

Generic Routing Encapsulation (GRE)

• Enables tunneling traffic from site to site over a Layer 3 path

Visibility

Customers can choose to upgrade the active, embedded CX Foundation license to the term-based CX Advanced license to unlock the following benefits for their business:

• Delivers deep visibility with HPE Aruba CX Edge Insights for application recognition, identification, and flow capture from layer 4 to layer 7. CX Edge Insights enables granular datapoint collection with search, sort and reporting as well as the ability to recognize 22 categories and more than 3700 applications.

Security

TAA Compliance

• TAA compliant product, uses FIPS 140-2 validated cryptography for protection of sensitive information

Federal Certification

• Compliant with DoDIN, APL, NDcPP, FIPS, and USGv6 requirements for federal certifications.

Access control list (ACL) Features

- Supports powerful ACLs for both IPv4 and IPv6. Supports creation of object groups representing sets of devices like IP addresses. For instance, IT management devices could be grouped in this way
- ACLs can also protect control plane services such as SSH, SNMP, NTP or web servers

Enrollment over Secure Transport (EST)

• Enables secure certificate enrollment, allowing for easier enterprise management of PKI.

Remote Authentication Dial-In User Service (RADIUS)

• Eases security access administration by using a password authentication server

Terminal Access Controller Access-Control System (TACACS+)

• Delivers an authentication tool using TCP with encryption of the full authentication request, providing additional security

RadSec

• Enable RADIUS authentication and accounting data to be passed safely and reliably across insecure networks such as the internet

Management access security

- AOS-CX provides for both on-box as well as off- box authentication for administrative access. RADIUS or TACACS+ can be used to provide encrypted user authentication
- Additionally, TACACS+ can also provide user authorization services

Secure shell (SSHv2)

• Uses external servers to securely log in to a remote device; with authentication and encryption, it protects against IP spoofing and plain-text password interception; increases the security of Secure FTP (SFTP) transfers

Multicast

Internet Group Management Protocol (IGMP)

• Enables establishing multicast group memberships in IPv4 networks; supports IGMPv1, v2, and v3

Multicast Listener Discovery (MLD)

• Enable discovery of IPv6 multicast listeners; supports MLDv, v2.

Multicast Service Delivery Protocol (MSDP) for Anycast RP

• MSDP used for Anycast RP is an intradomain feature that provides redundancy and load-sharing capabilities.

MSDP Mesh Groups

• Allows to avoid SA messages flood to other mesh group peers.

PIM-Dense Mode

• Floods multicast traffic to every corner of the network (push-model). Method is for delivering data to receivers without receivers requesting the data. Can be efficient in certain deployments in which there are active receivers on every subnet in the network. Branches without downstream receivers are pruned from the forwarding trees.

FastLeave (FL) and Forced-FastLeave (FFL)

FL and FFL for IGMP/MLD speed up the process of blocking unnecessary Multicast traffic to a switch port that is
connected to end nodes for IGMP. They help to eliminate the CPU overhead of having to generate an IGMP/MLD GroupSpecific Query message.

Protocol Independent Multicast (PIM)

 Protocol Independent Multicast for IPv4 and IPv6 supports one-to-many and many-to-many media casting use cases such as IPTV over IPv4 and IPv6 networks. Support for PIM Sparse Mode (PIM-SM, IPv4, IPv6), Source-Specific Multicast (SSM), and Dense Mode (DM).

Additional information

- Green initiative support
- Provides support for RoHS (EN 50581:2012) regulations

Korea Government Security Features

- Ensure configuration integrity
- Limit concurrent users for web access
- Platforms: All CX platforms

Analytics

- AIOPS NAE Agent & Engine Improvements Unicast Routing
- AIOPS NAE Agent & Engine Improvements Client Services

Customer first, customer last support

When your network is important to your business, then your business needs the backing of HPE Aruba Support Services. Partner with HPE Aruba product experts to increase your team productivity, keep pace with technology advances, software releases, and obtain break-fix support.

Tech Care for HPE Aruba support services include priority access to HPE Aruba Technical Assistance Center(TAC) engineers 24x7x365, flexible hardware and onsite support options, and total coverage for HPE Aruba products. HPE Aruba switches with assigned HPE Aruba Central subscriptions benefit with option for additional hardware support only.

HPE Aruba Pro Care adds fast access to senior HPE Aruba TAC engineers, who are assigned as a single point of contact for case management, reducing the time spent addressing and resolving issues.

For complete details on Tech Care and HPE Aruba Pro Care, please visit: <u>https://www.arubanetworks.com/supportservices/</u>

Warranty, services and support

Limited Lifetime Warranty

• See <u>https://www.arubanetworks.com/support-services/product-warranties/</u> for warranty and support information included with your product purchase.

For more detailed information HPE Aruba AOS-CX software releases and features **AOS-CX Switch Software Documentation Portal** and HPE **Aruba Switch Feature Navigator**

For Support and Services information, visit https://www.arubanetworks.com/support-services/arubacare/

Configuration Information

BTO Models

BIO Mode	AC Bundles	
Rule #	Description	SKU
1, 2, 3, 4, 5, 6, 7, 10, 11, 12	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle	SOF82A
	 Includes 2 FB Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 FB Fan Tray Bundles with no additional open FT Slots 	
	 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	 1U - Height 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle PDU	SOF82A#B2B
	• C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle PDU	SOF82A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC 220v Bundle	SOF82A#B2E
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(JL336A) 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle NoLoc	SOF82A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6, 7, 10, 11, 12	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle	SOF84A
12	 Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 	
	2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle PDU	SOF84A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle PDU	SOF84A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC 220v Bundle	SOF84A#B2E
	HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle NoLoc	SOF84A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	



1, 2, 3, 4, 5, 6, 9, 12	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A
	 Includes 2 FB Power Supplies (R8Z97A) with no additional open PS slots, Warning: 200-240VAC use only 	
	 Includes 6 FB Fan Tray Bundles (R8Z99A) with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP+/QSFP28/QSFP-DD 40/100/200/400G Transceivers 	
	 1U - Height HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU 	R9A29A
	Bundle	
	• C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent) HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A
	• C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6, 9, 12	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	 Includes 2 BF Power Supplies (R8Z98A) with no additional open PS slots, Warning: 200-240VAC use only 	
	 Includes 6 BF Fan Tray Bundles (R9A00A) with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP+/QSFP28/QSFP-DD 40/100/200/400G Transceivers 1U - Height 	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	• C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	 C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent) 	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	

Configuration Information

	DC Bundles	
1, 2, 3, 6, 7, 10, 11, 12	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xDC Bundle	SOF88A
	 Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 1U - Height 	
	AC TAA Bundles	
1, 2, 3, 6, 7, 10, 11, 12	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle	SOF81A
,,	 Includes 2 FB Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 FB Fan Tray Bundles with no additional open FT Slots 	
	2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle PDU	SOF81A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle PDU	SOF81A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA 220v Bundle	SOF81A#B2E
	• HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A)	00504 0 // 007
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle NoLoc	SOF81A#AC3
	• No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-20P)	
1, 2, 3, 6, 7, 10, 11, 12	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA Bundle	SOF83A
	 Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 	
	2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA Bundle PDU	SOF83A#B2B

• C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)

R9B44A

QuickSpecs

	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC	SOF83A#B2C
	TAA Bundle PDU	
	C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA 220v Bundle	SOF83A#B2E
	 HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A) HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6Fs 2xAC 	SOF83A#AC3
	TAA Bundle No Loc	501 05A#AC5
	No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	
	20P)	
	DC TAA Bundles	
1, 2, 3, 6, 7,	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xDC	SOF87A
10, 11, 12	TAA Bundle	
	• Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use	
	only	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 	
	2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	Configuration Rules	
Rule #	Description	
1	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Aruba Networking 4x100G DR QSFP-DD SN 500m SMF Transceiver	S3N90A
	HPE Aruba Networking 4x100G FR QSFP-DD SN 2km SMF Transceiver	S3N91A
	HPE Aruba Networking 4x100G LR QSFP-DD SN 10km SMF Transceiver	S3N92A
	HPE Aruba Networking 400G DR4 QSFP-DD MPO12 500m SMF Transceiver	S3N93A
	HPE Aruba Networking 400G PLR4 QSFP-DD MPO12 10km SMF Transceiver	S3N94A
	HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver	R9B41A
2	HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver	R9B42A
2	The following AOC's install into this Switch: (Use BTO only when adding to switch) HPE Aruba Networking 200G DD-2xQSFP28 100G 3m Active Optic Cable	R9B60A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 7m Active Optic Cable	R9B58A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 15m Active Optic Cable	R9B62A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 30m Active Optic Cable	R9B61A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 50m Active Optic Cable	R9B59A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable	R9B55A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable	R9B53A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable	R9B57A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable	R9B56A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable	R9B54A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable	R9B50A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable	R9B48A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable	R9B52A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable	R9B51A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable	R9B49A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable	R9B45A R9B43A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable	R9B47A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable	R9B46A

HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable

3	The following Transceivers install into this Switch: (Use BTO only when adding to switch) HPE Aruba Networking 100G QSFP28 MPO SR4 100m 12-fiber MPO OM3 MMF Transceiver HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver HPE Aruba Networking 100G QSFP28 LC CWDM4 2km SMF Transceiver HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable HPE Aruba Networking 100G DR QSFP28 LC 500m SMF Transceiver HPE Aruba Networking 100G LR QSFP28 LC 10km SMF Transceiver HPE Aruba Networking 100G SR2 MPO QSFP28 100m MMF Transceiver HPE Aruba Networking 100G QSFP28 to QSFP28 100m MMF Transceiver HPE Aruba Networking 100G QSFP28 to QSFP28 100m MMF Transceiver HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable	JL309A R9B63A R0Z30A JL310A JL743A JL856A S3N88A S3N89A S1C93A R0Z27A R0Z27A R0Z28A R0Z29A 845970-B21
4	Localization required on orders without B2B, B2C, B2E or AC3 options.	
5	Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C" Option, then Display the following:	
	For BTO shipments to India:	
	Please replace <base model=""/> #B2C option with <base model=""/> #AC3 in the Bill of	
	Materials and add the appropriate INDIA PDU Power Cord below via Ad-Hoc:	
	 JL671A - HPE 2.0m C13 to C14 PDU IN Power Cord 	
	 JL672A - HPE 2.5m C15 to C14 PDU IN Power Cord 	
	 JL673A - HPE 2.5m C19 to C20 PDU IN Power Cord 	
	• For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. (Ex. JL671A#0D1)	
6	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Networking X142 40G QSFP+ MPO SR4 Transceiver	JH231A
	HPE Networking X142 40G QSFP+ MPO eSR4 300M Transceiver	JH233A
	HPE Aruba Networking 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver	JL308A
	HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver	JH232A
	HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver	Q9G82A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable	R0Z22A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable	R0Z23A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable	R0Z24A
7	If qty1 of the folowing QSA28 Adapter(845970-B21) is selected, then increase max SFP28 Port	
	qty by 1 and allow user selection of the following SFP Transceivers. Refer to qty and port	
	restrictions for individual Switch in the "Additional Info" sections: (Use #0D1 for this XCVR	
	Adapter since switch is factory racked)	
	HPE Aruba Networking 10G SFP+ LC SR 300m OM3 MMF Transceiver	J9150D
	HPE Aruba Networking 10G SFP+ LC LR 10km SMF Transceiver	J9151E
	HPE Aruba Networking 10G SFP+ LC ER 40km SMF Transceiver	J9153D
	HPE Aruba Networking 10G SFP+ LC SR 300m MMF TAA Transceiver	JL748A
	HPE Aruba Networking 10G SFP+ LC LR 10km SMF TAA Transceiver	JL749A
	HPE Aruba Networking 25G SFP28 LC SR 100m MMF Transceiver	JL484A
	HPE Aruba Networking 25G SFP28 LC eSR 400m MMF Transceiver	JL485A
	HPE Aruba Networking 25G SFP28 LC LR 10km SMF Transceiver	JL486A
9	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	JLHOUR
·	HPE Aruba Networking 400G FR4 QSFP-DD LC 2km SMF Transceiver	S3N95A
	5	
10	HPE Aruba Networking 400G LR4 QSFP-DD LC 10km SMF Transceiver	S3N96A
10	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Aruba Networking 100G QSFP28 to QSFP28 1m Direct Attach Copper Cable	ROZ25A
	HPE Aruba Networking 100G QSFP28 to QSFP28 5m Direct Attach Copper Cable	ROZ26A
	HPE Aruba Networking 100G QSFP28 to QSFP28 3m Direct Attach Copper Cable	JL307A

11	The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable:	
	HPE Networking X242 40G QSFP+ to QSFP+ 1m Direct Attach Copper Cable	JH234A
	HPE Networking X242 40G QSFP+ to QSFP+ 3m Direct Attach Copper Cable	JH235A
	HPE Networking X242 40G QSFP+ to QSFP+ 5m Direct Attach Copper Cable	JH236A
12	If ANY Option is integrated 0D1 to this Switch, then the Switch requires 0D1. (Box level	
	integration is not allowed)	
Notes:	 Drop down under power supply should offer the following options and results: 	
	• Switch/Router/Power Supply to PDU Power Cord - B2B in North America, Mexico,	
	Taiwan, and Japan or B2C ROW. (OCA Default B2B or B2C for Rack Level CTO)	
	• Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default	
	for BTO and Box Level CTO)	
	• High Volt Switch/Router/Power Supply to Wall Power Cord - B2E Option. (Offered	
	only in North America, Mexico, Taiwan, and Japan)	
	 No Power Cord - AC3 Option 	
	– Locking Power Cord (J9955A) L6-20P is available through the OCA Accessories tab	
	 OCA Only Model Selection Form - HPE Aruba Networking > Switches > 	
	HPE ANW AOS-CX >9300 Switch Series	

Configuration Information

Rack Level Integration CTO Models


Rack Level	AC Bundles	
Rule #	Description	SKU
1, 2, 3, 4, 5, 6, 7, 8, 10, 11	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle	SOF82A
	 Includes 2 FB Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 FB Fan Tray Bundles with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	 1U - Height 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle PDU	SOF82A#B2B
	 C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A) 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle PDU	SOF82A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC 220v Bundle	SOF82A#B2E
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(JL336A) 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC Bundle NoLoc	SOF82A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6, 7, 8, 10, 11	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle	SOF84A
	 Includes 2 BF Power Supplies with no additional open PS slots, warning: 200-225VAC use only 	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 	
	 2 Post Rack Kit included, must select 4 Post Rack Kit 	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7)	
	• 1U - Height HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle PDU	SOF84A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC	SOF84A#B2C
	Bundle PDU	
	• C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC 220v Bundle	SOF84A#B2E
	 HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A) 	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC Bundle NoLoc	SOF84A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	

1, 2, 3, 4, 5, 6, 7, 8, 10,	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A
11		
	 Includes 2 FB Power Supplies (R8Z97A) with no additional open PS slots, Warning: 200-240VAC use only 	
	Includes 6 FB Fan Tray Bundles (R8Z99A) with no additional open FT Slots	
	2 Post Rack Kit included, must select 4 Post Rack Kit	
	 Min=0 \ Max = 32 QSFP+/QSFP28/QSFP-DD 40/100/200/400G Transceivers QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	 10 - Height 	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A#B2C
	C15 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle	R9A29A#B2E
	HPE 2.3m C13 to NEMA 6-15P Pwr Cord(JL336A) HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU	R9A29A#AC3
	Bundle	N9A29A#ACJ
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6, 8, 9	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A
	 Includes 2 BF Power Supplies (R8Z98A) with no additional open PS slots, Warning: 200-240VAC use only 	
	 Includes 6 BF Fan Tray Bundles (R9A00A) with no additional open FT Slots 	
	2 Post Rack Kit included, must select 4 Post Rack Kit	
	 Min=0 \ Max = 32 QSFP+/QSFP28/QSFP-DD 40/100/200/400G Transceivers 1U - Height 	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU	R9A30A#B2B
	Bundle	
	• C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent) HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU	R9A30A#B2C
	Bundle	K9AJUA#DZC
	• C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A#B2E
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	
	HPE Aruba Networking 9300-32D 32p QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans 2 AC PSU Bundle	R9A30A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1 2 7 4 7	DC Bundles	COF004
1, 2, 3, 6, 7, 8, 10, 11	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xDC Bundle	SOF88A
	Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 2 Post Rack Kit included 	

- 2 Post Rack Kit included
- Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers



	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	AC TAA Bundles	
1, 2, 3, 4, 5, 6, 7, 8, 10, 11	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle	SOF81A
	 Includes 2 FB Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 FB Fan Tray Bundles with no additional open FT Slots 	
	• 2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle PDU	SOF81A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC TAA Bundle PDU	SOF81A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A) HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC	SOF81A#B2E
	TAA 220v Bundle	JUI OIA#DZL
	• HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A) HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Front-to-Back 6xFan 2xAC	SOF81A#AC3
	TAA Bundle NoLoc	301 01A#AC3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6, 7, 8, 10, 11	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA Bundle	SOF83A
	 Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only 	
	 Includes 6 BF Fan Tray Bundles with no additional open FT Slots 	
	2 Post Rack Kit included	
	 Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers 	
	 Min=0 \ Max = 8 QSFP-DD 400G Transceivers 	
	 QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 	
	• 1U - Height	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA Bundle PDU	SOF83A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA Bundle PDU	SOF83A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A) HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xAC TAA 220v Bundle	SOF83A#B2E
	HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A)	
	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6Fs 2xAC TAA Bundle No Loc	SOF83A#AC3
	• No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	



Configuration Information

DC TAA Bundles 1, 2, 3, 5, 7, SOF87A HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Back-to-Front 6xFan 2xDC 8, 10, 11 TAA Bundle • Includes 2 BF Power Supplies with no additional open PS slots, Warning: 200-225VAC use only Includes 6 BF Fan Tray Bundles with no additional open FT Slots . 2 Post Rack Kit included • Min=0 \ Max = 32 QSFP+/QSFP28 40/100G Transceivers • Min=0 \ Max = 8 QSFP-DD 400G Transceivers • QSA28 Adapter Min=0 \ Max=40, ports 1-40 (rule7) 1U - Height **Configuration Rules** Rule # Description 1 The following Transceivers install into this Switch: (Use OD1 or BO1 quoted to switch if switch is CTO) - if applicable: HPE Aruba Networking 4x100G DR QSFP-DD SN 500m SMF Transceiver S3N90A HPE Aruba Networking 4x100G FR QSFP-DD SN 2km SMF Transceiver S3N91A HPE Aruba Networking 4x100G LR QSFP-DD SN 10km SMF Transceiver S3N92A HPE Aruba Networking 400G DR4 QSFP-DD MP012 500m SMF Transceiver S3N93A HPE Aruba Networking 400G PLR4 QSFP-DD MPO12 10km SMF Transceiver S3N94A HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver R9B41A HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver R9B42A 2 The following AOCs install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) if applicable: R9B60A HPE Aruba Networking 200G DD-2xQSFP28 100G 3m Active Optic Cable HPE Aruba Networking 200G DD-2xQSFP28 100G 7m Active Optic Cable R9B58A HPE Aruba Networking 200G DD-2xQSFP28 100G 15m Active Optic Cable R9B62A HPE Aruba Networking 200G DD-2xQSFP28 100G 30m Active Optic Cable R9B61A HPE Aruba Networking 200G DD-2xQSFP28 100G 50m Active Optic Cable R9B59A HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable R9B55A HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable R9B53A HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable R9B57A HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable R9B56A HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable R9B54A HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable R9B50A HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable R9B48A HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable R9B52A HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable R9B51A HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable R9B49A HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable R9B45A HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable R9B43A HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable R9B47A HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable R9B46A HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable R9B44A 3 The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable: HPE Aruba Networking 100G QSFP28 MPO SR4 100m 12-fiber MPO OM3 MMF Transceiver JL309A HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver R9B63A HPE Aruba Networking 100G QSFP28 LC CWDM4 2km SMF Transceiver ROZ30A HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver JL310A HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver JL743A HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable JL856A HPE Aruba Networking 100G DR QSFP28 LC 500m SMF Transceiver S3N88A

	HPE Aruba Networking 100G LR QSFP28 LC 10km SMF Transceiver HPE Aruba Networking 100G SR2 MPO QSFP28 100m MMF Transceiver HPE Aruba Networking 100G QSFP28 to QSFP28 7m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable HPE QSFP28 to SFP28 Adapter	S3N89A S1C93A R0Z27A R0Z28A R0Z29A 845970-B21
4	OCA Only: Required Custom Choice (Min1/Max1) Switch/Router/Power Supply to PDU Power Cord - B2B in North America, Mexico, Taiwan, and Japan or B2C ROW. (OCA Default B2B or B2C for Rack Level CTO) Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default for BTO) High Volt Switch/Router/Power Supply to Wall Power Cord - B2E Option. (Offered only in North America, Mexico, Taiwan, and Japan) No Power Cord - AC3 Option	
5	If the CTO Switch Chassis needs to be racked, Then the CTO Base Model needs to integrate (with 0D1) to the HPE Network Rack.	
6	 Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C" Option, then Display the following: For BTO shipments to India: Please replace <base model=""/>#B2C option with <base model=""/>#AC3 in the Bill of Materials and add the appropriate INDIA PDU Power Cord below via Ad-Hoc: JL671A - HPE 2.0m C13 to C14 PDU IN Power Cord JL672A - HPE 2.5m C15 to C14 PDU IN Power Cord JL673A - HPE 2.5m C19 to C20 PDU IN Power Cord 	
	For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. (Ex. JL671A#0D1)	
7	If qty1 of the folowing QSA28 Adapter(845970-B21) is selected, then increase max SFP28 Port qty by 1 and allow user selection of the following SFP Transceivers. Refer to qty and port restrictions for individual Switch in the "Additional Info" sections: (Use #0D1 for this XCVR Adapter since switch is factory racked) HPE Aruba Networking 10G SFP+ LC SR 300m OM3 MMF Transceiver HPE Aruba Networking 10G SFP+ LC LR 10km SMF Transceiver HPE Aruba Networking 10G SFP+ LC ER 40km SMF Transceiver HPE Aruba Networking 10G SFP+ LC SR 300m MMF TAA Transceiver HPE Aruba Networking 10G SFP+ LC LR 10km SMF TAA Transceiver	J9150D J9151E J9153D JL748A JL749A
	HPE Aruba Networking 25G SFP28 LC SR 100m MMF Transceiver HPE Aruba Networking 25G SFP28 LC eSR 400m MMF Transceiver	JL484A JL485A
8	 HPE Aruba Networking 25G SFP28 LC LR 10km SMF Transceiver The following Transceivers install into this Switch: (Use BTO only when adding to switch) HPE Networking X142 40G QSFP+ MPO SR4 Transceiver HPE Networking X142 40G QSFP+ MPO eSR4 300M Transceiver HPE Aruba Networking 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable 	JL486A JH231A JH233A JL308A JH232A Q9G82A R0Z22A R0Z23A
9	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable: HPE Aruba Networking 400G FR4 QSFP-DD LC 2km SMF Transceiver	ROZ24A S3N95A
10	HPE Aruba Networking 400G LR4 QSFP-DD LC 10km SMF Transceiver The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable:	S3N96A
	HPE Aruba Networking 100G QSFP28 to QSFP28 1m Direct Attach Copper Cable HPE Aruba Networking 100G QSFP28 to QSFP28 5m Direct Attach Copper Cable	R0Z25A R0Z26A

	HPE Aruba Networking 100G QSFP28 to QSFP28 3m Direct Attach Copper Cable	JL307A
11	The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is	
	CTO) - if applicable:	
	HPE Networking X242 40G QSFP+ to QSFP+ 1m Direct Attach Copper Cable	JH234A
	HPE Networking X242 40G QSFP+ to QSFP+ 3m Direct Attach Copper Cable	JH235A
	HPE Networking X242 40G QSFP+ to QSFP+ 5m Direct Attach Copper Cable	JH236A
Notes:	Locking Power Cord (J9955A) L6-20P is available through the OCA Accessories tab	
Transce	ivers	
	SFP+ Transceivers	
Notes:	Compatible with QSA28 adapter only	
	HPE Aruba Networking 10G SFP+ LC SR 300m OM3 MMF Transceiver	J9150D
	HPE Aruba Networking 10G SFP+ LC LR 10km SMF Transceiver	J9151E
	HPE Aruba Networking 10G SFP+ LC ER 40km SMF Transceiver	J9153D
	HPE Aruba Networking 10G SFP+ LC SR 300m MMF TAA Transceiver	JL748A
	HPE Aruba Networking 10G SFP+ LC LR 10km SMF TAA Transceiver	JL749A
	SFP28 Transceivers	
	HPE Aruba Networking 25G SFP28 LC SR 100m MMF Transceiver	JL484A
	HPE Aruba Networking 25G SFP28 LC eSR 400m MMF Transceiver	JL485A
	HPE Aruba Networking 25G SFP28 LC LR 10km SMF Transceiver	JL486A
	QSFP+ Transceivers	
	HPE Networking X142 40G QSFP+ MPO SR4 Transceiver	JH231A
	HPE Networking X142 40G QSFP+ MPO eSR4 300M Transceiver	JH233A
	HPE Aruba Networking 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver	JL308A
	HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver	JH232A
	HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver	Q9G82A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable	ROZ22A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable	ROZ23A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable	R0Z24A
	QSFP28 Transceivers	
	HPE Aruba Networking 100G QSFP28 MPO SR4 100m 12-fiber MPO OM3 MMF Transceiver	JL309A
	HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver	R9B63A
	HPE Aruba Networking 100G QSFP28 LC CWDM4 2km SMF Transceiver HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver	ROZ3OA JL310A
	HPE Aruba Networking 100G QSFP28 LC ER4 10km SMF 2-shand transceiver HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver	JLJIJA JL743A
	HPE Aruba Networking 100G QSFP28 LC 500m SMF Transceiver	S3N88A
	HPE Aruba Networking 100G LR QSFP28 LC 10km SMF Transceiver	S3N89A
	HPE Aruba Networking 100G SR2 MPO QSFP28 100m MMF Transceiver	S1C93A
	HPE Aruba Networking 100G QSFP28 to QSFP28 1m Direct Attach Copper Cable	R0Z25A
	HPE Aruba Networking 100G QSFP28 to QSFP28 5m Direct Attach Copper Cable	R0Z26A
	HPE Aruba Networking 100G QSFP28 to QSFP28 3m Direct Attach Copper Cable	JL307A
	HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable	JL856A
	HPE Aruba Networking 100G QSFP28 to QSFP28 7m Active Optical Cable	R0Z27A
	HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable	R0Z28A
	HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable	R0Z29A
Dula #	QSFP-DD Transceivers	CI/LI
Rule #	Description	SKU
	HPE Aruba Networking 4x100G DR QSFP-DD SN 500m SMF Transceiver	S3N90A
	HPE Aruba Networking 4x100G FR QSFP-DD SN 2km SMF Transceiver	S3N91A
	HPE Aruba Networking 4x100G LR QSFP-DD SN 10km SMF Transceiver	S3N92A
	HPE Aruba Networking 400G DR4 QSFP-DD MPO12 500m SMF Transceiver	S3N93A
	HPE Aruba Networking 400G PLR4 QSFP-DD MPO12 10km SMF Transceiver	S3N94A
	HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver	R9B41A
	HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver	R9B42A

	HPE Aruba Networking 400G FR4 QSFP-DD LC 2km SMF Transceiver	S3N95A
	HPE Aruba Networking 400G LR4 QSFP-DD LC 10km SMF Transceiver	S3N96A
	QSFP-DD AOC	
Rule #	Description	SKU
	HPE Aruba Networking 200G DD-2xQSFP28 100G 3m Active Optic Cable	R9B60A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 7m Active Optic Cable	R9B58A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 15m Active Optic Cable	R9B62A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 30m Active Optic Cable	R9B61A
	HPE Aruba Networking 200G DD-2xQSFP28 100G 50m Active Optic Cable	R9B59A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable	R9B55A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable	R9B53A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable	R9B57A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable	R9B56A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable	R9B54A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable	R9B50A R9B48A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable	R9B52A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable	R9B51A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable	R9B49A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable	R9B45A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable	R9B43A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable	R9B47A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable	R9B46A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable	R9B44A
Notes:	Only the QSFP-DD end of the AOC to the 9300 Switch is supported	
	QSA28 Adapter	
	HPE QSFP28 to SFP28 Adapter	845970-B21
Notes:	If selecting the 845970-B21 - QSFP28 to SFP28 Adapter, then see Aruba Transceiver Guide for	
	details.	
Switch O	ptions	
	Rack Mount Kit	
	For 9300 System (std 0 // max 1) User Selection (min 0 // max 1) per enclosure	
	For 9300S System (std 0 // max 1) User Selection (min 0 // max 1) per enclosure	
Rule #	Description	SKU
1, 3	HPE Aruba Networking X474 4-post Rack Kit	JL483C
	Default qty 1	
1, 2	HPE Aruba Networking X414 1U Universal 4-post Rack Mount Kit	J9583B
	Configuration Rules	
Rule#	Description	SKU
1	If the switch will be factory racked into an HPE Universal Rack, then (Min 1) of the 4 Post Rack	
	Mount kit is required.	
2	Compatible with 9300S only: S0F82A	
3	Compatible with 9300-32D: R9A29A, R9A30A	
	India PDU Cable	
	For 9300 (std 0 // max 2) User Selection (0 or 2) per enclosure	
	For 9300S System (std 0 // max 2) User Selection (0 or 2) per enclosure	
Rule #	Description	SKU
1, 3	HPE Networking 2.0m C13 to C14 PDU India Power Cord	JL671A
	C13 India PDU Cable for Factory Racked Systems Only	
1, 2	HPE Networking 2.5m C15 to C14 PDU India Power Cord	JL672A
	C15 India PDU Cable for Factory Racked Systems Only	

Rule #	Configuration Rules Description	SKU
1	This cable is intended for India use only. Typically power cord is ordered when power supply option #AC3 is selected.	
2	Compatible with 9300S only: S0F81A, S0F82A, S0F83A, S0F84A	
3	Compatible with 9300-32D: R9A29A, R9A30A	
Accessor	ies	
	Spare Items	
Rule #	Description	SKU
8	 HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G TAA Switch This is a Spare only 	SOF95A
	 Must be used with 2 Power Units (SOF90A, SOF91A, SOF92A) 	
	 Must be used with 6 Fan Tray (S0F93A, S0F94A) 	
	• 2 Post Rack Kit included, must use 4 Post Rack Mount Kit(J9583C) with HPE Racks	
	• 1U - Height	
7	HPE Aruba Networking 9300S 32p QSFP28 100G 8p QSFP-DD 400G Switch	SOF96A
	This is a Spare only	
	 Must be used with 2 Power Units (S0F90A, S0F91A, S0F92A) Must be used with (For Trans (S0F92A, S0F9(A)) 	
	 Must be used with 6 Fan Tray (S0F93A, S0F94A) 2 Post Rack Kit included, must use 4 Post Rack Mount Kit(J9583B) with HPE Racks 	
	 IU - Height 	
3	HPE Aruba Networking 9300-32D 32-port 100/200/400G QSFP-DD 2-port 10G Switch	R8Z96A
	This is a Spare only	
	 Must be used with 2 Power Units (R8Z97A, R8Z98A) 	
	 Must be used with 6 Fan Tray (R8Z99A, R9A00A) 	
	 2 Post Rack Kit included, must use 4 Post Rack Mount Kit(JL483C) with HPE Racks 	
	• 10 - Height	C0500A
4	HPE Aruba Networking X3A15 12VDC 1600W 40-75VDC Back-to-Front Input Screw Terminal Power Supply Unit	SOF90A
1, 2, 5	 Includes 1 x c15, 1600w HPE Aruba Networking X3A13 12VDC 1600W Front-to-Back C15 AC Power Supply Unit 	SOF91A
1, 2, 3	 Includes 1 x c15, 1600w 	301 71A
	HPE Aruba Networking X3A13 12VDC 1600W Front-to-Back C15 AC Power Supply Unit PDU	SOF91A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	HPE Aruba Networking X3A13 12VDC 1600W Front-to-Back C15 AC Power Supply Unit PDU	SOF91A#B2C
	C15 PDU Jumper Cord (ROW) (J9944A)	
	HPE Aruba Networking X3A13 12VDC 1600W Front-to-Back C15 AC Power Supply Unit 220v	SOF91A#B2E
	 HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A) HPE Aruba Networking X3A13 12VDC 1600W Front-to-Back C15 AC Power Supply Unit No Loc 	SOF91A#AC3
	No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	20LATU#YC2
	20P)	
1, 2, 6	HPE Aruba Networking X3A13 12VDC 1600W Back-to-Front C15 AC Power Supply Unit	SOF92A
	• Includes 1 x c15, 1600w	
	HPE Aruba Networking X3A13 12VDC 1600W Back-to-Front C15 AC Power Supply Unit PDU	SOF92A#B2B
	C15 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A)	
	 HPE Aruba Networking X3A13 12VDC 1600W Back-to-Front C15 AC Power Supply Unit PDU C15 PDU Jumper Cord (ROW) (J9944A) 	SOF92A#B2C
	• C15 PDU Jumper Cord (ROW) (J9944A) HPE Aruba Networking X3A13 12VDC 1600W Back-to-Front C15 AC Power Supply Unit 220v	SOF92A#B2E
	HPE 2.3m C15 to NEMA 6-15P Pwr Cord(JL336A)	JUI / ZATUZL
	HPE Aruba Networking X3A13 12VDC 1600W Back-to-Front C15 AC Power Supply Unit No Loc	SOF92A#AC3

	• No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	
	 No Eocalized Power Cold Selected. Ose J9955A to obtain a Eocking Plug Power Cold (E6- 20P) 	
1, 2, 3	 HPE Aruba Networking 9300 1500W 100-240VAC Front-to-Back AC Power Supply Includes 1 x c13, 1500w 	R8Z97A
	HPE Aruba Networking 9300 1500W 100-240VAC Front-to-Back AC Power Supply PDU	R8Z97A#B2 B
	C13 PDU Jumper Cord (NA/MEX/TW/JP) (JL697A)	
	HPE Aruba Networking 9300 1500W 100-240VAC Front-to-Back AC Power Supply PDU	R8Z97A#B2 C
	C13 PDU Jumper Cord (ROW) (JL697A)	
	HPE Aruba Networking 9300 1500W 100-240VAC Front-to-Back AC Power Supply 220v	R8Z97A#B2 E
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A) HPE Aruba Networking 9300 1500W 100-240VAC Front-to-Back AC Power Supply NoLoc 	R8Z97A#AC
		10297A#AC 3
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3	HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply	R8Z98A
	 includes 1 x c13, 1500w HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply PDU 	R8Z98A#B2
		В
	 C13 PDU Jumper Cord (NA/MEX/TW/JP) (JL697A) HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply PDU 	R8Z98A#B2
		C
	C13 PDU Jumper Cord (ROW) (JL697A)	
	HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply 220v	R8Z98A#B2 E
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	Ľ
	HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply NoLoc	R8Z98A#AC 3
	• No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	5
		D07004
5	HPE Aruba Networking 9300 1500W 100-240VAC Back-to-Front AC Power Supply HPE Aruba Networking X761 Front-to-Back Fan	R8Z98A S0F93A
4, 6	HPE Aruba Networking X762 Back-to-Front Fan	SOF94A
3	HPE Aruba Networking 9300 Front-to-Back Fan	R8Z99A
3	HPE Aruba Networking 9300 Back-to-Front Fan	R9A00A
3	HPE Aruba Networking X472 2-post Rack Kit	JL482C
7, 8	HPE Aruba Networking X412 1U Universal 2-post Rack Mount Kit	JL602A
3	HPE Aruba Networking X474 4-post Rack Kit	JL483C
	HPE Aruba Networking X414 1U Universal 4-post Rack Mount Kit	J9583B
	HPE Aruba Networking X2C2 RJ45 to DB9 Console Cable	JL448A
	HPE Aruba Networking USBA-RJ45 PC-to-Switch PIN6TX-3RX 2.5m Cable	R9G48B
	HPE Aruba Networking USB-A reversible to USB-C PC-to-Switch 3m Cable	R9J32A
	HPE Aruba Networking USB-C to USB-C PC-to-Switch 3m Cable HPE Aruba Networking CX Switch Bluetooth Adapter	R9J33A S1H23A
	Configuration Rules	JIIIZJA
Rule #	Description	SKU
1	Localization required on orders without B2B, B2C, B2E or AC3 options.	
2	Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C"	
	Option, then Display the following:	
	For BTO shipments to India:	
	Please replace <base model=""/> #B2C option with <base model=""/> #AC3 in the Bill of	
	Materials and add the appropriate INDIA PDU Power Cord below via Ad-Hoc:	

Configuration Information

	 JL671A - HPE 2.0m C13 to C14 PDU IN Power Cord 	
	 JL672A - HPE 2.5m C15 to C14 PDU IN Power Cord 	
	 JL673A - HPE 2.5m C19 to C20 PDU IN Power Cord 	
	For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. (Ex.	
	JL671A#0D1)	
3	Compatible with 9300-32D: R9A29A, R9A30A.	
4	Compatible with 9300S DC BF Switch: S0F87A, S0F88A.	
5	Compatible with 9300S AC FB Switch: S0F81A, S0F82A	
6	Compatible with 9300S AC BF Switch: S0F83A, S0F84A	
7	Compatible with 9300S Switches: S0F82A, S0F84A, S0F88A	
8	Compatible with 9300S TAA Switches: S0F81A, S0F83A, S0F87A	
Notes:	 Drop down under power supply should offer the following options and results: 	
	 Switch/Router/Power Supply to PDU Power Cord - #B2B in North America, Mexico, 	
	Taiwan, and Japan or #B2C ROW. (OCA Default B2B or B2C for Rack Level CTO)	
	 Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default for PTO) 	
	for BTO)	
	 High Volt Switch/Router/Power Supply to Wall Power Cord - #B2E Option. (Offered only in North America, Mexico, Taiwan, and Japan) 	
	 No Power Cord - #AC3 Option OCA Display Notes: Locking Power Cord (J9955A) L6-20P is available in the Accessories 	
	tab	
	 OCA Display Notes: 2 Power Supplies and 6 Fan Trays are included with the Switch Bundle 	
	OCA Display Notes. 21 ower Supplies and of an Trays are included with the Switch Bundle	
Software		
	HPE Aruba Fabric Composer	
	Single Node Subscription	
	HPE Aruba Networking Fabric Composer Device Management Service Tier 4 Switch 1y	R7G99AAE
	Subscription E-STU	
	HPE Aruba Networking Fabric Composer Device Management Service Tier 4 Switch 3y	R7H00AAE
	Subscription E-STU	
	HPE Aruba Networking Fabric Composer Device Management Service Tier 4 Switch 5y	R7H01AAE
	Subscription E-STU	
	Central	
Notes:	Add the Central Advanced Service Skus to the HPE Aruba Catalog as Standalone:	
	HPE Aruba > Network Management > Central > Advanced	
_	On-Prem Services / 8XXX/9XXX/10XXX Switch Advanced Subscriptions	
3	HPE Aruba Networking Central On-Premises Switch Class5 Advanced 1-year Subscription E-STU	R6V08AAE
3	HPE Aruba Networking Central On-Premises Switch Class5 Advanced 3-year Subscription E-STU	R6V09AAE
3	HPE Aruba Networking Central On-Premises Switch Class5 Advanced 5-year Subscription E-STU	R6V10AAE
3	HPE Aruba Networking Central On-Premises Switch Class5 Advanced 7-year Subscription E-STU	R6V11AAE
3	HPE Aruba Networking Central On-Premises Switch Class5 Advanced 10-year Subscription E-STU	R6V12AAE
2	Cloud Services / 8XXX/9XXX/10XXX Switch Foundation Subscriptions	
2	HPE Aruba Networking Central Switch Class5 Foundation 1-year Subscription E-STU	R3K03AAE R3K04AAE
2 2	HPE Aruba Networking Central Switch Class5 Foundation 3-year Subscription E-STU HPE Aruba Networking Central Switch Class5 Foundation 5-year Subscription E-STU	R3K04AAE R3K05AAE
2	HPE Aruba Networking Central Switch Class5 Foundation 5-year Subscription E-STU HPE Aruba Networking Central Switch Class5 Foundation 7-year Subscription E-STU	R3K06AAE
2	HPE Aruba Networking Central Switch Class5 Foundation 7-year Subscription E-STU	R3K07AAE
2	Configuration Rules	NJKU/AAL
Rule#	Description	SKU
2	Add the Central Cloud Skus to the Aruba Catalog as Standalone:	31.0
-	Aruba > Network Management > Central > Cloud Services	
3	Add the Central On-Prem Skus to the Aruba Catalog as Standalone:	
-	Aruba > Network Management > Central > On-Prem Services	

Aruba > Network Management > Central > On-Prem Services

Configuration Information

HPE Aruba OS-CX

CX Advanced Software Licenses

HPE Aruba Networking CX Software 8/9xxx Switch Advanced 1-year Subscription E-STU	SOT87AAE
HPE Aruba Networking CX Software 8/9xxx Switch Advanced 3-year Subscription E-STU	SOT88AAE
HPE Aruba Networking CX Software 8/9xxx Switch Advanced 5-year Subscription E-STU	SOT89AAE
HPE Aruba Networking CX Software 8/9xxx Switch Advanced 7-year Subscription E-STU	SOT90AAE
HPE Aruba Networking CX Software 8/9xxx Switch Advanced 10-year Subscription E-STU	SOT86AAE

As-a-Service

Notes:

HPE Aruba Networking Central

Cloud Services / Switch Advanced AAS Licenses

HPE Aruba Networking Central Switch Class-5 Advanced 7 year Subscription SaaS	SOW45AAS
HPE Aruba Networking Central Switch Class-5 Advanced 10 year Subscription SaaS	SOW46AAS
HPE Aruba Networking Central Switch Class-5 Advanced 1 year Subscription SaaS	SOW62AAS
HPE Aruba Networking Central Switch Class-5 Advanced 3 year Subscription SaaS	SOW63AAS
HPE Aruba Networking Central Switch Class-5 Advanced 5 year Subscription SaaS	SOW64AAS
HPE Aruba Networking Central Switch Class-5 Advanced 7 year Subscription SaaS	SOW65AAS
HPE Aruba Networking Central Switch Class-5 Advanced 10 year Subscription SaaS	SOW66AAS
HPE Aruba Networking Central Switch Class-5 Advanced 1 year Subscription SaaS	SOW87AAS
HPE Aruba Networking Central Switch Class-5 Advanced 3 year Subscription SaaS	SOW88AAS
HPE Aruba Networking Central Switch Class-5 Advanced 5 year Subscription SaaS	SOW89AAS
For IRIS reference only. No action required for OCX and Clic	

Technical Specifications

Description	HPE Aruba 9300-32D 32p 100/200/400G QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2 AC PSU Bundle (R9A29A) The HPE Aruba Networking CX 9300 Switch Series configuration switch supporting 32-ports of 100Gb solution for flexible, cost-effective, high-density net connectivity. This solution helps protect enterprises 10GbE and 25GbE to 100GbE/400GbE EVPN-VXI smaller footprint.	E, 200GbE or 400GbE. The switch is an ideal working for server, storage, and intra-fabric s investment as they transition server farms from AN spine configurations at reduced power and a	
Power supplies	2 redundant power supplies, field-replaceable, hot-	swappable	
Fans	6 redundant fans, field-replaceable, hot-swappable		
Physical characteristic Dimensions	s 17.26" x 23.23" x 1.71" (43.84 x 59 x 4.35 cm)		
Full configuration weight	26.12 lb (11.85 kg)		
Additional specificatio			
CPU	x86		
Memory, Drive and Flash	128GB m.2 SSD, 4GB mSATA, 16MB SPI Flash, 160	GB x2 SODIMM	
Packet Buffer	132MB		
Performance*			
Switching Capacity	25.6Tbps		
IPv4 Host Table	163,840		
IPv6 Host Table	81,920		
IPv4 Unicast Routes	65,536 (1,269,760 Unidimensional for Spine)		
IPv6 Unicast Routes	32,768 (624,640 Unidimensional for Spine)		
MAC Table Size	81,920 (32,768 Unidimensional for Spine)		
IGMP Groups	8,192		
MLD Groups	8,192		
IPv4 Multicast	8,192		
Routes			
IPv6 Multicast	4,096		
Routes			
Notes:	*Some of these scaling numbers assume shared ta	bles and uni-dimensional fraffic.	
Environmental	32°F to 113°F (0°C to 45°C) at sea level.	32°F to 95°F (0°C to 35°C) at sea level.	
Operating temperature	Derate -1°C for every 1,000 ft to 10,000 ft. (3.0 km)	Derate -1°C for every 1,000 ft to 10,000 ft. (3.0 km)	
Non-Operating/	-40°C to 70°C (-40°F to 158°F) up to 4.6km (15,00	00 ft)	
Storage Temperature			
Operating relative humidity	15% to 95% @ 113°F (45°C) non-condensing	15% to 95% @ 95°F (35°C) non-condensing	
Non-Operating/ Storage relative humidity	15% to 90% @ 158°F (70°C) non-condensing		
Max operating altitude	Up to 10,000ft (3km)		
Max non-operating	Up to 15,000ft (4.6km)		
Primary airflow	Front-to-Back	Back-to-Front	
Acoustic ¹	LWad = 8.1 Bel LpAm (Bystander) = 61 dB	LWad = 8.3 Bel LpAm (Bystander) = 62 dB	



Technical Specifications

Sound Pressure Level (Electrical characterist	•			
	50-60Hz			
Frequency	100-127 / 220-240 VAC			
AC Voltage	200-240V required to support 8-32 port production	an configuration		
Current	12A / 8A	Sh conngulation		
	100% Traffic Rate: 675W; Idle: 210W	100% Traffic Rate: 688W; Idle: 221W		
Power consumption (230VAC)				
	HPE Aruba 9300-32D 32p 100/200/400G	HPE Aruba 9300-32D 32p 100/200/400G		
	QSFP-DD 2p 10G SFP+ Front-to-Back 6 Fans 2	QSFP-DD 2p 10G SFP+ Back-to-Front 6 Fans		
	AC PSU Bundle (R9A29A)	AC PSU Bundle (R9A30A)		
Safety	Safety-EU EN 60950-1:2006 +A11:2009 +A1:202	10 +A12:2011 + A2:2013		
	EN 62368-1:2014 +A11:2017			
	EN 62368-1:2018+A11:2020			
	Safety-Worldwide IEC 60950-1:2005 (Second Ed	lition) + Am 1:2009 + Am 2: 2013		
	IEC 62368-1:2014 (Second Edition)			
	IEC 62368-1:2018 (Third Edition)			
	Safety-North America UL 62368-1 3rd, Ed.			
	CAN/CSA-C22.2 N. 62368-1.19 3rd. Ed.			
	Environmental Drop, Vibration, Shock: IEC 17025,	ISTA 3C		
EMC	Immunity			
	EN55024:2015 / CISPR 24:2015			
	ESD: EN 61000-4-2			
	Radiated: EN 61000-4-3			
	EFT/Burst: EN 61000-4-4			
	Surge: EN 61000-4-5			
	Conducted: EN 61000-4-6			
	Power frequency magnetic field: IEC 6100	0-4-8		
	Voltage dips and interruptions: EN 61000	-4-11		
	Harmonics: EN 61000-3-2, IEC 61000-3-			
	Flicker: EN 61000-3-3, IEC 61000-3-3			
	Emissions			
	EN 55032:2015 / CISPR 32:2015, Class A	Λ		
	VCCI-32:2016 Class A			
	CNS 13483			
	AS/NZS			
	ICES-003 Issue 5			
	FCC CFR 47 Part 15:2010, Class A			
	RoHS-6 Compliant (EN 50581:2012)			
Lasers	EN60825-1:2014/IEC 60825-1: 2014 Class 1			
	Class 1 Laser Products/Laser Klasse 1			
Management	SNMP			
	REST			
	RJ-45 serial			
	Micro USB console port			
	RJ-45 OOBM Port			
Mounting and	Mounts in an EIA standard 19-inch rack or other ec	guipment cabinet; horizontal surface mounting only		
enclosure	2-post Rack Mount Kit included with switch, option			
	- JL483C.			

Technical Specifications

Standards and Protocols

The following standards and protocols are supported.

- IEEE 802.1AB-2009
- IEEE 802.1ak-2007
- IEEE 802.1t-2001
- IEEE 802.1AX-2008 Link Aggregation
- IEEE 802.1p Traffic Class Expediting and Dynamic Multicast Filtering
- IEEE 802.1Q VLANs
- IEEE 802.1s Multiple Spanning Trees
- IEEE 802.1w Rapid Reconfiguration of Spanning Tree
- IEEE 802.3ad Link Aggregation Control Protocol (LACP)
- IEEE 802.3x Flow Control
- IEEE 802.3z Gigabit Ethernet
- IEEE 802.3by 25 Gigabit Ethernet
- IEEE 802.3ba 40 Gigabit Ethernet
- IEEE 802.3cd 50 Gigabit Ethernet
- IEEE 802.3ba and 802.3cd 100 Gigabit Ethernet
- IEEE 802.3bs 200 and 400 Gigabit Ethernet
- RFC 768 UDP
- RFC 791 IP
- RFC 792 ICMP
- RFC 793 TCP
- RFC 826 ARP
- RFC 768 User Datagram Protocol
- RFC 813 Window and Acknowledgement Strategy in TCP
- RFC 815 IP datagram reassembly algorithms
- RFC 879 TCP maximum segment size and related topics
- RFC 896 Congestion control in IP/TCP internetworks
- RFC 917 Internet subnets
- RFC 919 Broadcasting Internet Datagrams
- RFC 922 Broadcasting Internet Datagrams in the Presence of Subnets (IP_BROAD)
- RFC 925 Multi-LAN address resolution
- RFC 1215 Convention for defining traps for use with the SNMP
- RFC 1256 ICMP Router Discovery Messages
- RFC 1393 Traceroute Using an IP Option
- RFC 1591 Domain Name System Structure and Delegation
- RFC 1657 Definitions of Managed Objects for BGP-4 using SMIv2
- RFC 1772 Application of the Border Gateway Protocol in the Internet
- RFC 1981 Path MTU Discovery for IP version 6
- RFC 1997 BGP Communities Attribute
- RFC 1998 An Application of the BGP Community Attribute in Multi-home Routing
- RFC 2385 Protection of BGP Sessions via the TCP MD5 Signature Option
- RFC 2401 Security Architecture for the Internet Protocol
- RFC 2402 IP Authentication Header
- RFC 2406 IP Encapsulating Security Payload (ESP)
- RFC 2460 Internet Protocol, Version 6 (IPv6) Specification
- RFC 2545 Use of BGP-4 Multiprotocol Extensions for IPv6 Inter-Domain Routing
- RFC 2710 Multicast Listener Discovery (MLD) for IPv6
- RFC 2787 Definitions of Managed Objects for the Virtual Router Redundancy Protocol
- RFC 2918 Route Refresh Capability for BGP-4

QuickSpecs

- RFC 2934 Protocol Independent Multicast MIB for IPv4
- RFC 3137 OSPF Stub Router Advertisement
- RFC 3176 InMon Corporation's sFlow: A Method for Monitoring Traffic in Switched and Routed Networks
- RFC 3484: Default Address Selection for Internet Protocol version 6 (IPv6)
- RFC 3509 Alternative Implementations of OSPF Area Border Routers
- RFC 3623 Graceful OSPF Restart
- RFC 3810 Multicast Listener Discovery Version 2 (MLDv2) for IPv6
- RFC 4213 Basic Transition Mechanisms for IPv6 Hosts and Routers
- RFC 4251 The Secure Shell (SSH) Protocol
- RFC 4271 A Border Gateway Protocol 4 (BGP-4)
- RFC 4273 Definitions of Managed Objects for BGP-4
- RFC 4291 IP Version 6 Addressing Architecture
- RFC 4292 IP Forwarding Table MIB
- RFC 4293 Management Information Base for the Internet Protocol (IP)
- RFC 4360 BGP Extended Communities Attribute
- RFC 4486 Subcodes for BGP Cease Notification Message
- RFC 4552 Authentication/Confidentiality for OSPFv3
- RFC 4724 Graceful Restart Mechanism for BGP
- RFC 4760 Multiprotocol Extensions for BGP-4
- RFC 4940 IANA Considerations for OSPF
- RFC 5095: Deprecation of Type 0 Routing Headers in IPv6
- RFC 5187 OSPFv3 Graceful Restart
- RFC 5701 IPv6 Address Specific BGP Extended Community Attribute
- RFC 6987 OSPF Stub Router Advertisement
- RFC 7047 The Open vSwitch Database Management Protocol
- RFC 7059 A Comparison of IPv6-over-IPv4 Tunnel Mechanisms
- RFC 7313 Enhanced Route Refresh Capability for BGP-4
- RFC 8201 Path MTU Discovery for IP version 6

Aruba Data Center Networking Solution for HPE

New HPE Aruba Data Center Networking Solution SKUs for HPE

Hewlett Packard Enterprise and HPE Aruba offer customers highly differentiated pre-engineered IT infrastructure solutions that span a wide variety HPE compute, storage, networking that span virtualization, vSAN, HCI, HPC, MCS, Microsoft, SAP HANA, Vmware, Nutanix application and laaS service offerings. HPE Aruba 10/25 and 40/100G CX switches can be deployed as part of these solutions and is often designed into these integrated solutions along with HPE ProLiant DL/DX servers, SimpliVity, Nimble, Synergy, Cray Shasta, Cray ClusterStor, Superdome Flex and HPE GreenLake. These ready-to-deploy, integrated IT data center solutions help simplify and speed IT service delivery while reducing the time, risk, and expertise needed to deploy complex solutions.

To ensure that these Hewlett Packard Enterprise and Aruba integrated solutions receive simplified ordering and the highest-level of customer service and support, HPE Aruba has created a special tracking HPE Aruba Data Center networking SKUs for HPE deployments that identifies these integrated solutions to ensure they receive rapid support triage and streamlines escalation through HPE Services. Please use these new tracking SKUs when HPE Aruba CX switches are included in HPE integrated and mixed compute, storage and networking configuration and deployments, refer to this page for HPE Aruba Switches qualification with Storage solutions:

https://spock.corp.int.hpe.com/spock/utility/document.aspx?docurl=Shared%20Documents/hw/switches/HPE_Aruba_Sto rage_Networking_Connectivity.pdf

Notes: Current HPE Aruba "J#" SKUs should still be used for all data center network centric (HPE Aruba "only", Non HPE environments). Please contact your sales representative for additional information and ordering guidance.

Configuration Information BTO Models

	AC Bundles	
Rule #	Description	SKU
1, 2, 3, 4, 5, 6	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 Includes 2 FB Power Supplies (S1D05A) with no additional open PS slots, Warning: 200- 225VAC use only 	
	 Includes 6 FB Fan Tray Bundles (S1D15A) with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP28/QSFP-DD 100/200/400G Transceivers 1U - Height 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent) 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	• C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A) 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
1, 2, 3, 4, 5, 6	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	 Includes 2 BF Power Supplies (S1D06A) with no additional open PS slots, Warning: 200- 225VAC use only 	
	 Includes 6 BF Fan Tray Bundles (S1D16A) with no additional open FT Slots 2 Post Rack Kit included 	
	 Min=0 \ Max = 32 QSFP28/QSFP-DD 100/200/400G Transceivers 	

	• 1U - Height	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU	S1D08A
	Switch Bdl	
	• C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent) HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU	S1D08A
	Switch Bdl	SIDUOA
	 C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent) 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU	S1D08A
	Switch Bdl	01000/1
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A) 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU	S1D08A
	Switch Bdl	
	• No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-	
	20P)	
	Configuration Rules	
Rule #	Description	
1	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver	S1D18A
2	HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver	S1D19A
2	The following AOC's install into this Switch: (Use BTO only when adding to switch)	C1D20A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable	S1D20A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable	S1D21A S1D22A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable	S1D22A S1D23A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable	S1D23A S1D24A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 3m Active Optical Cable	S1D24A S1D25A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 7m Active Optical Cable	S1D25A S1D26A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 15m Active Optical Cable	S1D27A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 30m Active Optical Cable	S1D28A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 50m Active Optical Cable	S1D29A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable	S1D30A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable	S1D31A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable	S1D32A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable	S1D33A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable	S1D34A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable	S1D35A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable	S1D36A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable	S1D37A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable	S1D38A
7	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable	S1D39A
3	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	Aruba 100G QSFP28 MPO SR4 MMF Transceiver for HPE	R9F75A
	HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver	S1D17A JL310A
	HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver	JL743A
	HPE 100Gb QSFP28 Bidirectional Transceiver	845972-B21
	HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable	R9F76A
	HPE Aruba Networking 100G QSFP28 to QSFP28 7m Active Optical Cable	R9F79A
	HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable	R9F80A
	HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable	R9F81A
4	Localization required on orders without B2B, B2C, B2E or AC3 options.	
5	Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C"	
	Option, then Display the following:	

	 For BTO shipments to India: Please replace <base model=""/>#B2C option with <base Model>#AC3 in the Bill of Materials and add the appropriate INDIA PDU Power Cord below via Ad-Hoc:</base 	
	HPE Networking 2.0m C13 to C14 PDU India Power Cord	JL671A
	HPE Networking 2.5m C15 to C14 PDU India Power Cord	JL672A
	HPE Networking 2.5m C19 to C20 PDU India Power Cord	JL673A
	 For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. (Ex. JL671A#0D1) 	0207071
6	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Aruba Networking 40G QSFP+ MPO SR4 Transceiver	R9F97A
	HPE Aruba Networking 40G QSFP+ MPO eSR4 300M Transceiver	R9F98A
	Aruba 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver for HPE	R9G02A
	HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver	JH232A
	HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver	Q9G82A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable	R9G03A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable	R9G04A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable	R9G05A
Notes:	 Drop down under power supply should offer the following options and results: 	
	• Switch/Router/Power Supply to PDU Power Cord - B2B in North America, Mexico,	
	Taiwan, and Japan or B2C ROW. (OCA Default B2B or B2C for Rack Level CTO)	
	 Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default 	
	for BTO and Box Level CTO)	
	 High Volt Switch/Router/Power Supply to Wall Power Cord - B2E Option. (Offered 	
	only in North America, Mexico, Taiwan, and Japan)	
	 No Power Cord - AC3 Option 	
	 Locking Power Cord (J9955A) L6-20P is available through the OCA Accessories tab 	
	 OCA Only Model Selection Form – HPE Offering > Aruba > DC Solutions Switches for HPE > 	
	AOS-CX: Aruba 9300 DC Switch Series	
Rack Level	Integration CTO Models	
	AC Bundles	
Rule #	Description	SKU
1, 2, 3, 4, 5, 6, 7	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 Includes 2 FB Power Supplies (S1D05A) with no additional open PS slots, Warning: 200- 225VAC use only 	
	 Includes 6 FB Fan Tray Bundles (S1D15A) with no additional open FT Slots 	
	 2 Post Rack Kit included, must select 4 Post Rack Kit 	
	 Min=0 \ Max = 32 QSFP28/QSFP-DD 100/200/400G Transceivers 	
	• 1U - Height	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	• C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU	S1D07A
	Switch Bdl	
	• C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Prt2Pwr Airflow 6Fs 2AC PSU Switch Bdl	S1D07A
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	



1, 2, 3, 4, 5, 6, 7	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	 Includes 2 BF Power Supplies (S1D06A) with no additional open PS slots, Warning: 200- 225VAC use only 	
	 Includes 6 BF Fan Tray Bundles (S1D16A) with no additional open FT Slots 	
	 2 Post Rack Kit included, must select 4 Post Rack Kit 	
	 Min=0 \ Max = 32 QSFP28/QSFP-DD 100/200/400G Transceivers 	
	• 1U - Height	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	 C13 PDU Jumper Cord (NA/MEX/TW/JP) (J9943A C15 equivalent) 	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	C13 PDU Jumper Cord (ROW) (J9944A C15 equivalent)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	• HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A)	
	HPE Aruba Networking 9300-32D 32xQSFP-DD 400G 2xSFP+10G Pwr2Prt Airflow 6Fs 2AC PSU Switch Bdl	S1D08A
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 	
	Configuration Rules	
Rule #	Description	
1	The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable:	
	HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver	S1D18A
2	HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver	S1D19A
2	The following AOCs install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable:	
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable	S1D20A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable	S1D21A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable	S1D22A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable	S1D23A S1D24A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 3m Active Optical Cable	S1D24A S1D25A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 7m Active Optical Cable	S1D26A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 15m Active Optical Cable	S1D27A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 30m Active Optical Cable	S1D28A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 50m Active Optical Cable	S1D29A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable	S1D30A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable	S1D31A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable	S1D32A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable	S1D33A S1D34A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable	S1D34A S1D35A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable	S1D35A S1D36A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable	S1D37A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable	S1D38A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable	S1D39A
3	The following Transceivers install into this Switch: (Use 0D1 or B01 quoted to switch if switch is CTO) - if applicable:	
	Aruba 100G QSFP28 MPO SR4 MMF Transceiver for HPE	R9F75A
	HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver	S1D17A
	HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver	JL310A

	HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver	JL743A
	HPE 100Gb QSFP28 Bidirectional Transceiver	845972-B21
	HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable	R9F76A
	HPE Aruba Networking 100G QSFP28 to QSFP28 7m Active Optical Cable	R9F79A
	HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable	R9F80A
,	HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable	R9F81A
4	OCA Only:	
	Required Custom Choice (Min1/Max1) Switch (Deuter (Deuter Switch to DDL) Deuter Cond. D2D is North America. Maxies	
	 Switch/Router/Power Supply to PDU Power Cord - B2B in North America, Mexico, Taiwan, and Japan or B2C ROW. (OCA Default B2B or B2C for Rack Level CTO) 	
	 Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default for 	
	BTO)	
	High Volt Switch/Router/Power Supply to Wall Power Cord - B2E Option. (Offered only	
	in North America, Mexico, Taiwan, and Japan)	
	No Power Cord - AC3 Option	
5	If the CTO Switch Chassis needs to be racked, Then the CTO Base Model needs to integrate (with	
	0D1) to the HPE Network Rack.	
6	Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C"	
	Option, then Display the following:	
	 For BTO shipments to India: 	
	Please replace <base model=""/> #B2C option with <base model=""/> #AC3 in the Bill of	
	Materials and add the appropriate INDIA PDU Power Cord below via Ad-Hoc:	
	HPE Networking 2.0m C13 to C14 PDU India Power Cord	JL671A
	HPE Networking 2.5m C15 to C14 PDU India Power Cord	JL672A
	HPE Networking 2.5m C19 to C20 PDU India Power Cord	JL673A
	 For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. (Ex. JL671A#0D1) 	
7	The following Transceivers install into this Switch: (Use BTO only when adding to switch)	
	HPE Aruba Networking 40G QSFP+ MPO SR4 Transceiver	R9F97A
	HPE Aruba Networking 40G QSFP+ MPO eSR4 300M Transceiver	R9F98A
	Aruba 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver for HPE	R9G02A
	HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver	JH232A
	HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable	Q9G82A R9G03A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable	R9G03A R9G04A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable	R9G05A
Notes:	Locking Power Cord (J9955A) L6-20P is available through the OCA Accessories tab	10/000/1
Transcei		
	QSFP+ Transceivers	
	HPE Networking X142 40G QSFP+ MPO SR4 Transceiver	JH231A
	HPE Networking X142 40G QSFP+ MPO eSR4 300M Transceiver	JH233A
	HPE Aruba Networking 40G QSFP+ LC Bidirectional 150m MMF 2-strand Transceiver	JL308A
	HPE Networking X142 40G QSFP+ LC LR4 SM Transceiver	JH232A
	HPE Aruba Networking 40G QSFP+ LC ER4 40km SMF Transceiver	Q9G82A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 7m Active Optical Cable	ROZ22A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 15m Active Optical Cable	ROZ23A
	HPE Aruba Networking 40G QSFP+ to QSFP+ 30m Active Optical Cable	R0Z24A
	QSFP28 Transceivers	11 700 4
	HPE Aruba Networking 100G QSFP28 MPO SR4 100m 12-fiber MPO OM3 MMF Transceiver HPE Aruba Networking 100G QSFP28 LC FR1 SMF 2km Transceiver	JL309A R9B63A
	HPE Aruba Networking 100G QSFP28 LC CWDM4 2km SMF Transceiver	R9B03A R0Z30A
	HPE Aruba Networking 100G QSFP28 LC LR4 10km SMF 2-strand Transceiver	JL310A
	HPE Aruba Networking 100G QSFP28 LC ER4L 40km SMF Transceiver	JL743A
	HPE Aruba Networking 100G QSFP28 to QSFP28 2m Active Optical Cable	JL856A

	HPE Aruba Networking 100G QSFP28 to QSFP28 7m Active Optical Cable	ROZ27A
	HPE Aruba Networking 100G QSFP28 to QSFP28 15m Active Optical Cable	R0Z28A
	HPE Aruba Networking 100G QSFP28 to QSFP28 30m Active Optical Cable	R0Z29A
	QSFP-DD Transceivers	
Rule #	Description	SKU
	HPE Aruba Networking 400G QSFP-DD MPO-16 SR8 100m MMF Transceiver	S1D18A
	HPE Aruba Networking 400G QSFP-DD MPO-12 eDR4 2km SMF Transceiver	S1D19A
	QSFP-DD AOC	
Rule #	Description	SKU
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 3m Active Optical Cable	S1D20A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 7m Active Optical Cable	S1D21A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 15m Active Optical Cable	S1D22A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 30m Active Optical Cable	S1D23A
	HPE Aruba Networking 400G QSFP-DD to QSFP-DD 50m Active Optical Cable	S1D24A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 3m Active Optical Cable	S1D25A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 7m Active Optical Cable	S1D26A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 15m Active Optical Cable	S1D27A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 30m Active Optical Cable	S1D28A
	HPE Aruba Networking 200G QSFP-DD to 2x QSFP28 100G 50m Active Optical Cable	S1D29A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 3m Active Optical Cable	S1D30A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 7m Active Optical Cable	S1D31A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 15m Active Optical Cable	S1D32A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 30m Active Optical Cable	S1D33A
	HPE Aruba Networking 400G QSFP-DD to 2x QSFP56 200G 50m Active Optical Cable	S1D34A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 3m Active Optical Cable	S1D35A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 7m Active Optical Cable	S1D36A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 15m Active Optical Cable	S1D37A
	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 30m Active Optical Cable	S1D38A S1D39A
Notes:	HPE Aruba Networking 400G QSFP-DD to 4x QSFP56 100G 50m Active Optical Cable Only the QSFP-DD end of the AOC to the 9300 Switch is supported	21D2AM
Switch O		
	Rack Mount Kits	
Rule #	For 9300 DC System (std 0 // max 1) User Selection (min 0 // max 1) per enclosure	SKU
Rule #	Description HPE Aruba Networking X474 4-post Rack Kit	JL483C
		JL403C
Neter	 Default qty 1 If the switch will be factory racked into an HPE Universal Rack, then (Min 1) of the 4 Post Rack 	
Notes:	Mount kit is required.	
	India PDU Cable	
	For 9300 DC System (std 0 // max 1) User Selection (min 0 // max 1) per enclosure	
Rule #	Description	SKU
Rule #	HPE Networking 2.0m C13 to C14 PDU India Power Cord	JL671A
	C13 India PDU Cable for Factory Racked Systems Only	JLU/IA
Notes:	This cable is intended for India use only. Typically power cord is ordered when power supply option	#AC3 is
NUIES:	selected.	
	Second.	

Aruba Data Center Networking Solution for HPE

Accessories

ALLESSO	Spare Items				
Rule #	Description	SKU			
1, 2	 HPE Aruba Networking 9300 1500W 100-240VAC Port-to-Power Airflow Power Supply Unit includes 1 x c13, 1500w 	S1D05A			
	 HPE Aruba Networking 9300 1500W 100-240VAC Port-to-Power Airflow Power Supply Unit C13 PDU Jumper Cord (NA/MEX/TW/JP) (JL697A) 	S1D05A			
	 HPE Aruba Networking 9300 1500W 100-240VAC Port-to-Power Airflow Power Supply Unit C13 PDU Jumper Cord (ROW) (JL697A) 	S1D05A			
	 HPE Aruba Networking 9300 1500W 100-240VAC Port-to-Power Airflow Power Supply Unit HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A) 	S1D05A			
	HPE Aruba Networking 9300 1500W 100-240VAC Port-to-Power Airflow Power Supply Unit	S1D05A			
	 No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6- 20P) 				
1, 2	HPE Aruba Networking 9300 1500W 100-240VAC Power-to-Port Airflow Power Supply Unit	S1D06A			
	• includes 1 x c13, 1500w				
	HPE Aruba Networking 9300 1500W 100-240VAC Power-to-Port Airflow Power Supply Unit	S1D06A			
	C13 PDU Jumper Cord (NA/MEX/TW/JP) (JL697A)	6100/4			
	HPE Aruba Networking 9300 1500W 100-240VAC Power-to-Port Airflow Power Supply Unit	S1D06A			
	 C13 PDU Jumper Cord (ROW) (JL697A) HPE Aruba Networking 9300 1500W 100-240VAC Power-to-Port Airflow Power Supply Unit 	S1D06A			
	 HPE 2.3m C13 to NEMA 6-15P Pwr Cord(J9936A) 	51000/(
	HPE Aruba Networking 9300 1500W 100-240VAC Power-to-Port Airflow Power Supply Unit	S1D06A			
	No Localized Power Cord Selected. Use J9955A to obtain a Locking Plug Power Cord (L6-				
	20P)				
	HPE Aruba Networking 9300 Port-to-Power Fan	S1D15A			
	HPE Aruba Networking 9300 Power-to-Port Fan HPE Aruba Networking X472 2-post Rack Kit	S1D16A JL482C			
	HPE Aruba Networking X474 4-post Rack Kit	JL483C			
	Configuration Rules	02.000			
Rule #	Description				
1	Localization required on orders without B2B, B2C, B2E or AC3 options.				
2	Unbuildable/FAN required, generates CFGU: If order is quoted for India and contains "#B2C" Option,				
	then Display the following:				
	 For BTO shipments to India: 				
	Please replace <base model=""/> #B2C option with <base model=""/> #AC3 in the Bill of Materials				
	and add the appropriate INDIA PDU Power Cord below via Ad-Hoc:				
	HPE Networking 2.0m C13 to C14 PDU India Power Cord HPE Networking 2.5m C15 to C14 PDU India Power Cord	JL671A JL672A			
	HPE Networking 2.5m C19 to C20 PDU India Power Cord	JL673A			
	 For Factory Integration of Power Cord, please add "#0D1" to the Power Cord Sku suffix. 	520757			
	(Ex. JL671A#0D1)				
Notes:	 Drop down under power supply should offer the following options and results: 				
	 Switch/Router/Power Supply to PDU Power Cord - #B2B in North America, Mexico, 				
	Taiwan, and Japan or #B2C ROW. (OCA Default B2B or B2C for Rack Level CTO)				
	 Switch/Router/Power Supply to Wall Power Cord - Localized Option (OCA Default for 				
	BTO) Llink Vick Switch (Deuter (Deuter Swarks to Wick Deuter Cond., #D25, Ontion, 40fferred				
	High Volt Switch/Router/Power Supply to Wall Power Cord - #B2E Option. (Offered				
	 only in North America, Mexico, Taiwan, and Japan) No Power Cord - #AC3 Option 				
	 OCA Display Notes: Locking Power Cord (J9955A) L6-20P is available in the Accessories tab 				
	 OCA Display Notes: 2 Power Supplies and 6 Fan Trays are included with the Switch Bundle 				
	out Display Hores. 2 Fower Supplies and of an Hays are included with the Switch Buildle				



Summary of Changes

Date	Version History	Action	Description of Change
03-Sep-2024	Version 15	Changed	Configuration Information section was updated.
05-Aug-2024	Version 14	Changed	Configuration Information section was updated.
06-May-2024	Version 13	Changed	Configuration Information section was updated.
01-Apr-2024	Version 12	Changed	Configuration Information section was updated.
04-Mar-2024	Version 11	Changed	Configuration Information section was updated.
04-Dec-2023	Version 10	Changed	Obsolete SKU was removed. Configuration Information section was updated.
14-Aug-2023	Version 9	Changed	Configuration Information section was updated.
10-Jul-2023	Version 8	Changed	Configuration Information section was updated.
15-May-2023	Version 7	Changed	Configuration Information section was updated.
13-Mar-2023	Version 6	Changed	Configuration Information and Aruba Data Center Networking Solution for HPE sections were updated.
06-Feb-2023	Version 5	Changed	Configuration Information and Aruba Data Center Networking Solution for HPE sections were updated.
05-Dec-2022	Version 4	Changed	Configuration Information section was updated and new SKUs were added.
07-Nov-2022	Version 3	Changed	Overview, Standard Features, Configuration Information and Technical Specifications sections were updated.
03-Oct-2022	Version 2	Changed	Overview, Standard Features, Configuration Information and Technical Specifications sections were updated.
01-Aug-2022	Version 1	New	New QuickSpecs

Copyright

Make the right purchase decision. Contact our presales specialists.

Call now	þ,	Chat now (sales)
Get updates	\bigcirc	Call now
	프 Get updates	

Hewlett Packard Enterprise © Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

To learn more, visit: http://www.hpe.com/networking

a50004291enw - 16895 - Worldwide - V15 - 03-September-2024