

Poly Blackwire 3215 Monaural USB-A Headset TAA

Freedom to work your way

The Blackwire 3200 Series provides a quality audio experience in a headset that's built for enterprise needs. With a sleek design and flexible microphone boom for a customizable fit, what's not to love?

Poly signature audio quality

Experience the high-quality audio you expect from Poly with a headset that offers PC wideband, a noise-canceling mic, and hi-fi stereo sound options. Dynamic EQ optimizes call quality and automatically adjusts the settings for listening to multimedia.

Advanced connectivity

Ideal for managing calls on your PC, mobile phone, or tablet combined with the comfort and durability of a corded headset for greater flexibility.

Long-lasting comfort and portability

Relax while you talk knowing your headset is secure- lightweight metal headband offers durability plus a custom fit. Leatherette ear cushions fold flat for easy portability.

Poly Blackwire 3215 Monaural USB-A Headset TAA

Specifications

Compatible with

Compatible operating systems: Windows 11; Windows 10; macOS

Connectivity and communications

Ear cushions: Artificial leather (surface material)

User interface features

Button user controls: Call answer/ignore/end/hold; Redial; Mute; Volume +/-

Audio

Audio features:

Dynamic EQ optimized

Digital signal processing (DSP)

Noise cancellation (NC)

Microphone bandwidth: 100 Hz to 10 kHz

Speaker bandwidth: 200 Hz to 6.8 kHz (speech mode); 20 Hz to 20 kHz (media mode)

Speaker size: 28 mm

Frequency response (microphone): 100 Hz to 10 kHz

Sensitivity (microphone): -38 dBV/Pa

Sensitivity (speaker): 90 dB

Battery

Impedance: 32 ohms

Certifications

Certified collaboration software: Skype for Business; Cisco Jabber; Avaya

Special features: Adjustable headband; Voice alerts

Environmental

Acoustic protection technology: SoundGuard¹

Applications supported

Management software:

HP Headset Control Center

Weight and dimensions

Product Primary Color: Black

Weight (imperial): 0.19 lb (with cable); 0.14 lb (without cable)

Weight (metric): 87 g (with cable); 64 g (without cable)

Product dimensions (imperial): 6.1 x 1.25 x 7.1 in

Product Dimensions (metric): 155 x 32 x 178 mm

Package dimensions (imperial): 7.28 x 2.2 x 8.14 in

Package dimensions (metric): 185 x 56 x 207 mm

Package weight (imperial): 0.55 lb

Package Weight (metric): 250 g

UPC number: 197497915013

Product number: 8M3Y1AA

Warranty

Poly standard two-year limited warranty

Technical Specifications Footnotes

¹ Protects against Acoustic Shock by limiting sounds to below 118 dBA.