

Product data sheet

Specifications



APC Service Bypass Panel- 100-240V; 30A; BBM; Hardwire Input/Output

SBP3000

Overview

Lead time Usually in Stock

Main

Main Input Voltage	100 V 120 V 230 V
Product or Component Type	Bypass kit
Main Output Voltage	100 V 120 V 230 V
Other Output Voltage	110 V
Output connector type	Hard Wire 3-wire (H N + E) 1
Number of rack unit	2U
Provided Equipment	Installation guide Rack Mounting brackets User Manual

Physical

Color	Black
Height	3.5 in (8.9 cm)
Width	17.008 in (43.2 cm)
Depth	25.0000000000 in (63.5 cm)
Net Weight	26.5 lb(US) (12 kg)
Mounting Support	Wall
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

Input Frequency	50/60 Hz
Number of input connectors	1 Hard Wire 3-wire (H N + E)
Max line current	30 A
Input current limits	30 A
Load Power Factor Range	0...1

Output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Maximum Total Current Draw per Phase	30 A
Protection Type	Circuit breaker
Efficiency	99 %

Conformance

Product Certifications	CSA GOST VDE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature for Operation	-4.0000000000...122.0000000000 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40.0000000000...149.0000000000 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304212713
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.0 in (20.3 cm)
Package 1 Width	24.02 in (61 cm)
Package 1 Length	39.02 in (99.1 cm)
Package 1 Weight	48.400 lb(US) (21.954 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	12
Package 2 Height	52.0 in (132 cm)
Package 2 Width	39.4 in (100 cm)
Package 2 Length	47.2 in (120 cm)
Package 2 Weight	600.01 lb(US) (272.16 kg)

Contractual warranty

Warranty	2 years (parts only)
----------	----------------------

Sustainability


Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.


Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
