

## 4-Post Modular Rack with Adjustable Rails

A portable, open-design rack that's great for frequent moves, adds, and changes.



### FEATURES

- » Weight capacity of 600 pounds.
- » Constructed of 14-gauge steel.
- » Only 12U high.
- » Low-profile 23" height makes it ideal for racking and storing equipment underneath a shelf or desk.
- » Open design allows access to all sides of mounted equipment for everyday maintenance and troubleshooting.
- » Four 2" non-locking swivel casters make the rack easy to move.
- » Easy to assemble with front and rear frames, front-to-rear posts, and EIA rails. Hex bolts and nuts are included.
- » Adjust EIA standard M6 rails to accommodate different sizes of hardware.
- » Measures 23"H x 21"W x 36"D (25.5"H with casters).
- » Black finish.

### What's included

RM625A ships in two boxes:

#### Box #1

- ◆ Frame, front
- ◆ Frame, rear

#### Box #2

- ◆ (4) front to rear posts
- ◆ (2) EIA rails
- ◆ (4) casters, 2" swivel, non-locking
- ◆ (52) hex bolts 1/4-20 x 1/2
- ◆ (52) keep nuts
- ◆ Instruction sheet

### Item

4-Post Modular Rack with Adjustable Rails

### Code

**RM625A**