


REV.	DESCRIPTION	ENG.	APPROVAL



P1








P2

P2 USB(A) Male

Electrical Test:

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 100M ohm Min.
4. Hi-Pot: 300VDC/10ms.

Pin Assignment



NO.	DESCRIPTION	Q'TY	UNIT
⑦	W=5MM 25u FOIL COPPER	1	pcs
⑥	H.S.T ø1.0 BLACK	1	pcs
⑤	USB 3.1 C Type Connector Black Insulation Nickel Plated Shell With PCBA(Resistance56KΩ)	1	pcs
④	Outside Molding 45P PVC PMS:WHITE	16	g
③	Intside Molding: PE	4	g
②	USB2.0 AM SOLDER INSULATION:BLACK SHELL NICKEL PLATED	1	Set
①	UL30AWG(19/0.06TC)*2C+24AWG(26/0.1TC+250D)*1C+3E(19/0.05+250D) +AB(16/9/0.06TC95%TC) OD:3.0MM Color:BLACK	1.0	m

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF INTRACOM Asia Co.,Ltd. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF INTRACOM Asia Co.,Ltd.

UNLESS OTHERWISE SPECIFIED:DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE:±1°

TOLERANCE(INCH)		TOLERANCE(MM)	
x	±0.02"	x	±0.5mm
x.x	±0.01"	x.x	±0.20mm
x.xx	±0.008"	x.xx	±0.15mm
x.xxx	±0.005"	x.xxx	±0.10mm

manhattan
Life just got easier.

TITLE: MH USB2.0 Cbl AM-CM,Black,3.3ft/1m	APPD		
	Check		
CUSTOMER:	Drawer	joe	Date
CUSTOMER P/N: 353298	Unit	mm	Projection
ICT P/N:	Scale	1:1	Size. A4
DWG.NO:	Sheet	1 of	REV. A

THIS DRAWING MAY BE USED IN WHOLE OR PART