

VERISAFE NETWORK MODULE

UNIT MOUNTING LOCATIONS MARKED 'A' (SEE NOTE 1)

NOTES:

READ PRODUCT INSTRUCTIONS BEFORE USING

1. Attach unit to isolation module using four (4) #4 self-tapping screws (included). Use #4 OR #6 screws for mounting to panel (not incl.)
2. Mating connector is provided
3. 35mm DIN rail mounting



ENVIRONMENT

Operating Temperature: -25°C to 60°C (-13°F to +140°F)  
Storage Temperature: -45°C to 85°C (-49°F to 185°F)  
Humidity: 5 to 90% non-condensing: Rated 80% at 40°C, decreasing linearly to 50% at 60°C  
Pollution Degree: 3  
Degree of Protection: IP20  
Altitude: Up to 5000 meters (3.2 miles)

Power\*

Power over Ethernet: PoE (10/100)  
IEEE 802.at (-af) Type 1 Class III PoE topology  
DC Input: 12-24 VDC  
24-14 AWG (0.75 - 1.5mm<sup>2</sup>) Solid/Stranded  
Current Draw: 43 mA @ 24V (AVT + Network Module)  
Power Consumption: 1.1W (AVT + Network Module)  
\*Note: Network Module supplies power to the AVT.  
No additional AVT power required (battery or DC)

Weight: .4 lbs (.18kg)

							TITLE					
							VERISAFE 2.0 NETWORK MODULE					
							CUSTOMER DRAWING					
							ITEM REVISION NAME		18I216AW/01			
							DATASET FILE NAME		18I216AW_DC/01			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		MATERIAL:			
							.x ± .06 [ 1.50 ] .xxx ± .01 [ .25 ] .xx ± .02 [ .50 ] ANGLES ± 5 °		N/A			
									DRAWING NUMBER:			
									18I216AW_DC			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							DFA	4/8/22	MSAD	NONE		B

**PANDUIT**

N/A

18I216AW\_DC

THIRD ANGLE  
PROJECTION

SHT 1 OF 1