



Poly Studio Large Room Bundle for Zoom Rooms: Studio E70 Smart Camera and HP PC w/TC10 TAA (9D9Q9AA)

Overview

Smarter rooms, better meetings



Elevate virtual meetings with AI-driven features for immersive collaboration. Enjoy high-resolution video with smart camera framing, and a secure conferencing PC in Zoom Rooms. Experience the future with Poly Studio Room Bundles.

A better way to meet and share

Poly Studio Room bundles for Zoom Rooms give you distraction-free meetings with innovative Poly camera tech. From small to large conference rooms, stay productive with technology that empowers the whole team, wherever they work.

Peace of mind you can call on

Our Poly+ device support team is available 24/7, across the world. This extensive global network of support professionals help you confidently plan and successfully deploy Zoom Rooms.

Engineered for your enterprise

It's easy to make every Zoom Room a Poly Studio Room. Certified and purpose built, these cutting-edge meeting solutions fit perfectly into office workflows, offer a consistent user experience and are simple for IT to setup.

Additional specifications

Aspect ratio	16:10
Brightness	300 nits
Camera range (imperial)	Up to 25 ft
Camera range (metric)	Up to 7.62 m
Camera resolution	2160p, 4K UHD (3840 x 2160)
Camera type	Dual-lens
Certified collaboration software	Zoom
Color	White
Contrast ratio	1000:1
Diagonal field of view (dFoV)	140°; 78°
Display features	LED backlights; Designed with built-in stand support (no external stand required); Tap and touch control to access call controls and administrative menus; Intuitive user interface; Direct API command through network; Capacitive touch sensor supports multi-touch functionality; Side LED indicators; Positioning angle: 60° or 30° (on tabletop surface); Anti-smudge coating; Poly logo button for control dock launch; Ultra Sonic Emitter (for auto pairing)
Display size (diagonal)	25.7 cm (10.1")
Display size (diagonal)	10.1"
Horizontal field of view (hFoV)	120°; 70°
Horizontal viewing angle	75°
Interoperability	Support for native 3rd party applications includes: Zoom Rooms, 8x8, BlueJeans, GoToRoom, Tencent, RingCentral, DialPad and others (when paired to a Poly Video OS system); Integration with Extron (environmental controls)
Lens cover capabilities	Integrated
Management Software	Poly Lens
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	321 x 102 x 89.1 mm
Minimum dimensions (W x D x H)	12.63 x 4.02 x 3.51 in
Minimum order quantity	1
Native resolution	WXGA (1280 x 800)
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 70 °C
Non-operating temperature - fahrenheit	40 to 158 °F
Operating altitude	4,877 m

Operating altitude	16,000 ft
Operating humidity range	15 to 80%
Operating temperature range	0 to 40 °C
Operating temperature range	32 to 104 °F
Panel technology	IPS
Ports	1 USB Type-C® 5Gbps signaling rate; 1 RJ-45
Power	100 - 240 VAC 50/60 Hz, 1.5A input; 12 VDC, 5A, 60 W output; Power over Ethernet (PoE), compatible with IEEE 802.3af Class 4
Power adapter port	1 x 4.5 mm
Power supply type	External
SMART camera technology	Poly DirectorAI with speaker framing; People framing; Group framing; Presenter tracking; DirectorAI perimeter
Security management	802.1x support
Special features	Air Quality Sensor; Meeting participant counting; Electronic privacy shutter
Total camera resolution (megapixels)	2 x 20 MP
UNSPSC code	45111902
Vertical viewing angle	75°
Weight	2 lb
Weight	907 g
What's in the box	Poly Studio E70; USB Type-C® cable; Ethernet cable; Wall mount kit
Wireless technologies	Bluetooth® 5.0; WiFi 802.11a/b/g/n/ac (SISO)
Zoom capability	7.3x digital

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.