


DATA SHEET

LHC210A, LHC211A, LHC212A, LGC210A, LGC211A, LGC212A, LHGC-RACK, LGC215A, LGC220A

MEDIA CONVERTERS AND CHASSIS

24/7 TECHNICAL SUPPORT AT 877.877.2269 OR VISIT BLACKBOX.COM



OVERVIEW

MEDIA CONVERTERS DATA SHEET

INTRODUCTION

Black Box Media Converters enable you to connect twisted-pair networks or devices to fiber optic network links. This allows you to transfer data over secure, high-speed fiber optic cable.

Choose from three groups of Black Box Media Converters:

- FAST ETHERNET AND GIGABIT ETHERNET MEDIA CONVERTERS WITH FIXED AND SFP OPTICS, STANDALONE AND CHASSIS
- GIGABIT ETHERNET POE+ MEDIA CONVERTER
- 10 GIGABIT ETHERNET MEDIA CONVERTER

FEATURES

- FAST ETHERNET MEDIA CONVERTERS SUPPORT UP TO 100 MBPS
- GIGABIT ETHERNET MEDIA CONVERTERS SUPPORT UP TO 1000 MBPS
- CHASSIS ENABLES YOU TO SECURELY HOUSE UP TO 14 FAST ETHERNET OR GIGABIT ETHERNET MEDIA CONVERTERS IN TWO RACK UNITS (3.50") OF 19" RACK SPACE
- POE MEDIA CONVERTER PROVIDES DATA AND POWER OVER THE RJ-45 INTERFACE
- 10G MEDIA CONVERTERS ALLOW YOU TO BRIDGE TWO HIGH SPEED 10G NETWORKS TOGETHER OR ATTACH A HIGH SPEED 10G DEVICE TO A 10G NETWORK

COMPARISON CHART

SPECIFICATION COMPARISON CHART					
PRODUCT CODE	STANDALONE	RACKMOUNTABLE	SPEED	MEDIA/CONNECTOR	POE
LHC210A	YES	YES	10/100 MBPS	TP, FIBER SFP	NO
LHC211A	YES	YES	10/100 MBPS	TP, FIBER MM 1310 NM SC	NO
LHC212A	YES	YES	10/100 MBPS	TP, FIBER SM 1310 NM SC	NO
LGC210A	YES	YES	10/100/1000 MBPS	TP, FIBER SFP	NO
LGC211A	YES	YES	10/100/1000 MBPS	TP, FIBER MM 850 NM SC	NO
LGC212A	YES	YES	10/100/1000 MBPS	TP, FIBER SM 1310 NM SC	NO
LGC215A	YES	NO	10/100/1000 MBPS	TP, FIBER SFP	YES
LGC220A	YES	NO	10 GBPS	TP, FIBER SFP	NO
LHGC-RACK	NO	YES	N/A	N/A	NO



SPECIFICATIONS

LHC210A: 10/100BASE-TX TO 100BASE-FX MEDIA CONVERTER WITH ONE SFP SLOT



TOP VIEW



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LHC210A	
APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100BASE-TX to 100BASE-FX SFP
CONNECTORS	(1) RJ-45, (1) SFP cage
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μm , 62.5/125 μm); Single-mode fiber (8.3/125 μm , 9/125 μm , 10/125 μm)
DISTANCE	CATx: 328 ft. (100 m)
WAVELENGTH	Depends on SFP installed
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps
FRAME SIZE	Up to 9016 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHGC-RACK
WHAT'S INCLUDED	(1) 10/100BASE-TX to 100BASE-FX Media Converter with One SFP Slot, (1) 5- VDC power adapter

COMPATIBLE SFPS	
PART NUMBER	DESCRIPTION
LFP401	SFP - 155-Mbps, Extended Diagnostics, 850-nm Multimode Fiber, 2-km, LC
LFP402	SFP - 155-Mbps, Extended Diagnostics, 1310-nm Multimode Fiber, 2-km, LC
LFP403	SFP - 155-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 30-km, LC
LFP404	SFP - 155-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 60-km, LC

SPECIFICATIONS

LHC211A: 10/100BASE-TX TO 100BASE-FX FAST ETHERNET MEDIA CONVERTER, MULTIMODE



TOP VIEW

LHC211A



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LHC211A

APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100BASE-TX to 100BASE-FX, Multimode SC, 1310-nm, 2-km
CONNECTORS	(1) RJ-45, (1) pair of SC
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μ m, 62.5/125 μ m)
DISTANCE	CATx: 328 ft. (100 m); MM fiber: 1.2 mi. (2 km)
WAVELENGTH	1310 nm
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps
FRAME SIZE	Up to 9016 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHGC-RACK
WHAT'S INCLUDED	(1) 10/100BASE-TX to 100BASE-FX Fast Ethernet Media Converter, Multimode, (1) 5-VDC power adapter



SPECIFICATIONS

LHC212A: 10/100BASE-TX TO 100BASE-FX FAST ETHERNET MEDIA CONVERTER, SINGLE-MODE



TOP VIEW

LHC212A



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LHC212A


APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100BASE-TX to 10/100BASE-FX, Singlemode SC, 1310-nm, 10-km
CONNECTORS	(1) RJ-45, (1) pair of SC
MEDIA SUPPORTED	CATx UTP/STP; Single-mode fiber (8.3/125 μ m, 9/125 μ m, 10/125 μ m)
DISTANCE	CATx: 328 ft. (100 m); SM fiber: 6.2 mi. (10 km)
WAVELENGTH	1310 nm
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps
FRAME SIZE	Up to 9016 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHGC-RACK
WHAT'S INCLUDED	(1) 10/100BASE-TX to 100BASE-FX Fast Ethernet Media Converter, Single-mode, (1) 5-VDC power adapter

SPECIFICATIONS

LGC210A: 10/100/1000BASE-TX TO 1000BASE-FX MEDIA CONVERTER WITH ONE SFP SLOT



TOP VIEW



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LGC210A

APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100/1000BASE-TX to 1000BASE-X SFP
CONNECTORS	(1) RJ-45, (1) SFP cage
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μm , 62.5/125 μm); Single-mode fiber (8.3/125 μm , 9/125 μm , 10/125 μm)
DISTANCE	CATx: 328 ft. (100 m)
WAVELENGTH	Depends on SFP installed
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps, 1000 Mbps: 1,480,000 pps
FRAME SIZES	Up to 9216 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1 A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode, 802.3ab 1000BASE-T, 802.3z 1000BASE-X
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHGC-RACK
WHAT'S INCLUDED	(1) 10/100/1000BASE-TX to 1000BASE-FX Media Converter with One SFP Slot, (1) 5-VDC power adapter

COMPATIBLE SFPS

PART NUMBER	DESCRIPTION
LFP411	SFP - 1250-Mbps, Extended Diagnostics, 850-nm Multimode Fiber, 550-m, LC
LFP412	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Multimode Fiber, 2-km, LC
LFP413	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 10-km, LC
LFP414	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 30-km, LC
LFP418	SFP - 1250-Mbps, Extended Diagnostics, 1550-nm Single-Mode Fiber, 80-km, LC
LFP420, LFP421 (USED IN PAIRS)	SFP - 1250-Mbps, Extended Diagnostics, 1550-nm TX, 1310-nm RX, Simplex, Single-Mode Fiber, 10-km, LC; SFP - 1250-Mbps, Extended Diagnostics, 1310-nm TX, 1550-nm RX, Simplex Single-Mode Fiber, 10-km, LC
LFP416	SFP - 1250-Mbps, Extended Diagnostics, 10/100/1000BASE-T, SGMII Interface, RJ-45

NOTE: LFP420, LFP421 are single-strand fiber SFPs, so they must be used in pairs.

NOTE: Use the LFP416 for a copper interface.



SPECIFICATIONS

LGC211A: 10/100/1000BASE-TX TO 1000BASE-FX GIGABIT ETHERNET MEDIA CONVERTER, MULTIMODE




TOP VIEW

LGC211A



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LGC211A	
APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - Multimode SC 1000-Mbps 850-nm 500-m to RJ45 10/100/1000-Mbps
CONNECTORS	(1) RJ-45; (1) pair of SC
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μm, 62.5/125 μm)
DISTANCE	CATx: 328 ft. (100 m), MM fiber: 1640 ft. (500 m)
WAVELENGTH	850 nm
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps, 1000 Mbps: 1,480,000 pps
FRAME SIZES	Up to 9216 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode, 802.3ab 1000BASE-T, 802.3z 1000BASE-X
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHCG-RACK
WHAT'S INCLUDED	(1) 10/100/1000BASE-TX to 1000BASE-FX Media Converter, Multimode, (1) 5-VDC power adapter

SPECIFICATIONS

LGC212A: 10/100/1000BASE-TX TO 1000BASE-FX GIGABIT ETHERNET MEDIA CONVERTER, SINGLE-MODE



TOP VIEW

LGC212A



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LGC212A	
APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100/1000BASE-TX to 1000BASE-LX Singlemode SC, 1310-nm, 10-km
CONNECTORS	(1) RJ-45; (1) pair of SC
MEDIA SUPPORTED	CATx UTP/STP; Single-mode fiber (8.3/125 μm, 9/125 μm, 10/125 μm)
DISTANCE	CATx: 328 ft. (100 m), SM fiber: 6.2 mi. (10 km)
WAVELENGTH	1310 nm
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps, 1000 Mbps: 1,480,000 pps
FRAME SIZES	Up to 9216 bytes
POWER	Media converter: 5 VDC, 2.5 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 5 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode, 802.3ab 1000BASE-T, 802.3z 1000BASE-X
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone or in LHCG-RACK
WHAT'S INCLUDED	(1) 10/100/1000BASE-TX to 1000BASE-FX Media Converter, Single-mode, (1) 5-VDC power adapter



SPECIFICATIONS

LHGC-RACK: MEDIA CONVERTER CHASSIS



MAIN VIEW

LHGC-RACK



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LHGC-RACK

NUMBER OF SLOTS	14
COMPATIBLE MEDIA CONVERTERS	LHC210A, LHC211A, LHC212A, LGC210A, LGC211A, LGC212A
MEDIA SUPPORTED	10/100/1000BASE-TX: CAT5 UTP/STP, max. 328 ft. (100 m); 1000BASE-FX
CONNECTORS	Depends on media converters installed
POWER	Dual Power supplies included: (1) LHGC-RACK-PS-L and (1) LHGC-RACK-PS-R; Input: 100-240 VAC, 50/60 Hz, 3.0 A; Output: 5 VDC, 12 A, 60 W; Connector: IEC320 C14 on each power supply; Circuit breaker for overvoltage or short circuit protection
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +185° F (-20 to +85° C)
RELATIVE HUMIDITY	5 to 95%, noncondensing
DIMENSIONS	3.5" H (2U) x 19" W x 9.1" D (8.9 x 48.2 x 23.1 cm)
WEIGHT	15.4 lb (7.0 kg)
MOUNTING	Chassis comes with blanks and mounting hardware for 14 converters
WHAT'S INCLUDED	(1) Media Converter Chassis (unpopulated), (2) 5-VDC power supplies, (14) blank panels, (14) rackmount brackets

COMPATIBLE MEDIA CONVERTERS

PART NUMBER	DESCRIPTION
LHC210A	10/100BASE-TX to 100BASE-FX Media Converter with one SFP slot
LHC211A	10/100BASE-TX to 100BASE-FX Fast Ethernet Media Converter, MM 1310 SC
LHC212A	10/100BASE-TX to 100BASE-FX Fast Ethernet Media Converter, SM 1310 SC
LGC210A	10/100/1000BASE-TX to 1000BASE-FX Media Converter with one SFP slot
LGC211A	10/100/1000BASE-TX to 1000BASE-FX Gigabit Ethernet Media Converter, MM 850 SC
LGC212A	10/100/1000BASE-TX to 1000BASE-FX Gigabit Ethernet Media Converter, SM 1310 SC

NOTE: LGC215A and LGC220A Media Converters are not compatible with the LHGC-RACK Chassis.

SPECIFICATIONS

LGC215A: 1000BASE-X TO 10/100/1000BASE-T TO 1000BASE-X POE+ GBE MEDIA CONVERTER



TOP VIEW



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LGC215A

APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10/100/1000BASE-TX to 1000BASE-X SFP PoE+
CONNECTORS	(1) RJ-45; (1) SFP cage
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μm, 62.5/125 μm); Single-mode fiber (8.3/125 μm, 9/125 μm, 10/125 μm)
DISTANCE	CATx: 328 ft. (100 m)
WAVELENGTH	Depends on SFP installed
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps, 1000 Mbps: 1,480,000 pps
FRAME SIZES	Up to 9216 bytes
POWER	Media converter: 47–57 VDC, 33 W max., barrel connector; External power adapter included: In-line type, 100-240 VAC, 50/60 Hz, 48 VDC, 1.5 A, IEC320 C13/C14, with US power cord
STANDARDS	IEEE 802.3, IEEE 802.3U, 10/100BASE-TX, 100BASE-FX, IEEE 802.3x flow control for full-duplex mode, 802.3ab 1000BASE-T, 802.3z 1000BASE-X, 802.3at PoE+ (25W)
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone
WHAT'S INCLUDED	(1) PoE Media Converter, (1) 48-VDC power supply, (1) power cord

COMPATIBLE SFPS

PART NUMBER	DESCRIPTION
LFP411	SFP - 1250-Mbps, Extended Diagnostics, 850-nm Multimode Fiber, 550-m, LC
LFP412	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Multimode Fiber, 2-km, LC
LFP413	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 10-km, LC
LFP414	SFP - 1250-Mbps, Extended Diagnostics, 1310-nm Single-Mode Fiber, 30-km, LC
LFP418	SFP - 1250-Mbps, Extended Diagnostics, 1550-nm Single-Mode Fiber, 80-km, LC
LFP420, LFP421 (USED IN PAIRS)	SFP - 1250-Mbps, Extended Diagnostics, 1550-nm TX, 1310-nm RX, Simplex, Single-Mode Fiber, 10-km, LC; SFP - 1250-Mbps, Extended Diagnostics, 1310-nm TX, 1550-nm RX, Simplex Single-Mode Fiber, 10-km, LC
LFP416	SFP - 1250-Mbps, Extended Diagnostics, 10/100/1000BASE-T, SGMII Interface, RJ-45

NOTE: LFP420, LFP421 are single-strand fiber SFPs, so they must be used in pairs.

NOTE: Use the LFP416 for a copper interface.

NOTE: Only the built-in copper interface will do PoE.



SPECIFICATIONS

LGC220A: 10GBASE-T TO 10GBASE-FX MEDIA CONVERTER, SFP+



TOP VIEW

LGC220A



FRONT VIEW



BACK VIEW

SPECIFICATIONS FOR LGC220A

APPROVALS	FCC Class B, CE, RoHS
DESCRIPTION	Pure Networking Copper to Fiber Media Converter - 10GBASE-T to 10G SFP+
CONNECTORS	(1) RJ-45, (1) SFP cage
MEDIA SUPPORTED	CATx UTP/STP; Multimode fiber (50/125 μm, 62.5/125 μm); Single-mode fiber (8.3/125 μm, 9/125 μm, 10/125 μm)
DISTANCE	CATx: 328 ft. (100 m)
WAVELENGTH	Depends on SFP installed
FORWARDING RATE	10 Mbps: 14,880 pps, 100 Mbps: 148,800 pps, 1000 Mbps: 1,480,000 pps, 10 Gbps: 14,800,000 pps
FRAME SIZES	Up to 16383 bytes
POWER	Media converter: 12 VDC, 12 W, barrel connector; External power adapter included: Wall type, 100-240 VAC, 50/60 Hz, 12 VDC, 1A with 4 plug clips for US, EU, UK, AU
STANDARDS	802.3ab 1000BASE-T, 802.3z 1000BASE-X, 802.3an 10GBASE-T, 802.3ae 10GE over fiber
DIMENSIONS	1" H x 3.7" W x 2.7" D (2.5 x 9.4 x 6.9 cm)
WEIGHT	0.7 lb. (0.3 kg)
TEMPERATURE	Operating: 32 to 122° F (0 to 50° C); Storage: -4 to +158° F (-20 to +70° C)
MOUNTING	Standalone
WHAT'S INCLUDED	(1) 10GBASE-T to 10GBASE-FX Media Converter, (1) 12-VDC power supply, (1) power cord

COMPATIBLE SFPS

PART NUMBER	DESCRIPTION
LSP421	SFP+ - 10-Gb, Extended Diagnostics, 850-nm Multimode Fiber, 300-m, LC
LSP422	SFP+ - 10-Gb, Extended Diagnostics, 1310-nm Single-Mode Fiber, 10-km, LC
LSP431	SFP+ - 10-Gb, Extended Operating Temperature & Diagnostics, 850-nm Multimode Fiber, 300-m

ORDERING INFORMATION

ITEM	CODE
Fast Ethernet Media Converters	
10/100BT to 100BFX, (1) SFP slot	LHC210A
10/100BT to 100BFX, (1) MM SC	LHC211A
10/100BT to 100BFX, (1) SM SC	LHC212A
Gigabit Ethernet Media Converters	
10/100/1000BT to 1000BFX, (1) SFP slot	LGC210A
10/100/1000BT to 1000BFX, (1) MM SC	LGC211A
10/100/1000BT to 1000BFX, (1) SM SC	LGC212A
Media Converter Chassis	LHGC-RACK
NOTE: LHC210A, LHC211A, LHC212A, LGC210A, LGC211A and LGC212A media converters are compatible with the LHGC-RACK.	
Spare 5-VDC Power Supplies for Chassis	
Left Side	LHGC-RACK-PS-L
Right Side	LHGC-RACK-PS-R
PoE Media Converter	
1000BASE-X to 10/100/1000BASE-T PoE	LGC215A
10 Gigabit Media Converter	
10GBASE-TX to 10GBASE-FX Media Converter	LGC220A
NOTE: LGC215A and LGC220A media converters are NOT compatible with the LHGC-RACK.	

NOTES _____

DISCLAIMER

Black Box Corporation shall not be liable for damages of any kind, including, but not limited to, punitive, consequential or cost of cover damages, resulting from any errors in the product information or specifications set forth in this document and Black Box Corporation may revise this document at any time without notice.

ABOUT BLACK BOX

Black Box is a world leading technology solutions provider specializing in complete high-performance KVM, professional A/V signal distribution and extension and switching solutions for mission-critical applications. Black Box is dedicated to delivering superior project engineering, technical support, and 24/7 customer service you can rely on for your most critical operations.

Every day, our customers trust us to design, integrate, and maintain reliable control room solutions for broadcasting, post-production, stadiums & arenas, medical, air traffic control, oil & gas, government & military, and utility industries. Leave the tech to us and our comprehensive technology solutions will deliver secure connections, fast-response times, real-time collaboration and more.

FILENAME: LHC210A_DS_REV3.PDF

© COPYRIGHT 2021. BLACK BOX CORPORATION. ALL RIGHTS RESERVED.

